

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303615

Luminaire Tested: **PR6FS12D010 PR6M12MD9FSBZ 2000Lm3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303615
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-3)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS12D010 PR6M12MD9FSBZ 2000Lm3500K
Description: PR6 MEDIUM LENS WITH, BRONZE FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 90CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1978.0 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.2 / 1.24
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 20.4
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303615

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSBZ 2000Lm3500K

Luminous Intensity Polar Plot





TEST NUMBER: P303615

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSBZ 2000Lm3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	112	108	105	102	109	106	103	101	102	100	97	98	96	94	95	93	92	90
2	104	98	92	88	102	96	91	87	92	88	85	89	86	83	86	84	81	79
3	97	88	82	76	94	87	81	76	84	79	74	81	77	73	79	75	72	70
4	90	80	73	67	88	78	72	67	76	70	66	74	69	65	72	68	64	62
5	83	72	65	59	81	71	64	59	69	63	58	68	62	58	66	61	57	55
6	78	66	58	53	76	65	58	53	64	57	52	62	56	52	61	55	51	50
7	72	61	53	48	71	60	53	47	58	52	47	57	51	47	56	51	46	45
8	68	56	48	43	66	55	48	43	54	47	43	53	47	42	52	46	42	41
9	64	52	44	39	62	51	44	39	50	43	39	49	43	39	48	43	39	37
10	60	48	41	36	59	47	40	36	46	40	36	45	40	36	45	39	35	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68196
5°	68175
10°	67956
15°	67522
20°	66692
25°	65233
30°	63355
35°	60235
40°	55153
45°	47525
50°	37939
55°	27685
60°	18711
65°	11748
70°	6638
75°	2748
80°	0
85°	0



TEST NUMBER: P303615

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSBZ 2000Lm3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.9	5.0
10°-20°	281.5	14.2
20°-30°	417.0	21.1
30°-40°	469.8	23.8
40°-50°	394.7	20.0
50°-60°	222.2	11.2
60°-70°	79.7	4.0
70°-80°	14.2	0.7
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	797.3	40.3
0°-40°	1267.2	64.1
0°-60°	1884.1	95.3
0°-90°	1978.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1978.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1045	
5°	1041	99
15°	1000	282
25°	906	417
35°	756	470
45°	515	395
55°	243	222
65°	76	80
75°	11	14
85°	0	0
90°	0	



TEST NUMBER: P303615

CATALOG NUMBER: PR6FS12D010 PR6M12MD9FSBZ 2000Lm3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1045.3
2.5°	1043.2
5°	1041.0
7.5°	1034.5
10°	1025.8
12.5°	1012.7
15°	999.7
17.5°	980.1
20°	960.6
22.5°	934.5
25°	906.2
27.5°	875.8
30°	841.0
32.5°	801.9
35°	756.3
37.5°	704.1
40°	647.6
42.5°	584.6
45°	515.1
47.5°	443.3
50°	373.8
52.5°	306.4
55°	243.4
57.5°	191.2
60°	143.4
62.5°	106.5
65°	76.1
67.5°	52.2
70°	34.8
72.5°	21.7
75°	10.9
77.5°	4.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)