

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P303421

Luminaire Tested: **PR6FS24D010 PR6M24WD8FSMMS 2000Lm4000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P303421
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1903-195-5)
Test Lab: INNOVATION CENTER(G3)
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR6FS24D010 PR6M24WD8FSMMS 2000Lm4000K
Description: PR6 WIDE LENS WITH, MATTE METALLIC SILVER FINISH
Light Source: ARRAY OF HIGH LUMEN LEDs 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2378.8 lumens
Efficiency: N/A
Efficacy: 108.1 lumens/watt
Spacing Criteria (0/90/45): 1.33 / 1.33 / 1.27
Luminous Opening: Circular (Dia: 0.46' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P303421

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSMMS 2000Lm4000K

Luminous Intensity Polar Plot





TEST NUMBER: P303421

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSMMS 2000Lm4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	112	108	105	102	109	106	103	100	102	99	97		98	96	94		94	93	91	90
2	104	97	92	87	101	95	91	86	92	88	85		89	86	83		86	83	81	79
3	96	88	81	76	94	86	80	75	83	78	74		81	77	73		78	75	72	70
4	89	79	72	67	87	78	71	66	76	70	65		74	69	65		72	67	64	62
5	83	72	65	59	81	71	64	59	69	63	58		67	62	58		66	61	57	55
6	77	66	58	53	76	65	58	52	63	57	52		62	56	52		60	55	51	49
7	72	60	53	47	71	60	52	47	58	52	47		57	51	47		56	50	46	45
8	68	56	48	43	66	55	48	43	54	47	43		53	47	42		51	46	42	40
9	63	51	44	39	62	51	44	39	50	43	39		49	43	39		48	42	38	37
10	60	48	40	36	58	47	40	36	46	40	36		45	40	35		45	39	35	34

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	74198
5°	75778
10°	78132
15°	79990
20°	81022
25°	81156
30°	80260
35°	74985
40°	65629
45°	53264
50°	40487
55°	30438
60°	22952
65°	16441
70°	11350
75°	6251
80°	2780
85°	1871



TEST NUMBER: P303421

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSMMS 2000Lm4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	111.2	4.7
10°-20°	334.2	14.0
20°-30°	518.6	21.8
30°-40°	582.2	24.5
40°-50°	445.5	18.7
50°-60°	244.8	10.3
60°-70°	109.6	4.6
70°-80°	29.6	1.2
80°-90°	3.0	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	964.0	40.5
0°-40°	1546.1	65.0
0°-60°	2236.5	94.0
0°-90°	2378.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2378.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1137	
5°	1157	111
15°	1184	334
25°	1127	519
35°	942	582
45°	577	446
55°	268	245
65°	106	110
75°	25	30
85°	2	3
90°	0	



TEST NUMBER: P303421

CATALOG NUMBER: PR6FS24D010 PR6M24WD8FSMMS 2000Lm4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1137.3
2.5°	1144.7
5°	1157.1
7.5°	1169.5
10°	1179.4
12.5°	1184.3
15°	1184.3
17.5°	1176.9
20°	1167.0
22.5°	1149.7
25°	1127.4
27.5°	1100.1
30°	1065.4
32.5°	1010.9
35°	941.5
37.5°	859.8
40°	770.6
42.5°	676.4
45°	577.3
47.5°	483.2
50°	398.9
52.5°	327.1
55°	267.6
57.5°	218.0
60°	175.9
62.5°	138.8
65°	106.5
67.5°	81.8
70°	59.5
72.5°	39.6
75°	24.8
77.5°	14.9
80°	7.4
82.5°	5.0
85°	2.5
87.5°	0.0
90°	0.0

(END OF REPORT)