

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210475

Luminaire Tested: **PR8R40D010 - PR8M34WDMMS - 3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210475
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8R40D010 - PR8M34WDMMS - 3500K
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE METALLIC SILVER FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4740.5 lumens
Efficiency: N/A
Efficacy: 109.0 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 43.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210475

CATALOG NUMBER: PR8R40D010 - PR8M34WDMMS - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P210475

CATALOG NUMBER: PR8R40D010 - PR8M34WDMMS - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|--|-----|-----|-----|--|-----|-----|-----|-----|
| RF | 20 | | | | 20 | | | | 20 | | | | 20 | | | | 20 | | | |
| RC | 80 | | | | 70 | | | | 50 | | | | 30 | | | | 10 | 0 | | |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | | 50 | 30 | 10 | | 50 | 30 | 10 | 0 |
| RCR | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | | 106 | 106 | 106 | | 102 | 102 | 102 | 100 |
| 1 | 110 | 106 | 103 | 99 | 108 | 104 | 101 | 98 | 100 | 97 | 95 | | 96 | 94 | 92 | | 92 | 91 | 89 | 87 |
| 2 | 102 | 94 | 88 | 83 | 99 | 92 | 87 | 82 | 89 | 84 | 80 | | 86 | 82 | 79 | | 83 | 80 | 77 | 75 |
| 3 | 93 | 84 | 77 | 71 | 91 | 82 | 76 | 70 | 79 | 74 | 69 | | 77 | 72 | 68 | | 74 | 70 | 67 | 65 |
| 4 | 86 | 75 | 67 | 61 | 84 | 74 | 66 | 61 | 71 | 65 | 60 | | 69 | 64 | 59 | | 67 | 62 | 58 | 56 |
| 5 | 80 | 68 | 59 | 53 | 78 | 67 | 59 | 53 | 64 | 58 | 52 | | 63 | 57 | 52 | | 61 | 56 | 51 | 49 |
| 6 | 74 | 61 | 53 | 47 | 72 | 60 | 52 | 47 | 59 | 52 | 46 | | 57 | 51 | 46 | | 55 | 50 | 46 | 44 |
| 7 | 68 | 56 | 48 | 42 | 67 | 55 | 47 | 42 | 53 | 46 | 41 | | 52 | 46 | 41 | | 51 | 45 | 41 | 39 |
| 8 | 64 | 51 | 43 | 37 | 62 | 50 | 43 | 37 | 49 | 42 | 37 | | 48 | 42 | 37 | | 47 | 41 | 37 | 35 |
| 9 | 60 | 47 | 39 | 34 | 58 | 46 | 39 | 34 | 45 | 38 | 34 | | 44 | 38 | 33 | | 43 | 37 | 33 | 31 |
| 10 | 56 | 43 | 36 | 31 | 55 | 43 | 36 | 31 | 42 | 35 | 31 | | 41 | 35 | 30 | | 40 | 34 | 30 | 29 |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|-------|
| | 0° |
| 0° | 57516 |
| 5° | 58482 |
| 10° | 59189 |
| 15° | 60282 |
| 20° | 61555 |
| 25° | 62118 |
| 30° | 62020 |
| 35° | 61868 |
| 40° | 59717 |
| 45° | 54690 |
| 50° | 45689 |
| 55° | 37988 |
| 60° | 31922 |
| 65° | 26377 |
| 70° | 22684 |
| 75° | 17800 |
| 80° | 12324 |
| 85° | 12949 |



TEST NUMBER: P210475

CATALOG NUMBER: PR8R40D010 - PR8M34WDMMS - 3500K

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 180.0 | 3.8 |
| 10°-20° | 534.3 | 11.3 |
| 20°-30° | 839.1 | 17.7 |
| 30°-40° | 1022.9 | 21.6 |
| 40°-50° | 956.0 | 20.2 |
| 50°-60° | 637.7 | 13.5 |
| 60°-70° | 366.9 | 7.7 |
| 70°-80° | 169.2 | 3.6 |
| 80°-90° | 34.3 | 0.7 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1553.5 | 32.8 |
| 0°-40° | 2576.4 | 54.3 |
| 0°-60° | 4170.1 | 88.0 |
| 0°-90° | 4740.5 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 4740.5 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|------|------|
| 0° | 1865 | |
| 5° | 1889 | 180 |
| 15° | 1888 | 534 |
| 25° | 1826 | 839 |
| 35° | 1644 | 1023 |
| 45° | 1254 | 956 |
| 55° | 707 | 638 |
| 65° | 362 | 367 |
| 75° | 149 | 169 |
| 85° | 37 | 34 |
| 90° | 0 | |



TEST NUMBER: P210475

CATALOG NUMBER: PR8R40D010 - PR8M34WDMMS - 3500K

CANDELA DISTRIBUTION (FULL):

| 0° | |
|-------|--------|
| 0° | 1865.2 |
| 2.5° | 1868.1 |
| 5° | 1889.3 |
| 7.5° | 1887.4 |
| 10° | 1890.3 |
| 12.5° | 1886.4 |
| 15° | 1888.3 |
| 17.5° | 1884.5 |
| 20° | 1875.8 |
| 22.5° | 1845.0 |
| 25° | 1825.7 |
| 27.5° | 1787.1 |
| 30° | 1741.8 |
| 32.5° | 1696.5 |
| 35° | 1643.5 |
| 37.5° | 1579.9 |
| 40° | 1483.5 |
| 42.5° | 1378.4 |
| 45° | 1254.1 |
| 47.5° | 1116.2 |
| 50° | 952.4 |
| 52.5° | 813.6 |
| 55° | 706.6 |
| 57.5° | 604.4 |
| 60° | 517.6 |
| 62.5° | 442.4 |
| 65° | 361.5 |
| 67.5° | 296.9 |
| 70° | 251.6 |
| 72.5° | 214.0 |
| 75° | 149.4 |
| 77.5° | 118.6 |
| 80° | 69.4 |
| 82.5° | 44.3 |
| 85° | 36.6 |
| 87.5° | 10.6 |
| 90° | 0.0 |

(END OF REPORT)