

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210519

Luminaire Tested: **PR8S10D010 - PR8M12MDMB - 3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210519
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29044)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8S10D010 - PR8M12MDMB - 3000K
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE BLACK FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 906.6 lumens
Efficiency: N/A
Efficacy: 86.3 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210519

CATALOG NUMBER: PR8S10D010 - PR8M12MDMB - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P210519

CATALOG NUMBER: PR8S10D010 - PR8M12MDMB - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	75	71		77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63		72	67	62		70	65	61	60
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	15628
5°	15573
10°	15168
15°	14541
20°	13720
25°	12994
30°	12007
35°	10962
40°	10233
45°	9350
50°	8841
55°	7962
60°	6223
65°	4334
70°	2750
75°	1549
80°	426
85°	0



TEST NUMBER: P210519

CATALOG NUMBER: PR8S10D010 - PR8M12MDMB - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.4	5.2
10°-20°	127.6	14.1
20°-30°	174.8	19.3
30°-40°	183.2	20.2
40°-50°	167.0	18.4
50°-60°	130.3	14.4
60°-70°	60.7	6.7
70°-80°	15.1	1.7
80°-90°	0.4	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	349.8	38.6
0°-40°	533.1	58.8
0°-60°	830.4	91.6
0°-90°	906.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	906.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	507	
5°	503	47
15°	456	128
25°	382	175
35°	291	183
45°	214	167
55°	148	130
65°	59	61
75°	13	15
85°	0	0
90°	0	



TEST NUMBER: P210519

CATALOG NUMBER: PR8S10D010 - PR8M12MDMB - 3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	506.8
2.5°	504.4
5°	503.1
7.5°	497.0
10°	484.4
12.5°	469.8
15°	455.5
17.5°	437.7
20°	418.1
22.5°	399.8
25°	381.9
27.5°	360.4
30°	337.2
32.5°	313.6
35°	291.2
37.5°	272.5
40°	254.2
42.5°	234.7
45°	214.4
47.5°	198.1
50°	184.3
52.5°	168.8
55°	148.1
57.5°	124.9
60°	100.9
62.5°	78.1
65°	59.4
67.5°	43.1
70°	30.5
72.5°	20.7
75°	13.0
77.5°	7.3
80°	2.4
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)