

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210534

Luminaire Tested: **PR8S10D010 - PR8M12MDMMS - 3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29044)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8S10D010 - PR8M12MDMMS - 3000K
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE METALLIC SILVER FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 961.5 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210534

CATALOG NUMBER: PR8S10D010 - PR8M12MDMMS - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P210534

CATALOG NUMBER: PR8S10D010 - PR8M12MDMMS - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	75	71		77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63		72	67	62		70	65	61	60
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	16575
5°	16517
10°	16088
15°	15423
20°	14554
25°	13783
30°	12733
35°	11628
40°	10852
45°	9912
50°	9374
55°	8441
60°	6599
65°	4597
70°	2921
75°	1644
80°	462
85°	0



TEST NUMBER: P210534

CATALOG NUMBER: PR8S10D010 - PR8M12MDMMS - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.3	5.2
10°-20°	135.4	14.1
20°-30°	185.4	19.3
30°-40°	194.3	20.2
40°-50°	177.1	18.4
50°-60°	138.2	14.4
60°-70°	64.3	6.7
70°-80°	16.0	1.7
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	371.0	38.6
0°-40°	565.4	58.8
0°-60°	880.6	91.6
0°-90°	961.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	961.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	538	
5°	534	50
15°	483	135
25°	405	185
35°	309	194
45°	227	177
55°	157	138
65°	63	64
75°	14	16
85°	0	0
90°	0	



TEST NUMBER: P210534

CATALOG NUMBER: PR8S10D010 - PR8M12MDMMS - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	537.5
2.5°	534.9
5°	533.6
7.5°	527.1
10°	513.8
12.5°	498.2
15°	483.1
17.5°	464.2
20°	443.5
22.5°	424.0
25°	405.1
27.5°	382.2
30°	357.6
32.5°	332.6
35°	308.9
37.5°	289.0
40°	269.6
42.5°	248.9
45°	227.3
47.5°	210.1
50°	195.4
52.5°	179.0
55°	157.0
57.5°	132.4
60°	107.0
62.5°	82.8
65°	63.0
67.5°	45.7
70°	32.4
72.5°	22.0
75°	13.8
77.5°	7.8
80°	2.6
82.5°	0.4
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)