

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210535

Luminaire Tested: **PR8S10D010 - PR8M12MDMMS - 3500K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P210535  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29044)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR8S10D010 - PR8M12MDMMS - 3500K  
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE METALLIC SILVER FINISH  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1084.0 lumens  
Efficiency: N/A  
Efficacy: 103.2 lumens/watt  
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.13  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210535

CATALOG NUMBER: PR8S10D010 - PR8M12MDMMS - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P210535

CATALOG NUMBER: PR8S10D010 - PR8M12MDMMS - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	75	71		77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63		72	67	62		70	65	61	60
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	18687
5°	18622
10°	18136
15°	17389
20°	16404
25°	15539
30°	14357
35°	13108
40°	12237
45°	11177
50°	10568
55°	9516
60°	7438
65°	5181
70°	3291
75°	1859
80°	515
85°	0



TEST NUMBER: P210535

CATALOG NUMBER: PR8S10D010 - PR8M12MDMMS - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	56.7	5.2
10°-20°	152.6	14.1
20°-30°	209.0	19.3
30°-40°	219.1	20.2
40°-50°	199.7	18.4
50°-60°	155.8	14.4
60°-70°	72.6	6.7
70°-80°	18.1	1.7
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	418.3	38.6
0°-40°	637.4	58.8
0°-60°	992.8	91.6
0°-90°	1084.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1084.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	606	
5°	602	57
15°	545	153
25°	457	209
35°	348	219
45°	256	200
55°	177	156
65°	71	73
75°	16	18
85°	0	1
90°	0	



TEST NUMBER: P210535

CATALOG NUMBER: PR8S10D010 - PR8M12MDMMS - 3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	606.0
2.5°	603.0
5°	601.6
7.5°	594.3
10°	579.2
12.5°	561.7
15°	544.7
17.5°	523.3
20°	499.9
22.5°	478.1
25°	456.7
27.5°	430.9
30°	403.2
32.5°	375.0
35°	348.2
37.5°	325.8
40°	304.0
42.5°	280.6
45°	256.3
47.5°	236.8
50°	220.3
52.5°	201.8
55°	177.0
57.5°	149.3
60°	120.6
62.5°	93.4
65°	71.0
67.5°	51.6
70°	36.5
72.5°	24.8
75°	15.6
77.5°	8.8
80°	2.9
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)