

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210580

Luminaire Tested: **PR8S10D010 - PR8M12WDMMS - 3500K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P210580  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR8S10D010 - PR8M12WDMMS - 3500K  
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE METALLIC SILVER FINISH  
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1074.0 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 10.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210580

CATALOG NUMBER: PR8S10D010 - PR8M12WDMMS - 3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P210580

CATALOG NUMBER: PR8S10D010 - PR8M12WDMMS - 3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95		96	94	92		92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80		86	82	79		83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69		77	72	68		74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60		69	64	59		67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52		63	57	52		61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46		57	51	46		55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34		44	38	33		43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31		41	35	30		40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	13028
5°	13248
10°	13408
15°	13657
20°	13947
25°	14072
30°	14050
35°	14015
40°	13529
45°	12389
50°	10353
55°	8607
60°	7234
65°	5976
70°	5139
75°	4027
80°	2788
85°	2937



TEST NUMBER: P210580

CATALOG NUMBER: PR8S10D010 - PR8M12WDMMS - 3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.8	3.8
10°-20°	121.1	11.3
20°-30°	190.1	17.7
30°-40°	231.7	21.6
40°-50°	216.6	20.2
50°-60°	144.5	13.5
60°-70°	83.1	7.7
70°-80°	38.3	3.6
80°-90°	7.8	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	351.9	32.8
0°-40°	583.7	54.3
0°-60°	944.7	88.0
0°-90°	1074.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1074.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	422	
5°	428	41
15°	428	121
25°	414	190
35°	372	232
45°	284	217
55°	160	144
65°	82	83
75°	34	38
85°	8	8
90°	0	



TEST NUMBER: P210580

CATALOG NUMBER: PR8S10D010 - PR8M12WDMMS - 3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	422.5
2.5°	423.2
5°	428.0
7.5°	427.6
10°	428.2
12.5°	427.4
15°	427.8
17.5°	426.9
20°	425.0
22.5°	418.0
25°	413.6
27.5°	404.9
30°	394.6
32.5°	384.3
35°	372.3
37.5°	357.9
40°	336.1
42.5°	312.3
45°	284.1
47.5°	252.9
50°	215.8
52.5°	184.3
55°	160.1
57.5°	136.9
60°	117.3
62.5°	100.2
65°	81.9
67.5°	67.3
70°	57.0
72.5°	48.5
75°	33.8
77.5°	26.9
80°	15.7
82.5°	10.0
85°	8.3
87.5°	2.4
90°	0.0

(END OF REPORT)