

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210550

Luminaire Tested: **PR8S10D010 - PR8M12WDMW - 3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210550
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8S10D010 - PR8M12WDMW - 3500K
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE WHITE FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1117.7 lumens
Efficiency: N/A
Efficacy: 106.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210550

CATALOG NUMBER: PR8S10D010 - PR8M12WDMW - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P210550

CATALOG NUMBER: PR8S10D010 - PR8M12WDMW - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	13559
5°	13787
10°	13956
15°	14213
20°	14511
25°	14644
30°	14624
35°	14587
40°	14081
45°	12895
50°	10770
55°	8957
60°	7524
65°	6217
70°	5346
75°	4194
80°	2912
85°	3043



TEST NUMBER: P210550

CATALOG NUMBER: PR8S10D010 - PR8M12WDMW - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.4	3.8
10°-20°	126.0	11.3
20°-30°	197.8	17.7
30°-40°	241.2	21.6
40°-50°	225.4	20.2
50°-60°	150.3	13.5
60°-70°	86.5	7.7
70°-80°	39.9	3.6
80°-90°	8.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	366.2	32.8
0°-40°	607.4	54.3
0°-60°	983.2	88.0
0°-90°	1117.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1117.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	440	
5°	445	42
15°	445	126
25°	430	198
35°	388	241
45°	296	225
55°	167	150
65°	85	86
75°	35	40
85°	9	8
90°	0	



TEST NUMBER: P210550

CATALOG NUMBER: PR8S10D010 - PR8M12WDMW - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	439.7
2.5°	440.4
5°	445.4
7.5°	445.0
10°	445.7
12.5°	444.7
15°	445.2
17.5°	444.3
20°	442.2
22.5°	435.0
25°	430.4
27.5°	421.3
30°	410.7
32.5°	400.0
35°	387.5
37.5°	372.5
40°	349.8
42.5°	325.0
45°	295.7
47.5°	263.2
50°	224.5
52.5°	191.8
55°	166.6
57.5°	142.5
60°	122.0
62.5°	104.3
65°	85.2
67.5°	70.0
70°	59.3
72.5°	50.5
75°	35.2
77.5°	28.0
80°	16.4
82.5°	10.5
85°	8.6
87.5°	2.5
90°	0.0

(END OF REPORT)