

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210306

Luminaire Tested: **PR840D010 - PR8M34WDMW - 3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210306
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR840D010 - PR8M34WDMW - 3500K
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE WHITE FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4933.4 lumens
Efficiency: N/A
Efficacy: 113.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 43.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210306

CATALOG NUMBER: PR840D010 - PR8M34WDMW - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P210306

CATALOG NUMBER: PR840D010 - PR8M34WDMW - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	59856
5°	60862
10°	61597
15°	62737
20°	64062
25°	64646
30°	64544
35°	64387
40°	62148
45°	56914
50°	47546
55°	39531
60°	33223
65°	27449
70°	23604
75°	18527
80°	12821
85°	13480



TEST NUMBER: P210306

CATALOG NUMBER: PR840D010 - PR8M34WDMW - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	187.3	3.8
10°-20°	556.1	11.3
20°-30°	873.3	17.7
30°-40°	1064.5	21.6
40°-50°	994.9	20.2
50°-60°	663.6	13.5
60°-70°	381.8	7.7
70°-80°	176.1	3.6
80°-90°	35.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1616.7	32.8
0°-40°	2681.3	54.3
0°-60°	4339.8	88.0
0°-90°	4933.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	4933.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1941	
5°	1966	187
15°	1965	556
25°	1900	873
35°	1710	1065
45°	1305	995
55°	735	664
65°	376	382
75°	156	176
85°	38	36
90°	0	



TEST NUMBER: P210306

CATALOG NUMBER: PR840D010 - PR8M34WDMW - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1941.1
2.5°	1944.1
5°	1966.2
7.5°	1964.2
10°	1967.2
12.5°	1963.2
15°	1965.2
17.5°	1961.2
20°	1952.2
22.5°	1920.1
25°	1900.0
27.5°	1859.9
30°	1812.7
32.5°	1765.6
35°	1710.4
37.5°	1644.2
40°	1543.9
42.5°	1434.5
45°	1305.1
47.5°	1161.7
50°	991.1
52.5°	846.7
55°	735.3
57.5°	629.0
60°	538.7
62.5°	460.5
65°	376.2
67.5°	309.0
70°	261.8
72.5°	222.7
75°	155.5
77.5°	123.4
80°	72.2
82.5°	46.1
85°	38.1
87.5°	11.0
90°	0.0

(END OF REPORT)