

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210515

Luminaire Tested: **PR8S20D010 - PR8M12MDMW - 3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210515
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29044)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8S20D010 - PR8M12MDMW - 3500K
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE WHITE FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2084.1 lumens
Efficiency: N/A
Efficacy: 94.7 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210515

CATALOG NUMBER: PR8S20D010 - PR8M12MDMW - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P210515

CATALOG NUMBER: PR8S20D010 - PR8M12MDMW - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	75	71		77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63		72	67	62		70	65	61	60
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	35927
5°	35805
10°	34872
15°	33434
20°	31542
25°	29873
30°	27602
35°	25203
40°	23524
45°	21491
50°	20321
55°	18300
60°	14302
65°	9960
70°	6320
75°	3562
80°	994
85°	0



TEST NUMBER: P210515

CATALOG NUMBER: PR8S20D010 - PR8M12MDMW - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	109.1	5.2
10°-20°	293.4	14.1
20°-30°	401.8	19.3
30°-40°	421.2	20.2
40°-50°	383.9	18.4
50°-60°	299.6	14.4
60°-70°	139.5	6.7
70°-80°	34.7	1.7
80°-90°	1.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	804.3	38.6
0°-40°	1225.5	58.8
0°-60°	1909.0	91.6
0°-90°	2084.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2084.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1165	
5°	1157	109
15°	1047	293
25°	878	402
35°	670	421
45°	493	384
55°	340	300
65°	136	139
75°	30	35
85°	0	1
90°	0	



TEST NUMBER: P210515

CATALOG NUMBER: PR8S20D010 - PR8M12MDMW - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1165.1
2.5°	1159.5
5°	1156.7
7.5°	1142.6
10°	1113.7
12.5°	1080.0
15°	1047.3
17.5°	1006.1
20°	961.2
22.5°	919.2
25°	878.0
27.5°	828.5
30°	775.2
32.5°	720.9
35°	669.5
37.5°	626.5
40°	584.4
42.5°	539.5
45°	492.8
47.5°	455.4
50°	423.6
52.5°	388.0
55°	340.4
57.5°	287.1
60°	231.9
62.5°	179.5
65°	136.5
67.5°	99.1
70°	70.1
72.5°	47.7
75°	29.9
77.5°	16.8
80°	5.6
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)