

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210330

Luminaire Tested: **PR8R10D010 - PR8M12MDMB - 3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210330
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29044)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8R10D010 - PR8M12MDMB - 3500K
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE BLACK FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1208.8 lumens
Efficiency: N/A
Efficacy: 115.1 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210330

CATALOG NUMBER: PR8R10D010 - PR8M12MDMB - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P210330

CATALOG NUMBER: PR8R10D010 - PR8M12MDMB - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	20836
5°	20764
10°	20224
15°	19391
20°	18295
25°	17325
30°	16009
35°	14617
40°	13642
45°	12463
50°	11787
55°	10613
60°	8295
65°	5779
70°	3669
75°	2073
80°	586
85°	0



TEST NUMBER: P210330

CATALOG NUMBER: PR8R10D010 - PR8M12MDMB - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.3	5.2
10°-20°	170.2	14.1
20°-30°	233.0	19.3
30°-40°	244.3	20.2
40°-50°	222.6	18.4
50°-60°	173.8	14.4
60°-70°	80.9	6.7
70°-80°	20.2	1.7
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	466.5	38.6
0°-40°	710.7	58.8
0°-60°	1107.1	91.6
0°-90°	1208.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1208.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	676	
5°	671	63
15°	607	170
25°	509	233
35°	388	244
45°	286	223
55°	197	174
65°	79	81
75°	17	20
85°	0	1
90°	0	



TEST NUMBER: P210330

CATALOG NUMBER: PR8R10D010 - PR8M12MDMB - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	675.7
2.5°	672.4
5°	670.8
7.5°	662.7
10°	645.9
12.5°	626.3
15°	607.4
17.5°	583.5
20°	557.5
22.5°	533.1
25°	509.2
27.5°	480.5
30°	449.6
32.5°	418.1
35°	388.3
37.5°	363.3
40°	338.9
42.5°	312.9
45°	285.8
47.5°	264.1
50°	245.7
52.5°	225.0
55°	197.4
57.5°	166.5
60°	134.5
62.5°	104.1
65°	79.2
67.5°	57.5
70°	40.7
72.5°	27.7
75°	17.4
77.5°	9.8
80°	3.3
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)