

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210560

Luminaire Tested: **PR8S20D010 - PR8M12WDMW - 3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210560
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8S20D010 - PR8M12WDMW - 3500K
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE WHITE FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2076.9 lumens
Efficiency: N/A
Efficacy: 94.4 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210560

CATALOG NUMBER: PR8S20D010 - PR8M12WDMW - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P210560

CATALOG NUMBER: PR8S20D010 - PR8M12WDMW - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95		96	94	92		92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80		86	82	79		83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69		77	72	68		74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60		69	64	59		67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52		63	57	52		61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46		57	51	46		55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34		44	38	33		43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31		41	35	30		40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25199
5°	25624
10°	25933
15°	26411
20°	26968
25°	27216
30°	27171
35°	27108
40°	26165
45°	23959
50°	20019
55°	16645
60°	13987
65°	11558
70°	9936
75°	7804
80°	5398
85°	5661



TEST NUMBER: P210560

CATALOG NUMBER: PR8S20D010 - PR8M12WDMW - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	78.9	3.8
10°-20°	234.1	11.3
20°-30°	367.6	17.7
30°-40°	448.2	21.6
40°-50°	418.9	20.2
50°-60°	279.4	13.5
60°-70°	160.7	7.7
70°-80°	74.1	3.6
80°-90°	15.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	680.6	32.8
0°-40°	1128.8	54.3
0°-60°	1827.0	88.0
0°-90°	2076.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2076.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	817	
5°	828	79
15°	827	234
25°	800	368
35°	720	448
45°	549	419
55°	310	279
65°	158	161
75°	66	74
85°	16	15
90°	0	



TEST NUMBER: P210560

CATALOG NUMBER: PR8S20D010 - PR8M12WDMW - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	817.2
2.5°	818.5
5°	827.8
7.5°	826.9
10°	828.2
12.5°	826.5
15°	827.3
17.5°	825.6
20°	821.8
22.5°	808.3
25°	799.9
27.5°	783.0
30°	763.1
32.5°	743.3
35°	720.1
37.5°	692.2
40°	650.0
42.5°	603.9
45°	549.4
47.5°	489.1
50°	417.3
52.5°	356.4
55°	309.6
57.5°	264.8
60°	226.8
62.5°	193.8
65°	158.4
67.5°	130.1
70°	110.2
72.5°	93.8
75°	65.5
77.5°	51.9
80°	30.4
82.5°	19.4
85°	16.0
87.5°	4.6
90°	0.0

(END OF REPORT)