

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210650

Luminaire Tested: **PR8S30D010 - PR8M34WDMB - 3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210650
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8S30D010 - PR8M34WDMB - 3500K
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE BLACK FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2768.2 lumens
Efficiency: N/A
Efficacy: 97.1 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 28.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210650

CATALOG NUMBER: PR8S30D010 - PR8M34WDMB - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P210650

CATALOG NUMBER: PR8S30D010 - PR8M34WDMB - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95		96	94	92		92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80		86	82	79		83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69		77	72	68		74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60		69	64	59		67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52		63	57	52		61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46		57	51	46		55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34		44	38	33		43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31		41	35	30		40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	33587
5°	34152
10°	34562
15°	35203
20°	35946
25°	36273
30°	36219
35°	36127
40°	34872
45°	31935
50°	26678
55°	22182
60°	18644
65°	15403
70°	13244
75°	10389
80°	7192
85°	7571



TEST NUMBER: P210650

CATALOG NUMBER: PR8S30D010 - PR8M34WDMB - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.1	3.8
10°-20°	312.0	11.3
20°-30°	490.0	17.7
30°-40°	597.3	21.6
40°-50°	558.3	20.2
50°-60°	372.4	13.5
60°-70°	214.3	7.7
70°-80°	98.8	3.6
80°-90°	20.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	907.2	32.8
0°-40°	1504.5	54.3
0°-60°	2435.1	88.0
0°-90°	2768.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2768.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1089	
5°	1103	105
15°	1103	312
25°	1066	490
35°	960	597
45°	732	558
55°	413	372
65°	211	214
75°	87	99
85°	21	20
90°	0	



TEST NUMBER: P210650

CATALOG NUMBER: PR8S30D010 - PR8M34WDMB - 3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1089.2
2.5°	1090.9
5°	1103.3
7.5°	1102.2
10°	1103.8
12.5°	1101.6
15°	1102.7
17.5°	1100.5
20°	1095.4
22.5°	1077.4
25°	1066.1
27.5°	1043.6
30°	1017.2
32.5°	990.7
35°	959.7
37.5°	922.6
40°	866.3
42.5°	804.9
45°	732.3
47.5°	651.8
50°	556.1
52.5°	475.1
55°	412.6
57.5°	352.9
60°	302.3
62.5°	258.4
65°	211.1
67.5°	173.4
70°	146.9
72.5°	125.0
75°	87.2
77.5°	69.2
80°	40.5
82.5°	25.9
85°	21.4
87.5°	6.2
90°	0.0

(END OF REPORT)