

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210654

Luminaire Tested: **PR8S40D010 - PR8M34WDMB - 3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P210654  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR8S40D010 - PR8M34WDMB - 3000K  
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE BLACK FINISH  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3352.6 lumens  
Efficiency: N/A  
Efficacy: 77.1 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 43.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210654

CATALOG NUMBER: PR8S40D010 - PR8M34WDMB - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P210654

CATALOG NUMBER: PR8S40D010 - PR8M34WDMB - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	40676
5°	41361
10°	41858
15°	42635
20°	43533
25°	43932
30°	43864
35°	43754
40°	42234
45°	38677
50°	32310
55°	26865
60°	22578
65°	18650
70°	16039
75°	12593
80°	8719
85°	9164



TEST NUMBER: P210654

CATALOG NUMBER: PR8S40D010 - PR8M34WDMB - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	127.3	3.8
10°-20°	377.9	11.3
20°-30°	593.5	17.7
30°-40°	723.4	21.6
40°-50°	676.1	20.2
50°-60°	451.0	13.5
60°-70°	259.4	7.7
70°-80°	119.7	3.6
80°-90°	24.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1098.7	32.8
0°-40°	1822.1	54.3
0°-60°	2949.2	88.0
0°-90°	3352.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3352.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1319	
5°	1336	127
15°	1336	378
25°	1291	593
35°	1162	723
45°	887	676
55°	500	451
65°	256	259
75°	106	120
85°	26	24
90°	0	



TEST NUMBER: P210654

CATALOG NUMBER: PR8S40D010 - PR8M34WDMB - 3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	1319.1
2.5°	1321.2
5°	1336.2
7.5°	1334.8
10°	1336.8
12.5°	1334.1
15°	1335.5
17.5°	1332.7
20°	1326.6
22.5°	1304.8
25°	1291.2
27.5°	1263.9
30°	1231.9
32.5°	1199.8
35°	1162.3
37.5°	1117.3
40°	1049.2
42.5°	974.8
45°	886.9
47.5°	789.4
50°	673.5
52.5°	575.4
55°	499.7
57.5°	427.4
60°	366.1
62.5°	312.9
65°	255.6
67.5°	210.0
70°	177.9
72.5°	151.3
75°	105.7
77.5°	83.9
80°	49.1
82.5°	31.4
85°	25.9
87.5°	7.5
90°	0.0

(END OF REPORT)