

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO

Report Number: P600776

Luminaire Tested: **FE10A35GLMB**

Issue Date: 07/11/2022

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.



**Test Information**

Test Method: LM-79-08  
 Report Number: P600776  
 Test Lab: Third Party  
 Issue Date: 07/11/2022  
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
 Product Line: HALO  
 Catalog Number: FE10A35GLMB  
 Description: LED Entry Light w/ Night Light -Bronze 3500K (Main)  
 Light Source: 70 CRI LEDs  
 Ballast/Driver: (1) Electronic Driver

**Summary**

Lumens per Lamp: N/A  
 Luminaire Lumens: 980.6 lumens  
 Efficiency: N/A  
 Efficacy: 95.9 lumens/watt  
 Luminous Opening: Point Source (0m x 0m x 0m)  
 IES Classification: Type IV - Short  
 BUG Rating: B0 - U3 - G1


Input Watts (W): 10.22  
 Input Voltage (V): 120.0  
 Input Current (Ain): 0.085  
 Voltage Rise (V): NR  
 Power Factor: NR  
 Total Harmonic Distortion (THDi): NR  
 Frequency (hertz): 60  
 Stabilization Time: NR  
 Operation Time: NR  
 Ambient Temperature (°C): NR  
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

### Iso-Footcandle Lines of Horizontal Illumination


× Max cd  
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 0.9 fc  
 Type IV - Short - N/A

REPORT NUMBER: P600776  
CATALOG NUMBER: FE10A35GLMB

### Luminous Intensity Polar Plot



— Vertical Plane Through 22.5-Deg Lateral      - - - Horizontal Cone Through 65-Deg Vertical

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB


**FLUX DISTRIBUTION:**

		Downward	Upward	Total
<b>House Side</b>	Lumens	282.8	97.9	380.7
	% Fixture	28.8	10.0	38.8
<b>Street Side</b>	Lumens	384.5	215.4	599.9
	% Fixture	39.2	22.0	61.2
<b>Total</b>	Lumens	667.3	313.2	980.6
	% Fixture	68.1	31.9	100.0

**Coefficient of Utilization**

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	7.4	0.8
10°-20°	25.8	2.6
20°-30°	48.4	4.9
30°-40°	70.6	7.2
40°-50°	89.6	9.1
50°-60°	103.8	10.6
60°-70°	110.8	11.3
70°-80°	109.6	11.2
80°-90°	101.4	10.3
90°-100°	88.8	9.1
100°-110°	73.9	7.5
110°-120°	57.8	5.9
120°-130°	41.9	4.3
130°-140°	27.2	2.8
140°-150°	15.2	1.6
150°-160°	6.6	0.7
160°-170°	1.7	0.2
170°-180°	0.1	0.0
0°-90°	667.3	68.1
0°-180°	980.6	100.0




REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:**

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	40.0	4.1			
FM (30°-60°)	146.6	15.0			
FH (60°-80°)	133.6	13.6			G0/660
FVH (80°-90°)	64.3	6.6			G1/100
BL (0°-30°)	41.6	4.2	B0/110		
BM (30°-60°)	117.4	12.0	B0/220		
BH (60°-80°)	86.8	8.9	B0/110		G0/110
BVH (80°-90°)	37.0	3.8			G1/100
UL (90°-100°)	88.8	9.1		U3/500	
UH (100°-180°)	224.5	22.9		U3/500	

**BUG Rating: B0-U3-G1**  
 Type IV Short



REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (FULL):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	69.8	70.0	70.1	70.3	70.4	70.6	70.7	70.9	71.0	71.2	71.2
5°	71.0	71.2	71.4	71.5	71.7	71.8	72.0	72.1	72.3	72.4	72.4
7.5°	72.3	72.5	72.8	73.0	73.3	73.5	73.8	74.0	74.3	74.5	74.5
10°	76.5	76.6	76.7	76.7	76.8	76.9	77.0	77.1	77.1	77.2	77.2
12.5°	79.6	79.8	79.9	80.1	80.3	80.4	80.6	80.8	80.9	81.1	81.3
15°	85.2	85.2	85.1	85.1	85.1	85.1	85.1	85.0	85.0	85.0	85.2
17.5°	89.3	89.3	89.4	89.5	89.6	89.7	89.8	89.9	90.0	90.1	90.2
20°	94.1	94.1	94.1	94.1	94.1	94.1	94.1	94.1	94.1	94.1	94.2
22.5°	97.7	98.0	98.2	98.4	98.7	98.9	99.1	99.4	99.6	99.9	99.8
25°	103.3	103.3	103.3	103.2	103.2	103.2	103.1	103.1	103.1	103.1	103.0
27.5°	105.7	106.0	106.2	106.5	106.7	107.0	107.2	107.5	107.7	108.0	107.9
30°	109.2	109.5	109.7	109.9	110.2	110.4	110.6	110.8	111.1	111.3	111.3
32.5°	116.6	116.3	116.1	115.9	115.6	115.4	115.1	114.9	114.7	114.4	114.4
35°	119.7	119.6	119.5	119.4	119.3	119.2	119.1	119.0	118.9	118.8	118.7
37.5°	122.4	122.4	122.4	122.5	122.5	122.5	122.6	122.6	122.7	122.7	122.4
40°	124.8	124.8	124.8	124.9	124.9	125.0	125.0	125.0	125.1	125.1	125.0
42.5°	127.8	127.6	127.5	127.3	127.1	126.9	126.7	126.5	126.3	126.2	125.9
45°	131.1	131.0	130.8	130.6	130.5	130.3	130.1	130.0	129.8	129.6	129.5
47.5°	132.2	132.3	132.4	132.5	132.6	132.6	132.7	132.8	132.9	133.0	132.7
50°	133.7	134.0	134.2	134.4	134.7	134.9	135.1	135.3	135.6	135.8	135.4
52.5°	135.8	135.8	135.8	135.8	135.7	135.7	135.7	135.7	135.7	135.6	135.4
55°	135.5	135.7	135.8	135.9	136.1	136.2	136.3	136.5	136.6	136.7	136.5
57.5°	135.6	135.9	136.2	136.5	136.8	137.0	137.3	137.6	137.9	138.2	137.8
60°	137.1	137.2	137.3	137.4	137.4	137.5	137.6	137.7	137.8	137.9	137.7
62.5°	136.8	136.9	137.1	137.2	137.4	137.5	137.7	137.9	138.0	138.2	137.9
65°	136.4	136.6	136.8	137.1	137.3	137.5	137.8	138.0	138.2	138.5	137.9
67.5°	135.2	135.3	135.3	135.4	135.4	135.5	135.5	135.6	135.6	135.7	135.4
70°	134.3	134.2	134.1	134.0	133.8	133.7	133.6	133.5	133.3	133.2	133.2
72.5°	133.2	133.3	133.4	133.6	133.7	133.8	134.0	134.1	134.2	134.3	133.9
75°	130.7	130.7	130.8	130.9	131.0	131.1	131.2	131.3	131.4	131.5	131.1
77.5°	128.8	129.0	129.3	129.5	129.7	130.0	130.2	130.5	130.7	130.9	130.5
80°	128.4	128.5	128.6	128.7	128.9	129.0	129.1	129.2	129.4	129.5	128.9
82.5°	124.4	124.5	124.7	124.9	125.1	125.2	125.4	125.6	125.7	125.9	125.4
85°	122.3	122.3	122.4	122.4	122.5	122.5	122.6	122.6	122.7	122.7	122.3
87.5°	118.5	118.6	118.8	119.0	119.1	119.3	119.5	119.6	119.8	120.0	119.5
90°	116.0	116.2	116.3	116.5	116.7	116.8	117.0	117.2	117.4	117.5	117.0
92.5°	113.6	113.7	113.7	113.8	113.9	113.9	114.0	114.1	114.1	114.2	113.7
95°	110.3	110.4	110.5	110.6	110.7	110.8	110.9	111.0	111.1	111.2	110.7
97.5°	108.4	108.3	108.3	108.2	108.2	108.1	108.1	108.0	107.9	107.9	107.5
100°	104.2	104.3	104.4	104.4	104.5	104.6	104.7	104.8	104.9	105.0	104.5
102.5°	101.2	101.3	101.4	101.4	101.5	101.5	101.6	101.7	101.7	101.8	101.4
105°	99.0	99.0	99.0	99.0	99.0	99.0	99.0	99.0	99.0	98.9	98.5
107.5°	95.7	95.7	95.7	95.6	95.6	95.6	95.6	95.6	95.6	95.6	95.2
110°	91.7	91.8	91.9	92.0	92.0	92.1	92.2	92.3	92.3	92.4	92.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	89.0	89.0	89.0	89.0	89.0	88.9	88.9	88.9	88.9	88.9	88.5
115°	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.4	85.0
117.5°	81.6	81.6	81.6	81.6	81.6	81.5	81.5	81.5	81.5	81.5	81.1
120°	78.4	78.3	78.3	78.2	78.1	78.1	78.0	78.0	77.9	77.9	77.5
122.5°	74.7	74.6	74.5	74.4	74.4	74.3	74.2	74.2	74.1	74.0	73.6
125°	70.8	70.7	70.7	70.6	70.6	70.6	70.5	70.5	70.5	70.4	70.0
127.5°	66.5	66.5	66.5	66.5	66.4	66.4	66.4	66.4	66.3	66.3	66.0
130°	63.1	63.0	63.0	62.9	62.9	62.8	62.8	62.7	62.6	62.6	62.3
132.5°	59.1	59.0	59.0	59.0	58.9	58.9	58.8	58.8	58.7	58.7	58.4
135°	55.2	55.2	55.1	55.0	54.9	54.9	54.8	54.7	54.7	54.6	54.3
137.5°	51.5	51.4	51.3	51.2	51.1	51.0	50.9	50.8	50.7	50.6	50.3
140°	47.6	47.5	47.4	47.3	47.3	47.2	47.1	47.0	46.9	46.8	46.6
142.5°	44.0	43.9	43.8	43.7	43.6	43.5	43.4	43.3	43.2	43.1	42.8
145°	39.6	39.6	39.5	39.5	39.5	39.4	39.4	39.4	39.4	39.3	39.1
147.5°	35.7	35.7	35.6	35.5	35.5	35.4	35.3	35.3	35.2	35.2	34.9
150°	32.1	32.0	31.9	31.8	31.8	31.7	31.6	31.5	31.5	31.4	31.2
152.5°	27.8	27.8	27.8	27.8	27.8	27.8	27.7	27.7	27.7	27.7	27.5
155°	24.4	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.3	24.1
157.5°	20.6	20.5	20.5	20.5	20.5	20.5	20.4	20.4	20.4	20.4	20.3
160°	17.0	17.0	17.0	16.9	16.9	16.9	16.9	16.9	16.9	16.9	16.8
162.5°	13.9	13.8	13.8	13.8	13.7	13.7	13.7	13.6	13.6	13.5	13.4
165°	10.5	10.5	10.5	10.4	10.4	10.4	10.4	10.3	10.3	10.3	10.2
167.5°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
170°	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.6	4.5
172.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.4	2.4	2.3
175°	1.1	1.0	1.0	1.0	0.9	0.9	0.9	0.8	0.8	0.8	0.8
177.5°	0.7	0.6	0.6	0.6	0.5	0.5	0.4	0.4	0.4	0.3	0.3
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	71.3	71.3	71.3	71.4	71.4	71.5	71.5	71.5	71.5	71.5	71.5
5°	72.4	72.3	72.3	72.2	72.2	72.1	72.1	72.0	72.2	72.3	72.5
7.5°	74.5	74.6	74.6	74.6	74.6	74.6	74.7	74.7	74.9	75.0	75.2
10°	77.2	77.2	77.1	77.1	77.1	77.1	77.1	77.1	77.4	77.8	78.2
12.5°	81.5	81.7	81.9	82.1	82.3	82.5	82.7	82.9	82.9	83.0	83.1
15°	85.3	85.5	85.7	85.8	86.0	86.2	86.3	86.5	86.8	87.1	87.3
17.5°	90.3	90.4	90.5	90.6	90.7	90.8	90.9	91.0	91.2	91.3	91.5
20°	94.2	94.3	94.4	94.5	94.6	94.7	94.8	94.8	95.1	95.3	95.5
22.5°	99.7	99.7	99.6	99.5	99.5	99.4	99.4	99.3	99.5	99.7	99.9
25°	103.0	103.0	102.9	102.9	102.9	102.8	102.8	102.8	103.0	103.2	103.4
27.5°	107.8	107.7	107.6	107.5	107.5	107.4	107.3	107.2	107.3	107.4	107.5
30°	111.2	111.2	111.2	111.2	111.1	111.1	111.1	111.1	111.1	111.2	111.3
32.5°	114.4	114.3	114.3	114.3	114.3	114.3	114.2	114.2	114.3	114.3	114.4
35°	118.6	118.5	118.4	118.3	118.3	118.2	118.1	118.0	118.0	118.0	118.0
37.5°	122.2	121.9	121.6	121.4	121.1	120.8	120.5	120.3	120.4	120.4	120.5
40°	124.8	124.7	124.5	124.3	124.2	124.0	123.9	123.7	123.6	123.5	123.3
42.5°	125.7	125.5	125.3	125.0	124.8	124.6	124.3	124.1	124.1	124.1	124.1
45°	129.4	129.2	129.1	128.9	128.8	128.6	128.5	128.4	128.1	127.9	127.7
47.5°	132.4	132.1	131.8	131.5	131.2	130.9	130.5	130.2	130.0	129.7	129.4
50°	135.0	134.6	134.2	133.8	133.4	133.0	132.6	132.2	131.9	131.7	131.4
52.5°	135.2	135.0	134.7	134.5	134.3	134.1	133.9	133.6	133.3	133.0	132.6
55°	136.2	135.9	135.7	135.4	135.1	134.9	134.6	134.3	134.0	133.8	133.5
57.5°	137.5	137.1	136.8	136.4	136.1	135.7	135.4	135.0	134.7	134.4	134.1
60°	137.5	137.3	137.1	136.9	136.7	136.5	136.3	136.1	135.5	135.0	134.5
62.5°	137.7	137.4	137.2	136.9	136.7	136.4	136.1	135.9	135.3	134.7	134.1
65°	137.3	136.8	136.2	135.6	135.1	134.5	134.0	133.4	133.1	132.8	132.5
67.5°	135.2	134.9	134.6	134.3	134.1	133.8	133.5	133.3	132.7	132.1	131.5
70°	133.2	133.2	133.2	133.2	133.2	133.2	133.2	133.3	132.7	132.1	131.5
72.5°	133.5	133.0	132.6	132.1	131.7	131.3	130.8	130.4	129.7	129.1	128.4
75°	130.8	130.5	130.2	129.9	129.5	129.2	128.9	128.6	127.9	127.2	126.4
77.5°	130.0	129.5	129.1	128.6	128.1	127.7	127.2	126.8	126.1	125.5	124.9
80°	128.2	127.6	127.0	126.4	125.8	125.1	124.5	123.9	123.3	122.6	122.0
82.5°	125.0	124.5	124.1	123.6	123.1	122.7	122.2	121.7	121.2	120.6	120.0
85°	122.0	121.6	121.2	120.9	120.5	120.2	119.8	119.4	118.8	118.1	117.4
87.5°	119.0	118.6	118.1	117.6	117.1	116.7	116.2	115.7	115.2	114.6	114.0
90°	116.5	116.0	115.5	114.9	114.4	113.9	113.4	112.9	112.3	111.7	111.2
92.5°	113.3	112.8	112.4	111.9	111.5	111.0	110.6	110.1	109.5	108.9	108.2
95°	110.2	109.7	109.3	108.8	108.3	107.8	107.4	106.9	106.3	105.7	105.1
97.5°	107.0	106.6	106.2	105.8	105.4	104.9	104.5	104.1	103.5	102.9	102.3
100°	104.1	103.7	103.3	102.9	102.5	102.1	101.7	101.3	100.7	100.1	99.4
102.5°	101.1	100.7	100.3	100.0	99.6	99.2	98.9	98.5	97.9	97.3	96.6
105°	98.1	97.7	97.3	97.0	96.6	96.2	95.8	95.4	94.7	94.0	93.4
107.5°	94.8	94.5	94.1	93.7	93.3	93.0	92.6	92.2	91.5	90.9	90.2
110°	91.6	91.1	90.7	90.3	89.9	89.5	89.1	88.6	88.0	87.4	86.8

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	88.1	87.7	87.3	87.0	86.6	86.2	85.8	85.4	84.8	84.1	83.5
115°	84.5	84.1	83.7	83.3	82.8	82.4	82.0	81.6	81.0	80.4	79.8
117.5°	80.8	80.4	80.0	79.7	79.3	79.0	78.6	78.3	77.7	77.1	76.5
120°	77.2	76.8	76.4	76.1	75.7	75.4	75.0	74.6	74.0	73.4	72.8
122.5°	73.3	72.9	72.6	72.2	71.9	71.5	71.2	70.8	70.2	69.6	69.0
125°	69.6	69.2	68.9	68.5	68.1	67.7	67.3	66.9	66.3	65.8	65.2
127.5°	65.7	65.4	65.1	64.8	64.5	64.2	63.9	63.6	63.0	62.4	61.8
130°	61.9	61.6	61.3	60.9	60.6	60.2	59.9	59.6	59.0	58.4	57.9
132.5°	58.0	57.6	57.3	56.9	56.6	56.2	55.9	55.5	55.0	54.5	54.0
135°	54.0	53.7	53.4	53.1	52.8	52.5	52.2	51.9	51.4	50.9	50.4
137.5°	50.1	49.8	49.6	49.4	49.1	48.9	48.6	48.4	47.9	47.4	47.0
140°	46.3	46.0	45.7	45.4	45.2	44.9	44.6	44.3	43.9	43.4	42.9
142.5°	42.5	42.3	42.0	41.7	41.4	41.1	40.8	40.5	40.0	39.6	39.1
145°	38.8	38.6	38.3	38.0	37.8	37.5	37.3	37.0	36.6	36.1	35.7
147.5°	34.7	34.5	34.3	34.0	33.8	33.6	33.3	33.1	32.7	32.3	31.9
150°	31.0	30.8	30.5	30.3	30.1	29.9	29.7	29.5	29.1	28.8	28.4
152.5°	27.3	27.1	26.9	26.7	26.5	26.3	26.1	25.9	25.6	25.3	25.0
155°	23.9	23.7	23.5	23.2	23.0	22.8	22.6	22.4	22.2	21.9	21.6
157.5°	20.1	20.0	19.9	19.7	19.6	19.4	19.3	19.2	18.9	18.6	18.4
160°	16.6	16.5	16.4	16.3	16.2	16.0	15.9	15.8	15.6	15.3	15.1
162.5°	13.3	13.2	13.1	13.0	12.9	12.8	12.7	12.6	12.4	12.2	12.1
165°	10.1	10.0	9.9	9.8	9.7	9.6	9.5	9.4	9.2	9.1	8.9
167.5°	7.1	7.0	7.0	6.9	6.9	6.8	6.7	6.7	6.5	6.4	6.3
170°	4.5	4.4	4.4	4.3	4.3	4.3	4.2	4.2	4.0	3.9	3.8
172.5°	2.3	2.2	2.2	2.1	2.1	2.1	2.0	2.0	1.9	1.8	1.8
175°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
177.5°	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.4
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	71.5	71.5	71.5	71.5	71.4	71.4	71.6	71.7	71.8	72.0	72.1
5°	72.6	72.7	72.9	73.0	73.2	73.3	73.5	73.8	74.0	74.2	74.5
7.5°	75.4	75.6	75.8	76.0	76.2	76.4	76.6	76.8	77.1	77.3	77.6
10°	78.5	78.9	79.3	79.6	80.0	80.4	80.6	80.8	81.0	81.2	81.4
12.5°	83.1	83.2	83.3	83.3	83.4	83.5	83.8	84.2	84.5	84.9	85.2
15°	87.6	87.9	88.2	88.5	88.8	89.1	89.3	89.4	89.6	89.8	90.0
17.5°	91.6	91.8	91.9	92.1	92.2	92.4	92.6	92.9	93.2	93.4	93.7
20°	95.7	95.9	96.2	96.4	96.6	96.8	97.1	97.3	97.5	97.7	97.9
22.5°	100.1	100.3	100.5	100.7	100.9	101.1	101.3	101.4	101.6	101.7	101.9
25°	103.6	103.8	104.1	104.3	104.5	104.7	104.9	105.0	105.2	105.4	105.6
27.5°	107.6	107.7	107.8	107.9	108.0	108.2	108.3	108.5	108.7	108.8	109.0
30°	111.4	111.5	111.6	111.7	111.8	111.8	112.0	112.1	112.2	112.3	112.4
32.5°	114.4	114.5	114.5	114.6	114.6	114.7	114.8	114.9	115.0	115.2	115.3
35°	117.9	117.9	117.9	117.9	117.9	117.8	117.9	118.0	118.0	118.1	118.2
37.5°	120.6	120.7	120.8	120.8	120.9	121.0	121.0	121.0	121.0	121.0	121.0
40°	123.2	123.0	122.9	122.8	122.6	122.5	122.6	122.8	122.9	123.1	123.3
42.5°	124.0	124.0	124.0	124.0	124.0	124.0	124.1	124.2	124.3	124.5	124.6
45°	127.5	127.3	127.1	126.9	126.7	126.5	126.5	126.6	126.6	126.7	126.8
47.5°	129.2	128.9	128.6	128.4	128.1	127.8	127.9	128.0	128.0	128.1	128.2
50°	131.2	130.9	130.7	130.4	130.2	129.9	129.8	129.7	129.6	129.5	129.4
52.5°	132.3	131.9	131.6	131.2	130.9	130.5	130.4	130.3	130.1	130.0	129.9
55°	133.2	132.9	132.7	132.4	132.1	131.9	131.6	131.3	131.0	130.7	130.4
57.5°	133.8	133.4	133.1	132.8	132.5	132.2	131.9	131.5	131.2	130.8	130.5
60°	134.0	133.5	133.0	132.5	132.0	131.5	131.2	131.0	130.7	130.4	130.2
62.5°	133.5	132.8	132.2	131.6	131.0	130.4	130.1	129.8	129.5	129.3	129.0
65°	132.3	132.0	131.7	131.4	131.1	130.8	130.4	129.9	129.5	129.0	128.6
67.5°	131.0	130.4	129.8	129.3	128.7	128.1	127.8	127.5	127.2	127.0	126.7
70°	130.9	130.3	129.7	129.1	128.6	128.0	127.5	127.1	126.6	126.1	125.7
72.5°	127.7	127.1	126.4	125.8	125.1	124.4	124.2	123.9	123.6	123.3	123.0
75°	125.7	125.0	124.3	123.6	122.9	122.2	121.9	121.6	121.3	121.1	120.8
77.5°	124.3	123.6	123.0	122.4	121.8	121.1	120.7	120.2	119.8	119.3	118.9
80°	121.4	120.7	120.1	119.5	118.8	118.2	117.8	117.4	117.0	116.6	116.3
82.5°	119.5	118.9	118.3	117.8	117.2	116.7	116.2	115.7	115.2	114.7	114.2
85°	116.8	116.1	115.5	114.8	114.1	113.5	113.0	112.4	111.9	111.4	110.9
87.5°	113.5	112.9	112.3	111.8	111.2	110.6	110.1	109.7	109.2	108.7	108.2
90°	110.6	110.0	109.5	108.9	108.3	107.8	107.2	106.7	106.1	105.5	105.0
92.5°	107.6	106.9	106.3	105.7	105.0	104.4	103.9	103.3	102.8	102.3	101.7
95°	104.5	104.0	103.4	102.8	102.2	101.6	101.1	100.5	100.0	99.4	98.9
97.5°	101.7	101.1	100.5	99.9	99.3	98.7	98.1	97.5	96.9	96.3	95.7
100°	98.8	98.2	97.6	96.9	96.3	95.7	95.0	94.4	93.8	93.1	92.5
102.5°	96.0	95.4	94.8	94.1	93.5	92.9	92.2	91.6	91.0	90.3	89.7
105°	92.7	92.1	91.4	90.8	90.1	89.4	88.8	88.2	87.5	86.9	86.2
107.5°	89.6	88.9	88.3	87.6	86.9	86.3	85.6	85.0	84.3	83.7	83.0
110°	86.2	85.5	84.9	84.3	83.7	83.1	82.4	81.7	81.0	80.3	79.6

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	82.9	82.2	81.6	81.0	80.3	79.7	78.9	78.2	77.5	76.8	76.0
115°	79.2	78.6	78.0	77.4	76.8	76.2	75.5	74.7	74.0	73.3	72.5
117.5°	75.8	75.2	74.6	74.0	73.4	72.8	72.0	71.3	70.5	69.8	69.0
120°	72.2	71.6	71.0	70.3	69.7	69.1	68.4	67.7	66.9	66.2	65.5
122.5°	68.4	67.9	67.3	66.7	66.1	65.5	64.7	64.0	63.2	62.5	61.7
125°	64.6	64.1	63.5	62.9	62.4	61.8	61.1	60.3	59.6	58.8	58.1
127.5°	61.2	60.6	60.0	59.4	58.8	58.2	57.5	56.7	56.0	55.3	54.5
130°	57.3	56.8	56.2	55.6	55.1	54.5	53.8	53.1	52.4	51.7	51.0
132.5°	53.5	52.9	52.4	51.9	51.4	50.9	50.2	49.5	48.7	48.0	47.3
135°	49.9	49.4	48.9	48.4	47.9	47.4	46.7	46.0	45.3	44.6	44.0
137.5°	46.5	46.0	45.5	45.0	44.5	44.1	43.4	42.7	42.0	41.3	40.6
140°	42.5	42.0	41.6	41.1	40.6	40.2	39.5	38.8	38.2	37.5	36.8
142.5°	38.7	38.3	37.8	37.4	36.9	36.5	35.9	35.3	34.6	34.0	33.4
145°	35.3	34.8	34.4	34.0	33.5	33.1	32.5	31.9	31.4	30.8	30.2
147.5°	31.5	31.1	30.7	30.3	29.9	29.5	29.0	28.5	28.0	27.5	27.0
150°	28.0	27.7	27.3	26.9	26.6	26.2	25.7	25.3	24.8	24.4	23.9
152.5°	24.8	24.5	24.2	23.9	23.6	23.4	22.9	22.5	22.0	21.6	21.2
155°	21.3	21.1	20.8	20.5	20.3	20.0	19.6	19.2	18.8	18.3	17.9
157.5°	18.1	17.9	17.6	17.3	17.1	16.8	16.5	16.1	15.8	15.5	15.1
160°	14.9	14.6	14.4	14.2	14.0	13.7	13.5	13.2	12.9	12.6	12.3
162.5°	11.9	11.7	11.5	11.3	11.1	11.0	10.7	10.4	10.1	9.8	9.5
165°	8.8	8.6	8.4	8.3	8.1	8.0	7.8	7.5	7.3	7.1	6.9
167.5°	6.2	6.1	6.0	5.9	5.7	5.6	5.5	5.3	5.1	4.9	4.7
170°	3.7	3.6	3.4	3.3	3.2	3.1	3.0	2.8	2.7	2.5	2.4
172.5°	1.7	1.6	1.6	1.5	1.4	1.4	1.3	1.3	1.2	1.2	1.1
175°	0.8	0.8	0.8	0.8	0.8	0.8	0.7	0.7	0.7	0.7	0.7
177.5°	0.4	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	72.3	72.4	72.5	72.7	72.8	72.9	73.0	73.1	73.1	73.2	73.3
5°	74.7	74.9	75.2	75.4	75.5	75.7	75.8	75.9	76.1	76.2	76.3
7.5°	77.8	78.1	78.3	78.6	78.8	79.0	79.3	79.5	79.8	80.0	80.2
10°	81.6	81.8	82.0	82.2	82.4	82.7	82.9	83.2	83.4	83.7	83.9
12.5°	85.6	85.9	86.3	86.6	86.8	87.1	87.3	87.5	87.7	87.9	88.1
15°	90.2	90.4	90.6	90.8	91.0	91.2	91.4	91.7	91.9	92.1	92.3
17.5°	93.9	94.2	94.5	94.7	94.9	95.2	95.4	95.6	95.9	96.1	96.3
20°	98.2	98.4	98.6	98.8	99.0	99.3	99.5	99.7	99.9	100.1	100.3
22.5°	102.0	102.1	102.3	102.4	102.6	102.8	103.0	103.2	103.4	103.6	103.7
25°	105.7	105.9	106.1	106.3	106.4	106.5	106.6	106.7	106.9	107.0	107.1
27.5°	109.2	109.4	109.5	109.7	109.8	110.0	110.1	110.2	110.4	110.5	110.6
30°	112.5	112.6	112.8	112.9	113.0	113.1	113.1	113.2	113.3	113.4	113.5
32.5°	115.4	115.5	115.6	115.8	115.9	116.0	116.1	116.2	116.3	116.4	116.5
35°	118.2	118.3	118.4	118.4	118.5	118.6	118.6	118.7	118.8	118.8	118.9
37.5°	121.0	121.0	121.0	121.0	121.0	121.0	120.9	120.9	120.9	120.9	120.9
40°	123.4	123.6	123.7	123.9	123.7	123.5	123.3	123.1	122.9	122.7	122.5
42.5°	124.7	124.9	125.0	125.1	124.9	124.7	124.5	124.3	124.1	123.9	123.7
45°	126.8	126.9	126.9	127.0	126.7	126.4	126.1	125.8	125.5	125.2	124.9
47.5°	128.3	128.3	128.4	128.5	128.1	127.7	127.4	127.0	126.6	126.3	125.9
50°	129.3	129.2	129.1	129.0	128.6	128.2	127.8	127.4	127.0	126.6	126.2
52.5°	129.7	129.6	129.5	129.3	128.9	128.4	128.0	127.6	127.1	126.7	126.3
55°	130.2	129.9	129.6	129.3	128.9	128.4	127.9	127.5	127.0	126.5	126.1
57.5°	130.1	129.8	129.4	129.1	128.6	128.0	127.5	126.9	126.4	125.9	125.3
60°	129.9	129.6	129.4	129.1	128.5	127.8	127.2	126.5	125.9	125.3	124.6
62.5°	128.7	128.4	128.1	127.8	127.3	126.7	126.2	125.6	125.0	124.5	123.9
65°	128.1	127.7	127.2	126.8	126.2	125.7	125.1	124.6	124.0	123.4	122.9
67.5°	126.4	126.1	125.8	125.5	125.0	124.4	123.9	123.3	122.8	122.3	121.7
70°	125.2	124.8	124.3	123.8	123.3	122.7	122.1	121.5	120.9	120.3	119.7
72.5°	122.7	122.5	122.2	121.9	121.3	120.7	120.2	119.6	119.0	118.4	117.8
75°	120.5	120.2	119.9	119.7	119.1	118.5	117.9	117.4	116.8	116.2	115.7
77.5°	118.4	117.9	117.5	117.0	116.5	115.9	115.4	114.8	114.3	113.7	113.1
80°	115.9	115.5	115.1	114.7	114.1	113.5	112.9	112.4	111.8	111.2	110.6
82.5°	113.7	113.2	112.7	112.2	111.6	110.9	110.3	109.6	109.0	108.3	107.7
85°	110.4	109.8	109.3	108.8	108.2	107.5	106.9	106.2	105.6	104.9	104.3
87.5°	107.7	107.2	106.7	106.3	105.5	104.8	104.1	103.3	102.6	101.9	101.2
90°	104.4	103.9	103.3	102.7	102.0	101.3	100.6	99.8	99.1	98.4	97.7
92.5°	101.2	100.7	100.1	99.6	98.8	98.1	97.3	96.6	95.8	95.1	94.3
95°	98.3	97.8	97.2	96.7	95.8	94.9	94.1	93.2	92.4	91.5	90.7
97.5°	95.1	94.5	93.9	93.3	92.4	91.6	90.7	89.9	89.0	88.2	87.3
100°	91.9	91.2	90.6	90.0	89.1	88.3	87.4	86.5	85.7	84.8	83.9
102.5°	89.0	88.4	87.8	87.1	86.1	85.2	84.2	83.2	82.2	81.2	80.2
105°	85.6	85.0	84.3	83.7	82.6	81.6	80.6	79.6	78.5	77.5	76.5
107.5°	82.3	81.7	81.0	80.4	79.3	78.2	77.1	76.0	74.9	73.9	72.8
110°	78.9	78.2	77.5	76.8	75.7	74.6	73.5	72.4	71.3	70.2	69.1

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	75.3	74.6	73.8	73.1	72.0	70.9	69.8	68.7	67.5	66.4	65.3
115°	71.8	71.0	70.3	69.6	68.4	67.3	66.2	65.1	63.9	62.8	61.7
117.5°	68.2	67.5	66.7	66.0	64.8	63.7	62.6	61.4	60.3	59.2	58.0
120°	64.8	64.0	63.3	62.6	61.4	60.3	59.1	57.9	56.8	55.6	54.4
122.5°	61.0	60.2	59.5	58.7	57.6	56.5	55.3	54.2	53.1	51.9	50.8
125°	57.3	56.6	55.8	55.0	53.9	52.8	51.7	50.6	49.5	48.4	47.2
127.5°	53.8	53.1	52.3	51.6	50.5	49.3	48.2	47.1	45.9	44.8	43.7
130°	50.3	49.6	48.8	48.1	47.0	45.9	44.8	43.6	42.5	41.4	40.2
132.5°	46.6	45.8	45.1	44.4	43.3	42.2	41.2	40.1	39.0	37.9	36.8
135°	43.3	42.6	41.9	41.2	40.2	39.1	38.0	37.0	35.9	34.8	33.7
137.5°	39.9	39.2	38.5	37.8	36.7	35.7	34.6	33.6	32.5	31.5	30.4
140°	36.2	35.5	34.8	34.2	33.2	32.3	31.3	30.4	29.4	28.5	27.5
142.5°	32.8	32.2	31.6	31.0	30.1	29.2	28.3	27.4	26.5	25.6	24.8
145°	29.6	29.0	28.5	27.9	27.0	26.2	25.4	24.5	23.7	22.9	22.0
147.5°	26.5	26.0	25.5	25.0	24.2	23.4	22.7	21.9	21.1	20.3	19.5
150°	23.5	23.0	22.6	22.1	21.4	20.7	19.9	19.2	18.5	17.8	17.1
152.5°	20.7	20.3	19.8	19.4	18.7	18.1	17.4	16.8	16.1	15.5	14.8
155°	17.5	17.1	16.7	16.3	15.7	15.2	14.6	14.1	13.5	13.0	12.4
157.5°	14.8	14.4	14.1	13.8	13.3	12.8	12.3	11.8	11.3	10.8	10.3
160°	12.0	11.8	11.5	11.2	10.8	10.4	10.0	9.6	9.2	8.8	8.4
162.5°	9.3	9.0	8.7	8.4	8.1	7.8	7.5	7.1	6.8	6.5	6.2
165°	6.7	6.5	6.3	6.1	5.8	5.5	5.3	5.0	4.7	4.4	4.2
167.5°	4.5	4.3	4.2	4.0	3.8	3.5	3.3	3.1	2.9	2.7	2.5
170°	2.3	2.1	2.0	1.9	1.7	1.6	1.5	1.3	1.2	1.1	0.9
172.5°	1.1	1.0	1.0	0.9	0.9	0.8	0.8	0.7	0.7	0.7	0.6
175°	0.7	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
177.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	73.4	73.5	73.6	73.7	73.9	74.0	74.1	74.2	74.3	74.4	74.6
5°	76.5	76.6	76.8	77.0	77.1	77.3	77.5	77.7	77.8	78.0	78.2
7.5°	80.5	80.7	80.9	81.1	81.2	81.4	81.6	81.8	81.9	82.1	82.3
10°	84.1	84.4	84.6	84.8	85.0	85.3	85.5	85.7	85.9	86.1	86.4
12.5°	88.4	88.6	88.8	89.0	89.2	89.4	89.6	89.8	90.0	90.2	90.4
15°	92.5	92.8	93.0	93.2	93.4	93.6	93.8	94.1	94.3	94.5	94.7
17.5°	96.6	96.8	97.0	97.2	97.4	97.6	97.8	98.0	98.2	98.4	98.6
20°	100.5	100.7	100.9	101.0	101.2	101.3	101.5	101.6	101.8	101.9	102.0
22.5°	103.9	104.1	104.3	104.4	104.6	104.7	104.9	105.1	105.2	105.4	105.5
25°	107.2	107.3	107.4	107.4	107.4	107.5	107.5	107.5	107.6	107.6	107.6
27.5°	110.8	110.9	110.6	110.3	110.0	109.6	109.3	109.0	108.7	108.4	108.1
30°	113.6	113.7	113.1	112.4	111.8	111.2	110.5	109.9	109.3	108.6	108.0
32.5°	116.6	116.7	115.7	114.7	113.6	112.6	111.6	110.6	109.5	108.5	107.5
35°	119.0	119.0	117.7	116.3	114.9	113.6	112.2	110.8	109.5	108.1	106.7
37.5°	120.8	120.8	119.2	117.6	116.0	114.3	112.7	111.1	109.5	107.8	106.2
40°	122.3	122.1	120.2	118.3	116.4	114.6	112.7	110.8	108.9	107.0	105.1
42.5°	123.6	123.4	121.2	119.0	116.9	114.7	112.5	110.4	108.2	106.0	103.9
45°	124.6	124.3	121.9	119.5	117.1	114.7	112.3	109.9	107.5	105.1	102.7
47.5°	125.5	125.2	122.5	119.9	117.3	114.7	112.0	109.4	106.8	104.2	101.5
50°	125.8	125.4	122.6	119.8	117.0	114.1	111.3	108.5	105.7	102.9	100.1
52.5°	125.8	125.4	122.4	119.4	116.4	113.5	110.5	107.5	104.5	101.5	98.5
55°	125.6	125.1	122.0	118.9	115.7	112.6	109.4	106.3	103.2	100.0	96.9
57.5°	124.8	124.3	121.0	117.8	114.6	111.3	108.1	104.9	101.6	98.4	95.2
60°	124.0	123.4	120.0	116.6	113.2	109.9	106.5	103.1	99.7	96.4	93.0
62.5°	123.4	122.8	119.3	115.7	112.2	108.7	105.1	101.6	98.0	94.5	90.9
65°	122.3	121.8	118.1	114.4	110.8	107.1	103.4	99.8	96.1	92.4	88.8
67.5°	121.2	120.7	116.8	113.0	109.2	105.3	101.5	97.6	93.8	90.0	86.1
70°	119.1	118.6	114.7	110.8	107.0	103.1	99.2	95.3	91.5	87.6	83.7
72.5°	117.3	116.7	112.7	108.8	104.8	100.9	96.9	93.0	89.0	85.1	81.1
75°	115.1	114.5	110.5	106.4	102.4	98.3	94.3	90.2	86.2	82.2	78.1
77.5°	112.6	112.0	107.9	103.8	99.7	95.6	91.4	87.3	83.2	79.1	75.0
80°	110.0	109.4	105.2	101.1	96.9	92.7	88.5	84.3	80.2	76.0	71.8
82.5°	107.0	106.4	102.2	98.0	93.9	89.7	85.5	81.4	77.2	73.0	68.9
85°	103.6	103.0	98.8	94.6	90.5	86.3	82.1	77.9	73.8	69.6	65.4
87.5°	100.4	99.7	95.5	91.4	87.2	83.0	78.9	74.7	70.5	66.4	62.2
90°	97.0	96.2	92.1	88.0	83.9	79.7	75.6	71.5	67.4	63.2	59.1
92.5°	93.5	92.8	88.7	84.7	80.6	76.5	72.5	68.4	64.3	60.3	56.2
95°	89.8	88.9	85.0	81.0	77.1	73.1	69.2	65.2	61.3	57.3	53.4
97.5°	86.5	85.6	81.7	77.8	73.9	69.9	66.0	62.1	58.2	54.3	50.3
100°	83.1	82.2	78.3	74.5	70.7	66.8	63.0	59.1	55.3	51.5	47.6
102.5°	79.3	78.3	74.6	70.9	67.2	63.5	59.8	56.1	52.4	48.7	45.0
105°	75.4	74.4	70.9	67.3	63.7	60.2	56.6	53.1	49.5	46.0	42.4
107.5°	71.7	70.6	67.1	63.7	60.2	56.8	53.3	49.9	46.4	43.0	39.5
110°	68.0	66.8	63.5	60.2	56.9	53.6	50.3	47.0	43.7	40.3	37.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	64.2	63.1	59.9	56.8	53.6	50.4	47.3	44.1	41.0	37.8	34.6
115°	60.5	59.4	56.4	53.4	50.4	47.4	44.4	41.3	38.3	35.3	32.3
117.5°	56.9	55.8	52.9	50.1	47.2	44.4	41.5	38.7	35.8	33.0	30.1
120°	53.3	52.1	49.4	46.7	44.1	41.4	38.7	36.0	33.4	30.7	28.0
122.5°	49.7	48.5	46.0	43.5	40.9	38.4	35.9	33.4	30.8	28.3	25.8
125°	46.1	45.0	42.7	40.3	37.9	35.6	33.2	30.9	28.5	26.2	23.8
127.5°	42.5	41.4	39.2	37.0	34.8	32.7	30.5	28.3	26.1	23.9	21.7
130°	39.1	38.0	36.0	33.9	31.9	29.9	27.9	25.9	23.9	21.8	19.8
132.5°	35.8	34.7	32.8	30.9	29.0	27.1	25.2	23.3	21.4	19.6	17.7
135°	32.7	31.6	29.9	28.2	26.4	24.7	23.0	21.3	19.5	17.8	16.1
137.5°	29.4	28.3	26.7	25.1	23.6	22.0	20.4	18.8	17.2	15.6	14.1
140°	26.6	25.6	24.1	22.7	21.2	19.7	18.3	16.8	15.3	13.9	12.4
142.5°	23.9	23.0	21.7	20.4	19.1	17.8	16.5	15.2	13.9	12.6	11.3
145°	21.2	20.4	19.2	18.1	16.9	15.8	14.6	13.5	12.3	11.2	10.1
147.5°	18.7	17.9	16.9	15.8	14.8	13.7	12.7	11.6	10.6	9.5	8.5
150°	16.4	15.7	14.7	13.8	12.9	12.0	11.1	10.2	9.3	8.4	7.5
152.5°	14.1	13.5	12.7	11.9	11.1	10.3	9.5	8.8	8.0	7.2	6.4
155°	11.9	11.3	10.7	10.1	9.5	8.9	8.2	7.6	7.0	6.4	5.8
157.5°	9.8	9.3	8.7	8.2	7.6	7.0	6.5	5.9	5.3	4.8	4.2
160°	8.0	7.6	7.1	6.6	6.1	5.6	5.1	4.6	4.1	3.6	3.1
162.5°	5.9	5.5	5.2	4.8	4.4	4.0	3.6	3.2	2.8	2.4	2.0
165°	3.9	3.6	3.3	3.0	2.8	2.5	2.2	1.9	1.6	1.3	1.1
167.5°	2.2	2.0	1.9	1.7	1.6	1.4	1.3	1.1	1.0	0.8	0.7
170°	0.8	0.7	0.7	0.6	0.6	0.6	0.6	0.5	0.5	0.5	0.5
172.5°	0.6	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
175°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.7	0.7	0.7
177.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	74.6	74.6	74.7	74.7	74.7	74.8	74.8	74.8	74.9	74.8	74.8
5°	78.3	78.4	78.5	78.6	78.7	78.8	78.9	79.0	79.1	79.2	79.3
7.5°	82.4	82.5	82.6	82.7	82.9	83.0	83.1	83.2	83.3	83.4	83.4
10°	86.5	86.6	86.7	86.8	86.9	87.0	87.1	87.2	87.4	87.4	87.5
12.5°	90.5	90.7	90.8	90.9	91.0	91.1	91.3	91.4	91.5	91.6	91.8
15°	94.8	94.9	95.0	95.1	95.2	95.3	95.4	95.5	95.6	95.6	95.7
17.5°	98.7	98.8	98.8	98.9	99.0	99.1	99.2	99.3	99.4	99.5	99.6
20°	102.0	102.0	102.0	102.0	101.9	101.9	101.9	101.9	101.9	101.7	101.6
22.5°	105.1	104.7	104.3	103.9	103.5	103.1	102.7	102.3	101.9	101.8	101.6
25°	107.0	106.3	105.7	105.0	104.4	103.7	103.1	102.4	101.8	101.8	101.7
27.5°	107.2	106.4	105.5	104.7	103.8	103.0	102.1	101.3	100.4	100.2	100.0
30°	107.0	105.9	104.8	103.8	102.7	101.7	100.6	99.6	98.5	98.2	97.8
32.5°	106.1	104.8	103.5	102.1	100.8	99.5	98.1	96.8	95.5	95.2	94.9
35°	105.1	103.4	101.8	100.2	98.5	96.9	95.2	93.6	92.0	91.5	91.1
37.5°	104.3	102.3	100.4	98.4	96.5	94.6	92.6	90.7	88.7	88.3	87.8
40°	102.9	100.7	98.5	96.3	94.1	91.9	89.7	87.5	85.3	84.6	83.9
42.5°	101.5	99.1	96.7	94.3	91.8	89.4	87.0	84.6	82.2	81.5	80.9
45°	100.1	97.4	94.7	92.1	89.4	86.7	84.0	81.4	78.7	78.0	77.2
47.5°	98.6	95.7	92.8	89.9	87.0	84.1	81.1	78.2	75.3	74.6	73.9
50°	97.0	93.9	90.7	87.6	84.5	81.3	78.2	75.1	72.0	71.1	70.2
52.5°	95.3	92.0	88.7	85.4	82.1	78.8	75.5	72.2	69.0	67.9	66.9
55°	93.4	89.9	86.5	83.0	79.5	76.1	72.6	69.2	65.7	64.6	63.5
57.5°	91.6	87.9	84.3	80.7	77.1	73.5	69.9	66.3	62.6	61.6	60.6
60°	89.3	85.5	81.8	78.1	74.4	70.6	66.9	63.2	59.5	58.4	57.2
62.5°	87.1	83.2	79.3	75.5	71.6	67.7	63.9	60.0	56.1	55.0	53.8
65°	84.8	80.8	76.8	72.8	68.8	64.8	60.8	56.8	52.8	51.7	50.5
67.5°	82.1	78.0	73.9	69.9	65.8	61.7	57.7	53.6	49.5	48.3	47.0
70°	79.6	75.4	71.3	67.1	62.9	58.8	54.6	50.5	46.3	45.0	43.7
72.5°	76.8	72.6	68.3	64.0	59.7	55.5	51.2	46.9	42.6	41.3	40.1
75°	73.8	69.5	65.1	60.8	56.5	52.1	47.8	43.5	39.2	37.9	36.7
77.5°	70.6	66.2	61.9	57.5	53.2	48.8	44.4	40.1	35.7	34.5	33.3
80°	67.4	63.1	58.7	54.4	50.0	45.6	41.3	36.9	32.6	31.3	30.1
82.5°	64.5	60.1	55.7	51.3	46.9	42.6	38.2	33.8	29.4	28.2	27.0
85°	61.1	56.8	52.4	48.1	43.8	39.5	35.1	30.8	26.5	25.3	24.2
87.5°	58.0	53.7	49.5	45.2	41.0	36.7	32.5	28.2	24.0	22.9	21.7
90°	54.9	50.8	46.6	42.4	38.2	34.0	29.9	25.7	21.5	20.5	19.4
92.5°	52.1	48.0	43.9	39.8	35.7	31.6	27.5	23.4	19.3	18.3	17.3
95°	49.4	45.3	41.3	37.3	33.3	29.3	25.2	21.2	17.2	16.2	15.3
97.5°	46.4	42.5	38.6	34.7	30.7	26.8	22.9	19.0	15.0	14.2	13.3
100°	43.8	40.0	36.1	32.3	28.5	24.6	20.8	17.0	13.2	12.4	11.6
102.5°	41.3	37.5	33.8	30.1	26.3	22.6	18.9	15.2	11.4	10.7	9.9
105°	38.8	35.2	31.6	28.0	24.4	20.8	17.1	13.5	9.9	9.2	8.5
107.5°	36.0	32.5	29.0	25.6	22.1	18.6	15.1	11.6	8.1	7.5	6.9
110°	33.6	30.3	26.9	23.5	20.1	16.8	13.4	10.0	6.6	6.1	5.5

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	31.4	28.2	25.0	21.8	18.6	15.4	12.2	9.0	5.8	5.3	4.7
115°	29.2	26.2	23.1	20.0	17.0	13.9	10.9	7.8	4.7	4.3	3.8
117.5°	27.3	24.4	21.5	18.7	15.8	12.9	10.1	7.2	4.4	3.9	3.5
120°	25.3	22.6	19.9	17.1	14.4	11.7	9.0	6.3	3.5	3.2	2.9
122.5°	23.2	20.7	18.2	15.7	13.1	10.6	8.1	5.5	3.0	2.7	2.5
125°	21.5	19.1	16.7	14.4	12.0	9.6	7.3	4.9	2.6	2.3	2.1
127.5°	19.5	17.3	15.2	13.0	10.8	8.6	6.4	4.2	2.0	1.9	1.7
130°	17.8	15.9	13.9	11.9	9.9	7.9	5.9	3.9	2.0	1.8	1.6
132.5°	15.8	14.0	12.2	10.3	8.5	6.7	4.9	3.0	1.2	1.1	1.0
135°	14.4	12.7	11.0	9.3	7.6	6.0	4.3	2.6	0.9	0.8	0.8
137.5°	12.6	11.1	9.7	8.2	6.8	5.3	3.8	2.4	0.9	0.8	0.8
140°	11.1	9.9	8.6	7.3	6.0	4.7	3.5	2.2	0.9	0.8	0.8
142.5°	10.1	9.0	7.8	6.7	5.5	4.4	3.2	2.1	0.9	0.8	0.8
145°	9.0	8.0	7.0	6.0	4.9	3.9	2.9	1.9	0.8	0.8	0.7
147.5°	7.6	6.8	6.0	5.1	4.3	3.4	2.6	1.7	0.9	0.8	0.8
150°	6.8	6.0	5.3	4.5	3.8	3.0	2.3	1.5	0.8	0.7	0.7
152.5°	5.8	5.1	4.5	3.8	3.2	2.6	1.9	1.3	0.7	0.6	0.6
155°	5.2	4.6	4.0	3.4	2.9	2.3	1.7	1.1	0.5	0.5	0.5
157.5°	3.8	3.4	3.0	2.5	2.1	1.7	1.3	0.9	0.4	0.4	0.4
160°	2.8	2.5	2.2	1.8	1.5	1.2	0.9	0.6	0.3	0.3	0.3
162.5°	1.8	1.6	1.5	1.3	1.1	0.9	0.7	0.5	0.3	0.3	0.3
165°	1.0	0.9	0.8	0.7	0.6	0.6	0.5	0.4	0.3	0.3	0.3
167.5°	0.6	0.6	0.6	0.5	0.5	0.4	0.4	0.3	0.3	0.3	0.3
170°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
172.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.4	0.4
175°	0.7	0.7	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.5
177.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.5
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	74.7	74.6	74.6	74.5	74.5	74.4	74.4	74.5	74.7	74.9	75.1
5°	79.4	79.5	79.6	79.7	79.8	79.9	80.0	80.0	79.9	79.9	79.8
7.5°	83.4	83.5	83.5	83.6	83.6	83.7	83.7	83.8	83.8	83.9	84.0
10°	87.6	87.7	87.8	87.9	88.0	88.1	88.2	88.0	87.9	87.8	87.6
12.5°	91.9	92.1	92.2	92.4	92.5	92.7	92.8	92.9	92.9	92.9	92.9
15°	95.7	95.7	95.7	95.7	95.7	95.7	95.8	95.8	95.9	96.0	96.1
17.5°	99.7	99.8	99.9	100.1	100.2	100.3	100.4	100.3	100.3	100.2	100.1
20°	101.4	101.3	101.1	101.0	100.8	100.7	100.5	100.8	101.1	101.3	101.6
22.5°	101.4	101.2	101.1	100.9	100.7	100.6	100.4	100.9	101.4	101.9	102.4
25°	101.7	101.6	101.6	101.6	101.5	101.5	101.5	101.9	102.3	102.7	103.2
27.5°	99.8	99.6	99.5	99.3	99.1	98.9	98.7	99.3	99.9	100.5	101.1
30°	97.5	97.1	96.8	96.4	96.1	95.7	95.4	96.2	97.1	98.0	98.9
32.5°	94.7	94.4	94.1	93.9	93.6	93.3	93.1	93.8	94.6	95.4	96.2
35°	90.7	90.2	89.8	89.4	89.0	88.5	88.1	89.2	90.3	91.3	92.4
37.5°	87.4	86.9	86.4	86.0	85.5	85.1	84.6	85.6	86.6	87.7	88.7
40°	83.2	82.6	81.9	81.2	80.5	79.8	79.1	80.3	81.5	82.7	83.9
42.5°	80.2	79.5	78.8	78.1	77.4	76.7	76.1	77.5	78.8	80.2	81.6
45°	76.5	75.8	75.0	74.3	73.6	72.8	72.1	73.7	75.2	76.8	78.3
47.5°	73.2	72.5	71.8	71.1	70.5	69.8	69.1	70.5	72.0	73.5	74.9
50°	69.3	68.4	67.5	66.6	65.7	64.8	63.9	65.7	67.5	69.2	71.0
52.5°	65.8	64.8	63.7	62.7	61.6	60.6	59.6	61.6	63.7	65.7	67.8
55°	62.4	61.4	60.3	59.2	58.1	57.0	56.0	58.0	60.1	62.1	64.2
57.5°	59.6	58.6	57.6	56.6	55.6	54.6	53.6	55.7	57.8	59.9	62.1
60°	56.1	55.0	53.9	52.8	51.7	50.6	49.5	51.6	53.8	56.0	58.2
62.5°	52.6	51.4	50.3	49.1	47.9	46.7	45.6	47.8	50.1	52.4	54.7
65°	49.3	48.1	47.0	45.8	44.6	43.4	42.3	44.6	46.9	49.2	51.5
67.5°	45.8	44.6	43.3	42.1	40.8	39.6	38.3	40.7	43.1	45.4	47.8
70°	42.4	41.1	39.8	38.5	37.2	35.9	34.6	37.1	39.7	42.2	44.7
72.5°	38.8	37.5	36.2	34.9	33.6	32.3	31.1	33.5	36.0	38.5	41.0
75°	35.4	34.2	33.0	31.7	30.5	29.2	28.0	30.5	32.9	35.4	37.8
77.5°	32.1	30.9	29.7	28.5	27.2	26.0	24.8	27.2	29.6	32.0	34.5
80°	28.8	27.6	26.4	25.1	23.9	22.7	21.4	23.9	26.4	28.8	31.3
82.5°	25.9	24.7	23.5	22.3	21.1	19.9	18.8	21.1	23.4	25.8	28.1
85°	23.0	21.9	20.7	19.6	18.4	17.3	16.1	18.4	20.7	23.0	25.3
87.5°	20.6	19.5	18.3	17.2	16.1	15.0	13.8	16.1	18.5	20.8	23.1
90°	18.3	17.3	16.2	15.2	14.1	13.1	12.0	14.2	16.4	18.6	20.7
92.5°	16.2	15.2	14.1	13.1	12.1	11.0	10.0	12.1	14.3	16.4	18.5
95°	14.3	13.3	12.4	11.4	10.4	9.5	8.5	10.6	12.7	14.7	16.8
97.5°	12.4	11.5	10.6	9.8	8.9	8.0	7.1	9.1	11.1	13.1	15.1
100°	10.8	10.0	9.2	8.4	7.6	6.8	6.0	7.9	9.8	11.7	13.5
102.5°	9.1	8.4	7.6	6.9	6.1	5.3	4.6	6.4	8.2	10.0	11.8
105°	7.8	7.0	6.3	5.6	4.9	4.1	3.4	5.1	6.8	8.6	10.3
107.5°	6.2	5.6	5.0	4.4	3.8	3.1	2.5	4.1	5.7	7.3	8.8
110°	5.0	4.4	3.9	3.3	2.8	2.2	1.7	3.1	4.6	6.1	7.6

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	4.2	3.7	3.1	2.6	2.1	1.5	1.0	2.4	3.8	5.2	6.5
115°	3.4	2.9	2.4	2.0	1.5	1.1	0.6	1.9	3.2	4.5	5.8
117.5°	3.1	2.7	2.3	1.9	1.4	1.0	0.6	1.8	3.0	4.2	5.3
120°	2.5	2.2	1.9	1.5	1.2	0.9	0.5	1.6	2.7	3.8	4.8
122.5°	2.2	1.9	1.6	1.4	1.1	0.8	0.5	1.5	2.5	3.4	4.4
125°	1.9	1.7	1.4	1.2	1.0	0.8	0.5	1.4	2.3	3.1	4.0
127.5°	1.5	1.3	1.2	1.0	0.8	0.6	0.5	1.2	2.0	2.7	3.5
130°	1.5	1.3	1.1	1.0	0.8	0.6	0.5	1.1	1.8	2.4	3.1
132.5°	1.0	0.9	0.8	0.7	0.6	0.5	0.5	1.0	1.6	2.2	2.7
135°	0.7	0.7	0.6	0.6	0.5	0.4	0.4	0.9	1.3	1.8	2.3
137.5°	0.7	0.6	0.6	0.5	0.4	0.4	0.3	0.7	1.1	1.6	2.0
140°	0.7	0.6	0.6	0.5	0.4	0.4	0.3	0.6	1.0	1.3	1.6
142.5°	0.7	0.6	0.6	0.5	0.4	0.4	0.3	0.6	0.8	1.1	1.4
145°	0.7	0.6	0.5	0.5	0.4	0.4	0.3	0.5	0.7	0.9	1.0
147.5°	0.7	0.6	0.6	0.5	0.4	0.4	0.3	0.4	0.6	0.7	0.8
150°	0.6	0.6	0.5	0.5	0.4	0.4	0.3	0.4	0.5	0.6	0.6
152.5°	0.6	0.5	0.5	0.4	0.4	0.3	0.3	0.3	0.4	0.4	0.5
155°	0.5	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.4	0.4
157.5°	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3	0.3	0.3
160°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
162.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
165°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
167.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
170°	0.4	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
172.5°	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3	0.3
177.5°	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3	0.3
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	75.3	75.5	75.7	75.9	76.1	75.9	75.8	75.6	75.5	75.3	75.2
5°	79.7	79.7	79.6	79.5	79.5	79.4	79.4	79.3	79.2	79.2	79.1
7.5°	84.0	84.1	84.2	84.2	84.3	84.1	83.9	83.7	83.5	83.3	83.1
10°	87.5	87.3	87.2	87.1	86.9	86.9	86.8	86.7	86.6	86.5	86.5
12.5°	92.9	93.0	93.0	93.0	93.0	92.6	92.1	91.6	91.1	90.7	90.2
15°	96.2	96.3	96.4	96.5	96.6	96.3	96.0	95.7	95.4	95.2	94.9
17.5°	100.1	100.0	99.9	99.9	99.8	99.7	99.5	99.4	99.2	99.1	98.9
20°	101.9	102.2	102.4	102.7	103.0	102.9	102.9	102.8	102.8	102.7	102.7
22.5°	102.9	103.4	103.9	104.4	104.9	104.9	104.9	104.9	104.9	104.9	104.9
25°	103.6	104.0	104.4	104.9	105.3	105.7	106.1	106.5	106.9	107.3	107.7
27.5°	101.7	102.4	103.0	103.6	104.2	104.9	105.6	106.3	107.0	107.7	108.5
30°	99.8	100.7	101.5	102.4	103.3	104.2	105.1	106.0	106.9	107.9	108.8
32.5°	96.9	97.7	98.5	99.2	100.0	101.5	102.9	104.4	105.8	107.3	108.7
35°	93.5	94.6	95.7	96.7	97.8	99.5	101.1	102.8	104.5	106.1	107.8
37.5°	89.7	90.7	91.7	92.7	93.7	95.9	98.0	100.2	102.3	104.5	106.6
40°	85.1	86.3	87.5	88.7	89.9	92.2	94.6	96.9	99.2	101.5	103.9
42.5°	83.0	84.4	85.8	87.2	88.6	91.1	93.5	96.0	98.5	100.9	103.4
45°	79.9	81.4	83.0	84.5	86.1	88.7	91.3	93.9	96.5	99.2	101.8
47.5°	76.4	77.9	79.4	80.8	82.3	85.4	88.5	91.6	94.7	97.8	101.0
50°	72.8	74.6	76.4	78.1	79.9	83.1	86.2	89.3	92.5	95.6	98.7
52.5°	69.8	71.9	73.9	76.0	78.0	81.4	84.8	88.2	91.6	94.9	98.3
55°	66.2	68.3	70.3	72.4	74.4	78.0	81.6	85.2	88.8	92.4	95.9
57.5°	64.2	66.3	68.4	70.6	72.7	76.3	79.9	83.5	87.1	90.6	94.2
60°	60.4	62.6	64.7	66.9	69.1	73.0	77.0	80.9	84.8	88.7	92.7
62.5°	57.0	59.3	61.6	63.9	66.1	70.1	74.0	78.0	81.9	85.9	89.8
65°	53.8	56.1	58.4	60.7	63.0	66.8	70.6	74.3	78.1	81.9	85.7
67.5°	50.1	52.5	54.8	57.2	59.5	63.8	68.0	72.3	76.5	80.8	85.0
70°	47.2	49.8	52.3	54.8	57.3	61.4	65.5	69.6	73.7	77.8	81.9
72.5°	43.5	46.0	48.5	51.0	53.5	57.8	62.0	66.3	70.6	74.8	79.1
75°	40.3	42.7	45.2	47.6	50.1	54.4	58.8	63.1	67.5	71.8	76.2
77.5°	36.9	39.3	41.7	44.1	46.5	51.1	55.6	60.1	64.7	69.2	73.8
80°	33.8	36.2	38.7	41.2	43.7	48.2	52.7	57.2	61.7	66.2	70.7
82.5°	30.4	32.7	35.1	37.4	39.7	44.3	48.9	53.5	58.1	62.7	67.3
85°	27.6	29.9	32.2	34.5	36.8	41.4	45.9	50.4	54.9	59.4	64.0
87.5°	25.4	27.7	30.0	32.3	34.6	39.0	43.4	47.8	52.2	56.5	60.9
90°	22.9	25.1	27.3	29.5	31.7	36.0	40.3	44.6	48.9	53.3	57.6
92.5°	20.7	22.8	25.0	27.1	29.2	33.6	37.9	42.3	46.6	50.9	55.3
95°	18.9	21.0	23.0	25.1	27.2	31.4	35.6	39.7	43.9	48.1	52.3
97.5°	17.1	19.1	21.1	23.1	25.1	29.2	33.2	37.3	41.3	45.4	49.4
100°	15.4	17.3	19.2	21.1	23.0	27.0	31.0	35.0	39.0	43.0	47.0
102.5°	13.6	15.4	17.2	19.0	20.8	24.7	28.5	32.4	36.2	40.1	44.0
105°	12.0	13.7	15.4	17.1	18.8	22.6	26.4	30.1	33.9	37.7	41.4
107.5°	10.4	12.0	13.6	15.2	16.7	20.4	24.1	27.7	31.4	35.1	38.7
110°	9.0	10.5	12.0	13.4	14.9	18.5	22.0	25.6	29.2	32.7	36.3

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	7.9	9.3	10.7	12.1	13.5	16.9	20.3	23.7	27.1	30.5	33.9
115°	7.2	8.5	9.8	11.1	12.4	15.6	18.8	22.1	25.3	28.5	31.7
117.5°	6.5	7.7	8.9	10.1	11.3	14.3	17.4	20.5	23.5	26.6	29.7
120°	5.9	7.0	8.1	9.1	10.2	13.1	16.0	18.9	21.7	24.6	27.5
122.5°	5.4	6.4	7.3	8.3	9.3	12.0	14.7	17.4	20.1	22.8	25.5
125°	4.9	5.8	6.6	7.5	8.4	10.9	13.4	15.9	18.4	20.9	23.4
127.5°	4.3	5.0	5.8	6.5	7.3	9.6	12.0	14.3	16.6	19.0	21.3
130°	3.8	4.4	5.1	5.7	6.4	8.6	10.8	12.9	15.1	17.3	19.5
132.5°	3.3	3.9	4.4	5.0	5.6	7.6	9.6	11.6	13.6	15.6	17.6
135°	2.8	3.3	3.8	4.2	4.7	6.5	8.4	10.2	12.0	13.8	15.7
137.5°	2.4	2.8	3.3	3.7	4.1	5.7	7.4	9.0	10.6	12.3	13.9
140°	2.0	2.3	2.6	2.9	3.3	4.7	6.2	7.7	9.1	10.6	12.1
142.5°	1.6	1.9	2.1	2.4	2.7	4.0	5.2	6.5	7.8	9.1	10.4
145°	1.2	1.4	1.6	1.8	2.0	3.1	4.2	5.3	6.4	7.5	8.6
147.5°	0.9	1.1	1.2	1.3	1.4	2.4	3.3	4.3	5.2	6.2	7.1
150°	0.7	0.8	0.9	1.0	1.1	1.8	2.6	3.4	4.2	5.0	5.8
152.5°	0.5	0.6	0.6	0.6	0.7	1.3	2.0	2.6	3.2	3.9	4.5
155°	0.4	0.4	0.4	0.4	0.5	1.0	1.4	1.9	2.4	2.9	3.4
157.5°	0.3	0.4	0.4	0.4	0.4	0.7	1.1	1.5	1.8	2.2	2.5
160°	0.3	0.4	0.4	0.4	0.4	0.6	0.8	1.1	1.3	1.6	1.8
162.5°	0.3	0.4	0.4	0.4	0.4	0.5	0.7	0.8	0.9	1.1	1.2
165°	0.3	0.4	0.4	0.4	0.4	0.5	0.5	0.6	0.7	0.8	0.8
167.5°	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.6
170°	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5
172.5°	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5
175°	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5
177.5°	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	75.0	74.9	74.7	74.5	74.4	74.2	74.0	73.8	73.6	73.4	73.3
5°	79.1	79.0	78.9	78.6	78.3	78.0	77.7	77.4	77.1	76.7	76.4
7.5°	82.9	82.7	82.5	82.2	81.8	81.5	81.2	80.8	80.5	80.1	79.8
10°	86.4	86.3	86.2	86.0	85.8	85.6	85.3	85.1	84.9	84.7	84.4
12.5°	89.7	89.3	88.8	88.7	88.5	88.4	88.3	88.2	88.1	87.9	87.8
15°	94.6	94.3	94.0	93.8	93.6	93.5	93.3	93.1	92.9	92.7	92.5
17.5°	98.8	98.7	98.5	98.2	97.9	97.5	97.2	96.9	96.5	96.2	95.9
20°	102.6	102.6	102.5	102.2	102.0	101.7	101.4	101.1	100.9	100.6	100.3
22.5°	104.9	104.9	104.9	104.7	104.5	104.3	104.1	103.9	103.7	103.5	103.3
25°	108.1	108.5	108.9	108.8	108.6	108.5	108.3	108.2	108.1	107.9	107.8
27.5°	109.2	109.9	110.6	110.6	110.6	110.6	110.6	110.6	110.7	110.7	110.7
30°	109.7	110.6	111.5	111.7	111.9	112.1	112.3	112.5	112.7	112.8	113.0
32.5°	110.2	111.6	113.1	113.5	113.9	114.3	114.7	115.2	115.6	116.0	116.4
35°	109.5	111.1	112.8	113.7	114.5	115.4	116.3	117.1	118.0	118.8	119.7
37.5°	108.8	110.9	113.1	114.0	114.8	115.7	116.6	117.5	118.4	119.2	120.1
40°	106.2	108.5	110.8	112.2	113.6	115.0	116.4	117.8	119.2	120.6	122.0
42.5°	105.8	108.3	110.8	112.3	113.8	115.4	116.9	118.5	120.0	121.6	123.1
45°	104.4	107.0	109.6	111.8	113.9	116.0	118.1	120.3	122.4	124.5	126.7
47.5°	104.1	107.2	110.3	112.3	114.3	116.4	118.4	120.4	122.4	124.4	126.5
50°	101.8	105.0	108.1	110.4	112.8	115.1	117.4	119.7	122.1	124.4	126.7
52.5°	101.7	105.1	108.5	110.9	113.2	115.6	118.0	120.3	122.7	125.1	127.5
55°	99.5	103.1	106.7	109.2	111.7	114.2	116.7	119.2	121.7	124.2	126.7
57.5°	97.8	101.4	105.0	107.5	110.0	112.5	115.0	117.5	120.0	122.5	125.0
60°	96.6	100.5	104.4	107.1	109.7	112.4	115.0	117.7	120.3	123.0	125.6
62.5°	93.8	97.7	101.7	104.7	107.7	110.7	113.6	116.6	119.6	122.6	125.6
65°	89.5	93.3	97.1	100.3	103.6	106.8	110.1	113.4	116.6	119.9	123.1
67.5°	89.3	93.5	97.8	100.8	103.8	106.8	109.8	112.9	115.9	118.9	121.9
70°	86.0	90.1	94.2	97.3	100.4	103.6	106.7	109.9	113.0	116.1	119.3
72.5°	83.4	87.7	91.9	95.0	98.1	101.2	104.2	107.3	110.4	113.5	116.6
75°	80.5	84.9	89.2	92.4	95.5	98.7	101.9	105.0	108.2	111.4	114.5
77.5°	78.3	82.9	87.4	90.5	93.5	96.6	99.7	102.7	105.8	108.9	111.9
80°	75.2	79.7	84.2	87.4	90.6	93.8	96.9	100.1	103.3	106.5	109.6
82.5°	71.9	76.5	81.1	84.3	87.5	90.7	93.8	97.0	100.2	103.3	106.5
85°	68.5	73.0	77.5	80.8	84.1	87.4	90.7	94.0	97.2	100.5	103.8
87.5°	65.3	69.7	74.1	77.3	80.5	83.8	87.0	90.2	93.4	96.7	99.9
90°	61.9	66.2	70.5	74.0	77.4	80.8	84.3	87.7	91.2	94.6	98.0
92.5°	59.6	64.0	68.3	71.3	74.3	77.3	80.3	83.3	86.3	89.3	92.3
95°	56.5	60.7	64.9	68.0	71.1	74.2	77.4	80.5	83.6	86.7	89.8
97.5°	53.4	57.5	61.5	64.6	67.6	70.7	73.7	76.7	79.8	82.8	85.9
100°	51.0	55.0	59.0	61.8	64.7	67.5	70.4	73.2	76.0	78.9	81.7
102.5°	47.8	51.7	55.6	58.6	61.6	64.6	67.5	70.5	73.5	76.5	79.5
105°	45.2	49.0	52.8	55.5	58.2	61.0	63.7	66.4	69.2	71.9	74.6
107.5°	42.4	46.1	49.7	52.6	55.4	58.3	61.1	64.0	66.8	69.7	72.5
110°	39.9	43.5	47.0	49.7	52.3	55.0	57.7	60.3	63.0	65.6	68.3

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	37.3	40.7	44.1	46.5	49.0	51.5	53.9	56.4	58.8	61.3	63.7
115°	34.9	38.1	41.4	43.7	46.1	48.5	50.9	53.2	55.6	58.0	60.3
117.5°	32.7	35.8	38.9	41.2	43.5	45.8	48.1	50.4	52.7	55.0	57.3
120°	30.4	33.3	36.2	38.3	40.5	42.6	44.8	47.0	49.1	51.3	53.4
122.5°	28.2	30.9	33.6	35.7	37.8	40.0	42.1	44.2	46.3	48.4	50.5
125°	25.9	28.4	31.0	33.0	35.0	37.1	39.1	41.2	43.2	45.3	47.3
127.5°	23.6	26.0	28.3	30.2	32.0	33.9	35.8	37.6	39.5	41.3	43.2
130°	21.7	23.9	26.0	27.8	29.5	31.3	33.0	34.7	36.5	38.2	39.9
132.5°	19.6	21.6	23.6	25.2	26.9	28.5	30.1	31.8	33.4	35.1	36.7
135°	17.5	19.3	21.1	22.7	24.2	25.8	27.3	28.8	30.4	31.9	33.5
137.5°	15.5	17.2	18.8	20.2	21.6	23.1	24.5	25.9	27.3	28.7	30.1
140°	13.5	15.0	16.5	17.8	19.1	20.4	21.7	23.0	24.4	25.7	27.0
142.5°	11.7	13.0	14.3	15.5	16.7	17.9	19.2	20.4	21.6	22.8	24.0
145°	9.7	10.8	11.9	13.1	14.2	15.4	16.5	17.7	18.8	19.9	21.1
147.5°	8.1	9.0	10.0	11.0	12.0	13.0	14.1	15.1	16.1	17.1	18.1
150°	6.6	7.4	8.1	9.1	10.0	10.9	11.8	12.7	13.6	14.5	15.4
152.5°	5.2	5.8	6.4	7.2	8.0	8.8	9.6	10.4	11.2	12.0	12.8
155°	3.9	4.4	4.9	5.6	6.3	6.9	7.6	8.3	9.0	9.6	10.3
157.5°	2.9	3.3	3.6	4.2	4.7	5.3	5.8	6.4	6.9	7.5	8.0
160°	2.0	2.3	2.5	2.9	3.4	3.8	4.3	4.7	5.1	5.6	6.0
162.5°	1.4	1.5	1.7	2.0	2.3	2.6	3.0	3.3	3.6	3.9	4.3
165°	0.9	1.0	1.1	1.3	1.5	1.7	1.9	2.1	2.4	2.6	2.8
167.5°	0.6	0.6	0.7	0.8	0.9	1.0	1.2	1.3	1.4	1.5	1.6
170°	0.5	0.5	0.5	0.6	0.6	0.7	0.8	0.8	0.9	0.9	1.0
172.5°	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6	0.6	0.7
175°	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6	0.6
177.5°	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6	0.6
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	73.1	72.9	72.8	72.7	72.5	72.4	72.2	72.1	71.9	71.8	71.8
5°	76.1	75.9	75.7	75.5	75.2	75.0	74.8	74.6	74.3	74.1	73.9
7.5°	79.5	79.2	79.0	78.8	78.6	78.4	78.2	78.0	77.8	77.6	77.3
10°	84.2	84.0	83.7	83.5	83.2	83.0	82.8	82.5	82.3	82.0	81.7
12.5°	87.7	87.5	87.2	87.0	86.8	86.5	86.3	86.1	85.8	85.6	85.3
15°	92.4	92.1	91.9	91.6	91.3	91.1	90.8	90.6	90.3	90.1	89.8
17.5°	95.5	95.4	95.2	95.0	94.8	94.7	94.5	94.3	94.1	94.0	93.7
20°	100.0	99.9	99.7	99.5	99.3	99.1	98.9	98.7	98.5	98.3	98.1
22.5°	103.1	103.0	102.9	102.7	102.6	102.5	102.3	102.2	102.1	101.9	101.7
25°	107.6	107.4	107.1	106.9	106.7	106.4	106.2	105.9	105.7	105.4	105.3
27.5°	110.7	110.5	110.4	110.2	110.0	109.9	109.7	109.5	109.4	109.2	109.0
30°	113.2	113.2	113.1	113.1	113.0	113.0	113.0	112.9	112.9	112.8	112.6
32.5°	116.8	116.7	116.6	116.5	116.4	116.3	116.2	116.1	116.0	115.9	115.7
35°	120.6	120.4	120.1	119.9	119.7	119.4	119.2	119.0	118.7	118.5	118.4
37.5°	121.0	121.0	121.0	121.0	121.0	121.0	121.0	121.0	121.0	121.0	121.0
40°	123.4	123.4	123.4	123.4	123.4	123.4	123.4	123.4	123.4	123.4	123.4
42.5°	124.7	124.8	124.9	125.0	125.1	125.2	125.3	125.4	125.5	125.6	125.5
45°	128.8	128.6	128.4	128.2	128.0	127.8	127.7	127.5	127.3	127.1	127.1
47.5°	128.5	128.5	128.5	128.6	128.6	128.6	128.7	128.7	128.7	128.7	128.7
50°	129.0	129.1	129.1	129.1	129.2	129.2	129.2	129.3	129.3	129.3	129.4
52.5°	129.8	129.9	129.9	130.0	130.1	130.1	130.2	130.2	130.3	130.4	130.5
55°	129.2	129.4	129.6	129.7	129.9	130.1	130.3	130.5	130.6	130.8	130.9
57.5°	127.6	127.9	128.3	128.6	129.0	129.4	129.7	130.1	130.5	130.8	130.9
60°	128.3	128.5	128.8	129.0	129.3	129.5	129.7	130.0	130.2	130.5	130.6
62.5°	128.6	128.7	128.8	129.0	129.1	129.2	129.3	129.4	129.6	129.7	129.9
65°	126.4	126.6	126.9	127.1	127.4	127.6	127.8	128.1	128.3	128.6	128.9
67.5°	125.0	125.3	125.6	125.9	126.2	126.5	126.8	127.1	127.4	127.7	128.0
70°	122.4	122.8	123.2	123.6	124.1	124.5	124.9	125.3	125.7	126.2	126.4
72.5°	119.6	120.1	120.6	121.0	121.5	122.0	122.4	122.9	123.4	123.8	124.2
75°	117.7	118.1	118.6	119.0	119.4	119.8	120.3	120.7	121.1	121.6	122.0
77.5°	115.0	115.4	115.9	116.3	116.7	117.1	117.6	118.0	118.4	118.9	119.3
80°	112.8	113.2	113.6	114.0	114.4	114.8	115.2	115.7	116.1	116.5	116.9
82.5°	109.7	110.1	110.6	111.1	111.6	112.1	112.5	113.0	113.5	114.0	114.4
85°	107.1	107.5	107.9	108.3	108.7	109.1	109.5	109.9	110.3	110.7	111.1
87.5°	103.1	103.7	104.3	104.8	105.4	105.9	106.5	107.0	107.6	108.1	108.5
90°	101.5	101.8	102.2	102.6	103.0	103.3	103.7	104.1	104.5	104.8	105.4
92.5°	95.3	96.1	96.9	97.6	98.4	99.2	99.9	100.7	101.4	102.2	102.7
95°	93.0	93.6	94.2	94.9	95.5	96.1	96.8	97.4	98.0	98.7	99.2
97.5°	88.9	89.7	90.4	91.1	91.9	92.6	93.4	94.1	94.9	95.6	96.2
100°	84.6	85.4	86.3	87.2	88.1	88.9	89.8	90.7	91.5	92.4	93.0
102.5°	82.5	83.2	84.0	84.7	85.4	86.1	86.8	87.6	88.3	89.0	89.6
105°	77.4	78.3	79.2	80.2	81.1	82.1	83.0	84.0	84.9	85.8	86.5
107.5°	75.4	76.2	77.0	77.7	78.5	79.3	80.1	80.9	81.6	82.4	83.1
110°	71.0	71.9	72.7	73.6	74.5	75.4	76.3	77.2	78.1	78.9	79.6

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	66.2	67.2	68.3	69.3	70.3	71.4	72.4	73.4	74.5	75.5	76.2
115°	62.7	63.7	64.8	65.8	66.8	67.8	68.9	69.9	70.9	72.0	72.6
117.5°	59.6	60.6	61.6	62.6	63.6	64.5	65.5	66.5	67.5	68.4	69.1
120°	55.6	56.6	57.7	58.7	59.8	60.8	61.8	62.9	63.9	64.9	65.6
122.5°	52.7	53.6	54.6	55.6	56.6	57.6	58.5	59.5	60.5	61.5	62.1
125°	49.4	50.3	51.2	52.2	53.1	54.0	55.0	55.9	56.9	57.8	58.5
127.5°	45.1	46.1	47.1	48.1	49.1	50.1	51.1	52.1	53.1	54.1	54.8
130°	41.7	42.7	43.7	44.6	45.6	46.6	47.6	48.6	49.6	50.6	51.2
132.5°	38.4	39.3	40.3	41.2	42.2	43.1	44.1	45.0	46.0	46.9	47.6
135°	35.0	35.9	36.9	37.8	38.7	39.7	40.6	41.5	42.5	43.4	44.0
137.5°	31.5	32.5	33.4	34.3	35.2	36.1	37.0	37.9	38.8	39.7	40.3
140°	28.3	29.2	30.0	30.9	31.8	32.6	33.5	34.4	35.2	36.1	36.7
142.5°	25.2	26.1	26.9	27.7	28.5	29.3	30.1	30.9	31.7	32.5	33.1
145°	22.2	23.0	23.8	24.5	25.3	26.1	26.8	27.6	28.4	29.1	29.7
147.5°	19.2	19.9	20.7	21.4	22.2	22.9	23.7	24.4	25.2	25.9	26.4
150°	16.3	17.0	17.7	18.4	19.1	19.8	20.4	21.1	21.8	22.5	23.0
152.5°	13.6	14.2	14.9	15.5	16.1	16.8	17.4	18.0	18.7	19.3	19.8
155°	11.0	11.6	12.1	12.7	13.3	13.9	14.5	15.0	15.6	16.2	16.6
157.5°	8.6	9.1	9.6	10.1	10.6	11.1	11.7	12.2	12.7	13.2	13.6
160°	6.5	6.9	7.3	7.8	8.2	8.7	9.1	9.5	10.0	10.4	10.7
162.5°	4.6	5.0	5.3	5.7	6.1	6.4	6.8	7.1	7.5	7.9	8.2
165°	3.0	3.3	3.6	3.8	4.1	4.4	4.7	4.9	5.2	5.5	5.7
167.5°	1.7	1.9	2.2	2.4	2.6	2.8	3.0	3.2	3.4	3.6	3.8
170°	1.1	1.2	1.3	1.4	1.5	1.5	1.6	1.7	1.8	1.9	2.1
172.5°	0.7	0.7	0.8	0.8	0.8	0.9	0.9	1.0	1.0	1.0	1.1
175°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
177.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	71.7	71.7	71.7	71.7	71.6	71.6	71.6	71.6	71.5	71.4	71.4
5°	73.7	73.5	73.3	73.0	72.8	72.6	72.4	72.2	72.1	71.9	71.8
7.5°	77.0	76.7	76.4	76.1	75.8	75.5	75.2	75.0	74.7	74.5	74.3
10°	81.3	81.0	80.7	80.3	80.0	79.6	79.3	79.0	78.7	78.5	78.2
12.5°	85.1	84.8	84.5	84.3	84.0	83.7	83.5	83.2	82.9	82.7	82.4
15°	89.5	89.2	88.9	88.7	88.4	88.1	87.8	87.5	87.3	87.1	86.8
17.5°	93.5	93.2	93.0	92.7	92.5	92.2	92.0	91.7	91.5	91.3	91.2
20°	97.8	97.5	97.2	96.9	96.6	96.3	96.0	95.7	95.6	95.4	95.3
22.5°	101.5	101.3	101.1	100.9	100.7	100.5	100.3	100.1	100.0	99.8	99.7
25°	105.1	104.9	104.7	104.6	104.4	104.2	104.0	103.9	103.7	103.6	103.5
27.5°	108.9	108.7	108.5	108.3	108.2	108.0	107.8	107.6	107.5	107.4	107.3
30°	112.5	112.3	112.1	112.0	111.8	111.6	111.5	111.3	111.2	111.1	111.0
32.5°	115.5	115.4	115.2	115.0	114.9	114.7	114.5	114.4	114.3	114.3	114.2
35°	118.3	118.2	118.1	118.0	117.9	117.8	117.7	117.6	117.6	117.6	117.6
37.5°	120.9	120.9	120.8	120.8	120.8	120.7	120.7	120.7	120.7	120.7	120.7
40°	123.3	123.3	123.2	123.2	123.1	123.1	123.0	123.0	123.0	123.1	123.1
42.5°	125.5	125.5	125.4	125.4	125.3	125.3	125.3	125.2	125.4	125.5	125.6
45°	127.1	127.1	127.1	127.1	127.1	127.1	127.1	127.1	127.3	127.5	127.7
47.5°	128.7	128.7	128.7	128.7	128.7	128.7	128.7	128.8	128.9	129.1	129.3
50°	129.5	129.6	129.7	129.8	129.9	130.0	130.1	130.2	130.4	130.6	130.9
52.5°	130.6	130.7	130.8	130.9	131.0	131.1	131.2	131.3	131.5	131.8	132.0
55°	131.0	131.1	131.1	131.2	131.3	131.4	131.4	131.5	131.8	132.1	132.4
57.5°	131.1	131.2	131.3	131.4	131.5	131.7	131.8	131.9	132.3	132.6	133.0
60°	130.8	130.9	131.1	131.2	131.4	131.5	131.7	131.8	132.2	132.6	133.0
62.5°	130.2	130.4	130.6	130.9	131.1	131.4	131.6	131.8	132.2	132.6	133.0
65°	129.2	129.5	129.9	130.2	130.5	130.9	131.2	131.5	131.9	132.3	132.8
67.5°	128.3	128.6	128.9	129.2	129.5	129.7	130.0	130.3	130.8	131.2	131.7
70°	126.7	127.0	127.3	127.6	127.9	128.2	128.5	128.8	129.3	129.8	130.3
72.5°	124.6	125.0	125.4	125.8	126.2	126.5	126.9	127.3	127.8	128.3	128.7
75°	122.4	122.8	123.2	123.6	124.0	124.4	124.8	125.2	125.7	126.2	126.7
77.5°	119.7	120.2	120.6	121.0	121.5	121.9	122.3	122.8	123.3	123.8	124.4
80°	117.4	117.9	118.4	118.8	119.3	119.8	120.3	120.7	121.2	121.7	122.2
82.5°	114.8	115.2	115.5	115.9	116.3	116.7	117.1	117.5	118.1	118.7	119.2
85°	111.6	112.0	112.5	112.9	113.3	113.8	114.2	114.7	115.3	115.8	116.4
87.5°	108.9	109.3	109.7	110.1	110.5	110.9	111.3	111.8	112.3	112.9	113.5
90°	105.9	106.4	107.0	107.5	108.0	108.6	109.1	109.7	110.2	110.7	111.2
92.5°	103.2	103.7	104.2	104.8	105.3	105.8	106.3	106.8	107.3	107.8	108.3
95°	99.8	100.3	100.9	101.4	102.0	102.5	103.0	103.6	104.1	104.6	105.2
97.5°	96.8	97.3	97.9	98.5	99.1	99.6	100.2	100.8	101.3	101.8	102.4
100°	93.6	94.2	94.7	95.3	95.9	96.5	97.1	97.6	98.2	98.8	99.3
102.5°	90.2	90.8	91.4	92.0	92.6	93.2	93.9	94.5	95.0	95.6	96.2
105°	87.1	87.7	88.4	89.0	89.6	90.2	90.9	91.5	92.0	92.6	93.1
107.5°	83.7	84.4	85.0	85.6	86.3	86.9	87.6	88.2	88.7	89.2	89.7
110°	80.3	81.0	81.6	82.3	83.0	83.6	84.3	85.0	85.5	86.0	86.6

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	76.8	77.5	78.2	78.8	79.5	80.1	80.8	81.5	82.0	82.5	83.1
115°	73.3	74.0	74.6	75.3	76.0	76.7	77.3	78.0	78.5	79.0	79.5
117.5°	69.8	70.4	71.1	71.8	72.4	73.1	73.8	74.4	74.9	75.5	76.0
120°	66.3	67.0	67.6	68.3	69.0	69.6	70.3	71.0	71.5	72.0	72.4
122.5°	62.8	63.4	64.1	64.8	65.4	66.1	66.7	67.4	67.9	68.3	68.8
125°	59.1	59.8	60.5	61.2	61.8	62.5	63.2	63.9	64.3	64.8	65.3
127.5°	55.5	56.2	56.9	57.5	58.2	58.9	59.6	60.3	60.7	61.2	61.7
130°	51.9	52.5	53.1	53.8	54.4	55.0	55.7	56.3	56.8	57.3	57.7
132.5°	48.2	48.8	49.5	50.1	50.7	51.4	52.0	52.6	53.1	53.6	54.0
135°	44.6	45.2	45.9	46.5	47.1	47.7	48.3	49.0	49.4	49.8	50.2
137.5°	40.9	41.5	42.1	42.7	43.3	43.9	44.5	45.1	45.5	46.0	46.4
140°	37.3	37.9	38.5	39.1	39.7	40.3	40.9	41.5	41.9	42.3	42.7
142.5°	33.7	34.3	34.8	35.4	36.0	36.6	37.2	37.8	38.1	38.5	38.9
145°	30.2	30.8	31.3	31.9	32.4	33.0	33.5	34.1	34.4	34.8	35.2
147.5°	26.9	27.4	27.9	28.3	28.8	29.3	29.8	30.3	30.6	31.0	31.3
150°	23.4	23.9	24.4	24.8	25.3	25.8	26.2	26.7	27.0	27.4	27.7
152.5°	20.2	20.7	21.1	21.6	22.0	22.5	22.9	23.4	23.7	24.0	24.3
155°	17.0	17.5	17.9	18.3	18.7	19.1	19.5	20.0	20.2	20.5	20.8
157.5°	13.9	14.3	14.7	15.1	15.4	15.8	16.2	16.6	16.8	17.1	17.4
160°	11.1	11.4	11.7	12.0	12.4	12.7	13.0	13.3	13.6	13.8	14.1
162.5°	8.4	8.7	9.0	9.3	9.6	9.9	10.1	10.4	10.6	10.8	11.1
165°	6.0	6.2	6.5	6.7	7.0	7.2	7.5	7.7	7.9	8.1	8.3
167.5°	4.0	4.1	4.3	4.5	4.7	4.9	5.1	5.3	5.4	5.5	5.7
170°	2.2	2.4	2.5	2.7	2.8	2.9	3.1	3.2	3.3	3.4	3.6
172.5°	1.2	1.2	1.3	1.4	1.4	1.5	1.6	1.7	1.7	1.8	1.9
175°	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.8	0.9	0.9	1.0
177.5°	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.7	0.7	0.7
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	71.3	71.2	71.2	71.1	71.0	71.0	70.9	70.9	70.8	70.8	70.7
5°	71.7	71.6	71.4	71.3	71.2	71.1	71.0	70.9	70.7	70.6	70.5
7.5°	74.1	73.9	73.7	73.4	73.2	73.0	72.9	72.7	72.5	72.4	72.2
10°	78.0	77.8	77.5	77.3	77.0	76.8	76.6	76.4	76.2	76.1	75.9
12.5°	82.2	82.0	81.7	81.5	81.2	81.0	80.8	80.7	80.6	80.4	80.3
15°	86.6	86.4	86.2	85.9	85.7	85.5	85.3	85.2	85.0	84.9	84.7
17.5°	91.0	90.8	90.6	90.4	90.2	90.0	89.9	89.7	89.5	89.4	89.2
20°	95.1	95.0	94.8	94.7	94.5	94.4	94.2	94.1	94.0	93.8	93.7
22.5°	99.5	99.3	99.2	99.0	98.9	98.7	98.6	98.5	98.4	98.2	98.1
25°	103.3	103.2	103.1	102.9	102.8	102.7	102.6	102.5	102.4	102.3	102.2
27.5°	107.3	107.2	107.1	107.0	106.9	106.8	106.7	106.6	106.5	106.3	106.2
30°	110.9	110.8	110.7	110.7	110.6	110.5	110.4	110.3	110.3	110.2	110.2
32.5°	114.2	114.1	114.1	114.0	114.0	113.9	113.9	113.9	114.0	114.0	114.0
35°	117.6	117.5	117.5	117.5	117.5	117.5	117.5	117.5	117.5	117.5	117.5
37.5°	120.7	120.7	120.7	120.8	120.8	120.8	120.8	120.8	120.9	120.9	120.9
40°	123.2	123.3	123.3	123.4	123.4	123.5	123.6	123.7	123.8	123.9	124.0
42.5°	125.8	125.9	126.0	126.1	126.3	126.4	126.4	126.4	126.4	126.4	126.4
45°	127.9	128.1	128.2	128.4	128.6	128.8	128.8	128.8	128.8	128.8	128.7
47.5°	129.5	129.7	129.8	130.0	130.2	130.4	130.4	130.5	130.5	130.5	130.6
50°	131.1	131.3	131.6	131.8	132.0	132.3	132.3	132.3	132.4	132.4	132.5
52.5°	132.3	132.5	132.7	133.0	133.2	133.5	133.5	133.6	133.7	133.7	133.8
55°	132.7	133.0	133.3	133.6	133.8	134.1	134.2	134.2	134.3	134.4	134.4
57.5°	133.3	133.7	134.0	134.4	134.8	135.1	135.1	135.2	135.2	135.2	135.3
60°	133.4	133.8	134.2	134.6	134.9	135.3	135.4	135.5	135.6	135.7	135.8
62.5°	133.4	133.8	134.2	134.6	135.0	135.4	135.5	135.6	135.7	135.8	135.9
65°	133.2	133.6	134.0	134.4	134.8	135.3	135.4	135.5	135.6	135.7	135.8
67.5°	132.2	132.6	133.1	133.5	134.0	134.4	134.5	134.7	134.8	134.9	135.0
70°	130.8	131.3	131.8	132.2	132.7	133.2	133.4	133.6	133.7	133.9	134.1
72.5°	129.2	129.7	130.2	130.6	131.1	131.6	131.8	131.9	132.1	132.3	132.5
75°	127.2	127.7	128.2	128.7	129.2	129.7	129.9	130.1	130.3	130.6	130.8
77.5°	124.9	125.4	126.0	126.5	127.1	127.6	127.8	128.0	128.2	128.4	128.6
80°	122.7	123.2	123.7	124.2	124.7	125.2	125.4	125.7	125.9	126.1	126.3
82.5°	119.8	120.4	121.0	121.6	122.1	122.7	122.9	123.2	123.4	123.6	123.8
85°	117.0	117.6	118.2	118.8	119.4	119.9	120.2	120.4	120.6	120.8	121.1
87.5°	114.1	114.7	115.3	115.9	116.4	117.0	117.3	117.5	117.7	118.0	118.2
90°	111.7	112.2	112.7	113.2	113.7	114.2	114.4	114.6	114.9	115.1	115.3
92.5°	108.8	109.4	109.9	110.4	110.9	111.4	111.6	111.8	112.1	112.3	112.5
95°	105.7	106.2	106.8	107.3	107.8	108.3	108.6	108.9	109.1	109.4	109.7
97.5°	102.9	103.4	103.9	104.5	105.0	105.5	105.8	106.0	106.3	106.5	106.8
100°	99.9	100.4	101.0	101.5	102.1	102.7	102.9	103.1	103.3	103.5	103.7
102.5°	96.8	97.4	98.0	98.5	99.1	99.7	99.9	100.2	100.4	100.6	100.8
105°	93.6	94.1	94.7	95.2	95.7	96.3	96.5	96.7	97.0	97.2	97.4
107.5°	90.3	90.8	91.3	91.8	92.3	92.8	93.1	93.4	93.7	93.9	94.2
110°	87.1	87.6	88.1	88.7	89.2	89.7	90.0	90.2	90.5	90.7	91.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	83.6	84.1	84.7	85.2	85.7	86.3	86.5	86.8	87.0	87.2	87.5
115°	80.1	80.6	81.1	81.6	82.1	82.6	82.9	83.1	83.4	83.6	83.9
117.5°	76.5	77.0	77.5	78.0	78.6	79.1	79.3	79.6	79.8	80.0	80.3
120°	72.9	73.4	73.9	74.4	74.9	75.4	75.6	75.9	76.1	76.3	76.6
122.5°	69.3	69.8	70.3	70.8	71.2	71.7	72.0	72.2	72.4	72.7	72.9
125°	65.8	66.3	66.7	67.2	67.7	68.2	68.4	68.7	68.9	69.2	69.4
127.5°	62.1	62.6	63.1	63.5	64.0	64.4	64.7	64.9	65.1	65.3	65.5
130°	58.2	58.7	59.2	59.7	60.1	60.6	60.9	61.1	61.3	61.6	61.8
132.5°	54.5	54.9	55.4	55.9	56.3	56.8	57.0	57.2	57.4	57.7	57.9
135°	50.7	51.1	51.5	52.0	52.4	52.8	53.0	53.3	53.5	53.7	54.0
137.5°	46.8	47.3	47.7	48.1	48.6	49.0	49.2	49.4	49.6	49.8	50.0
140°	43.1	43.5	43.8	44.2	44.6	45.0	45.2	45.4	45.6	45.9	46.1
142.5°	39.3	39.6	40.0	40.4	40.7	41.1	41.3	41.5	41.7	41.9	42.1
145°	35.5	35.9	36.2	36.6	36.9	37.3	37.5	37.7	37.9	38.1	38.3
147.5°	31.7	32.1	32.4	32.8	33.1	33.5	33.7	33.9	34.0	34.2	34.4
150°	28.0	28.4	28.7	29.0	29.4	29.7	29.9	30.1	30.3	30.5	30.7
152.5°	24.6	24.9	25.1	25.4	25.7	26.0	26.2	26.4	26.6	26.8	26.9
155°	21.1	21.3	21.6	21.9	22.2	22.4	22.6	22.8	23.0	23.2	23.3
157.5°	17.6	17.9	18.2	18.4	18.7	19.0	19.1	19.3	19.5	19.6	19.8
160°	14.4	14.6	14.9	15.1	15.4	15.6	15.8	15.9	16.0	16.2	16.3
162.5°	11.3	11.5	11.7	11.9	12.1	12.3	12.4	12.6	12.7	12.9	13.0
165°	8.4	8.6	8.8	9.0	9.1	9.3	9.4	9.6	9.7	9.8	9.9
167.5°	5.8	6.0	6.1	6.2	6.4	6.5	6.6	6.7	6.9	7.0	7.1
170°	3.7	3.8	3.9	4.0	4.1	4.2	4.3	4.4	4.5	4.6	4.7
172.5°	1.9	2.0	2.1	2.2	2.2	2.3	2.4	2.5	2.5	2.6	2.7
175°	1.0	1.0	1.1	1.1	1.2	1.2	1.2	1.2	1.3	1.3	1.3
177.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.8	0.8
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9	71.9
2.5°	70.7	70.6	70.6	70.5	70.4	70.4	70.3	70.2	70.1	70.1	70.0
5°	70.4	70.3	70.2	70.1	70.2	70.3	70.4	70.5	70.6	70.7	70.8
7.5°	72.0	71.9	71.7	71.6	71.6	71.7	71.8	71.9	72.0	72.1	72.1
10°	75.7	75.5	75.3	75.1	75.3	75.4	75.6	75.8	75.9	76.1	76.2
12.5°	80.2	80.0	79.9	79.8	79.7	79.7	79.7	79.7	79.7	79.6	79.6
15°	84.6	84.4	84.3	84.1	84.2	84.4	84.5	84.6	84.7	84.8	84.9
17.5°	89.0	88.9	88.7	88.5	88.6	88.7	88.8	88.9	88.9	89.0	89.1
20°	93.6	93.4	93.3	93.2	93.3	93.4	93.5	93.6	93.7	93.8	93.9
22.5°	98.0	97.9	97.8	97.7	97.7	97.7	97.7	97.7	97.7	97.7	97.7
25°	102.2	102.1	102.0	101.9	102.0	102.2	102.4	102.5	102.7	102.8	103.0
27.5°	106.1	106.0	105.9	105.8	105.8	105.8	105.8	105.8	105.7	105.7	105.7
30°	110.1	110.0	110.0	109.9	109.8	109.8	109.7	109.6	109.5	109.5	109.4
32.5°	114.0	114.0	114.0	114.0	114.3	114.6	114.9	115.2	115.4	115.7	116.0
35°	117.5	117.5	117.5	117.5	117.7	118.0	118.2	118.5	118.7	119.0	119.2
37.5°	120.9	120.9	121.0	121.0	121.1	121.3	121.4	121.6	121.7	121.9	122.1
40°	124.1	124.2	124.2	124.3	124.4	124.4	124.5	124.5	124.6	124.6	124.7
42.5°	126.4	126.4	126.4	126.4	126.5	126.7	126.9	127.0	127.2	127.3	127.5
45°	128.7	128.7	128.7	128.7	129.0	129.2	129.5	129.8	130.1	130.3	130.6
47.5°	130.6	130.7	130.7	130.7	130.9	131.1	131.2	131.4	131.5	131.7	131.9
50°	132.5	132.5	132.6	132.6	132.7	132.9	133.0	133.1	133.2	133.4	133.5
52.5°	133.9	134.0	134.0	134.1	134.3	134.5	134.7	134.9	135.1	135.3	135.4
55°	134.5	134.5	134.6	134.6	134.7	134.8	134.9	135.0	135.1	135.2	135.3
57.5°	135.3	135.3	135.4	135.4	135.4	135.4	135.5	135.5	135.5	135.5	135.6
60°	135.9	136.0	136.1	136.2	136.3	136.4	136.5	136.6	136.7	136.8	136.9
62.5°	136.0	136.0	136.1	136.2	136.3	136.3	136.4	136.5	136.5	136.6	136.6
65°	135.9	136.1	136.2	136.3	136.3	136.3	136.3	136.3	136.3	136.3	136.3
67.5°	135.2	135.3	135.4	135.5	135.5	135.5	135.4	135.4	135.4	135.3	135.3
70°	134.3	134.4	134.6	134.8	134.7	134.7	134.6	134.6	134.5	134.5	134.4
72.5°	132.7	132.8	133.0	133.2	133.2	133.2	133.2	133.2	133.2	133.2	133.2
75°	131.0	131.2	131.4	131.6	131.5	131.4	131.3	131.2	131.1	131.0	130.9
77.5°	128.8	129.0	129.2	129.4	129.3	129.3	129.2	129.1	129.1	129.0	128.9
80°	126.6	126.8	127.0	127.3	127.4	127.5	127.6	127.8	127.9	128.0	128.1
82.5°	124.1	124.3	124.5	124.7	124.7	124.7	124.6	124.6	124.5	124.5	124.5
85°	121.3	121.5	121.7	121.9	122.0	122.0	122.0	122.1	122.1	122.1	122.2
87.5°	118.5	118.7	118.9	119.2	119.1	119.0	118.9	118.9	118.8	118.7	118.6
90°	115.5	115.8	116.0	116.2	116.2	116.2	116.2	116.1	116.1	116.1	116.0
92.5°	112.7	112.9	113.2	113.4	113.4	113.4	113.5	113.5	113.5	113.5	113.6
95°	109.9	110.2	110.4	110.7	110.7	110.6	110.6	110.5	110.5	110.4	110.4
97.5°	107.0	107.3	107.5	107.8	107.9	107.9	108.0	108.1	108.1	108.2	108.3
100°	103.9	104.1	104.3	104.5	104.5	104.4	104.4	104.4	104.3	104.3	104.3
102.5°	101.0	101.3	101.5	101.7	101.6	101.6	101.5	101.5	101.4	101.4	101.3
105°	97.7	97.9	98.2	98.4	98.5	98.5	98.6	98.7	98.8	98.8	98.9
107.5°	94.5	94.8	95.0	95.3	95.4	95.4	95.4	95.5	95.5	95.6	95.6
110°	91.2	91.4	91.7	91.9	91.9	91.9	91.9	91.8	91.8	91.8	91.8

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	87.7	87.9	88.2	88.4	88.5	88.5	88.6	88.7	88.7	88.8	88.9
115°	84.1	84.4	84.6	84.9	84.9	85.0	85.1	85.1	85.2	85.2	85.3
117.5°	80.5	80.8	81.0	81.3	81.3	81.3	81.4	81.4	81.5	81.5	81.5
120°	76.8	77.0	77.3	77.5	77.6	77.7	77.8	77.9	78.0	78.1	78.2
122.5°	73.2	73.4	73.7	73.9	74.0	74.1	74.2	74.2	74.3	74.4	74.5
125°	69.6	69.9	70.1	70.4	70.4	70.5	70.5	70.5	70.6	70.6	70.7
127.5°	65.7	65.9	66.1	66.3	66.3	66.4	66.4	66.4	66.4	66.5	66.5
130°	62.1	62.3	62.5	62.8	62.8	62.8	62.9	62.9	62.9	63.0	63.0
132.5°	58.1	58.3	58.5	58.7	58.8	58.8	58.8	58.9	58.9	59.0	59.0
135°	54.2	54.4	54.7	54.9	54.9	55.0	55.0	55.0	55.1	55.1	55.1
137.5°	50.2	50.4	50.6	50.8	50.9	51.0	51.0	51.1	51.2	51.3	51.4
140°	46.3	46.5	46.7	46.9	47.0	47.1	47.1	47.2	47.3	47.4	47.4
142.5°	42.3	42.5	42.7	42.9	43.1	43.2	43.3	43.4	43.5	43.6	43.7
145°	38.5	38.7	38.9	39.2	39.2	39.3	39.3	39.3	39.4	39.4	39.5
147.5°	34.6	34.8	35.0	35.2	35.2	35.3	35.4	35.4	35.5	35.5	35.6
150°	30.9	31.1	31.2	31.4	31.5	31.6	31.6	31.7	31.8	31.9	31.9
152.5°	27.1	27.3	27.5	27.7	27.7	27.7	27.7	27.7	27.8	27.8	27.8
155°	23.5	23.7	23.9	24.1	24.1	24.1	24.2	24.2	24.2	24.3	24.3
157.5°	20.0	20.1	20.3	20.5	20.5	20.5	20.5	20.5	20.5	20.5	20.5
160°	16.5	16.6	16.8	16.9	16.9	16.9	16.9	16.9	16.9	17.0	17.0
162.5°	13.2	13.3	13.4	13.6	13.6	13.7	13.7	13.7	13.7	13.8	13.8
165°	10.1	10.2	10.3	10.4	10.5	10.5	10.5	10.5	10.5	10.5	10.5
167.5°	7.2	7.3	7.4	7.5	7.5	7.4	7.4	7.4	7.3	7.3	7.3
170°	4.8	4.9	4.9	5.0	5.0	4.9	4.9	4.8	4.8	4.7	4.7
172.5°	2.7	2.8	2.9	2.9	2.8	2.8	2.7	2.6	2.6	2.5	2.4
175°	1.3	1.4	1.4	1.4	1.4	1.3	1.3	1.3	1.2	1.2	1.1
177.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.7	0.7	0.7
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0



REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
0°	71.9	71.9
2.5°	69.9	69.8
5°	70.9	71.0
7.5°	72.2	72.3
10°	76.4	76.5
12.5°	79.6	79.6
15°	85.1	85.2
17.5°	89.2	89.3
20°	94.0	94.1
22.5°	97.7	97.7
25°	103.2	103.3
27.5°	105.7	105.7
30°	109.3	109.2
32.5°	116.3	116.6
35°	119.5	119.7
37.5°	122.2	122.4
40°	124.7	124.8
42.5°	127.7	127.8
45°	130.9	131.1
47.5°	132.0	132.2
50°	133.6	133.7
52.5°	135.6	135.8
55°	135.4	135.5
57.5°	135.6	135.6
60°	137.0	137.1
62.5°	136.7	136.8
65°	136.4	136.4
67.5°	135.2	135.2
70°	134.4	134.3
72.5°	133.2	133.2
75°	130.8	130.7
77.5°	128.8	128.8
80°	128.2	128.4
82.5°	124.4	124.4
85°	122.2	122.3
87.5°	118.5	118.5
90°	116.0	116.0
92.5°	113.6	113.6
95°	110.3	110.3
97.5°	108.3	108.4
100°	104.2	104.2
102.5°	101.3	101.2
105°	99.0	99.0
107.5°	95.6	95.7
110°	91.8	91.7

REPORT NUMBER: P600776  
 CATALOG NUMBER: FE10A35GLMB

**CANDELA DISTRIBUTION (continued):**

	357.5°	360°
112.5°	88.9	89.0
115°	85.4	85.4
117.5°	81.6	81.6
120°	78.3	78.4
122.5°	74.6	74.7
125°	70.7	70.8
127.5°	66.5	66.5
130°	63.0	63.1
132.5°	59.0	59.1
135°	55.2	55.2
137.5°	51.4	51.5
140°	47.5	47.6
142.5°	43.9	44.0
145°	39.5	39.6
147.5°	35.7	35.7
150°	32.0	32.1
152.5°	27.8	27.8
155°	24.3	24.4
157.5°	20.5	20.6
160°	17.0	17.0
162.5°	13.8	13.9
165°	10.5	10.5
167.5°	7.2	7.2
170°	4.6	4.6
172.5°	2.3	2.3
175°	1.1	1.1
177.5°	0.7	0.7
180°	0.0	0.0

(END OF REPORT)