

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P600777

Luminaire Tested: **FE10A35GLMB-NL**

Issue Date: 07/11/2022

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P600777
 Test Lab: Third Party
 Issue Date: 07/11/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: FE10A35GLMB-NL
 Description: LED Entry Light w/ Night Light -Bronze 3500K (Night Light)
 Light Source: 70 CRI LEDs
 Ballast/Driver: (1) Electronic Driver

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 14.5 lumens
 Efficiency: N/A
 Efficacy: 4.2 lumens/watt
 Luminous Opening: Point Source (0m x 0m x 0m)
 IES Classification: Type IV - V Long
 BUG Rating: B0 - U1 - G0


Input Watts (W): 3.42
 Input Voltage (V): 120.0
 Input Current (Ain): 0.0285
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 0 fc
 Type IV - V Long - N/A

REPORT NUMBER: P600777
CATALOG NUMBER: FE10A35GLMB-NL

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 87.5-Deg Vertical

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	1.6	1.6	3.2
	% Fixture	11.1	10.9	22.1
Street Side	Lumens	5.6	5.6	11.3
	% Fixture	39.0	39.0	77.9
Total	Lumens	7.3	7.2	14.5
	% Fixture	50.1	49.9	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.0
10°-20°	0.1	0.3
20°-30°	0.2	1.4
30°-40°	0.4	3.0
40°-50°	0.7	5.1
50°-60°	1.1	7.4
60°-70°	1.4	9.6
70°-80°	1.6	11.2
80°-90°	1.8	12.1
90°-100°	1.7	12.1
100°-110°	1.6	11.1
110°-120°	1.4	9.4
120°-130°	1.1	7.3
130°-140°	0.7	5.0
140°-150°	0.4	3.1
150°-160°	0.2	1.5
160°-170°	0.1	0.5
170°-180°	0.0	0.0
0°-90°	7.3	50.1
0°-180°	14.5	100.0




REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	0.2	1.3			
FM (30°-60°)	1.8	12.1			
FH (60°-80°)	2.3	16.1			G0/660
FVH (80°-90°)	1.4	9.4			G0/10
BL (0°-30°)	0.1	0.4	B0/110		
BM (30°-60°)	0.5	3.4	B0/220		
BH (60°-80°)	0.7	4.6	B0/110		G0/110
BVH (80°-90°)	0.4	2.7			G0/10
UL (90°-100°)	1.7	12.1		U1/10	
UH (100°-180°)	5.5	37.8		U1/10	

BUG Rating: B0-U1-G0
 Type IV V Long



REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
12.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
15°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2
17.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3
20°	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
22.5°	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.4
25°	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.5	0.5
27.5°	0.4	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6
30°	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.7
32.5°	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.8	0.8	0.8	0.8
35°	0.6	0.7	0.7	0.7	0.8	0.8	0.8	0.8	0.9	0.9	0.9
37.5°	0.7	0.7	0.8	0.8	0.8	0.9	0.9	0.9	1.0	1.0	1.0
40°	0.8	0.8	0.8	0.9	0.9	0.9	1.0	1.0	1.1	1.1	1.1
42.5°	0.8	0.9	0.9	0.9	1.0	1.0	1.1	1.1	1.1	1.2	1.2
45°	0.9	0.9	1.0	1.0	1.1	1.1	1.1	1.2	1.2	1.3	1.3
47.5°	0.9	1.0	1.0	1.1	1.1	1.2	1.2	1.3	1.3	1.4	1.4
50°	1.0	1.1	1.1	1.2	1.2	1.3	1.3	1.4	1.4	1.5	1.5
52.5°	1.1	1.1	1.2	1.2	1.3	1.3	1.4	1.4	1.5	1.5	1.5
55°	1.1	1.2	1.2	1.3	1.3	1.4	1.4	1.5	1.6	1.6	1.6
57.5°	1.2	1.2	1.3	1.3	1.4	1.5	1.5	1.6	1.6	1.7	1.7
60°	1.2	1.3	1.3	1.4	1.5	1.5	1.6	1.6	1.7	1.8	1.8
62.5°	1.3	1.3	1.4	1.5	1.5	1.6	1.6	1.7	1.8	1.8	1.8
65°	1.3	1.4	1.4	1.5	1.6	1.6	1.7	1.8	1.8	1.9	1.9
67.5°	1.3	1.4	1.5	1.5	1.6	1.7	1.8	1.8	1.9	2.0	2.0
70°	1.4	1.5	1.5	1.6	1.7	1.7	1.8	1.9	1.9	2.0	2.0
72.5°	1.4	1.5	1.6	1.6	1.7	1.8	1.8	1.9	2.0	2.1	2.1
75°	1.4	1.5	1.6	1.7	1.7	1.8	1.9	2.0	2.0	2.1	2.1
77.5°	1.5	1.5	1.6	1.7	1.8	1.8	1.9	2.0	2.1	2.1	2.2
80°	1.5	1.6	1.6	1.7	1.8	1.9	1.9	2.0	2.1	2.2	2.2
82.5°	1.5	1.6	1.7	1.7	1.8	1.9	2.0	2.0	2.1	2.2	2.2
85°	1.5	1.6	1.7	1.8	1.8	1.9	2.0	2.1	2.1	2.2	2.2
87.5°	1.5	1.6	1.7	1.8	1.8	1.9	2.0	2.1	2.1	2.2	2.2
90°	1.5	1.6	1.7	1.8	1.8	1.9	2.0	2.1	2.2	2.2	2.2
92.5°	1.5	1.6	1.7	1.8	1.8	1.9	2.0	2.1	2.2	2.2	2.2
95°	1.5	1.6	1.7	1.8	1.8	1.9	2.0	2.1	2.1	2.2	2.2
97.5°	1.5	1.6	1.7	1.7	1.8	1.9	2.0	2.1	2.1	2.2	2.2
100°	1.5	1.6	1.7	1.7	1.8	1.9	2.0	2.0	2.1	2.2	2.2
102.5°	1.5	1.6	1.6	1.7	1.8	1.9	1.9	2.0	2.1	2.2	2.2
105°	1.5	1.5	1.6	1.7	1.8	1.8	1.9	2.0	2.0	2.1	2.1
107.5°	1.4	1.5	1.6	1.6	1.7	1.8	1.9	1.9	2.0	2.1	2.1
110°	1.4	1.5	1.5	1.6	1.7	1.8	1.8	1.9	2.0	2.0	2.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	1.4	1.4	1.5	1.6	1.6	1.7	1.8	1.8	1.9	2.0	2.0
115°	1.3	1.4	1.5	1.5	1.6	1.7	1.7	1.8	1.9	1.9	1.9
117.5°	1.3	1.3	1.4	1.5	1.5	1.6	1.7	1.7	1.8	1.9	1.9
120°	1.2	1.3	1.4	1.4	1.5	1.5	1.6	1.7	1.7	1.8	1.8
122.5°	1.2	1.2	1.3	1.4	1.4	1.5	1.5	1.6	1.7	1.7	1.7
125°	1.1	1.2	1.3	1.3	1.4	1.4	1.5	1.5	1.6	1.7	1.7
127.5°	1.1	1.1	1.2	1.3	1.3	1.4	1.4	1.5	1.5	1.6	1.6
130°	1.0	1.1	1.1	1.2	1.2	1.3	1.4	1.4	1.5	1.5	1.5
132.5°	1.0	1.0	1.1	1.1	1.2	1.2	1.3	1.3	1.4	1.4	1.4
135°	0.9	1.0	1.0	1.1	1.1	1.2	1.2	1.3	1.3	1.4	1.4
137.5°	0.9	0.9	1.0	1.0	1.0	1.1	1.1	1.2	1.2	1.3	1.3
140°	0.8	0.8	0.9	0.9	1.0	1.0	1.1	1.1	1.1	1.2	1.2
142.5°	0.7	0.8	0.8	0.9	0.9	0.9	1.0	1.0	1.1	1.1	1.1
145°	0.7	0.7	0.8	0.8	0.8	0.9	0.9	0.9	1.0	1.0	1.0
147.5°	0.6	0.7	0.7	0.7	0.8	0.8	0.8	0.9	0.9	0.9	0.9
150°	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.8
152.5°	0.5	0.5	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.8	0.8
155°	0.4	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.7	0.7
157.5°	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.5	0.6	0.6
160°	0.3	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5
162.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4
165°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3
167.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
170°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
12.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
15°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
17.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
20°	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
22.5°	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
25°	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6	0.6	0.6
27.5°	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.7	0.7	0.7
30°	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.8	0.8	0.8	0.8
32.5°	0.8	0.8	0.8	0.8	0.9	0.9	0.9	0.9	0.9	0.9	0.9
35°	0.9	0.9	0.9	0.9	0.9	1.0	1.0	1.0	1.0	1.0	1.0
37.5°	1.0	1.0	1.0	1.0	1.0	1.1	1.1	1.1	1.1	1.1	1.1
40°	1.1	1.1	1.1	1.1	1.1	1.2	1.2	1.2	1.2	1.2	1.2
42.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.3	1.3	1.3	1.3	1.4
45°	1.3	1.3	1.3	1.3	1.3	1.3	1.4	1.4	1.4	1.4	1.5
47.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.5	1.5	1.5	1.6
50°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.6	1.6	1.7
52.5°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.7	1.7	1.7
55°	1.6	1.6	1.7	1.7	1.7	1.7	1.7	1.7	1.8	1.8	1.8
57.5°	1.7	1.7	1.7	1.7	1.8	1.8	1.8	1.8	1.8	1.9	1.9
60°	1.8	1.8	1.8	1.8	1.8	1.9	1.9	1.9	1.9	2.0	2.0
62.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9	2.0	2.0	2.1
65°	1.9	1.9	1.9	2.0	2.0	2.0	2.0	2.0	2.1	2.1	2.2
67.5°	2.0	2.0	2.0	2.0	2.0	2.1	2.1	2.1	2.1	2.2	2.2
70°	2.0	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.2	2.2	2.3
72.5°	2.1	2.1	2.1	2.1	2.1	2.2	2.2	2.2	2.2	2.3	2.3
75°	2.1	2.1	2.2	2.2	2.2	2.2	2.2	2.2	2.3	2.3	2.4
77.5°	2.2	2.2	2.2	2.2	2.2	2.2	2.3	2.3	2.3	2.4	2.4
80°	2.2	2.2	2.2	2.2	2.3	2.3	2.3	2.3	2.4	2.4	2.5
82.5°	2.2	2.2	2.3	2.3	2.3	2.3	2.3	2.3	2.4	2.4	2.5
85°	2.2	2.3	2.3	2.3	2.3	2.3	2.3	2.4	2.4	2.5	2.5
87.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.4	2.4	2.4	2.5	2.5
90°	2.3	2.3	2.3	2.3	2.3	2.3	2.4	2.4	2.4	2.5	2.5
92.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.4	2.4	2.4	2.5	2.5
95°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.4	2.4	2.5	2.5
97.5°	2.2	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.4	2.5	2.5
100°	2.2	2.2	2.2	2.3	2.3	2.3	2.3	2.3	2.4	2.4	2.5
102.5°	2.2	2.2	2.2	2.2	2.2	2.3	2.3	2.3	2.3	2.4	2.5
105°	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.3	2.3	2.4	2.4
107.5°	2.1	2.1	2.1	2.2	2.2	2.2	2.2	2.2	2.3	2.3	2.4
110°	2.1	2.1	2.1	2.1	2.1	2.1	2.2	2.2	2.2	2.3	2.3

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	2.0	2.0	2.0	2.1	2.1	2.1	2.1	2.1	2.2	2.2	2.3
115°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.1	2.1	2.1	2.2
117.5°	1.9	1.9	1.9	1.9	1.9	2.0	2.0	2.0	2.0	2.1	2.1
120°	1.8	1.8	1.9	1.9	1.9	1.9	1.9	1.9	2.0	2.0	2.0
122.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.9	1.9	2.0
125°	1.7	1.7	1.7	1.7	1.7	1.7	1.8	1.8	1.8	1.8	1.9
127.5°	1.6	1.6	1.6	1.6	1.7	1.7	1.7	1.7	1.7	1.8	1.8
130°	1.5	1.5	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.7	1.7
132.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.6	1.6	1.6
135°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.5	1.5	1.5
137.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.4	1.4	1.4	1.4
140°	1.2	1.2	1.2	1.2	1.2	1.2	1.3	1.3	1.3	1.3	1.3
142.5°	1.1	1.1	1.1	1.1	1.2	1.2	1.2	1.2	1.2	1.2	1.3
145°	1.0	1.0	1.0	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.2
147.5°	0.9	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.1
150°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.0	1.0
152.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.9	0.9
155°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.8	0.8
157.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.7	0.7
160°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6
162.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5
165°	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4
167.5°	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
170°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
12.5°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1
15°	0.2	0.2	0.2	0.2	0.2	0.3	0.2	0.2	0.2	0.2	0.2
17.5°	0.3	0.3	0.3	0.3	0.3	0.4	0.3	0.3	0.3	0.3	0.3
20°	0.4	0.4	0.4	0.4	0.4	0.5	0.4	0.4	0.4	0.4	0.4
22.5°	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.5	0.5	0.5	0.5
25°	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.6	0.6	0.6	0.6
27.5°	0.7	0.7	0.8	0.8	0.8	0.8	0.8	0.8	0.7	0.7	0.7
30°	0.8	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.8	0.8	0.8
32.5°	0.9	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	0.9	0.9
35°	1.1	1.1	1.1	1.1	1.1	1.2	1.1	1.1	1.1	1.0	1.0
37.5°	1.2	1.2	1.2	1.2	1.3	1.3	1.3	1.2	1.2	1.1	1.1
40°	1.3	1.3	1.3	1.4	1.4	1.4	1.4	1.3	1.3	1.2	1.2
42.5°	1.4	1.4	1.4	1.5	1.5	1.5	1.5	1.4	1.4	1.3	1.3
45°	1.5	1.5	1.5	1.6	1.6	1.6	1.6	1.5	1.5	1.5	1.4
47.5°	1.6	1.6	1.7	1.7	1.7	1.8	1.7	1.7	1.6	1.6	1.5
50°	1.7	1.7	1.8	1.8	1.8	1.9	1.8	1.8	1.7	1.6	1.6
52.5°	1.8	1.8	1.9	1.9	1.9	2.0	1.9	1.9	1.8	1.7	1.7
55°	1.9	1.9	2.0	2.0	2.0	2.1	2.0	1.9	1.9	1.8	1.8
57.5°	2.0	2.0	2.0	2.1	2.1	2.2	2.1	2.0	2.0	1.9	1.9
60°	2.0	2.1	2.1	2.2	2.2	2.3	2.2	2.1	2.1	2.0	1.9
62.5°	2.1	2.2	2.2	2.3	2.3	2.3	2.3	2.2	2.1	2.1	2.0
65°	2.2	2.2	2.3	2.3	2.4	2.4	2.4	2.3	2.2	2.2	2.1
67.5°	2.3	2.3	2.4	2.4	2.5	2.5	2.4	2.4	2.3	2.2	2.1
70°	2.3	2.4	2.4	2.5	2.5	2.6	2.5	2.4	2.4	2.3	2.2
72.5°	2.4	2.4	2.5	2.5	2.6	2.6	2.6	2.5	2.4	2.3	2.3
75°	2.4	2.5	2.5	2.6	2.6	2.7	2.6	2.5	2.5	2.4	2.3
77.5°	2.5	2.5	2.6	2.6	2.7	2.7	2.7	2.6	2.5	2.4	2.3
80°	2.5	2.6	2.6	2.7	2.7	2.8	2.7	2.6	2.5	2.5	2.4
82.5°	2.6	2.6	2.7	2.7	2.8	2.8	2.7	2.7	2.6	2.5	2.4
85°	2.6	2.6	2.7	2.7	2.8	2.8	2.8	2.7	2.6	2.5	2.4
87.5°	2.6	2.6	2.7	2.7	2.8	2.9	2.8	2.7	2.6	2.5	2.4
90°	2.6	2.6	2.7	2.8	2.8	2.9	2.8	2.7	2.6	2.5	2.4
92.5°	2.6	2.6	2.7	2.8	2.8	2.9	2.8	2.7	2.6	2.5	2.4
95°	2.6	2.6	2.7	2.7	2.8	2.9	2.8	2.7	2.6	2.5	2.4
97.5°	2.6	2.6	2.7	2.7	2.8	2.8	2.8	2.7	2.6	2.5	2.4
100°	2.5	2.6	2.6	2.7	2.8	2.8	2.7	2.6	2.6	2.5	2.4
102.5°	2.5	2.6	2.6	2.7	2.7	2.8	2.7	2.6	2.5	2.4	2.4
105°	2.5	2.5	2.6	2.6	2.7	2.7	2.6	2.6	2.5	2.4	2.3
107.5°	2.4	2.5	2.5	2.6	2.6	2.7	2.6	2.5	2.4	2.4	2.3
110°	2.4	2.4	2.5	2.5	2.6	2.6	2.5	2.5	2.4	2.3	2.2

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	2.3	2.4	2.4	2.4	2.5	2.5	2.5	2.4	2.3	2.2	2.2
115°	2.2	2.3	2.3	2.4	2.4	2.5	2.4	2.3	2.3	2.2	2.1
117.5°	2.2	2.2	2.3	2.3	2.3	2.4	2.3	2.2	2.2	2.1	2.0
120°	2.1	2.1	2.2	2.2	2.3	2.3	2.2	2.2	2.1	2.0	2.0
122.5°	2.0	2.0	2.1	2.1	2.2	2.2	2.1	2.1	2.0	2.0	1.9
125°	1.9	2.0	2.0	2.0	2.1	2.1	2.1	2.0	1.9	1.9	1.8
127.5°	1.8	1.9	1.9	1.9	2.0	2.0	2.0	1.9	1.8	1.8	1.7
130°	1.7	1.8	1.8	1.8	1.9	1.9	1.9	1.8	1.7	1.7	1.6
132.5°	1.7	1.7	1.7	1.7	1.8	1.8	1.8	1.7	1.7	1.6	1.6
135°	1.6	1.6	1.6	1.6	1.7	1.7	1.7	1.6	1.6	1.5	1.5
137.5°	1.5	1.5	1.5	1.5	1.6	1.6	1.6	1.5	1.5	1.4	1.4
140°	1.4	1.4	1.4	1.4	1.5	1.5	1.5	1.4	1.4	1.3	1.3
142.5°	1.3	1.3	1.3	1.4	1.4	1.4	1.4	1.3	1.3	1.2	1.2
145°	1.2	1.2	1.2	1.3	1.3	1.3	1.3	1.2	1.2	1.2	1.1
147.5°	1.1	1.1	1.1	1.2	1.2	1.2	1.2	1.1	1.1	1.1	1.1
150°	1.0	1.0	1.0	1.1	1.1	1.1	1.1	1.1	1.0	1.0	1.0
152.5°	0.9	0.9	0.9	1.0	1.0	1.0	1.0	1.0	0.9	0.9	0.9
155°	0.8	0.8	0.8	0.9	0.9	0.9	0.9	0.9	0.8	0.8	0.8
157.5°	0.7	0.7	0.7	0.8	0.8	0.8	0.8	0.8	0.8	0.7	0.7
160°	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.7	0.7	0.6	0.6
162.5°	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6	0.6	0.5	0.5
165°	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.5	0.4	0.4
167.5°	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.3
170°	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
172.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
12.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
15°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1
17.5°	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2
20°	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
22.5°	0.5	0.5	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3
25°	0.6	0.6	0.5	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.4
27.5°	0.7	0.6	0.6	0.6	0.6	0.6	0.5	0.5	0.5	0.5	0.5
30°	0.8	0.7	0.7	0.7	0.7	0.6	0.6	0.6	0.6	0.6	0.5
32.5°	0.9	0.8	0.8	0.8	0.8	0.7	0.7	0.7	0.7	0.6	0.6
35°	1.0	0.9	0.9	0.9	0.8	0.8	0.8	0.8	0.7	0.7	0.7
37.5°	1.1	1.0	1.0	1.0	0.9	0.9	0.9	0.8	0.8	0.8	0.8
40°	1.2	1.1	1.1	1.0	1.0	1.0	0.9	0.9	0.9	0.9	0.8
42.5°	1.3	1.2	1.2	1.1	1.1	1.1	1.0	1.0	1.0	0.9	0.9
45°	1.4	1.3	1.3	1.2	1.2	1.1	1.1	1.1	1.0	1.0	1.0
47.5°	1.4	1.4	1.3	1.3	1.3	1.2	1.2	1.1	1.1	1.1	1.0
50°	1.5	1.5	1.4	1.4	1.3	1.3	1.3	1.2	1.2	1.1	1.1
52.5°	1.6	1.6	1.5	1.5	1.4	1.4	1.3	1.3	1.2	1.2	1.2
55°	1.7	1.7	1.6	1.5	1.5	1.4	1.4	1.4	1.3	1.3	1.2
57.5°	1.8	1.7	1.7	1.6	1.6	1.5	1.5	1.4	1.4	1.3	1.3
60°	1.9	1.8	1.7	1.7	1.6	1.6	1.5	1.5	1.4	1.4	1.3
62.5°	1.9	1.9	1.8	1.7	1.7	1.6	1.6	1.5	1.5	1.4	1.4
65°	2.0	1.9	1.9	1.8	1.7	1.7	1.6	1.6	1.5	1.5	1.4
67.5°	2.1	2.0	1.9	1.9	1.8	1.8	1.7	1.6	1.6	1.5	1.5
70°	2.1	2.1	2.0	1.9	1.9	1.8	1.7	1.7	1.6	1.6	1.5
72.5°	2.2	2.1	2.0	2.0	1.9	1.8	1.8	1.7	1.7	1.6	1.6
75°	2.2	2.2	2.1	2.0	1.9	1.9	1.8	1.8	1.7	1.7	1.6
77.5°	2.3	2.2	2.1	2.0	2.0	1.9	1.9	1.8	1.7	1.7	1.6
80°	2.3	2.2	2.1	2.1	2.0	1.9	1.9	1.8	1.8	1.7	1.6
82.5°	2.3	2.2	2.2	2.1	2.0	2.0	1.9	1.8	1.8	1.7	1.7
85°	2.3	2.3	2.2	2.1	2.0	2.0	1.9	1.9	1.8	1.7	1.7
87.5°	2.4	2.3	2.2	2.1	2.0	2.0	1.9	1.9	1.8	1.7	1.7
90°	2.4	2.3	2.2	2.1	2.1	2.0	1.9	1.9	1.8	1.7	1.7
92.5°	2.4	2.3	2.2	2.1	2.0	2.0	1.9	1.9	1.8	1.7	1.7
95°	2.4	2.3	2.2	2.1	2.0	2.0	1.9	1.9	1.8	1.7	1.7
97.5°	2.3	2.3	2.2	2.1	2.0	2.0	1.9	1.9	1.8	1.7	1.7
100°	2.3	2.2	2.2	2.1	2.0	2.0	1.9	1.8	1.8	1.7	1.7
102.5°	2.3	2.2	2.1	2.0	2.0	1.9	1.9	1.8	1.7	1.7	1.6
105°	2.2	2.2	2.1	2.0	1.9	1.9	1.8	1.8	1.7	1.7	1.6
107.5°	2.2	2.1	2.0	2.0	1.9	1.9	1.8	1.7	1.7	1.6	1.6
110°	2.2	2.1	2.0	1.9	1.9	1.8	1.8	1.7	1.6	1.6	1.5

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	2.1	2.0	1.9	1.9	1.8	1.8	1.7	1.7	1.6	1.5	1.5
115°	2.0	2.0	1.9	1.8	1.8	1.7	1.7	1.6	1.6	1.5	1.4
117.5°	2.0	1.9	1.8	1.8	1.7	1.7	1.6	1.6	1.5	1.5	1.4
120°	1.9	1.8	1.8	1.7	1.6	1.6	1.5	1.5	1.4	1.4	1.3
122.5°	1.8	1.8	1.7	1.6	1.6	1.5	1.5	1.4	1.4	1.3	1.3
125°	1.7	1.7	1.6	1.6	1.5	1.5	1.4	1.4	1.3	1.3	1.2
127.5°	1.7	1.6	1.5	1.5	1.4	1.4	1.4	1.3	1.3	1.2	1.2
130°	1.6	1.5	1.5	1.4	1.4	1.3	1.3	1.2	1.2	1.2	1.1
132.5°	1.5	1.4	1.4	1.3	1.3	1.3	1.2	1.2	1.1	1.1	1.1
135°	1.4	1.4	1.3	1.3	1.2	1.2	1.2	1.1	1.1	1.0	1.0
137.5°	1.3	1.3	1.2	1.2	1.2	1.1	1.1	1.1	1.0	1.0	1.0
140°	1.3	1.2	1.2	1.1	1.1	1.1	1.0	1.0	1.0	0.9	0.9
142.5°	1.2	1.1	1.1	1.1	1.0	1.0	1.0	0.9	0.9	0.9	0.8
145°	1.1	1.1	1.0	1.0	1.0	0.9	0.9	0.9	0.9	0.8	0.8
147.5°	1.0	1.0	1.0	0.9	0.9	0.9	0.9	0.8	0.8	0.8	0.8
150°	0.9	0.9	0.9	0.9	0.8	0.8	0.8	0.8	0.8	0.7	0.7
152.5°	0.9	0.8	0.8	0.8	0.8	0.8	0.7	0.7	0.7	0.7	0.7
155°	0.8	0.8	0.8	0.7	0.7	0.7	0.7	0.7	0.7	0.6	0.6
157.5°	0.7	0.7	0.7	0.7	0.6	0.6	0.6	0.6	0.6	0.6	0.6
160°	0.6	0.6	0.6	0.6	0.6	0.6	0.5	0.5	0.5	0.5	0.5
162.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.4	0.4
165°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
167.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
170°	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
172.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
12.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
15°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0
17.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
20°	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1
22.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.1	0.1	0.1
25°	0.4	0.4	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.1
27.5°	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.2	0.2	0.2	0.2
30°	0.5	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.3	0.2	0.2
32.5°	0.6	0.6	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.2	0.2
35°	0.7	0.6	0.6	0.5	0.5	0.5	0.4	0.4	0.3	0.3	0.2
37.5°	0.7	0.7	0.6	0.6	0.6	0.5	0.5	0.4	0.4	0.3	0.3
40°	0.8	0.8	0.7	0.7	0.6	0.6	0.5	0.5	0.4	0.3	0.3
42.5°	0.9	0.8	0.8	0.7	0.7	0.6	0.5	0.5	0.4	0.4	0.3
45°	0.9	0.9	0.8	0.8	0.7	0.7	0.6	0.5	0.5	0.4	0.3
47.5°	1.0	1.0	0.9	0.8	0.8	0.7	0.6	0.6	0.5	0.4	0.4
50°	1.1	1.0	0.9	0.9	0.8	0.7	0.7	0.6	0.5	0.5	0.4
52.5°	1.1	1.1	1.0	0.9	0.9	0.8	0.7	0.6	0.6	0.5	0.4
55°	1.2	1.1	1.1	1.0	0.9	0.8	0.8	0.7	0.6	0.5	0.4
57.5°	1.2	1.2	1.1	1.0	1.0	0.9	0.8	0.7	0.6	0.6	0.5
60°	1.3	1.2	1.2	1.1	1.0	0.9	0.8	0.7	0.7	0.6	0.5
62.5°	1.3	1.3	1.2	1.1	1.0	0.9	0.9	0.8	0.7	0.6	0.5
65°	1.4	1.3	1.2	1.2	1.1	1.0	0.9	0.8	0.7	0.6	0.5
67.5°	1.4	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6	0.6
70°	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.9	0.8	0.7	0.6
72.5°	1.5	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6
75°	1.5	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6
77.5°	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6
80°	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6
82.5°	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6
85°	1.6	1.6	1.5	1.4	1.2	1.1	1.0	0.9	0.8	0.7	0.6
87.5°	1.6	1.6	1.5	1.4	1.3	1.1	1.0	0.9	0.8	0.7	0.6
90°	1.6	1.6	1.5	1.4	1.3	1.1	1.0	0.9	0.8	0.7	0.6
92.5°	1.6	1.6	1.5	1.4	1.3	1.1	1.0	0.9	0.8	0.7	0.6
95°	1.6	1.6	1.5	1.4	1.2	1.1	1.0	0.9	0.8	0.7	0.6
97.5°	1.6	1.6	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6
100°	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6
102.5°	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6
105°	1.5	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6
107.5°	1.5	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6
110°	1.5	1.4	1.3	1.2	1.1	1.0	1.0	0.9	0.8	0.7	0.6

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	1.4	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6	0.6
115°	1.4	1.3	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6	0.5
117.5°	1.3	1.3	1.2	1.1	1.0	1.0	0.9	0.8	0.7	0.6	0.5
120°	1.3	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.7	0.6	0.5
122.5°	1.2	1.2	1.1	1.0	1.0	0.9	0.8	0.7	0.6	0.6	0.5
125°	1.2	1.1	1.1	1.0	0.9	0.8	0.8	0.7	0.6	0.5	0.5
127.5°	1.1	1.1	1.0	0.9	0.9	0.8	0.7	0.7	0.6	0.5	0.4
130°	1.1	1.0	1.0	0.9	0.8	0.8	0.7	0.6	0.6	0.5	0.4
132.5°	1.0	1.0	0.9	0.9	0.8	0.7	0.7	0.6	0.5	0.5	0.4
135°	1.0	0.9	0.9	0.8	0.7	0.7	0.6	0.6	0.5	0.4	0.4
137.5°	0.9	0.9	0.8	0.8	0.7	0.6	0.6	0.5	0.5	0.4	0.3
140°	0.9	0.8	0.8	0.7	0.7	0.6	0.6	0.5	0.4	0.4	0.3
142.5°	0.8	0.8	0.7	0.7	0.6	0.6	0.5	0.5	0.4	0.4	0.3
145°	0.8	0.7	0.7	0.6	0.6	0.5	0.5	0.4	0.4	0.4	0.3
147.5°	0.7	0.7	0.7	0.6	0.6	0.5	0.5	0.4	0.4	0.3	0.3
150°	0.7	0.7	0.6	0.6	0.5	0.5	0.5	0.4	0.4	0.3	0.3
152.5°	0.6	0.6	0.6	0.5	0.5	0.5	0.4	0.4	0.3	0.3	0.3
155°	0.6	0.6	0.5	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.3
157.5°	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.3	0.2
160°	0.5	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.2
162.5°	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.2	0.2	0.2
165°	0.4	0.4	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2
167.5°	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1
170°	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
17.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
20°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
22.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
25°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
27.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
30°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
32.5°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0
35°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0
37.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.0	0.0	0.0
40°	0.3	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.0	0.0	0.0
42.5°	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.0	0.0
45°	0.3	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.0
47.5°	0.3	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1
50°	0.4	0.3	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1	0.1
52.5°	0.4	0.3	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1
55°	0.4	0.4	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1
57.5°	0.4	0.4	0.3	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
60°	0.4	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
62.5°	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
65°	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
67.5°	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
70°	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
72.5°	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
75°	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
77.5°	0.6	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
80°	0.6	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
82.5°	0.6	0.5	0.5	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
85°	0.6	0.5	0.5	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
87.5°	0.6	0.5	0.5	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
90°	0.6	0.5	0.5	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
92.5°	0.6	0.5	0.5	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
95°	0.6	0.5	0.5	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
97.5°	0.6	0.5	0.5	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
100°	0.6	0.5	0.5	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
102.5°	0.6	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
105°	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
107.5°	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
110°	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
115°	0.5	0.4	0.4	0.3	0.3	0.3	0.2	0.2	0.1	0.1	0.1
117.5°	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
120°	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
122.5°	0.4	0.4	0.3	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
125°	0.4	0.4	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1
127.5°	0.4	0.4	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1
130°	0.4	0.3	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1
132.5°	0.4	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1
135°	0.3	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1
137.5°	0.3	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.0
140°	0.3	0.3	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.0
142.5°	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.0
145°	0.3	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.0
147.5°	0.3	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.0
150°	0.3	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.0
152.5°	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1
155°	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1
157.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.0
160°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.0
162.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
165°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0
167.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
170°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
172.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
42.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
45°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
47.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
50°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
52.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
55°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
57.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
60°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
62.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
65°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
67.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
70°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
72.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
75°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
77.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
80°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0
92.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
95°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
97.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
100°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
102.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
105°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
107.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
110°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
115°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
117.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
120°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
122.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
125°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
127.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
130°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
12.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
15°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
17.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
20°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
22.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1
25°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1
27.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1
30°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1
32.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1
35°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
37.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
40°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
42.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1
45°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2
47.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2
50°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2
52.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2
55°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2
57.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2
60°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.2
62.5°	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2	0.2
65°	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2	0.2
67.5°	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2	0.2
70°	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2	0.2
72.5°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
75°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
77.5°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
80°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
82.5°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2
85°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2
87.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2
90°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
92.5°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
95°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2
97.5°	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2	0.2
100°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.2
102.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.2
105°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.2
107.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2
110°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2
115°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2
117.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2
120°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2
122.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2
125°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
127.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
130°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
132.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
135°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1
137.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1
140°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1
142.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1
145°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
147.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
10°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1
12.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1
15°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
17.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
20°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2
22.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.3
25°	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.3	0.3
27.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.3	0.3	0.3	0.3
30°	0.1	0.1	0.1	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.4
32.5°	0.1	0.1	0.1	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.4
35°	0.1	0.1	0.2	0.2	0.2	0.3	0.3	0.3	0.4	0.4	0.5
37.5°	0.1	0.2	0.2	0.2	0.3	0.3	0.3	0.4	0.4	0.5	0.5
40°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.5	0.5
42.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.5	0.6
45°	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.5	0.6	0.6
47.5°	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.6	0.6	0.7
50°	0.2	0.2	0.2	0.3	0.4	0.4	0.5	0.5	0.6	0.6	0.7
52.5°	0.2	0.2	0.2	0.3	0.4	0.4	0.5	0.6	0.6	0.7	0.7
55°	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.6	0.6	0.7	0.8
57.5°	0.2	0.2	0.3	0.3	0.4	0.5	0.5	0.6	0.7	0.7	0.8
60°	0.2	0.3	0.3	0.3	0.4	0.5	0.6	0.6	0.7	0.8	0.8
62.5°	0.2	0.3	0.3	0.4	0.4	0.5	0.6	0.6	0.7	0.8	0.9
65°	0.2	0.3	0.3	0.4	0.4	0.5	0.6	0.7	0.7	0.8	0.9
67.5°	0.2	0.3	0.3	0.4	0.5	0.5	0.6	0.7	0.8	0.8	0.9
70°	0.3	0.3	0.3	0.4	0.5	0.5	0.6	0.7	0.8	0.8	0.9
72.5°	0.3	0.3	0.3	0.4	0.5	0.5	0.6	0.7	0.8	0.9	0.9
75°	0.3	0.3	0.3	0.4	0.5	0.6	0.6	0.7	0.8	0.9	1.0
77.5°	0.3	0.3	0.3	0.4	0.5	0.6	0.6	0.7	0.8	0.9	1.0
80°	0.3	0.3	0.3	0.4	0.5	0.6	0.6	0.7	0.8	0.9	1.0
82.5°	0.3	0.3	0.3	0.4	0.5	0.6	0.7	0.7	0.8	0.9	1.0
85°	0.3	0.3	0.3	0.4	0.5	0.6	0.7	0.7	0.8	0.9	1.0
87.5°	0.3	0.3	0.3	0.4	0.5	0.6	0.7	0.7	0.8	0.9	1.0
90°	0.3	0.3	0.3	0.4	0.5	0.6	0.6	0.7	0.8	0.9	1.0
92.5°	0.3	0.3	0.3	0.4	0.5	0.6	0.6	0.7	0.8	0.9	1.0
95°	0.3	0.3	0.3	0.4	0.5	0.6	0.6	0.7	0.8	0.9	1.0
97.5°	0.3	0.3	0.3	0.4	0.5	0.5	0.6	0.7	0.8	0.9	0.9
100°	0.2	0.3	0.3	0.4	0.5	0.5	0.6	0.7	0.8	0.9	0.9
102.5°	0.2	0.3	0.3	0.4	0.5	0.5	0.6	0.7	0.8	0.8	0.9
105°	0.2	0.3	0.3	0.4	0.4	0.5	0.6	0.7	0.7	0.8	0.9
107.5°	0.2	0.3	0.3	0.4	0.4	0.5	0.6	0.6	0.7	0.8	0.9
110°	0.2	0.2	0.3	0.3	0.4	0.5	0.6	0.6	0.7	0.8	0.8

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	0.2	0.2	0.3	0.3	0.4	0.5	0.5	0.6	0.7	0.7	0.8
115°	0.2	0.2	0.3	0.3	0.4	0.5	0.5	0.6	0.7	0.7	0.8
117.5°	0.2	0.2	0.2	0.3	0.4	0.4	0.5	0.6	0.6	0.7	0.8
120°	0.2	0.2	0.2	0.3	0.4	0.4	0.5	0.5	0.6	0.7	0.7
122.5°	0.2	0.2	0.2	0.3	0.3	0.4	0.5	0.5	0.6	0.6	0.7
125°	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.5	0.6	0.7
127.5°	0.2	0.2	0.2	0.2	0.3	0.4	0.4	0.5	0.5	0.6	0.6
130°	0.1	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.5	0.6
132.5°	0.1	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.5	0.6
135°	0.1	0.1	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.5
137.5°	0.1	0.1	0.1	0.2	0.2	0.3	0.3	0.3	0.4	0.4	0.5
140°	0.1	0.1	0.1	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.4
142.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.3	0.3	0.4	0.4
145°	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.3	0.3	0.4
147.5°	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.3	0.3
150°	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.3
152.5°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
155°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2
157.5°	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
10°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
12.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2
15°	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3
17.5°	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3
20°	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4
22.5°	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4	0.5	0.5
25°	0.3	0.3	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.6
27.5°	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.6	0.6	0.6
30°	0.4	0.4	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.7	0.7
32.5°	0.5	0.5	0.5	0.6	0.6	0.6	0.7	0.7	0.7	0.8	0.8
35°	0.5	0.5	0.6	0.6	0.6	0.7	0.7	0.8	0.8	0.8	0.9
37.5°	0.5	0.6	0.6	0.7	0.7	0.7	0.8	0.8	0.9	0.9	1.0
40°	0.6	0.6	0.7	0.7	0.8	0.8	0.9	0.9	0.9	1.0	1.1
42.5°	0.6	0.7	0.7	0.8	0.8	0.9	0.9	1.0	1.0	1.1	1.1
45°	0.7	0.7	0.8	0.8	0.9	0.9	1.0	1.0	1.1	1.1	1.2
47.5°	0.7	0.8	0.8	0.9	0.9	1.0	1.0	1.1	1.1	1.2	1.3
50°	0.8	0.8	0.9	0.9	1.0	1.0	1.1	1.1	1.2	1.3	1.4
52.5°	0.8	0.9	0.9	1.0	1.0	1.1	1.1	1.2	1.3	1.3	1.4
55°	0.8	0.9	1.0	1.0	1.1	1.1	1.2	1.3	1.3	1.4	1.5
57.5°	0.9	0.9	1.0	1.1	1.1	1.2	1.3	1.3	1.4	1.4	1.6
60°	0.9	1.0	1.0	1.1	1.2	1.2	1.3	1.4	1.4	1.5	1.6
62.5°	0.9	1.0	1.1	1.1	1.2	1.3	1.3	1.4	1.5	1.6	1.7
65°	1.0	1.0	1.1	1.2	1.2	1.3	1.4	1.5	1.5	1.6	1.7
67.5°	1.0	1.1	1.1	1.2	1.3	1.3	1.4	1.5	1.6	1.6	1.8
70°	1.0	1.1	1.2	1.2	1.3	1.4	1.5	1.5	1.6	1.7	1.8
72.5°	1.0	1.1	1.2	1.3	1.3	1.4	1.5	1.6	1.6	1.7	1.8
75°	1.0	1.1	1.2	1.3	1.4	1.4	1.5	1.6	1.7	1.7	1.9
77.5°	1.0	1.1	1.2	1.3	1.4	1.4	1.5	1.6	1.7	1.8	1.9
80°	1.1	1.1	1.2	1.3	1.4	1.5	1.5	1.6	1.7	1.8	1.9
82.5°	1.1	1.1	1.2	1.3	1.4	1.5	1.6	1.6	1.7	1.8	1.9
85°	1.1	1.1	1.2	1.3	1.4	1.5	1.6	1.6	1.7	1.8	1.9
87.5°	1.1	1.1	1.2	1.3	1.4	1.5	1.6	1.6	1.7	1.8	1.9
90°	1.1	1.1	1.2	1.3	1.4	1.5	1.6	1.6	1.7	1.8	1.9
92.5°	1.1	1.1	1.2	1.3	1.4	1.5	1.5	1.6	1.7	1.8	1.9
95°	1.0	1.1	1.2	1.3	1.4	1.4	1.5	1.6	1.7	1.8	1.9
97.5°	1.0	1.1	1.2	1.3	1.3	1.4	1.5	1.6	1.7	1.8	1.9
100°	1.0	1.1	1.2	1.2	1.3	1.4	1.5	1.6	1.6	1.7	1.9
102.5°	1.0	1.1	1.1	1.2	1.3	1.4	1.5	1.5	1.6	1.7	1.8
105°	1.0	1.0	1.1	1.2	1.3	1.4	1.4	1.5	1.6	1.7	1.8
107.5°	0.9	1.0	1.1	1.2	1.2	1.3	1.4	1.5	1.5	1.6	1.7
110°	0.9	1.0	1.1	1.1	1.2	1.3	1.4	1.4	1.5	1.6	1.7

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	0.9	1.0	1.0	1.1	1.2	1.2	1.3	1.4	1.5	1.5	1.7
115°	0.9	0.9	1.0	1.1	1.1	1.2	1.3	1.3	1.4	1.5	1.6
117.5°	0.8	0.9	1.0	1.0	1.1	1.2	1.2	1.3	1.4	1.4	1.5
120°	0.8	0.9	0.9	1.0	1.0	1.1	1.2	1.2	1.3	1.4	1.5
122.5°	0.8	0.8	0.9	0.9	1.0	1.1	1.1	1.2	1.3	1.3	1.4
125°	0.7	0.8	0.8	0.9	1.0	1.0	1.1	1.1	1.2	1.3	1.4
127.5°	0.7	0.7	0.8	0.8	0.9	1.0	1.0	1.1	1.1	1.2	1.3
130°	0.6	0.7	0.7	0.8	0.9	0.9	1.0	1.0	1.1	1.1	1.2
132.5°	0.6	0.7	0.7	0.8	0.8	0.9	0.9	1.0	1.0	1.1	1.1
135°	0.6	0.6	0.7	0.7	0.8	0.8	0.8	0.9	0.9	1.0	1.1
137.5°	0.5	0.6	0.6	0.7	0.7	0.7	0.8	0.8	0.9	0.9	1.0
140°	0.5	0.5	0.6	0.6	0.6	0.7	0.7	0.8	0.8	0.9	0.9
142.5°	0.4	0.5	0.5	0.6	0.6	0.6	0.7	0.7	0.7	0.8	0.8
145°	0.4	0.4	0.5	0.5	0.5	0.6	0.6	0.6	0.7	0.7	0.8
147.5°	0.3	0.4	0.4	0.4	0.5	0.5	0.5	0.6	0.6	0.6	0.7
150°	0.3	0.3	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.6	0.6
152.5°	0.2	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.5	0.5	0.5
155°	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.5
157.5°	0.1	0.1	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.4
160°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3
162.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2
165°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2
167.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
170°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.0	0.0
7.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
10°	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
12.5°	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3
15°	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4
17.5°	0.3	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.5	0.5
20°	0.4	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6	0.6
22.5°	0.5	0.5	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.7	0.7
25°	0.6	0.6	0.7	0.7	0.7	0.8	0.8	0.9	0.9	0.9	0.9
27.5°	0.7	0.7	0.8	0.8	0.9	0.9	0.9	1.0	1.0	1.0	1.0
30°	0.8	0.8	0.9	0.9	1.0	1.0	1.1	1.1	1.1	1.1	1.1
32.5°	0.9	0.9	1.0	1.0	1.1	1.1	1.2	1.2	1.3	1.3	1.3
35°	1.0	1.0	1.1	1.1	1.2	1.3	1.3	1.4	1.4	1.4	1.4
37.5°	1.0	1.1	1.2	1.2	1.3	1.4	1.4	1.5	1.5	1.5	1.5
40°	1.1	1.2	1.3	1.3	1.4	1.5	1.6	1.6	1.6	1.6	1.6
42.5°	1.2	1.3	1.4	1.4	1.5	1.6	1.7	1.7	1.8	1.8	1.8
45°	1.3	1.4	1.5	1.5	1.6	1.7	1.8	1.9	1.9	1.9	1.9
47.5°	1.4	1.5	1.5	1.6	1.7	1.8	1.9	2.0	2.0	2.0	2.0
50°	1.4	1.5	1.6	1.7	1.8	1.9	2.0	2.1	2.1	2.1	2.1
52.5°	1.5	1.6	1.7	1.8	1.9	2.0	2.1	2.2	2.2	2.2	2.2
55°	1.6	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.3	2.3	2.4
57.5°	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.4	2.4	2.4	2.5
60°	1.7	1.8	1.9	2.1	2.2	2.3	2.4	2.5	2.5	2.5	2.6
62.5°	1.8	1.9	2.0	2.1	2.3	2.4	2.5	2.6	2.6	2.6	2.6
65°	1.8	2.0	2.1	2.2	2.3	2.4	2.6	2.7	2.7	2.7	2.7
67.5°	1.9	2.0	2.1	2.3	2.4	2.5	2.6	2.8	2.8	2.8	2.8
70°	1.9	2.1	2.2	2.3	2.4	2.6	2.7	2.8	2.8	2.9	2.9
72.5°	2.0	2.1	2.2	2.4	2.5	2.6	2.8	2.9	2.9	2.9	2.9
75°	2.0	2.1	2.3	2.4	2.5	2.7	2.8	2.9	3.0	3.0	3.0
77.5°	2.0	2.2	2.3	2.4	2.6	2.7	2.8	3.0	3.0	3.0	3.0
80°	2.1	2.2	2.3	2.5	2.6	2.7	2.9	3.0	3.0	3.0	3.1
82.5°	2.1	2.2	2.3	2.5	2.6	2.8	2.9	3.0	3.1	3.1	3.1
85°	2.1	2.2	2.4	2.5	2.6	2.8	2.9	3.0	3.1	3.1	3.1
87.5°	2.1	2.2	2.4	2.5	2.6	2.8	2.9	3.1	3.1	3.1	3.1
90°	2.1	2.2	2.4	2.5	2.6	2.8	2.9	3.1	3.1	3.1	3.1
92.5°	2.1	2.2	2.3	2.5	2.6	2.8	2.9	3.0	3.1	3.1	3.1
95°	2.0	2.2	2.3	2.5	2.6	2.7	2.9	3.0	3.0	3.1	3.1
97.5°	2.0	2.2	2.3	2.4	2.6	2.7	2.8	3.0	3.0	3.0	3.0
100°	2.0	2.1	2.3	2.4	2.5	2.7	2.8	2.9	3.0	3.0	3.0
102.5°	2.0	2.1	2.2	2.4	2.5	2.6	2.8	2.9	2.9	2.9	3.0
105°	1.9	2.1	2.2	2.3	2.4	2.6	2.7	2.8	2.9	2.9	2.9
107.5°	1.9	2.0	2.1	2.3	2.4	2.5	2.6	2.8	2.8	2.8	2.8
110°	1.8	2.0	2.1	2.2	2.3	2.5	2.6	2.7	2.7	2.7	2.8

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	1.8	1.9	2.0	2.1	2.3	2.4	2.5	2.6	2.6	2.7	2.7
115°	1.7	1.8	2.0	2.1	2.2	2.3	2.4	2.5	2.6	2.6	2.6
117.5°	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.5	2.5	2.5	2.5
120°	1.6	1.7	1.8	1.9	2.0	2.1	2.2	2.4	2.4	2.4	2.4
122.5°	1.5	1.6	1.7	1.8	1.9	2.0	2.2	2.3	2.3	2.3	2.3
125°	1.5	1.6	1.7	1.8	1.9	2.0	2.1	2.2	2.2	2.2	2.2
127.5°	1.4	1.5	1.6	1.7	1.8	1.9	1.9	2.0	2.1	2.1	2.1
130°	1.3	1.4	1.5	1.6	1.7	1.8	1.8	1.9	2.0	2.0	2.0
132.5°	1.2	1.3	1.4	1.5	1.6	1.7	1.7	1.8	1.8	1.9	1.9
135°	1.2	1.2	1.3	1.4	1.5	1.5	1.6	1.7	1.7	1.7	1.8
137.5°	1.1	1.1	1.2	1.3	1.4	1.4	1.5	1.6	1.6	1.6	1.6
140°	1.0	1.1	1.1	1.2	1.3	1.3	1.4	1.5	1.5	1.5	1.5
142.5°	0.9	1.0	1.0	1.1	1.2	1.2	1.3	1.4	1.4	1.4	1.4
145°	0.8	0.9	0.9	1.0	1.1	1.1	1.2	1.2	1.3	1.3	1.3
147.5°	0.8	0.8	0.9	0.9	1.0	1.0	1.1	1.1	1.1	1.1	1.2
150°	0.7	0.7	0.8	0.8	0.9	0.9	1.0	1.0	1.0	1.0	1.0
152.5°	0.6	0.6	0.7	0.7	0.8	0.8	0.8	0.9	0.9	0.9	0.9
155°	0.5	0.5	0.6	0.6	0.7	0.7	0.7	0.8	0.8	0.8	0.8
157.5°	0.4	0.4	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6	0.6
160°	0.3	0.3	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5	0.5
162.5°	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4
165°	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3
167.5°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
170°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
10°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1
12.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2
15°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3	0.3
17.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.4
20°	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6	0.6
22.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
25°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.8	0.8	0.8
27.5°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	0.9
30°	1.1	1.1	1.1	1.1	1.1	1.2	1.1	1.1	1.1	1.1	1.1
32.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.2	1.2	1.2
35°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.3	1.3
37.5°	1.5	1.5	1.5	1.5	1.6	1.6	1.5	1.5	1.5	1.5	1.5
40°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.6	1.6	1.6	1.6
42.5°	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.8	1.7	1.7
45°	1.9	1.9	1.9	1.9	1.9	2.0	1.9	1.9	1.9	1.9	1.8
47.5°	2.0	2.0	2.0	2.1	2.1	2.1	2.0	2.0	2.0	2.0	1.9
50°	2.1	2.2	2.2	2.2	2.2	2.2	2.2	2.1	2.1	2.1	2.1
52.5°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.2	2.2	2.2
55°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.3	2.3	2.3
57.5°	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.4	2.4	2.4
60°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.5	2.5	2.5
62.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.6	2.6	2.6
65°	2.7	2.8	2.8	2.8	2.8	2.8	2.8	2.7	2.7	2.7	2.7
67.5°	2.8	2.8	2.8	2.9	2.9	2.9	2.9	2.8	2.8	2.8	2.7
70°	2.9	2.9	2.9	2.9	3.0	3.0	2.9	2.9	2.9	2.8	2.8
72.5°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.9	2.9	2.9
75°	3.0	3.0	3.0	3.1	3.1	3.1	3.1	3.0	3.0	3.0	2.9
77.5°	3.0	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.0	3.0	3.0
80°	3.1	3.1	3.1	3.1	3.2	3.2	3.1	3.1	3.1	3.0	3.0
82.5°	3.1	3.1	3.1	3.2	3.2	3.2	3.2	3.1	3.1	3.1	3.0
85°	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.0
87.5°	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.1
90°	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.1
92.5°	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.1	3.1	3.1
95°	3.1	3.1	3.1	3.2	3.2	3.2	3.2	3.1	3.1	3.1	3.0
97.5°	3.1	3.1	3.1	3.1	3.1	3.2	3.1	3.1	3.1	3.0	3.0
100°	3.0	3.0	3.1	3.1	3.1	3.1	3.1	3.1	3.0	3.0	3.0
102.5°	3.0	3.0	3.0	3.0	3.1	3.1	3.1	3.0	3.0	3.0	2.9
105°	2.9	2.9	3.0	3.0	3.0	3.0	3.0	3.0	2.9	2.9	2.9
107.5°	2.9	2.9	2.9	2.9	2.9	3.0	2.9	2.9	2.9	2.8	2.8
110°	2.8	2.8	2.8	2.8	2.9	2.9	2.9	2.8	2.8	2.8	2.7

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	2.7	2.7	2.7	2.8	2.8	2.8	2.8	2.8	2.7	2.7	2.7
115°	2.6	2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.6	2.6	2.6
117.5°	2.5	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.5	2.5
120°	2.4	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.5	2.4	2.4
122.5°	2.3	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.3	2.3
125°	2.2	2.2	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.2	2.2
127.5°	2.1	2.1	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.1	2.1
130°	2.0	2.0	2.0	2.1	2.1	2.1	2.1	2.1	2.0	2.0	2.0
132.5°	1.9	1.9	1.9	1.9	2.0	2.0	2.0	2.0	1.9	1.9	1.9
135°	1.8	1.8	1.8	1.8	1.8	1.9	1.8	1.8	1.8	1.8	1.8
137.5°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
140°	1.5	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
142.5°	1.4	1.4	1.4	1.5	1.5	1.5	1.5	1.5	1.5	1.4	1.4
145°	1.3	1.3	1.3	1.3	1.3	1.4	1.3	1.3	1.3	1.3	1.3
147.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.2
150°	1.0	1.0	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.0
152.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
155°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
157.5°	0.6	0.6	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
160°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
162.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
165°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
167.5°	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
170°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
2.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
7.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0
10°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
12.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1
15°	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2
17.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.2
20°	0.5	0.5	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.3	0.3
22.5°	0.7	0.7	0.6	0.6	0.6	0.6	0.5	0.5	0.5	0.4	0.4
25°	0.8	0.8	0.8	0.8	0.7	0.7	0.6	0.6	0.5	0.5	0.5
27.5°	0.9	0.9	0.9	0.9	0.8	0.8	0.7	0.7	0.6	0.6	0.5
30°	1.1	1.0	1.0	1.0	1.0	0.9	0.8	0.8	0.7	0.7	0.6
32.5°	1.2	1.2	1.1	1.1	1.1	1.0	0.9	0.9	0.8	0.8	0.7
35°	1.3	1.3	1.3	1.3	1.2	1.1	1.0	1.0	0.9	0.8	0.8
37.5°	1.4	1.4	1.4	1.4	1.3	1.2	1.2	1.1	1.0	0.9	0.8
40°	1.6	1.5	1.5	1.5	1.4	1.3	1.3	1.2	1.1	1.0	0.9
42.5°	1.7	1.7	1.6	1.6	1.5	1.4	1.4	1.3	1.2	1.1	1.0
45°	1.8	1.8	1.8	1.7	1.6	1.5	1.5	1.4	1.3	1.2	1.1
47.5°	1.9	1.9	1.9	1.8	1.7	1.6	1.5	1.4	1.3	1.2	1.1
50°	2.0	2.0	2.0	2.0	1.9	1.7	1.6	1.5	1.4	1.3	1.2
52.5°	2.1	2.1	2.1	2.1	2.0	1.8	1.7	1.6	1.5	1.4	1.3
55°	2.3	2.2	2.2	2.2	2.0	1.9	1.8	1.7	1.6	1.5	1.3
57.5°	2.4	2.3	2.3	2.3	2.1	2.0	1.9	1.8	1.7	1.5	1.4
60°	2.4	2.4	2.4	2.4	2.2	2.1	2.0	1.8	1.7	1.6	1.5
62.5°	2.5	2.5	2.5	2.4	2.3	2.2	2.0	1.9	1.8	1.7	1.5
65°	2.6	2.6	2.6	2.5	2.4	2.3	2.1	2.0	1.8	1.7	1.6
67.5°	2.7	2.7	2.6	2.6	2.5	2.3	2.2	2.0	1.9	1.8	1.6
70°	2.8	2.7	2.7	2.7	2.5	2.4	2.2	2.1	2.0	1.8	1.7
72.5°	2.8	2.8	2.8	2.7	2.6	2.4	2.3	2.1	2.0	1.9	1.7
75°	2.9	2.8	2.8	2.8	2.6	2.5	2.3	2.2	2.0	1.9	1.7
77.5°	2.9	2.9	2.9	2.8	2.7	2.5	2.4	2.2	2.1	1.9	1.8
80°	3.0	2.9	2.9	2.9	2.7	2.6	2.4	2.3	2.1	2.0	1.8
82.5°	3.0	3.0	2.9	2.9	2.7	2.6	2.4	2.3	2.1	2.0	1.8
85°	3.0	3.0	2.9	2.9	2.8	2.6	2.4	2.3	2.1	2.0	1.8
87.5°	3.0	3.0	3.0	2.9	2.8	2.6	2.5	2.3	2.1	2.0	1.8
90°	3.0	3.0	3.0	2.9	2.8	2.6	2.5	2.3	2.2	2.0	1.8
92.5°	3.0	3.0	3.0	2.9	2.8	2.6	2.5	2.3	2.1	2.0	1.8
95°	3.0	3.0	2.9	2.9	2.7	2.6	2.4	2.3	2.1	2.0	1.8
97.5°	3.0	2.9	2.9	2.9	2.7	2.6	2.4	2.3	2.1	2.0	1.8
100°	2.9	2.9	2.9	2.8	2.7	2.5	2.4	2.2	2.1	1.9	1.8
102.5°	2.9	2.9	2.8	2.8	2.7	2.5	2.4	2.2	2.1	1.9	1.8
105°	2.8	2.8	2.8	2.8	2.6	2.5	2.3	2.2	2.0	1.9	1.7
107.5°	2.8	2.8	2.7	2.7	2.6	2.4	2.3	2.1	2.0	1.8	1.7
110°	2.7	2.7	2.7	2.6	2.5	2.4	2.2	2.1	1.9	1.8	1.7

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	2.6	2.6	2.6	2.6	2.4	2.3	2.2	2.0	1.9	1.8	1.6
115°	2.6	2.5	2.5	2.5	2.4	2.2	2.1	2.0	1.8	1.7	1.6
117.5°	2.5	2.5	2.4	2.4	2.3	2.2	2.0	1.9	1.8	1.7	1.5
120°	2.4	2.4	2.3	2.3	2.2	2.1	2.0	1.8	1.7	1.6	1.5
122.5°	2.3	2.3	2.3	2.2	2.1	2.0	1.9	1.8	1.6	1.5	1.4
125°	2.2	2.2	2.2	2.1	2.0	1.9	1.8	1.7	1.6	1.5	1.4
127.5°	2.1	2.1	2.1	2.0	1.9	1.8	1.7	1.6	1.5	1.4	1.3
130°	2.0	2.0	2.0	1.9	1.8	1.7	1.6	1.5	1.4	1.3	1.2
132.5°	1.9	1.9	1.8	1.8	1.7	1.6	1.5	1.5	1.4	1.3	1.2
135°	1.8	1.8	1.7	1.7	1.6	1.5	1.5	1.4	1.3	1.2	1.1
137.5°	1.7	1.6	1.6	1.6	1.5	1.4	1.4	1.3	1.2	1.1	1.0
140°	1.5	1.5	1.5	1.5	1.4	1.3	1.3	1.2	1.1	1.0	1.0
142.5°	1.4	1.4	1.4	1.4	1.3	1.2	1.2	1.1	1.0	1.0	0.9
145°	1.3	1.3	1.3	1.3	1.2	1.1	1.1	1.0	0.9	0.9	0.8
147.5°	1.2	1.2	1.2	1.1	1.1	1.0	1.0	0.9	0.9	0.8	0.7
150°	1.0	1.0	1.0	1.0	1.0	0.9	0.9	0.8	0.8	0.7	0.7
152.5°	0.9	0.9	0.9	0.9	0.8	0.8	0.8	0.7	0.7	0.6	0.6
155°	0.8	0.8	0.8	0.8	0.7	0.7	0.7	0.6	0.6	0.6	0.5
157.5°	0.7	0.7	0.7	0.7	0.6	0.6	0.6	0.5	0.5	0.5	0.4
160°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.4
162.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3	0.3
165°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.2
167.5°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2
170°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	0.0	0.0
2.5°	0.0	0.0
5°	0.0	0.0
7.5°	0.0	0.0
10°	0.1	0.0
12.5°	0.1	0.1
15°	0.1	0.1
17.5°	0.2	0.2
20°	0.3	0.2
22.5°	0.3	0.3
25°	0.4	0.4
27.5°	0.5	0.4
30°	0.6	0.5
32.5°	0.6	0.6
35°	0.7	0.6
37.5°	0.8	0.7
40°	0.8	0.8
42.5°	0.9	0.8
45°	1.0	0.9
47.5°	1.0	0.9
50°	1.1	1.0
52.5°	1.2	1.1
55°	1.2	1.1
57.5°	1.3	1.2
60°	1.3	1.2
62.5°	1.4	1.3
65°	1.4	1.3
67.5°	1.5	1.3
70°	1.5	1.4
72.5°	1.6	1.4
75°	1.6	1.4
77.5°	1.6	1.5
80°	1.6	1.5
82.5°	1.7	1.5
85°	1.7	1.5
87.5°	1.7	1.5
90°	1.7	1.5
92.5°	1.7	1.5
95°	1.7	1.5
97.5°	1.7	1.5
100°	1.6	1.5
102.5°	1.6	1.5
105°	1.6	1.5
107.5°	1.6	1.4
110°	1.5	1.4

REPORT NUMBER: P600777
 CATALOG NUMBER: FE10A35GLMB-NL

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	1.5	1.4
115°	1.4	1.3
117.5°	1.4	1.3
120°	1.4	1.2
122.5°	1.3	1.2
125°	1.2	1.1
127.5°	1.2	1.1
130°	1.1	1.0
132.5°	1.1	1.0
135°	1.0	0.9
137.5°	0.9	0.9
140°	0.9	0.8
142.5°	0.8	0.7
145°	0.8	0.7
147.5°	0.7	0.6
150°	0.6	0.6
152.5°	0.5	0.5
155°	0.5	0.4
157.5°	0.4	0.4
160°	0.3	0.3
162.5°	0.3	0.3
165°	0.2	0.2
167.5°	0.2	0.2
170°	0.1	0.1
172.5°	0.1	0.1
175°	0.0	0.0
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)