

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210366

Luminaire Tested: **PR8R15D010 - PR8M12WDMW - 4000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P210366  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR8R15D010 - PR8M12WDMW - 4000K  
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE WHITE FINISH  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1683.8 lumens  
Efficiency: N/A  
Efficacy: 112.3 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 15  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210366

CATALOG NUMBER: PR8R15D010 - PR8M12WDMW - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P210366

CATALOG NUMBER: PR8R15D010 - PR8M12WDMW - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	20429
5°	20770
10°	21023
15°	21411
20°	21862
25°	22061
30°	22030
35°	21973
40°	21210
45°	19424
50°	16229
55°	13494
60°	11342
65°	9369
70°	8060
75°	6326
80°	4386
85°	4599



TEST NUMBER: P210366

CATALOG NUMBER: PR8R15D010 - PR8M12WDMW - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	63.9	3.8
10°-20°	189.8	11.3
20°-30°	298.0	17.7
30°-40°	363.3	21.6
40°-50°	339.6	20.2
50°-60°	226.5	13.5
60°-70°	130.3	7.7
70°-80°	60.1	3.6
80°-90°	12.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	551.7	32.8
0°-40°	915.1	54.3
0°-60°	1481.2	88.0
0°-90°	1683.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1683.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	662	
5°	671	64
15°	671	190
25°	648	298
35°	584	363
45°	445	340
55°	251	227
65°	128	130
75°	53	60
85°	13	12
90°	0	



TEST NUMBER: P210366

CATALOG NUMBER: PR8R15D010 - PR8M12WDMW - 4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	662.5
2.5°	663.5
5°	671.0
7.5°	670.4
10°	671.4
12.5°	670.0
15°	670.7
17.5°	669.3
20°	666.2
22.5°	655.3
25°	648.4
27.5°	634.7
30°	618.7
32.5°	602.6
35°	583.7
37.5°	561.1
40°	526.9
42.5°	489.6
45°	445.4
47.5°	396.5
50°	338.3
52.5°	289.0
55°	251.0
57.5°	214.7
60°	183.9
62.5°	157.1
65°	128.4
67.5°	105.4
70°	89.4
72.5°	76.0
75°	53.1
77.5°	42.1
80°	24.7
82.5°	15.7
85°	13.0
87.5°	3.8
90°	0.0

(END OF REPORT)