

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210385

Luminaire Tested: **PR8R20D010 - PR8M12WDMB - 3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210385
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8R20D010 - PR8M12WDMB - 3500K
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE BLACK FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2227.1 lumens
Efficiency: N/A
Efficacy: 101.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210385

CATALOG NUMBER: PR8R20D010 - PR8M12WDMB - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P210385

CATALOG NUMBER: PR8R20D010 - PR8M12WDMB - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	27022
5°	27475
10°	27808
15°	28323
20°	28920
25°	29182
30°	29137
35°	29065
40°	28057
45°	25695
50°	21463
55°	17843
60°	14999
65°	12389
70°	10657
75°	8364
80°	5789
85°	6085



TEST NUMBER: P210385

CATALOG NUMBER: PR8R20D010 - PR8M12WDMB - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	84.6	3.8
10°-20°	251.0	11.3
20°-30°	394.2	17.7
30°-40°	480.6	21.6
40°-50°	449.2	20.2
50°-60°	299.6	13.5
60°-70°	172.4	7.7
70°-80°	79.5	3.6
80°-90°	16.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	729.8	32.8
0°-40°	1210.4	54.3
0°-60°	1959.1	88.0
0°-90°	2227.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2227.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	876	
5°	888	85
15°	887	251
25°	858	394
35°	772	481
45°	589	449
55°	332	300
65°	170	172
75°	70	79
85°	17	16
90°	0	



TEST NUMBER: P210385

CATALOG NUMBER: PR8R20D010 - PR8M12WDMB - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	876.3
2.5°	877.6
5°	887.6
7.5°	886.7
10°	888.1
12.5°	886.3
15°	887.2
17.5°	885.3
20°	881.3
22.5°	866.8
25°	857.7
27.5°	839.6
30°	818.3
32.5°	797.0
35°	772.1
37.5°	742.2
40°	697.0
42.5°	647.6
45°	589.2
47.5°	524.4
50°	447.4
52.5°	382.2
55°	331.9
57.5°	283.9
60°	243.2
62.5°	207.9
65°	169.8
67.5°	139.5
70°	118.2
72.5°	100.5
75°	70.2
77.5°	55.7
80°	32.6
82.5°	20.8
85°	17.2
87.5°	5.0
90°	0.0

(END OF REPORT)