

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P600778

Luminaire Tested: **FE10A35GLMW**

Issue Date: 07/11/2022

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P600778
 Test Lab: Third Party
 Issue Date: 07/11/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: FE10A35GLMW
 Description: LED Entry Light w/ Night Light - White 3500K (Main)
 Light Source: 70 CRI LEDs
 Ballast/Driver: (1) Electronic Driver

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 1122.1 lumens
 Efficiency: N/A
 Efficacy: 110.3 lumens/watt
 Luminous Opening: Point Source (0m x 0m x 0m)
 IES Classification: Type IV - Short
 BUG Rating: B0 - U3 - G1


Input Watts (W): 10.1714
 Input Voltage (V): 120.0
 Input Current (Ain): 0.085
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

Iso-Footcandle Lines of Horizontal Illumination


✕ Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 1 fc
 Type IV - Short - N/A

REPORT NUMBER: P600778
CATALOG NUMBER: FE10A35GLMW

Luminous Intensity Polar Plot



— Vertical Plane Through 45-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	315.7	105.6	421.3
	% Fixture	28.1	9.4	37.5
Street Side	Lumens	457.8	243.0	700.8
	% Fixture	40.8	21.7	62.5
Total	Lumens	773.5	348.6	1122.1
	% Fixture	68.9	31.1	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	9.7	0.9
10°-20°	32.3	2.9
20°-30°	58.4	5.2
30°-40°	83.5	7.4
40°-50°	104.3	9.3
50°-60°	119.3	10.6
60°-70°	126.6	11.3
70°-80°	124.7	11.1
80°-90°	114.7	10.2
90°-100°	100.0	8.9
100°-110°	83.0	7.4
110°-120°	64.5	5.7
120°-130°	46.2	4.1
130°-140°	29.7	2.6
140°-150°	16.3	1.5
150°-160°	7.0	0.6
160°-170°	1.7	0.2
170°-180°	0.1	0.0
0°-90°	773.5	68.9
0°-180°	1122.1	100.0




REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	51.5	4.6			
FM (30°-60°)	176.1	15.7			
FH (60°-80°)	155.8	13.9			G0/660
FVH (80°-90°)	74.4	6.6			G1/100
BL (0°-30°)	49.0	4.4	B0/110		
BM (30°-60°)	131.0	11.7	B0/220		
BH (60°-80°)	95.5	8.5	B0/110		G0/110
BVH (80°-90°)	40.3	3.6			G1/100
UL (90°-100°)	100.0	8.9		U3/500	
UH (100°-180°)	248.6	22.2		U3/500	

BUG Rating: B0-U3-G1
 Type IV Short



REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	99.3	99.2	99.0	98.9	98.7	98.6	98.4	98.3	98.2	98.0	98.0
5°	99.8	99.9	99.9	99.9	100.0	100.0	100.0	100.1	100.1	100.2	99.8
7.5°	102.4	102.4	102.4	102.3	102.3	102.3	102.3	102.3	102.3	102.3	102.1
10°	105.3	105.3	105.4	105.4	105.4	105.5	105.5	105.6	105.6	105.7	105.5
12.5°	110.1	110.0	109.9	109.8	109.7	109.6	109.5	109.3	109.2	109.1	109.0
15°	113.5	113.5	113.5	113.5	113.6	113.6	113.6	113.6	113.7	113.7	113.6
17.5°	118.5	118.5	118.4	118.4	118.4	118.4	118.4	118.3	118.3	118.3	118.1
20°	123.1	123.3	123.4	123.6	123.7	123.9	124.0	124.2	124.3	124.5	124.3
22.5°	127.9	127.7	127.5	127.3	127.1	126.9	126.6	126.4	126.2	126.0	126.0
25°	131.5	131.5	131.6	131.7	131.8	131.9	132.0	132.0	132.1	132.2	132.0
27.5°	136.4	136.3	136.2	136.1	136.0	136.0	135.9	135.8	135.7	135.6	135.6
30°	138.5	138.6	138.8	139.0	139.1	139.3	139.4	139.6	139.8	139.9	140.0
32.5°	142.3	142.5	142.6	142.8	143.0	143.1	143.3	143.4	143.6	143.8	143.7
35°	147.0	147.0	147.0	147.1	147.1	147.1	147.2	147.2	147.3	147.3	147.2
37.5°	147.0	147.1	147.3	147.4	147.6	147.8	147.9	148.1	148.3	148.4	148.7
40°	149.0	149.4	149.7	150.1	150.4	150.8	151.1	151.5	151.8	152.2	152.5
42.5°	150.2	150.6	150.9	151.3	151.6	152.0	152.3	152.7	153.0	153.4	153.7
45°	152.2	152.5	152.8	153.1	153.4	153.7	154.0	154.4	154.7	155.0	155.4
47.5°	153.8	154.2	154.6	155.0	155.4	155.8	156.2	156.5	156.9	157.3	157.7
50°	153.5	154.0	154.4	154.8	155.2	155.6	156.1	156.5	156.9	157.3	157.9
52.5°	153.5	154.1	154.8	155.4	156.1	156.7	157.4	158.0	158.7	159.4	159.8
55°	154.2	154.7	155.2	155.7	156.2	156.7	157.2	157.6	158.1	158.6	159.4
57.5°	153.6	154.2	154.8	155.4	156.0	156.6	157.2	157.8	158.5	159.1	159.6
60°	153.0	153.7	154.3	155.0	155.7	156.3	157.0	157.7	158.3	159.0	159.6
62.5°	156.8	157.0	157.2	157.3	157.5	157.7	157.9	158.1	158.2	158.4	159.0
65°	152.4	153.0	153.7	154.4	155.1	155.8	156.4	157.1	157.8	158.5	159.0
67.5°	152.4	153.0	153.6	154.1	154.7	155.3	155.9	156.5	157.0	157.6	158.1
70°	150.0	150.7	151.4	152.1	152.9	153.6	154.3	155.0	155.7	156.4	156.9
72.5°	146.2	147.0	147.9	148.7	149.5	150.4	151.2	152.0	152.9	153.7	154.3
75°	146.7	147.2	147.8	148.4	148.9	149.5	150.1	150.6	151.2	151.7	152.3
77.5°	145.1	145.6	146.0	146.5	146.9	147.3	147.8	148.2	148.7	149.1	149.6
80°	141.6	142.2	142.7	143.3	143.8	144.3	144.9	145.4	145.9	146.5	146.9
82.5°	139.3	139.7	140.2	140.6	141.1	141.5	142.0	142.4	142.9	143.3	143.8
85°	135.6	136.1	136.7	137.3	137.9	138.4	139.0	139.6	140.2	140.8	141.2
87.5°	132.4	133.0	133.6	134.2	134.8	135.4	136.1	136.7	137.3	137.9	138.2
90°	127.7	128.5	129.3	130.0	130.8	131.5	132.3	133.1	133.8	134.6	134.9
92.5°	125.4	126.0	126.6	127.1	127.7	128.3	128.9	129.5	130.0	130.6	131.0
95°	121.2	121.8	122.3	122.9	123.4	124.0	124.5	125.1	125.7	126.2	126.6
97.5°	117.6	118.2	118.9	119.5	120.2	120.8	121.5	122.1	122.8	123.4	123.7
100°	114.7	115.2	115.8	116.4	117.0	117.5	118.1	118.7	119.2	119.8	120.1
102.5°	111.4	111.9	112.5	113.0	113.6	114.1	114.6	115.2	115.7	116.3	116.5
105°	108.0	108.5	109.0	109.5	110.0	110.5	111.0	111.5	112.1	112.6	112.8
107.5°	103.8	104.3	104.8	105.3	105.9	106.4	106.9	107.4	107.9	108.4	108.7
110°	99.9	100.4	101.0	101.6	102.1	102.7	103.2	103.8	104.3	104.9	105.1

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	97.0	97.4	97.7	98.1	98.4	98.8	99.2	99.5	99.9	100.2	100.4
115°	91.5	92.1	92.7	93.2	93.8	94.4	94.9	95.5	96.0	96.6	96.7
117.5°	87.5	88.0	88.5	89.0	89.5	90.0	90.5	91.0	91.5	92.0	92.1
120°	83.9	84.3	84.8	85.2	85.6	86.0	86.5	86.9	87.3	87.8	87.8
122.5°	79.5	80.0	80.4	80.9	81.3	81.7	82.2	82.6	83.1	83.5	83.5
125°	75.2	75.6	76.0	76.4	76.8	77.2	77.6	78.0	78.4	78.8	78.8
127.5°	70.6	71.0	71.4	71.7	72.1	72.5	72.9	73.3	73.7	74.1	74.0
130°	66.9	67.2	67.4	67.6	67.9	68.1	68.4	68.6	68.9	69.1	69.1
132.5°	62.2	62.5	62.8	63.0	63.3	63.6	63.8	64.1	64.4	64.6	64.6
135°	57.9	58.1	58.4	58.6	58.9	59.1	59.3	59.6	59.8	60.0	60.0
137.5°	53.6	53.8	54.0	54.2	54.5	54.7	54.9	55.1	55.3	55.6	55.5
140°	49.4	49.6	49.7	49.9	50.1	50.2	50.4	50.6	50.7	50.9	50.8
142.5°	45.2	45.4	45.5	45.7	45.8	46.0	46.2	46.3	46.5	46.7	46.5
145°	41.1	41.2	41.3	41.4	41.5	41.5	41.6	41.7	41.8	41.9	41.8
147.5°	36.7	36.8	36.9	37.0	37.1	37.2	37.3	37.4	37.5	37.6	37.5
150°	32.7	32.7	32.8	32.9	32.9	33.0	33.1	33.1	33.2	33.3	33.2
152.5°	28.7	28.7	28.8	28.9	28.9	29.0	29.1	29.2	29.2	29.3	29.2
155°	24.8	24.8	24.8	24.9	24.9	24.9	24.9	25.0	25.0	25.0	25.0
157.5°	21.0	21.0	21.0	21.0	21.0	21.0	21.1	21.1	21.1	21.1	21.1
160°	16.9	16.9	17.0	17.0	17.1	17.1	17.2	17.2	17.3	17.3	17.3
162.5°	13.5	13.5	13.5	13.6	13.6	13.6	13.7	13.7	13.7	13.8	13.7
165°	10.5	10.5	10.5	10.4	10.4	10.4	10.3	10.3	10.3	10.3	10.2
167.5°	6.9	6.9	6.9	6.9	6.9	6.9	7.0	7.0	7.0	7.0	7.0
170°	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3	4.3
172.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.1
175°	1.0	1.0	0.9	0.9	0.9	0.9	0.8	0.8	0.8	0.8	0.8
177.5°	1.1	1.0	1.0	0.9	0.9	0.8	0.8	0.7	0.7	0.6	0.6
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	97.9	97.9	97.9	97.8	97.8	97.7	97.7	97.7	97.6	97.5	97.4
5°	99.5	99.2	98.9	98.6	98.3	98.0	97.7	97.4	97.4	97.4	97.5
7.5°	102.0	101.9	101.7	101.6	101.5	101.4	101.2	101.1	101.0	100.8	100.7
10°	105.3	105.1	104.8	104.6	104.4	104.2	104.0	103.8	103.8	103.7	103.7
12.5°	108.9	108.7	108.6	108.5	108.3	108.2	108.1	107.9	107.8	107.6	107.4
15°	113.4	113.3	113.1	113.0	112.9	112.7	112.6	112.5	112.4	112.3	112.2
17.5°	117.9	117.6	117.4	117.2	117.0	116.8	116.6	116.3	116.4	116.5	116.5
20°	124.0	123.8	123.6	123.4	123.2	123.0	122.7	122.5	122.3	122.1	121.8
22.5°	126.1	126.1	126.1	126.2	126.2	126.3	126.3	126.3	126.1	125.9	125.7
25°	131.9	131.7	131.6	131.4	131.2	131.1	130.9	130.8	130.5	130.2	130.0
27.5°	135.6	135.6	135.6	135.5	135.5	135.5	135.5	135.4	135.1	134.8	134.5
30°	140.1	140.1	140.2	140.3	140.4	140.4	140.5	140.6	140.1	139.6	139.1
32.5°	143.7	143.7	143.7	143.7	143.6	143.6	143.6	143.6	143.1	142.5	142.0
35°	147.2	147.1	147.0	147.0	146.9	146.9	146.8	146.7	146.3	145.8	145.3
37.5°	149.0	149.3	149.6	149.9	150.2	150.5	150.8	151.1	150.5	150.0	149.5
40°	152.7	153.0	153.3	153.5	153.8	154.1	154.4	154.6	154.0	153.4	152.8
42.5°	154.0	154.2	154.5	154.8	155.1	155.4	155.6	155.9	155.4	154.9	154.4
45°	155.8	156.2	156.6	157.0	157.4	157.8	158.2	158.6	158.1	157.7	157.2
47.5°	158.1	158.6	159.0	159.4	159.8	160.2	160.7	161.1	160.4	159.8	159.1
50°	158.4	159.0	159.5	160.1	160.7	161.2	161.8	162.3	161.8	161.2	160.6
52.5°	160.3	160.7	161.2	161.7	162.1	162.6	163.1	163.5	163.0	162.4	161.8
55°	160.1	160.9	161.6	162.4	163.1	163.9	164.6	165.4	164.6	163.8	162.9
57.5°	160.2	160.7	161.3	161.8	162.3	162.9	163.4	164.0	163.3	162.7	162.1
60°	160.1	160.7	161.3	161.8	162.4	163.0	163.6	164.1	163.5	162.9	162.3
62.5°	159.5	160.0	160.6	161.1	161.7	162.2	162.8	163.3	162.7	162.0	161.3
65°	159.5	160.0	160.5	161.0	161.5	162.0	162.5	163.0	162.4	161.7	161.1
67.5°	158.5	159.0	159.4	159.8	160.3	160.7	161.2	161.6	160.9	160.2	159.4
70°	157.4	157.9	158.4	158.9	159.5	160.0	160.5	161.0	160.2	159.3	158.5
72.5°	155.0	155.6	156.3	156.9	157.6	158.2	158.9	159.5	158.7	157.8	156.9
75°	152.8	153.3	153.8	154.4	154.9	155.4	155.9	156.5	155.6	154.8	153.9
77.5°	150.1	150.6	151.0	151.5	152.0	152.5	153.0	153.5	152.6	151.7	150.9
80°	147.4	147.8	148.3	148.7	149.2	149.6	150.1	150.5	149.6	148.7	147.7
82.5°	144.3	144.8	145.3	145.8	146.2	146.7	147.2	147.7	146.7	145.7	144.7
85°	141.6	142.0	142.3	142.7	143.1	143.5	143.9	144.3	143.4	142.5	141.7
87.5°	138.5	138.8	139.1	139.4	139.8	140.1	140.4	140.7	139.8	138.9	138.1
90°	135.1	135.4	135.7	136.0	136.3	136.5	136.8	137.1	136.3	135.5	134.7
92.5°	131.4	131.8	132.2	132.6	133.0	133.4	133.9	134.3	133.3	132.4	131.4
95°	127.1	127.5	127.9	128.4	128.8	129.2	129.7	130.1	129.2	128.2	127.3
97.5°	123.9	124.1	124.4	124.6	124.9	125.1	125.4	125.6	124.8	124.0	123.1
100°	120.4	120.8	121.1	121.4	121.7	122.1	122.4	122.7	121.8	120.8	119.8
102.5°	116.8	117.1	117.4	117.6	117.9	118.2	118.5	118.8	117.8	116.9	115.9
105°	113.1	113.3	113.6	113.8	114.1	114.3	114.5	114.8	113.8	112.9	111.9
107.5°	108.9	109.1	109.3	109.5	109.7	110.0	110.2	110.4	109.6	108.7	107.9
110°	105.3	105.5	105.7	105.9	106.1	106.3	106.5	106.8	105.9	105.0	104.1

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	100.6	100.8	101.0	101.2	101.4	101.6	101.8	102.0	101.1	100.3	99.4
115°	96.9	97.0	97.1	97.3	97.4	97.5	97.7	97.8	96.9	96.0	95.2
117.5°	92.2	92.3	92.4	92.5	92.6	92.6	92.7	92.8	92.0	91.2	90.4
120°	87.9	87.9	88.0	88.0	88.1	88.1	88.2	88.2	87.4	86.6	85.8
122.5°	83.5	83.4	83.4	83.4	83.4	83.3	83.3	83.3	82.5	81.7	81.0
125°	78.7	78.7	78.7	78.7	78.6	78.6	78.6	78.6	77.8	77.0	76.2
127.5°	74.0	74.0	73.9	73.9	73.9	73.8	73.8	73.8	73.0	72.3	71.5
130°	69.1	69.1	69.1	69.1	69.1	69.1	69.1	69.1	68.4	67.7	66.9
132.5°	64.5	64.4	64.3	64.2	64.2	64.1	64.0	63.9	63.3	62.6	62.0
135°	59.9	59.8	59.7	59.7	59.6	59.5	59.5	59.4	58.8	58.2	57.6
137.5°	55.4	55.2	55.1	55.0	54.9	54.8	54.7	54.6	54.1	53.5	52.9
140°	50.7	50.6	50.6	50.5	50.4	50.3	50.2	50.1	49.6	49.1	48.6
142.5°	46.4	46.3	46.2	46.1	45.9	45.8	45.7	45.6	45.1	44.6	44.2
145°	41.7	41.6	41.5	41.4	41.3	41.2	41.1	41.0	40.6	40.2	39.8
147.5°	37.4	37.3	37.3	37.2	37.1	37.0	36.9	36.9	36.5	36.2	35.8
150°	33.1	33.1	33.0	32.9	32.9	32.8	32.7	32.7	32.4	32.0	31.7
152.5°	29.1	29.0	28.9	28.8	28.7	28.6	28.5	28.4	28.1	27.8	27.6
155°	24.9	24.9	24.8	24.8	24.7	24.7	24.6	24.6	24.3	24.1	23.9
157.5°	21.0	21.0	21.0	20.9	20.9	20.9	20.8	20.8	20.7	20.5	20.3
160°	17.2	17.2	17.2	17.1	17.1	17.0	17.0	16.9	16.8	16.7	16.5
162.5°	13.7	13.7	13.6	13.6	13.5	13.5	13.5	13.4	13.3	13.2	13.1
165°	10.2	10.2	10.2	10.2	10.2	10.2	10.2	10.2	10.0	9.9	9.8
167.5°	7.0	7.0	7.0	7.0	7.0	6.9	6.9	6.9	6.9	6.8	6.7
170°	4.3	4.2	4.2	4.2	4.2	4.2	4.1	4.1	4.1	4.0	4.0
172.5°	2.1	2.1	2.1	2.1	2.1	2.0	2.0	2.0	2.0	2.0	2.0
175°	0.8	0.8	0.8	0.8	0.8	0.7	0.7	0.7	0.8	0.8	0.8
177.5°	0.6	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.7	0.8
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	97.3	97.2	97.1	97.0	96.9	96.8	97.0	97.2	97.5	97.7	97.9
5°	97.5	97.5	97.6	97.6	97.6	97.7	97.9	98.2	98.4	98.7	98.9
7.5°	100.5	100.4	100.2	100.1	99.9	99.8	100.0	100.3	100.5	100.8	101.0
10°	103.6	103.6	103.5	103.5	103.4	103.4	103.5	103.6	103.8	103.9	104.0
12.5°	107.2	107.1	106.9	106.7	106.6	106.4	106.6	106.9	107.1	107.3	107.6
15°	112.1	112.1	112.0	111.9	111.8	111.7	111.8	112.0	112.1	112.2	112.3
17.5°	116.6	116.6	116.7	116.8	116.8	116.9	117.1	117.3	117.5	117.6	117.8
20°	121.6	121.3	121.1	120.9	120.6	120.4	120.4	120.4	120.5	120.5	120.5
22.5°	125.4	125.2	125.0	124.7	124.5	124.3	124.3	124.4	124.4	124.5	124.5
25°	129.7	129.4	129.2	128.9	128.6	128.4	128.4	128.4	128.5	128.5	128.6
27.5°	134.1	133.8	133.5	133.1	132.8	132.5	132.5	132.5	132.5	132.5	132.5
30°	138.7	138.2	137.7	137.2	136.7	136.3	136.1	135.9	135.7	135.5	135.3
32.5°	141.5	140.9	140.4	139.9	139.3	138.8	138.7	138.6	138.5	138.5	138.4
35°	144.9	144.4	143.9	143.5	143.0	142.6	142.6	142.6	142.7	142.7	142.7
37.5°	149.0	148.5	147.9	147.4	146.9	146.4	146.2	146.0	145.8	145.6	145.4
40°	152.1	151.5	150.9	150.2	149.6	149.0	148.7	148.5	148.3	148.1	147.8
42.5°	153.9	153.4	152.9	152.4	151.8	151.3	150.9	150.5	150.2	149.8	149.4
45°	156.8	156.3	155.8	155.4	154.9	154.4	153.8	153.2	152.6	152.0	151.4
47.5°	158.5	157.8	157.2	156.5	155.8	155.2	154.5	153.9	153.2	152.6	152.0
50°	160.0	159.5	158.9	158.3	157.7	157.2	156.4	155.7	155.0	154.3	153.5
52.5°	161.2	160.7	160.1	159.5	159.0	158.4	157.5	156.7	155.8	154.9	154.1
55°	162.1	161.3	160.5	159.7	158.9	158.1	157.2	156.3	155.4	154.6	153.7
57.5°	161.4	160.8	160.1	159.5	158.9	158.2	157.3	156.4	155.4	154.5	153.6
60°	161.7	161.1	160.5	159.9	159.3	158.7	157.8	156.8	155.8	154.8	153.8
62.5°	160.7	160.0	159.4	158.7	158.1	157.4	156.5	155.5	154.6	153.6	152.7
65°	160.4	159.8	159.1	158.5	157.8	157.2	156.0	154.8	153.6	152.4	151.2
67.5°	158.7	158.0	157.2	156.5	155.8	155.0	153.8	152.5	151.3	150.0	148.8
70°	157.7	156.9	156.0	155.2	154.4	153.6	152.2	150.9	149.6	148.2	146.9
72.5°	156.1	155.2	154.3	153.4	152.6	151.7	150.3	148.8	147.4	145.9	144.5
75°	153.1	152.2	151.4	150.5	149.7	148.8	147.4	146.0	144.7	143.3	141.9
77.5°	150.0	149.2	148.3	147.5	146.6	145.7	144.4	143.0	141.6	140.2	138.8
80°	146.8	145.9	144.9	144.0	143.1	142.2	140.7	139.2	137.8	136.3	134.9
82.5°	143.6	142.6	141.6	140.6	139.6	138.6	137.1	135.7	134.3	132.8	131.4
85°	140.8	139.9	139.0	138.1	137.2	136.3	134.8	133.3	131.8	130.3	128.7
87.5°	137.2	136.4	135.5	134.6	133.8	132.9	131.2	129.5	127.9	126.2	124.5
90°	133.9	133.1	132.3	131.4	130.6	129.8	128.1	126.3	124.5	122.7	121.0
92.5°	130.5	129.6	128.6	127.7	126.7	125.8	124.0	122.3	120.6	118.8	117.1
95°	126.4	125.5	124.6	123.7	122.7	121.8	120.2	118.5	116.9	115.2	113.6
97.5°	122.3	121.5	120.7	119.8	119.0	118.2	116.6	114.9	113.3	111.7	110.1
100°	118.9	117.9	116.9	116.0	115.0	114.0	112.5	110.9	109.3	107.8	106.2
102.5°	115.0	114.1	113.1	112.2	111.3	110.3	108.8	107.4	105.9	104.4	103.0
105°	111.0	110.0	109.1	108.1	107.1	106.2	104.8	103.3	101.9	100.5	99.1
107.5°	107.0	106.2	105.3	104.5	103.6	102.8	101.3	99.9	98.4	97.0	95.5
110°	103.2	102.3	101.4	100.5	99.6	98.7	97.2	95.8	94.3	92.9	91.4



REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	98.5	97.7	96.8	96.0	95.1	94.3	92.9	91.6	90.2	88.8	87.5
115°	94.3	93.4	92.5	91.6	90.8	89.9	88.6	87.3	86.0	84.7	83.3
117.5°	89.6	88.8	88.0	87.2	86.4	85.6	84.3	83.0	81.7	80.4	79.2
120°	85.0	84.2	83.4	82.6	81.8	81.0	79.8	78.5	77.3	76.0	74.8
122.5°	80.2	79.4	78.6	77.9	77.1	76.3	75.2	74.1	72.9	71.8	70.6
125°	75.4	74.6	73.8	73.0	72.2	71.4	70.4	69.4	68.4	67.4	66.4
127.5°	70.8	70.0	69.3	68.5	67.8	67.0	66.0	65.0	64.1	63.1	62.1
130°	66.2	65.5	64.8	64.1	63.3	62.6	61.7	60.8	59.9	59.0	58.0
132.5°	61.4	60.7	60.1	59.5	58.8	58.2	57.3	56.4	55.6	54.7	53.8
135°	57.0	56.4	55.8	55.2	54.5	53.9	53.1	52.3	51.5	50.7	49.9
137.5°	52.4	51.8	51.2	50.6	50.1	49.5	48.8	48.0	47.3	46.6	45.8
140°	48.1	47.6	47.1	46.6	46.1	45.6	44.9	44.2	43.5	42.8	42.1
142.5°	43.7	43.2	42.8	42.3	41.8	41.4	40.7	40.1	39.4	38.8	38.2
145°	39.4	39.0	38.6	38.2	37.8	37.4	36.8	36.2	35.7	35.1	34.5
147.5°	35.5	35.1	34.8	34.4	34.1	33.7	33.2	32.6	32.0	31.5	30.9
150°	31.4	31.1	30.8	30.5	30.2	29.8	29.4	28.9	28.4	28.0	27.5
152.5°	27.3	27.1	26.8	26.5	26.3	26.0	25.6	25.2	24.8	24.4	24.1
155°	23.7	23.5	23.3	23.1	22.8	22.6	22.3	21.9	21.6	21.2	20.9
157.5°	20.2	20.0	19.9	19.7	19.5	19.4	19.0	18.7	18.4	18.0	17.7
160°	16.4	16.2	16.1	15.9	15.8	15.7	15.4	15.1	14.9	14.6	14.3
162.5°	12.9	12.8	12.7	12.6	12.4	12.3	12.1	11.9	11.6	11.4	11.2
165°	9.7	9.6	9.4	9.3	9.2	9.1	8.9	8.8	8.6	8.4	8.3
167.5°	6.7	6.6	6.5	6.4	6.4	6.3	6.2	6.1	6.1	6.0	5.9
170°	3.9	3.9	3.8	3.8	3.8	3.7	3.6	3.5	3.4	3.3	3.2
172.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.8	1.7	1.6	1.5	1.4
175°	0.8	0.9	0.9	0.9	0.9	1.0	1.0	0.9	0.9	0.9	0.9
177.5°	0.8	0.8	0.9	0.9	0.9	1.0	0.9	0.9	0.9	0.9	0.9
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	98.1	98.3	98.5	98.7	98.7	98.6	98.6	98.5	98.5	98.4	98.4
5°	99.2	99.5	99.7	100.0	99.7	99.5	99.3	99.1	98.8	98.6	98.4
7.5°	101.3	101.6	101.8	102.1	102.2	102.3	102.4	102.5	102.7	102.8	102.9
10°	104.1	104.3	104.4	104.5	104.7	104.8	105.0	105.1	105.3	105.4	105.6
12.5°	107.8	108.0	108.3	108.5	108.7	108.9	109.1	109.3	109.5	109.7	109.9
15°	112.4	112.5	112.6	112.8	112.8	112.9	113.0	113.1	113.2	113.2	113.3
17.5°	118.0	118.2	118.4	118.6	118.5	118.5	118.4	118.3	118.2	118.1	118.1
20°	120.6	120.6	120.6	120.6	120.8	120.9	121.0	121.1	121.2	121.3	121.5
22.5°	124.6	124.6	124.6	124.7	124.7	124.7	124.7	124.7	124.6	124.6	124.6
25°	128.6	128.7	128.7	128.7	128.4	128.1	127.8	127.5	127.2	126.9	126.5
27.5°	132.5	132.5	132.5	132.5	132.3	132.1	131.9	131.7	131.4	131.2	131.0
30°	135.1	135.0	134.8	134.6	134.4	134.2	134.0	133.8	133.6	133.4	133.2
32.5°	138.3	138.2	138.1	138.1	137.7	137.4	137.1	136.8	136.4	136.1	135.8
35°	142.8	142.8	142.8	142.9	142.5	142.0	141.6	141.2	140.8	140.4	140.0
37.5°	145.2	145.0	144.8	144.6	144.0	143.5	142.9	142.3	141.8	141.2	140.6
40°	147.6	147.4	147.2	146.9	146.3	145.7	145.1	144.4	143.8	143.2	142.6
42.5°	149.0	148.6	148.2	147.8	147.5	147.2	146.9	146.7	146.4	146.1	145.8
45°	150.8	150.2	149.6	149.0	148.4	147.8	147.2	146.6	146.0	145.3	144.7
47.5°	151.3	150.7	150.0	149.4	148.8	148.3	147.8	147.2	146.7	146.2	145.7
50°	152.8	152.1	151.4	150.6	149.9	149.2	148.6	147.9	147.2	146.5	145.8
52.5°	153.2	152.4	151.5	150.6	150.2	149.7	149.3	148.8	148.4	147.9	147.5
55°	152.8	151.9	151.0	150.2	149.4	148.6	147.9	147.1	146.3	145.5	144.8
57.5°	152.7	151.7	150.8	149.9	149.2	148.5	147.9	147.2	146.5	145.8	145.2
60°	152.8	151.8	150.9	149.9	149.1	148.3	147.6	146.8	146.0	145.3	144.5
62.5°	151.7	150.8	149.8	148.9	148.1	147.4	146.6	145.8	145.1	144.3	143.6
65°	150.0	148.8	147.6	146.4	145.7	145.1	144.4	143.8	143.1	142.5	141.8
67.5°	147.5	146.3	145.0	143.8	143.1	142.5	141.9	141.3	140.7	140.1	139.5
70°	145.6	144.2	142.9	141.6	141.0	140.4	139.8	139.2	138.6	138.0	137.4
72.5°	143.1	141.6	140.2	138.8	138.3	137.8	137.3	136.8	136.3	135.8	135.3
75°	140.5	139.1	137.7	136.3	135.9	135.5	135.1	134.7	134.3	133.9	133.5
77.5°	137.4	136.0	134.7	133.3	132.8	132.3	131.8	131.4	130.9	130.4	129.9
80°	133.4	132.0	130.5	129.1	128.6	128.1	127.6	127.1	126.6	126.1	125.6
82.5°	130.0	128.6	127.1	125.7	125.3	124.9	124.5	124.0	123.6	123.2	122.8
85°	127.2	125.7	124.2	122.7	122.1	121.5	120.9	120.3	119.7	119.1	118.6
87.5°	122.8	121.2	119.5	117.8	117.5	117.1	116.7	116.4	116.0	115.7	115.3
90°	119.2	117.4	115.7	113.9	113.4	112.9	112.3	111.8	111.3	110.8	110.3
92.5°	115.3	113.6	111.8	110.1	109.5	109.0	108.5	107.9	107.4	106.9	106.3
95°	111.9	110.3	108.6	107.0	106.4	105.7	105.1	104.5	103.9	103.2	102.6
97.5°	108.4	106.8	105.2	103.6	102.9	102.2	101.6	100.9	100.2	99.5	98.8
100°	104.6	103.1	101.5	99.9	99.2	98.5	97.8	97.1	96.3	95.6	94.9
102.5°	101.5	100.0	98.5	97.1	96.2	95.4	94.5	93.7	92.8	92.0	91.1
105°	97.6	96.2	94.8	93.4	92.5	91.6	90.7	89.8	88.9	88.1	87.2
107.5°	94.1	92.6	91.2	89.7	88.8	87.8	86.8	85.8	84.9	83.9	82.9
110°	89.9	88.5	87.0	85.6	84.6	83.6	82.6	81.6	80.7	79.7	78.7

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	86.1	84.8	83.4	82.1	81.0	80.0	78.9	77.8	76.8	75.7	74.6
115°	82.0	80.7	79.4	78.1	77.1	76.1	75.0	74.0	72.9	71.9	70.9
117.5°	77.9	76.6	75.3	74.0	73.0	72.0	70.9	69.9	68.9	67.9	66.8
120°	73.6	72.3	71.1	69.8	68.8	67.8	66.8	65.8	64.8	63.9	62.9
122.5°	69.5	68.3	67.2	66.1	65.0	64.0	63.0	62.0	60.9	59.9	58.9
125°	65.4	64.4	63.3	62.3	61.3	60.3	59.2	58.2	57.1	56.1	55.1
127.5°	61.1	60.1	59.2	58.2	57.2	56.2	55.2	54.1	53.1	52.1	51.1
130°	57.1	56.2	55.3	54.4	53.4	52.3	51.3	50.3	49.3	48.3	47.2
132.5°	53.0	52.1	51.2	50.4	49.4	48.4	47.4	46.4	45.5	44.5	43.5
135°	49.1	48.3	47.5	46.7	45.7	44.7	43.8	42.8	41.8	40.9	39.9
137.5°	45.1	44.3	43.6	42.9	41.9	41.0	40.1	39.2	38.2	37.3	36.4
140°	41.4	40.7	39.9	39.2	38.3	37.4	36.5	35.6	34.6	33.7	32.8
142.5°	37.5	36.9	36.2	35.6	34.7	33.9	33.0	32.1	31.3	30.4	29.5
145°	33.9	33.3	32.7	32.1	31.3	30.5	29.8	29.0	28.2	27.4	26.6
147.5°	30.4	29.8	29.3	28.7	28.0	27.3	26.6	25.9	25.2	24.5	23.8
150°	27.0	26.5	26.1	25.6	24.9	24.3	23.6	22.9	22.2	21.6	20.9
152.5°	23.7	23.3	22.9	22.5	21.9	21.3	20.6	20.0	19.4	18.8	18.1
155°	20.5	20.2	19.8	19.5	18.9	18.3	17.8	17.2	16.7	16.1	15.5
157.5°	17.4	17.0	16.7	16.4	15.9	15.4	14.9	14.4	13.9	13.4	12.9
160°	14.1	13.8	13.5	13.3	12.9	12.5	12.1	11.7	11.3	10.8	10.4
162.5°	11.0	10.8	10.5	10.3	10.0	9.7	9.3	9.0	8.7	8.3	8.0
165°	8.1	8.0	7.8	7.7	7.4	7.2	7.0	6.7	6.5	6.3	6.1
167.5°	5.8	5.7	5.6	5.6	5.3	5.0	4.7	4.5	4.2	3.9	3.7
170°	3.1	3.0	2.9	2.8	2.7	2.5	2.4	2.3	2.1	2.0	1.9
172.5°	1.3	1.2	1.1	1.0	1.0	1.0	1.0	1.0	0.9	0.9	0.9
175°	0.9	0.9	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
177.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	98.3	98.3	98.3	98.3	98.2	98.2	98.2	98.2	98.2	98.1	98.1
5°	98.2	97.9	98.2	98.5	98.7	99.0	99.3	99.6	99.8	100.1	100.4
7.5°	103.0	103.1	103.1	103.1	103.1	103.1	103.1	103.0	103.0	103.0	103.0
10°	105.7	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.9	105.9
12.5°	110.1	110.3	110.2	110.1	110.0	109.9	109.8	109.7	109.6	109.5	109.4
15°	113.4	113.5	113.4	113.2	113.1	113.0	112.8	112.7	112.6	112.4	112.3
17.5°	118.0	117.9	117.7	117.4	117.2	117.0	116.7	116.5	116.3	116.1	115.8
20°	121.6	121.7	121.3	120.9	120.5	120.1	119.7	119.3	118.9	118.6	118.2
22.5°	124.6	124.6	124.3	124.0	123.7	123.4	123.1	122.8	122.5	122.2	121.9
25°	126.2	125.9	125.7	125.5	125.2	125.0	124.8	124.6	124.3	124.1	123.9
27.5°	130.8	130.6	130.0	129.4	128.9	128.3	127.8	127.2	126.6	126.1	125.5
30°	133.0	132.8	132.0	131.2	130.5	129.7	128.9	128.1	127.3	126.5	125.8
32.5°	135.5	135.2	134.1	133.0	131.9	130.8	129.7	128.6	127.6	126.5	125.4
35°	139.6	139.2	137.5	135.9	134.2	132.6	130.9	129.3	127.6	126.0	124.3
37.5°	140.1	139.5	137.7	135.9	134.1	132.2	130.4	128.6	126.8	125.0	123.2
40°	141.9	141.3	139.2	137.2	135.1	133.0	130.9	128.8	126.8	124.7	122.6
42.5°	145.5	145.2	142.6	139.9	137.2	134.5	131.8	129.1	126.5	123.8	121.1
45°	144.1	143.5	140.9	138.3	135.7	133.0	130.4	127.8	125.2	122.6	120.0
47.5°	145.1	144.6	141.7	138.9	136.0	133.2	130.3	127.5	124.6	121.8	118.9
50°	145.1	144.4	141.5	138.6	135.6	132.7	129.8	126.9	124.0	121.1	118.2
52.5°	147.0	146.5	143.2	139.8	136.4	133.0	129.7	126.3	122.9	119.5	116.2
55°	144.0	143.2	140.1	137.0	133.9	130.7	127.6	124.5	121.4	118.3	115.2
57.5°	144.5	143.8	140.4	137.0	133.6	130.2	126.9	123.5	120.1	116.7	113.3
60°	143.7	143.0	139.4	135.7	132.1	128.5	124.9	121.3	117.7	114.0	110.4
62.5°	142.8	142.1	138.4	134.7	131.1	127.4	123.8	120.1	116.5	112.8	109.2
65°	141.2	140.5	136.7	132.9	129.1	125.3	121.5	117.7	113.9	110.1	106.3
67.5°	138.9	138.2	134.5	130.7	127.0	123.2	119.5	115.7	111.9	108.2	104.4
70°	136.8	136.2	132.2	128.2	124.2	120.3	116.3	112.3	108.3	104.4	100.4
72.5°	134.8	134.3	130.4	126.5	122.6	118.7	114.8	110.9	107.0	103.1	99.2
75°	133.1	132.7	128.6	124.4	120.3	116.1	111.9	107.8	103.6	99.5	95.3
77.5°	129.4	129.0	124.8	120.7	116.6	112.4	108.3	104.2	100.0	95.9	91.7
80°	125.1	124.6	120.6	116.6	112.6	108.6	104.6	100.6	96.6	92.6	88.6
82.5°	122.4	122.0	117.9	113.8	109.7	105.6	101.5	97.4	93.3	89.2	85.1
85°	118.0	117.4	113.4	109.5	105.5	101.6	97.6	93.7	89.7	85.8	81.8
87.5°	114.9	114.6	110.5	106.5	102.4	98.4	94.3	90.2	86.2	82.1	78.1
90°	109.8	109.3	105.4	101.6	97.7	93.9	90.0	86.2	82.3	78.5	74.6
92.5°	105.8	105.3	101.5	97.7	93.9	90.1	86.3	82.5	78.7	74.9	71.2
95°	102.0	101.4	97.6	93.9	90.2	86.4	82.7	79.0	75.3	71.5	67.8
97.5°	98.2	97.5	93.8	90.2	86.5	82.8	79.2	75.5	71.8	68.2	64.5
100°	94.2	93.5	89.9	86.3	82.7	79.1	75.5	71.9	68.3	64.7	61.1
102.5°	90.3	89.4	86.0	82.5	79.0	75.5	72.0	68.6	65.1	61.6	58.1
105°	86.3	85.4	82.0	78.6	75.2	71.8	68.4	65.0	61.6	58.2	54.8
107.5°	81.9	81.0	77.7	74.4	71.2	67.9	64.7	61.4	58.1	54.9	51.6
110°	77.7	76.7	73.6	70.5	67.3	64.2	61.1	58.0	54.8	51.7	48.6

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	73.6	72.5	69.6	66.6	63.7	60.7	57.8	54.9	51.9	49.0	46.0
115°	69.8	68.8	65.9	63.0	60.2	57.3	54.4	51.5	48.7	45.8	42.9
117.5°	65.8	64.8	62.1	59.3	56.6	53.9	51.1	48.4	45.6	42.9	40.2
120°	61.9	60.9	58.3	55.7	53.1	50.5	47.9	45.3	42.7	40.1	37.5
122.5°	57.9	56.8	54.4	51.9	49.5	47.0	44.5	42.1	39.6	37.2	34.7
125°	54.0	53.0	50.7	48.3	46.0	43.7	41.3	39.0	36.7	34.3	32.0
127.5°	50.1	49.1	46.9	44.7	42.5	40.3	38.1	35.9	33.7	31.6	29.4
130°	46.2	45.2	43.2	41.1	39.1	37.1	35.0	33.0	30.9	28.9	26.9
132.5°	42.5	41.5	39.7	37.8	35.9	34.0	32.1	30.3	28.4	26.5	24.6
135°	39.0	38.0	36.2	34.5	32.7	30.9	29.2	27.4	25.6	23.8	22.1
137.5°	35.4	34.5	32.9	31.2	29.6	28.0	26.4	24.7	23.1	21.5	19.8
140°	31.9	30.9	29.5	28.0	26.6	25.1	23.6	22.2	20.7	19.3	17.8
142.5°	28.6	27.8	26.5	25.2	23.9	22.6	21.3	20.0	18.7	17.4	16.1
145°	25.8	25.0	23.8	22.6	21.4	20.2	19.0	17.8	16.5	15.3	14.1
147.5°	23.1	22.4	21.3	20.2	19.1	18.0	16.9	15.8	14.7	13.6	12.5
150°	20.2	19.5	18.6	17.6	16.6	15.7	14.7	13.7	12.7	11.8	10.8
152.5°	17.5	16.9	16.0	15.2	14.3	13.5	12.6	11.8	10.9	10.1	9.2
155°	15.0	14.4	13.7	13.0	12.2	11.5	10.8	10.1	9.3	8.6	7.9
157.5°	12.5	12.0	11.4	10.8	10.2	9.6	9.0	8.4	7.8	7.2	6.6
160°	10.0	9.6	9.2	8.7	8.3	7.9	7.4	7.0	6.5	6.1	5.6
162.5°	7.7	7.4	6.9	6.5	6.1	5.7	5.3	4.9	4.4	4.0	3.6
165°	5.8	5.6	5.2	4.9	4.5	4.1	3.7	3.4	3.0	2.6	2.3
167.5°	3.4	3.1	2.9	2.7	2.5	2.2	2.0	1.8	1.6	1.4	1.1
170°	1.7	1.6	1.5	1.4	1.3	1.3	1.2	1.1	1.0	0.9	0.8
172.5°	0.9	0.9	0.9	0.9	0.8	0.8	0.8	0.8	0.7	0.7	0.7
175°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
177.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	98.0	98.0	97.9	97.8	97.7	97.7	97.6	97.5	97.4	97.5	97.6
5°	100.3	100.3	100.2	100.2	100.1	100.1	100.0	100.0	100.0	100.2	100.4
7.5°	102.9	102.9	102.8	102.8	102.7	102.7	102.6	102.6	102.5	102.8	103.1
10°	105.8	105.8	105.8	105.8	105.8	105.8	105.8	105.8	105.8	106.0	106.1
12.5°	109.3	109.3	109.2	109.2	109.1	109.0	109.0	108.9	108.9	108.9	109.0
15°	112.2	112.1	112.1	112.0	111.9	111.8	111.7	111.6	111.6	111.6	111.7
17.5°	115.6	115.5	115.3	115.1	114.9	114.8	114.6	114.4	114.2	114.3	114.3
20°	117.9	117.7	117.5	117.3	117.1	116.9	116.7	116.5	116.3	116.1	116.0
22.5°	121.3	120.7	120.1	119.5	118.9	118.3	117.7	117.1	116.5	116.3	116.1
25°	122.9	122.0	121.1	120.1	119.2	118.3	117.3	116.4	115.5	115.1	114.8
27.5°	124.3	123.0	121.7	120.4	119.2	117.9	116.6	115.4	114.1	113.6	113.1
30°	124.2	122.6	121.1	119.5	118.0	116.4	114.8	113.3	111.7	111.1	110.4
32.5°	123.5	121.6	119.7	117.8	115.9	114.0	112.1	110.3	108.4	107.6	106.8
35°	122.2	120.0	117.9	115.7	113.6	111.5	109.3	107.2	105.0	104.2	103.5
37.5°	120.8	118.5	116.1	113.7	111.3	109.0	106.6	104.2	101.9	100.8	99.7
40°	119.9	117.2	114.5	111.8	109.0	106.3	103.6	100.9	98.2	97.1	96.0
42.5°	118.2	115.3	112.4	109.5	106.6	103.7	100.8	97.9	95.0	93.7	92.4
45°	116.8	113.7	110.5	107.4	104.2	101.1	97.9	94.8	91.6	90.2	88.8
47.5°	115.6	112.2	108.9	105.6	102.2	98.9	95.5	92.2	88.9	87.2	85.5
50°	114.5	110.9	107.3	103.7	100.1	96.4	92.8	89.2	85.6	83.8	82.0
52.5°	112.4	108.6	104.8	101.0	97.3	93.5	89.7	85.9	82.1	80.3	78.4
55°	111.2	107.2	103.1	99.1	95.1	91.1	87.1	83.1	79.1	77.2	75.3
57.5°	109.1	104.9	100.7	96.5	92.3	88.2	84.0	79.8	75.6	73.5	71.5
60°	106.3	102.1	97.9	93.7	89.6	85.4	81.2	77.0	72.9	70.8	68.8
62.5°	104.7	100.3	95.8	91.4	87.0	82.5	78.1	73.7	69.2	67.1	64.9
65°	101.8	97.4	92.9	88.5	84.0	79.6	75.1	70.7	66.2	64.0	61.8
67.5°	99.8	95.2	90.6	86.0	81.4	76.8	72.1	67.5	62.9	60.6	58.4
70°	95.8	91.3	86.7	82.1	77.5	73.0	68.4	63.8	59.3	57.0	54.6
72.5°	94.3	89.5	84.7	79.9	75.0	70.2	65.4	60.6	55.7	53.4	51.1
75°	90.5	85.7	80.9	76.1	71.3	66.5	61.7	56.9	52.2	49.8	47.4
77.5°	86.9	82.1	77.3	72.5	67.6	62.8	58.0	53.2	48.3	46.0	43.6
80°	83.8	78.9	74.0	69.2	64.3	59.4	54.6	49.7	44.8	42.5	40.2
82.5°	80.2	75.3	70.5	65.6	60.8	55.9	51.0	46.2	41.3	39.0	36.8
85°	77.0	72.1	67.3	62.4	57.5	52.7	47.8	43.0	38.1	35.9	33.6
87.5°	73.3	68.5	63.8	59.0	54.2	49.4	44.7	39.9	35.1	32.9	30.7
90°	69.9	65.2	60.5	55.7	51.0	46.3	41.6	36.9	32.1	30.1	28.0
92.5°	66.5	61.9	57.3	52.6	48.0	43.4	38.7	34.1	29.5	27.5	25.5
95°	63.2	58.7	54.1	49.6	45.0	40.5	35.9	31.4	26.8	24.9	23.0
97.5°	60.1	55.6	51.2	46.8	42.4	37.9	33.5	29.1	24.7	22.8	21.0
100°	56.8	52.5	48.2	43.9	39.6	35.3	31.0	26.7	22.4	20.7	18.9
102.5°	53.9	49.7	45.5	41.3	37.1	32.9	28.7	24.5	20.3	18.7	17.0
105°	50.8	46.7	42.6	38.6	34.5	30.4	26.4	22.3	18.3	16.7	15.1
107.5°	47.7	43.7	39.8	35.9	32.0	28.0	24.1	20.2	16.2	14.8	13.3
110°	44.8	41.0	37.2	33.4	29.6	25.8	22.0	18.1	14.3	13.0	11.6

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	42.3	38.6	34.9	31.2	27.4	23.7	20.0	16.3	12.6	11.3	10.1
115°	39.4	35.9	32.4	28.9	25.4	21.9	18.4	14.9	11.4	10.2	9.0
117.5°	36.9	33.5	30.2	26.9	23.6	20.3	17.0	13.7	10.4	9.3	8.2
120°	34.4	31.3	28.2	25.0	21.9	18.8	15.7	12.5	9.4	8.4	7.5
122.5°	31.8	28.8	25.9	23.0	20.1	17.1	14.2	11.3	8.4	7.5	6.7
125°	29.3	26.6	23.9	21.2	18.5	15.8	13.2	10.5	7.8	7.0	6.2
127.5°	26.8	24.3	21.8	19.3	16.7	14.2	11.7	9.2	6.7	6.0	5.3
130°	24.5	22.2	19.8	17.4	15.1	12.7	10.3	8.0	5.6	5.1	4.5
132.5°	22.5	20.4	18.3	16.2	14.1	11.9	9.8	7.7	5.6	5.0	4.5
135°	20.1	18.1	16.1	14.2	12.2	10.2	8.2	6.2	4.3	3.8	3.4
137.5°	18.0	16.2	14.4	12.6	10.9	9.1	7.3	5.5	3.7	3.3	3.0
140°	16.2	14.6	12.9	11.3	9.7	8.0	6.4	4.8	3.1	2.9	2.6
142.5°	14.7	13.3	11.8	10.4	8.9	7.5	6.0	4.6	3.1	2.8	2.5
145°	12.8	11.6	10.3	9.0	7.7	6.4	5.1	3.8	2.6	2.3	2.1
147.5°	11.3	10.2	9.0	7.9	6.7	5.6	4.5	3.3	2.2	2.0	1.8
150°	9.8	8.8	7.8	6.9	5.9	4.9	3.9	2.9	1.9	1.8	1.6
152.5°	8.4	7.6	6.8	6.0	5.1	4.3	3.5	2.7	1.9	1.7	1.6
155°	7.2	6.5	5.9	5.2	4.5	3.9	3.2	2.5	1.9	1.7	1.6
157.5°	6.0	5.4	4.8	4.2	3.6	2.9	2.3	1.7	1.1	1.0	1.0
160°	5.1	4.6	4.1	3.6	3.0	2.5	2.0	1.5	1.0	0.9	0.9
162.5°	3.3	3.0	2.7	2.4	2.1	1.8	1.6	1.3	1.0	0.9	0.9
165°	2.1	1.9	1.7	1.5	1.3	1.2	1.0	0.8	0.6	0.6	0.6
167.5°	1.1	1.0	0.9	0.9	0.8	0.7	0.7	0.6	0.5	0.5	0.5
170°	0.8	0.8	0.7	0.7	0.7	0.6	0.6	0.6	0.5	0.5	0.5
172.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.6	0.6
175°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.7
177.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	97.6	97.7	97.8	97.9	97.9	98.0	98.1	98.2	98.3	98.4	98.5
5°	100.6	100.8	101.0	101.2	101.4	101.6	101.8	101.8	101.8	101.7	101.7
7.5°	103.5	103.8	104.1	104.4	104.7	105.0	105.3	105.1	104.9	104.7	104.5
10°	106.3	106.5	106.6	106.8	107.0	107.2	107.3	107.4	107.6	107.7	107.8
12.5°	109.0	109.0	109.1	109.1	109.2	109.2	109.2	109.4	109.6	109.7	109.9
15°	111.8	111.9	111.9	112.0	112.1	112.2	112.3	112.4	112.6	112.7	112.9
17.5°	114.4	114.5	114.5	114.6	114.6	114.7	114.7	114.8	114.8	114.9	114.9
20°	115.8	115.7	115.6	115.4	115.3	115.1	115.0	115.3	115.6	116.0	116.3
22.5°	115.9	115.7	115.5	115.3	115.1	114.8	114.6	114.9	115.2	115.5	115.8
25°	114.5	114.2	113.9	113.5	113.2	112.9	112.6	113.0	113.4	113.9	114.3
27.5°	112.6	112.1	111.6	111.1	110.6	110.1	109.6	110.1	110.5	111.0	111.5
30°	109.8	109.1	108.5	107.9	107.2	106.6	105.9	106.5	107.1	107.7	108.3
32.5°	106.1	105.3	104.5	103.8	103.0	102.3	101.5	102.2	103.0	103.7	104.4
35°	102.7	101.9	101.1	100.4	99.6	98.8	98.0	98.6	99.2	99.7	100.3
37.5°	98.6	97.5	96.5	95.4	94.3	93.2	92.1	92.9	93.6	94.3	95.0
40°	94.9	93.8	92.7	91.6	90.5	89.4	88.3	89.2	90.0	90.9	91.7
42.5°	91.1	89.8	88.6	87.3	86.0	84.7	83.4	84.4	85.4	86.4	87.4
45°	87.3	85.9	84.5	83.0	81.6	80.2	78.7	79.8	80.9	81.9	83.0
47.5°	83.8	82.1	80.5	78.8	77.1	75.4	73.8	75.0	76.2	77.4	78.7
50°	80.3	78.5	76.8	75.0	73.2	71.5	69.7	71.0	72.2	73.5	74.7
52.5°	76.5	74.6	72.8	70.9	69.0	67.1	65.2	66.6	68.0	69.4	70.8
55°	73.4	71.5	69.6	67.8	65.9	64.0	62.1	63.4	64.7	66.0	67.3
57.5°	69.4	67.3	65.3	63.2	61.1	59.1	57.0	58.6	60.1	61.7	63.3
60°	66.7	64.6	62.6	60.5	58.4	56.4	54.3	55.8	57.2	58.7	60.2
62.5°	62.8	60.7	58.5	56.4	54.2	52.1	50.0	51.5	53.0	54.6	56.1
65°	59.6	57.3	55.1	52.9	50.7	48.4	46.2	47.8	49.4	50.9	52.5
67.5°	56.1	53.8	51.6	49.3	47.0	44.7	42.5	44.0	45.6	47.2	48.8
70°	52.3	50.0	47.7	45.4	43.1	40.8	38.5	40.1	41.7	43.3	44.9
72.5°	48.7	46.4	44.0	41.7	39.3	37.0	34.7	36.2	37.7	39.3	40.8
75°	45.1	42.7	40.3	37.9	35.6	33.2	30.8	32.5	34.1	35.7	37.3
77.5°	41.2	38.8	36.4	34.1	31.7	29.3	26.9	28.5	30.1	31.7	33.3
80°	37.8	35.5	33.2	30.9	28.5	26.2	23.9	25.4	27.0	28.5	30.1
82.5°	34.5	32.2	29.9	27.6	25.3	23.0	20.7	22.3	23.8	25.3	26.8
85°	31.3	29.1	26.8	24.6	22.3	20.1	17.8	19.3	20.8	22.3	23.7
87.5°	28.5	26.4	24.2	22.0	19.8	17.6	15.4	16.8	18.2	19.6	21.1
90°	25.9	23.8	21.7	19.7	17.6	15.5	13.4	14.8	16.1	17.5	18.9
92.5°	23.5	21.5	19.5	17.5	15.5	13.5	11.5	12.8	14.0	15.3	16.6
95°	21.1	19.2	17.3	15.3	13.4	11.5	9.6	10.8	12.0	13.3	14.5
97.5°	19.1	17.3	15.5	13.6	11.8	9.9	8.1	9.2	10.4	11.5	12.7
100°	17.1	15.4	13.6	11.9	10.1	8.3	6.6	7.7	8.8	9.9	10.9
102.5°	15.3	13.7	12.0	10.3	8.6	7.0	5.3	6.3	7.3	8.3	9.3
105°	13.5	11.9	10.3	8.8	7.2	5.6	4.0	5.0	5.9	6.8	7.8
107.5°	11.8	10.4	8.9	7.4	6.0	4.5	3.0	3.9	4.7	5.5	6.4
110°	10.2	8.9	7.5	6.1	4.8	3.4	2.0	2.8	3.6	4.3	5.1

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	8.8	7.6	6.3	5.1	3.8	2.6	1.4	2.1	2.7	3.4	4.1
115°	7.9	6.7	5.6	4.4	3.2	2.1	0.9	1.6	2.2	2.9	3.5
117.5°	7.2	6.1	5.0	4.0	2.9	1.8	0.8	1.3	1.9	2.5	3.1
120°	6.5	5.5	4.6	3.6	2.6	1.7	0.7	1.2	1.7	2.2	2.8
122.5°	5.8	5.0	4.1	3.2	2.4	1.5	0.7	1.1	1.6	2.0	2.5
125°	5.4	4.6	3.8	3.0	2.3	1.5	0.7	1.0	1.4	1.8	2.2
127.5°	4.6	4.0	3.3	2.6	1.9	1.3	0.6	0.9	1.2	1.6	1.9
130°	4.0	3.4	2.9	2.3	1.8	1.2	0.7	0.9	1.2	1.4	1.6
132.5°	3.9	3.3	2.8	2.2	1.7	1.1	0.5	0.7	0.9	1.2	1.4
135°	3.0	2.6	2.2	1.8	1.4	0.9	0.5	0.7	0.8	1.0	1.2
137.5°	2.6	2.3	1.9	1.6	1.2	0.9	0.5	0.6	0.8	0.9	1.0
140°	2.3	2.0	1.7	1.4	1.1	0.8	0.5	0.6	0.7	0.8	0.8
142.5°	2.2	1.9	1.6	1.3	1.0	0.8	0.5	0.5	0.6	0.6	0.7
145°	1.9	1.6	1.4	1.2	0.9	0.7	0.5	0.5	0.5	0.6	0.6
147.5°	1.6	1.4	1.2	1.0	0.8	0.6	0.5	0.5	0.5	0.5	0.5
150°	1.4	1.3	1.1	0.9	0.8	0.6	0.5	0.5	0.5	0.5	0.5
152.5°	1.4	1.2	1.1	0.9	0.8	0.6	0.5	0.5	0.5	0.5	0.5
155°	1.4	1.2	1.1	0.9	0.8	0.6	0.5	0.4	0.4	0.4	0.4
157.5°	0.9	0.8	0.7	0.7	0.6	0.5	0.5	0.4	0.4	0.4	0.4
160°	0.8	0.7	0.7	0.6	0.6	0.5	0.5	0.4	0.4	0.4	0.4
162.5°	0.8	0.7	0.7	0.6	0.6	0.5	0.5	0.4	0.4	0.4	0.4
165°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.4
167.5°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.4
170°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.4
172.5°	0.6	0.6	0.6	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.4
175°	0.7	0.7	0.6	0.6	0.5	0.5	0.5	0.4	0.4	0.4	0.4
177.5°	0.7	0.7	0.7	0.7	0.7	0.6	0.6	0.6	0.6	0.6	0.6
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	98.6	98.7	98.9	99.0	99.1	99.0	98.9	98.8	98.8	98.7	98.6
5°	101.7	101.7	101.7	101.7	101.7	101.5	101.3	101.0	100.8	100.6	100.4
7.5°	104.3	104.1	103.9	103.7	103.4	103.3	103.2	103.1	102.9	102.8	102.7
10°	108.0	108.1	108.2	108.4	108.5	108.2	107.9	107.6	107.3	107.0	106.7
12.5°	110.1	110.3	110.4	110.6	110.8	110.7	110.6	110.6	110.5	110.4	110.4
15°	113.0	113.2	113.3	113.5	113.6	113.6	113.6	113.6	113.6	113.6	113.6
17.5°	115.0	115.1	115.1	115.2	115.2	115.2	115.2	115.2	115.2	115.2	115.2
20°	116.6	116.9	117.2	117.6	117.9	117.9	117.9	117.8	117.8	117.8	117.8
22.5°	116.1	116.4	116.7	117.0	117.2	117.4	117.6	117.7	117.9	118.0	118.2
25°	114.7	115.1	115.6	116.0	116.4	117.0	117.6	118.1	118.7	119.3	119.8
27.5°	111.9	112.4	112.8	113.3	113.8	114.9	116.0	117.1	118.3	119.4	120.5
30°	108.9	109.5	110.0	110.6	111.2	112.4	113.6	114.7	115.9	117.1	118.2
32.5°	105.1	105.9	106.6	107.3	108.1	109.6	111.2	112.7	114.3	115.8	117.4
35°	100.9	101.5	102.0	102.6	103.2	105.1	107.0	109.0	110.9	112.8	114.7
37.5°	95.7	96.5	97.2	97.9	98.6	101.0	103.3	105.7	108.0	110.4	112.7
40°	92.6	93.4	94.3	95.1	95.9	98.4	100.9	103.3	105.8	108.3	110.7
42.5°	88.4	89.4	90.4	91.4	92.4	95.0	97.6	100.2	102.8	105.4	108.0
45°	84.0	85.1	86.2	87.2	88.3	91.1	94.0	96.9	99.7	102.6	105.4
47.5°	79.9	81.1	82.3	83.6	84.8	87.8	90.8	93.8	96.8	99.8	102.8
50°	76.0	77.2	78.5	79.8	81.0	84.3	87.7	91.0	94.4	97.7	101.0
52.5°	72.2	73.6	75.0	76.4	77.8	81.3	84.8	88.3	91.8	95.3	98.8
55°	68.6	69.9	71.3	72.6	73.9	77.7	81.4	85.2	89.0	92.8	96.6
57.5°	64.8	66.4	68.0	69.5	71.1	74.8	78.5	82.3	86.0	89.7	93.5
60°	61.6	63.1	64.5	66.0	67.5	71.4	75.4	79.4	83.3	87.3	91.3
62.5°	57.6	59.2	60.7	62.2	63.8	67.9	72.0	76.0	80.1	84.2	88.3
65°	54.1	55.6	57.2	58.8	60.4	64.6	68.8	73.0	77.2	81.5	85.7
67.5°	50.3	51.9	53.5	55.1	56.6	60.9	65.2	69.5	73.9	78.2	82.5
70°	46.5	48.1	49.7	51.3	52.9	57.4	61.8	66.2	70.6	75.0	79.4
72.5°	42.4	43.9	45.5	47.0	48.6	53.1	57.6	62.1	66.6	71.1	75.6
75°	38.9	40.5	42.2	43.8	45.4	49.9	54.4	58.8	63.3	67.8	72.3
77.5°	34.9	36.5	38.1	39.7	41.3	45.9	50.5	55.2	59.8	64.5	69.1
80°	31.6	33.2	34.7	36.2	37.8	42.4	47.0	51.6	56.2	60.9	65.5
82.5°	28.4	29.9	31.4	33.0	34.5	39.1	43.7	48.3	53.0	57.6	62.2
85°	25.2	26.7	28.2	29.7	31.2	35.7	40.3	44.9	49.5	54.0	58.6
87.5°	22.5	23.9	25.3	26.7	28.2	32.7	37.2	41.7	46.2	50.8	55.3
90°	20.2	21.6	23.0	24.3	25.7	30.1	34.4	38.8	43.2	47.5	51.9
92.5°	17.9	19.2	20.5	21.8	23.0	27.4	31.7	36.0	40.4	44.7	49.0
95°	15.7	17.0	18.2	19.4	20.6	25.0	29.3	33.6	38.0	42.3	46.6
97.5°	13.8	15.0	16.2	17.3	18.5	22.6	26.7	30.9	35.0	39.2	43.3
100°	12.0	13.1	14.2	15.3	16.4	20.4	24.5	28.5	32.6	36.6	40.7
102.5°	10.3	11.3	12.4	13.4	14.4	18.3	22.2	26.2	30.1	34.0	38.0
105°	8.7	9.7	10.6	11.5	12.5	16.3	20.1	23.9	27.7	31.6	35.4
107.5°	7.2	8.1	8.9	9.8	10.6	14.3	18.1	21.8	25.5	29.3	33.0
110°	5.9	6.6	7.4	8.2	9.0	12.5	16.1	19.7	23.3	26.9	30.5

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	4.8	5.5	6.2	6.9	7.6	11.1	14.5	18.0	21.4	24.9	28.3
115°	4.2	4.8	5.5	6.1	6.8	10.0	13.3	16.6	19.8	23.1	26.4
117.5°	3.7	4.3	4.9	5.4	6.0	9.1	12.2	15.2	18.3	21.4	24.5
120°	3.3	3.8	4.3	4.8	5.3	8.2	11.1	14.0	16.9	19.8	22.7
122.5°	2.9	3.3	3.8	4.2	4.7	7.4	10.1	12.7	15.4	18.1	20.8
125°	2.5	2.9	3.3	3.6	4.0	6.5	9.0	11.4	13.9	16.4	18.9
127.5°	2.2	2.5	2.8	3.1	3.5	5.8	8.1	10.4	12.8	15.1	17.4
130°	1.9	2.1	2.4	2.6	2.9	5.0	7.1	9.2	11.3	13.5	15.6
132.5°	1.6	1.8	2.0	2.2	2.4	4.3	6.3	8.2	10.1	12.1	14.0
135°	1.3	1.5	1.6	1.8	2.0	3.7	5.4	7.2	8.9	10.6	12.3
137.5°	1.1	1.2	1.3	1.5	1.6	3.1	4.7	6.2	7.8	9.3	10.9
140°	0.9	1.0	1.1	1.1	1.2	2.6	3.9	5.3	6.6	8.0	9.3
142.5°	0.7	0.8	0.8	0.9	0.9	2.1	3.2	4.4	5.6	6.8	7.9
145°	0.6	0.6	0.7	0.7	0.7	1.7	2.7	3.7	4.7	5.6	6.6
147.5°	0.5	0.5	0.5	0.5	0.5	1.3	2.1	2.9	3.7	4.5	5.3
150°	0.5	0.5	0.5	0.5	0.5	1.1	1.7	2.3	2.9	3.6	4.2
152.5°	0.5	0.5	0.5	0.5	0.5	0.9	1.4	1.8	2.3	2.7	3.2
155°	0.4	0.4	0.4	0.4	0.4	0.7	1.0	1.4	1.7	2.0	2.4
157.5°	0.4	0.4	0.4	0.4	0.4	0.6	0.8	1.0	1.2	1.5	1.7
160°	0.4	0.4	0.4	0.4	0.4	0.5	0.6	0.8	0.9	1.0	1.2
162.5°	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.6	0.7	0.8	0.8
165°	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.6	0.6
167.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5
170°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5
172.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.6
175°	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.6	0.7	0.7
177.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.8	0.8
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	98.5	98.4	98.3	98.2	98.0	97.8	97.6	97.4	97.2	97.0	96.8
5°	100.1	99.9	99.7	99.6	99.5	99.4	99.3	99.1	99.0	98.9	98.8
7.5°	102.6	102.4	102.3	102.1	102.0	101.8	101.7	101.5	101.3	101.2	101.0
10°	106.5	106.2	105.9	105.8	105.8	105.7	105.7	105.6	105.6	105.5	105.5
12.5°	110.3	110.2	110.1	109.9	109.7	109.5	109.3	109.1	108.9	108.7	108.5
15°	113.5	113.5	113.5	113.3	113.2	113.0	112.8	112.6	112.5	112.3	112.1
17.5°	115.2	115.2	115.2	115.3	115.3	115.4	115.5	115.5	115.6	115.6	115.7
20°	117.8	117.8	117.8	118.0	118.2	118.4	118.6	118.8	119.0	119.2	119.4
22.5°	118.3	118.5	118.7	119.0	119.3	119.7	120.0	120.4	120.7	121.1	121.4
25°	120.4	121.0	121.6	122.0	122.4	122.8	123.2	123.6	124.0	124.4	124.8
27.5°	121.6	122.8	123.9	124.3	124.8	125.2	125.7	126.2	126.6	127.1	127.5
30°	119.4	120.6	121.8	122.7	123.7	124.7	125.7	126.7	127.7	128.7	129.7
32.5°	119.0	120.5	122.1	123.2	124.3	125.3	126.4	127.5	128.6	129.7	130.8
35°	116.7	118.6	120.5	122.0	123.5	125.0	126.6	128.1	129.6	131.1	132.6
37.5°	115.1	117.4	119.8	121.4	123.1	124.8	126.5	128.1	129.8	131.5	133.1
40°	113.2	115.7	118.1	120.2	122.3	124.3	126.4	128.5	130.5	132.6	134.7
42.5°	110.6	113.2	115.8	118.1	120.5	122.9	125.3	127.6	130.0	132.4	134.8
45°	108.3	111.2	114.0	116.7	119.4	122.1	124.8	127.4	130.1	132.8	135.5
47.5°	105.8	108.8	111.8	114.7	117.6	120.5	123.4	126.3	129.2	132.1	135.0
50°	104.4	107.7	111.1	114.0	116.9	119.8	122.7	125.6	128.5	131.4	134.3
52.5°	102.3	105.8	109.3	112.4	115.5	118.6	121.7	124.8	127.9	131.0	134.1
55°	100.4	104.2	107.9	111.2	114.4	117.7	121.0	124.2	127.5	130.7	134.0
57.5°	97.2	100.9	104.7	108.2	111.7	115.2	118.8	122.3	125.8	129.3	132.8
60°	95.2	99.2	103.2	106.8	110.4	114.0	117.6	121.2	124.9	128.5	132.1
62.5°	92.4	96.5	100.6	104.3	107.9	111.6	115.3	119.0	122.6	126.3	130.0
65°	89.9	94.1	98.3	102.3	106.3	110.3	114.2	118.2	122.2	126.1	130.1
67.5°	86.8	91.1	95.4	99.5	103.6	107.7	111.8	115.9	120.0	124.2	128.3
70°	83.8	88.2	92.6	96.8	101.0	105.2	109.4	113.7	117.9	122.1	126.3
72.5°	80.1	84.6	89.1	93.3	97.6	101.9	106.1	110.4	114.6	118.9	123.1
75°	76.8	81.3	85.7	90.0	94.3	98.6	103.0	107.3	111.6	115.9	120.2
77.5°	73.8	78.4	83.0	87.3	91.6	95.9	100.2	104.5	108.8	113.1	117.4
80°	70.1	74.7	79.3	83.6	88.0	92.3	96.6	100.9	105.3	109.6	113.9
82.5°	66.8	71.4	76.1	80.4	84.7	88.9	93.2	97.5	101.8	106.1	110.4
85°	63.2	67.8	72.3	76.7	81.0	85.4	89.8	94.1	98.5	102.8	107.2
87.5°	59.8	64.3	68.8	73.1	77.4	81.6	85.9	90.2	94.4	98.7	102.9
90°	56.3	60.7	65.0	69.3	73.6	77.9	82.2	86.4	90.7	95.0	99.3
92.5°	53.4	57.7	62.0	66.3	70.5	74.8	79.1	83.3	87.6	91.8	96.1
95°	50.9	55.3	59.6	63.7	67.9	72.0	76.1	80.3	84.4	88.5	92.7
97.5°	47.4	51.6	55.7	59.7	63.6	67.6	71.6	75.5	79.5	83.5	87.4
100°	44.7	48.8	52.8	56.6	60.3	64.1	67.8	71.6	75.3	79.1	82.8
102.5°	41.9	45.8	49.7	53.4	57.1	60.7	64.4	68.1	71.7	75.4	79.1
105°	39.2	43.0	46.8	50.5	54.1	57.8	61.4	65.1	68.8	72.4	76.1
107.5°	36.7	40.5	44.2	47.7	51.1	54.6	58.0	61.5	64.9	68.4	71.8
110°	34.1	37.6	41.2	44.6	48.0	51.4	54.7	58.1	61.5	64.9	68.2

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	31.8	35.2	38.7	41.9	45.1	48.2	51.4	54.6	57.8	61.0	64.2
115°	29.6	32.9	36.1	39.2	42.3	45.4	48.5	51.5	54.6	57.7	60.8
117.5°	27.5	30.6	33.7	36.7	39.7	42.7	45.7	48.6	51.6	54.6	57.6
120°	25.6	28.5	31.4	34.1	36.8	39.6	42.3	45.0	47.7	50.5	53.2
122.5°	23.5	26.2	28.9	31.5	34.1	36.7	39.3	41.9	44.5	47.1	49.7
125°	21.4	23.8	26.3	28.8	31.2	33.6	36.1	38.5	41.0	43.4	45.8
127.5°	19.7	22.1	24.4	26.7	28.9	31.1	33.4	35.6	37.9	40.1	42.4
130°	17.7	19.8	21.9	24.1	26.2	28.3	30.4	32.5	34.6	36.7	38.8
132.5°	15.9	17.9	19.8	21.7	23.7	25.6	27.5	29.5	31.4	33.4	35.3
135°	14.1	15.8	17.5	19.4	21.2	23.0	24.8	26.6	28.4	30.3	32.1
137.5°	12.4	14.0	15.5	17.2	18.8	20.4	22.1	23.7	25.4	27.0	28.6
140°	10.7	12.0	13.4	14.9	16.3	17.8	19.3	20.8	22.3	23.8	25.3
142.5°	9.1	10.3	11.4	12.8	14.1	15.5	16.8	18.2	19.5	20.9	22.2
145°	7.6	8.6	9.6	10.8	12.0	13.2	14.4	15.6	16.8	18.0	19.2
147.5°	6.1	6.9	7.7	8.8	9.8	10.9	12.0	13.0	14.1	15.2	16.3
150°	4.8	5.4	6.1	7.0	7.9	8.9	9.8	10.8	11.7	12.6	13.6
152.5°	3.6	4.1	4.6	5.4	6.2	7.0	7.8	8.6	9.4	10.2	11.0
155°	2.7	3.0	3.4	4.0	4.7	5.4	6.1	6.7	7.4	8.1	8.7
157.5°	1.9	2.1	2.3	2.9	3.4	3.9	4.4	5.0	5.5	6.0	6.6
160°	1.3	1.4	1.6	2.0	2.4	2.8	3.2	3.6	4.0	4.4	4.8
162.5°	0.9	1.0	1.0	1.3	1.6	1.9	2.2	2.4	2.7	3.0	3.3
165°	0.7	0.7	0.7	0.9	1.1	1.2	1.4	1.5	1.7	1.8	2.0
167.5°	0.5	0.6	0.6	0.7	0.8	0.8	0.9	1.0	1.1	1.2	1.2
170°	0.5	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.8	0.8
172.5°	0.6	0.6	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
175°	0.8	0.8	0.9	0.9	0.8	0.8	0.8	0.8	0.7	0.7	0.7
177.5°	0.8	0.9	0.9	0.9	0.9	0.8	0.8	0.8	0.8	0.8	0.8
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	96.7	96.9	97.1	97.3	97.5	97.7	97.9	98.1	98.3	98.5	98.5
5°	98.7	98.9	99.1	99.2	99.4	99.6	99.8	99.9	100.1	100.3	100.2
7.5°	100.8	101.1	101.3	101.6	101.8	102.1	102.3	102.6	102.8	103.1	103.1
10°	105.4	105.6	105.8	105.9	106.1	106.3	106.5	106.6	106.8	107.0	107.1
12.5°	108.4	108.5	108.7	108.8	109.0	109.1	109.3	109.4	109.6	109.7	109.8
15°	112.0	112.4	112.8	113.3	113.7	114.2	114.6	115.1	115.5	116.0	115.9
17.5°	115.7	116.0	116.3	116.6	116.9	117.2	117.4	117.7	118.0	118.3	118.6
20°	119.6	119.8	120.0	120.2	120.4	120.6	120.8	121.0	121.2	121.4	122.0
22.5°	121.7	122.2	122.6	123.0	123.4	123.8	124.2	124.6	125.1	125.5	126.0
25°	125.2	125.7	126.3	126.9	127.5	128.1	128.7	129.3	129.9	130.5	130.6
27.5°	128.0	128.7	129.3	130.0	130.7	131.4	132.1	132.7	133.4	134.1	134.2
30°	130.6	131.2	131.8	132.4	133.0	133.6	134.2	134.8	135.4	136.0	136.4
32.5°	131.9	132.6	133.3	134.0	134.7	135.4	136.1	136.8	137.5	138.2	138.8
35°	134.1	135.2	136.2	137.3	138.3	139.4	140.4	141.5	142.5	143.6	143.7
37.5°	134.8	135.7	136.5	137.3	138.1	139.0	139.8	140.6	141.5	142.3	143.0
40°	136.7	137.7	138.7	139.7	140.7	141.6	142.6	143.6	144.6	145.6	146.3
42.5°	137.2	138.0	138.9	139.7	140.6	141.4	142.3	143.1	144.0	144.8	145.6
45°	138.2	139.2	140.2	141.2	142.2	143.2	144.2	145.2	146.2	147.2	148.0
47.5°	137.9	138.9	139.8	140.8	141.7	142.7	143.6	144.6	145.5	146.5	147.3
50°	137.2	138.4	139.6	140.8	142.0	143.3	144.5	145.7	146.9	148.1	149.0
52.5°	137.2	138.5	139.8	141.1	142.4	143.8	145.1	146.4	147.7	149.0	150.0
55°	137.2	138.5	139.7	141.0	142.2	143.5	144.7	146.0	147.2	148.5	149.4
57.5°	136.4	137.4	138.4	139.5	140.5	141.6	142.6	143.7	144.7	145.8	146.9
60°	135.7	136.8	137.9	139.0	140.1	141.2	142.3	143.3	144.4	145.5	146.6
62.5°	133.7	134.9	136.1	137.3	138.6	139.8	141.0	142.2	143.4	144.7	145.5
65°	134.1	135.0	136.0	136.9	137.8	138.8	139.7	140.7	141.6	142.5	143.8
67.5°	132.4	133.4	134.3	135.3	136.3	137.3	138.2	139.2	140.2	141.2	142.2
70°	130.5	131.2	132.0	132.7	133.4	134.2	134.9	135.6	136.3	137.1	138.7
72.5°	127.4	128.2	129.1	130.0	130.9	131.7	132.6	133.5	134.4	135.3	136.8
75°	124.5	125.2	125.9	126.7	127.4	128.1	128.9	129.6	130.3	131.1	132.8
77.5°	121.7	122.6	123.4	124.2	125.0	125.9	126.7	127.5	128.3	129.2	130.6
80°	118.2	118.9	119.6	120.3	121.0	121.6	122.3	123.0	123.7	124.4	126.0
82.5°	114.7	115.5	116.3	117.1	117.8	118.6	119.4	120.2	121.0	121.8	123.3
85°	111.6	112.3	113.0	113.7	114.4	115.1	115.8	116.5	117.3	118.0	119.6
87.5°	107.2	108.1	109.0	109.8	110.7	111.6	112.5	113.3	114.2	115.1	116.7
90°	103.6	104.4	105.3	106.2	107.0	107.9	108.8	109.6	110.5	111.4	113.0
92.5°	100.3	101.2	102.0	102.8	103.7	104.5	105.4	106.2	107.0	107.9	109.4
95°	96.8	97.6	98.4	99.1	99.9	100.7	101.5	102.3	103.0	103.8	105.6
97.5°	91.4	92.5	93.5	94.6	95.7	96.8	97.9	98.9	100.0	101.1	102.7
100°	86.6	87.8	88.9	90.1	91.3	92.5	93.7	94.9	96.0	97.2	98.8
102.5°	82.7	83.9	85.1	86.2	87.4	88.6	89.8	90.9	92.1	93.3	94.9
105°	79.7	80.9	82.0	83.2	84.3	85.5	86.6	87.8	88.9	90.1	91.6
107.5°	75.3	76.5	77.8	79.0	80.3	81.5	82.7	84.0	85.2	86.5	88.0
110°	71.6	72.8	74.1	75.3	76.6	77.8	79.0	80.3	81.5	82.7	84.2

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	67.3	68.6	69.9	71.2	72.5	73.8	75.0	76.3	77.6	78.9	80.4
115°	63.8	65.0	66.3	67.5	68.7	69.9	71.1	72.4	73.6	74.8	76.2
117.5°	60.6	61.8	62.9	64.1	65.3	66.4	67.6	68.8	69.9	71.1	72.4
120°	55.9	57.2	58.4	59.7	60.9	62.2	63.5	64.7	66.0	67.2	68.5
122.5°	52.4	53.6	54.9	56.1	57.4	58.6	59.9	61.1	62.4	63.6	64.8
125°	48.3	49.5	50.8	52.0	53.3	54.5	55.8	57.0	58.3	59.5	60.6
127.5°	44.6	45.9	47.1	48.3	49.5	50.7	51.9	53.1	54.4	55.6	56.7
130°	40.9	42.1	43.3	44.5	45.7	46.9	48.1	49.3	50.5	51.7	52.7
132.5°	37.2	38.4	39.6	40.8	42.0	43.1	44.3	45.5	46.7	47.8	48.8
135°	33.9	35.0	36.1	37.3	38.4	39.5	40.7	41.8	42.9	44.1	44.9
137.5°	30.3	31.4	32.4	33.5	34.6	35.7	36.8	37.9	39.0	40.1	40.9
140°	26.8	27.8	28.9	29.9	31.0	32.0	33.1	34.2	35.2	36.3	37.1
142.5°	23.6	24.6	25.6	26.5	27.5	28.5	29.5	30.5	31.4	32.4	33.2
145°	20.4	21.4	22.3	23.2	24.2	25.1	26.1	27.0	27.9	28.9	29.6
147.5°	17.3	18.2	19.1	20.0	20.9	21.8	22.7	23.6	24.5	25.4	26.0
150°	14.5	15.3	16.2	17.0	17.8	18.7	19.5	20.3	21.1	22.0	22.5
152.5°	11.8	12.6	13.3	14.1	14.8	15.6	16.3	17.1	17.8	18.6	19.1
155°	9.4	10.0	10.7	11.3	12.0	12.6	13.2	13.9	14.5	15.2	15.7
157.5°	7.1	7.7	8.2	8.8	9.4	9.9	10.5	11.1	11.6	12.2	12.7
160°	5.2	5.6	6.1	6.6	7.0	7.5	7.9	8.4	8.9	9.3	9.7
162.5°	3.5	3.9	4.3	4.6	5.0	5.3	5.7	6.0	6.4	6.8	7.1
165°	2.1	2.4	2.7	2.9	3.2	3.4	3.7	4.0	4.2	4.5	4.7
167.5°	1.3	1.5	1.6	1.8	2.0	2.1	2.3	2.4	2.6	2.7	2.9
170°	0.8	0.9	1.0	1.0	1.1	1.2	1.3	1.4	1.4	1.5	1.6
172.5°	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.9	0.9	0.9	1.0
175°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.8	0.8
177.5°	0.7	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.8	0.8	0.8
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	98.4	98.3	98.3	98.2	98.2	98.1	98.0	98.0	98.0	97.9	97.9
5°	100.1	100.0	100.0	99.9	99.8	99.7	99.6	99.6	99.5	99.4	99.4
7.5°	103.1	103.2	103.2	103.3	103.3	103.3	103.4	103.4	103.2	103.0	102.8
10°	107.2	107.3	107.3	107.4	107.5	107.6	107.7	107.8	107.5	107.3	107.1
12.5°	110.0	110.1	110.2	110.3	110.4	110.5	110.6	110.8	110.7	110.6	110.5
15°	115.9	115.9	115.8	115.8	115.8	115.7	115.7	115.7	115.5	115.4	115.2
17.5°	118.9	119.2	119.5	119.7	120.0	120.3	120.6	120.9	120.6	120.3	120.0
20°	122.5	123.1	123.6	124.2	124.8	125.3	125.9	126.5	126.1	125.7	125.3
22.5°	126.5	126.9	127.4	127.9	128.4	128.9	129.4	129.9	129.6	129.4	129.2
25°	130.8	130.9	131.1	131.2	131.4	131.5	131.7	131.8	131.9	131.9	132.0
27.5°	134.3	134.4	134.5	134.6	134.7	134.8	134.9	135.0	135.2	135.3	135.4
30°	136.7	137.0	137.4	137.7	138.1	138.4	138.8	139.1	139.3	139.4	139.6
32.5°	139.4	140.0	140.6	141.2	141.8	142.3	142.9	143.5	143.6	143.7	143.8
35°	143.9	144.1	144.3	144.5	144.6	144.8	145.0	145.2	145.5	145.8	146.1
37.5°	143.7	144.4	145.1	145.8	146.5	147.1	147.8	148.5	148.8	149.1	149.4
40°	147.0	147.7	148.4	149.1	149.9	150.6	151.3	152.0	152.3	152.5	152.8
42.5°	146.5	147.3	148.1	148.9	149.8	150.6	151.4	152.3	152.8	153.3	153.8
45°	148.9	149.7	150.5	151.3	152.2	153.0	153.8	154.6	155.1	155.6	156.1
47.5°	148.2	149.0	149.9	150.7	151.5	152.4	153.2	154.1	154.8	155.5	156.2
50°	149.9	150.8	151.7	152.5	153.4	154.3	155.2	156.1	156.7	157.3	157.9
52.5°	151.1	152.2	153.2	154.3	155.4	156.4	157.5	158.6	159.1	159.6	160.0
55°	150.3	151.3	152.2	153.1	154.0	154.9	155.9	156.8	157.5	158.2	158.9
57.5°	148.1	149.3	150.5	151.7	152.8	154.0	155.2	156.4	157.2	158.0	158.8
60°	147.7	148.8	149.9	151.0	152.1	153.2	154.2	155.3	156.3	157.2	158.1
62.5°	146.3	147.1	147.9	148.7	149.5	150.3	151.1	151.9	153.2	154.5	155.8
65°	145.0	146.3	147.5	148.8	150.0	151.3	152.5	153.8	154.8	155.7	156.7
67.5°	143.2	144.3	145.3	146.3	147.4	148.4	149.4	150.5	151.6	152.8	153.9
70°	140.3	141.9	143.5	145.1	146.7	148.3	149.9	151.5	152.4	153.3	154.1
72.5°	138.3	139.8	141.3	142.8	144.3	145.8	147.3	148.8	149.7	150.6	151.5
75°	134.6	136.3	138.1	139.9	141.6	143.4	145.1	146.9	147.8	148.7	149.7
77.5°	132.1	133.6	135.0	136.5	138.0	139.4	140.9	142.4	143.4	144.5	145.5
80°	127.6	129.2	130.8	132.4	134.0	135.6	137.2	138.8	139.9	141.1	142.2
82.5°	124.8	126.3	127.8	129.4	130.9	132.4	133.9	135.4	136.6	137.8	139.0
85°	121.1	122.7	124.3	125.9	127.5	129.0	130.6	132.2	133.4	134.6	135.8
87.5°	118.4	120.1	121.7	123.4	125.1	126.7	128.4	130.1	131.1	132.1	133.1
90°	114.6	116.1	117.7	119.3	120.9	122.5	124.1	125.7	126.8	128.0	129.1
92.5°	110.8	112.3	113.8	115.3	116.8	118.3	119.8	121.2	122.5	123.7	124.9
95°	107.3	109.1	110.9	112.6	114.4	116.2	117.9	119.7	120.7	121.6	122.6
97.5°	104.2	105.8	107.3	108.9	110.5	112.0	113.6	115.2	116.2	117.3	118.4
100°	100.4	102.0	103.6	105.2	106.7	108.3	109.9	111.5	112.6	113.7	114.8
102.5°	96.5	98.0	99.6	101.2	102.8	104.4	106.0	107.6	108.6	109.6	110.7
105°	93.1	94.7	96.2	97.7	99.2	100.7	102.3	103.8	104.8	105.9	106.9
107.5°	89.5	91.0	92.6	94.1	95.6	97.1	98.7	100.2	101.2	102.1	103.1
110°	85.7	87.2	88.7	90.1	91.6	93.1	94.6	96.1	97.0	97.9	98.9

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	81.8	83.3	84.7	86.2	87.6	89.1	90.6	92.0	92.9	93.9	94.8
115°	77.6	79.1	80.5	81.9	83.3	84.7	86.1	87.6	88.5	89.4	90.3
117.5°	73.7	75.1	76.4	77.7	79.0	80.4	81.7	83.0	83.9	84.8	85.7
120°	69.7	70.9	72.2	73.4	74.6	75.9	77.1	78.3	79.2	80.1	81.0
122.5°	65.9	67.1	68.2	69.4	70.5	71.7	72.9	74.0	74.9	75.7	76.6
125°	61.8	62.9	64.1	65.2	66.3	67.5	68.6	69.8	70.6	71.4	72.2
127.5°	57.8	58.8	59.9	61.0	62.1	63.2	64.3	65.4	66.1	66.9	67.7
130°	53.8	54.8	55.8	56.9	57.9	58.9	60.0	61.0	61.7	62.4	63.1
132.5°	49.8	50.7	51.7	52.6	53.6	54.5	55.5	56.4	57.1	57.8	58.5
135°	45.8	46.7	47.6	48.5	49.4	50.3	51.2	52.1	52.7	53.3	54.0
137.5°	41.8	42.7	43.5	44.4	45.3	46.1	47.0	47.8	48.4	49.0	49.5
140°	37.9	38.7	39.5	40.3	41.1	41.9	42.8	43.6	44.1	44.6	45.2
142.5°	33.9	34.7	35.5	36.2	37.0	37.8	38.5	39.3	39.8	40.3	40.8
145°	30.3	31.0	31.7	32.4	33.1	33.8	34.5	35.2	35.7	36.1	36.6
147.5°	26.7	27.3	27.9	28.6	29.2	29.8	30.5	31.1	31.5	32.0	32.4
150°	23.1	23.7	24.3	24.8	25.4	26.0	26.5	27.1	27.5	27.9	28.3
152.5°	19.7	20.2	20.8	21.3	21.9	22.4	23.0	23.5	23.9	24.2	24.6
155°	16.2	16.7	17.2	17.7	18.2	18.7	19.3	19.8	20.1	20.4	20.8
157.5°	13.1	13.5	14.0	14.4	14.9	15.3	15.7	16.2	16.5	16.8	17.1
160°	10.1	10.5	10.8	11.2	11.6	12.0	12.3	12.7	13.0	13.3	13.6
162.5°	7.4	7.7	8.1	8.4	8.7	9.0	9.4	9.7	9.9	10.1	10.4
165°	5.0	5.3	5.5	5.8	6.0	6.3	6.6	6.8	7.0	7.2	7.4
167.5°	3.1	3.3	3.5	3.7	3.8	4.0	4.2	4.4	4.6	4.7	4.9
170°	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.4	2.5	2.6	2.8
172.5°	1.0	1.0	1.1	1.1	1.2	1.2	1.2	1.3	1.3	1.4	1.4
175°	0.8	0.8	0.8	0.8	0.9	0.9	0.9	0.9	0.9	0.9	0.9
177.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.9
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	97.9	97.8	97.8	97.7	97.7	97.7	97.6	97.6	97.5	97.5	97.4
5°	99.3	99.3	99.2	99.1	99.1	99.0	99.0	99.0	99.0	98.9	98.9
7.5°	102.5	102.3	102.1	101.9	101.7	101.4	101.4	101.4	101.3	101.3	101.3
10°	106.9	106.6	106.4	106.2	106.0	105.7	105.6	105.5	105.3	105.2	105.1
12.5°	110.3	110.2	110.1	110.0	109.9	109.8	109.7	109.5	109.4	109.2	109.1
15°	115.1	114.9	114.8	114.6	114.5	114.3	114.2	114.0	113.9	113.8	113.6
17.5°	119.7	119.3	119.0	118.7	118.4	118.1	118.0	118.0	117.9	117.9	117.8
20°	124.9	124.6	124.2	123.8	123.4	123.1	123.0	122.9	122.8	122.7	122.6
22.5°	128.9	128.7	128.4	128.2	128.0	127.7	127.7	127.6	127.5	127.5	127.4
25°	132.0	132.1	132.1	132.2	132.2	132.3	132.2	132.0	131.9	131.8	131.6
27.5°	135.6	135.7	135.9	136.0	136.1	136.3	136.1	136.0	135.9	135.8	135.7
30°	139.7	139.9	140.0	140.2	140.3	140.5	140.3	140.1	139.9	139.7	139.5
32.5°	143.9	144.0	144.1	144.2	144.3	144.4	144.2	143.9	143.7	143.5	143.2
35°	146.5	146.8	147.1	147.4	147.7	148.1	147.8	147.6	147.3	147.1	146.8
37.5°	149.7	150.0	150.3	150.6	150.9	151.1	150.9	150.6	150.3	150.0	149.7
40°	153.0	153.3	153.6	153.8	154.1	154.4	154.0	153.6	153.3	152.9	152.6
42.5°	154.3	154.8	155.3	155.8	156.3	156.8	156.4	155.9	155.5	155.0	154.6
45°	156.5	157.0	157.5	158.0	158.5	158.9	158.4	157.9	157.3	156.8	156.2
47.5°	156.8	157.5	158.2	158.9	159.6	160.3	159.8	159.4	158.9	158.5	158.0
50°	158.5	159.2	159.8	160.4	161.0	161.6	161.1	160.7	160.2	159.7	159.2
52.5°	160.5	161.0	161.5	162.0	162.5	163.0	162.4	161.8	161.2	160.6	160.0
55°	159.7	160.4	161.1	161.8	162.6	163.3	162.7	162.2	161.7	161.2	160.6
57.5°	159.6	160.4	161.2	162.0	162.8	163.6	163.0	162.5	161.9	161.4	160.8
60°	159.0	160.0	160.9	161.8	162.7	163.7	163.1	162.5	162.0	161.4	160.9
62.5°	157.0	158.3	159.6	160.9	162.2	163.4	162.9	162.3	161.8	161.2	160.7
65°	157.6	158.6	159.5	160.5	161.4	162.4	161.9	161.4	160.9	160.4	159.9
67.5°	155.0	156.2	157.3	158.5	159.6	160.7	160.2	159.8	159.3	158.8	158.3
70°	155.0	155.9	156.7	157.6	158.4	159.3	158.8	158.4	157.9	157.4	156.9
72.5°	152.4	153.3	154.2	155.2	156.1	157.0	156.6	156.2	155.8	155.4	155.0
75°	150.6	151.5	152.5	153.4	154.3	155.3	154.8	154.4	153.9	153.5	153.1
77.5°	146.6	147.7	148.7	149.8	150.8	151.9	151.5	151.1	150.8	150.4	150.0
80°	143.3	144.4	145.6	146.7	147.8	149.0	148.6	148.2	147.9	147.5	147.2
82.5°	140.3	141.5	142.7	143.9	145.1	146.3	145.9	145.5	145.1	144.7	144.3
85°	136.9	138.1	139.3	140.5	141.7	142.9	142.6	142.3	142.0	141.7	141.4
87.5°	134.1	135.1	136.1	137.1	138.1	139.2	138.9	138.6	138.3	138.0	137.8
90°	130.2	131.4	132.5	133.7	134.8	135.9	135.6	135.3	135.0	134.7	134.4
92.5°	126.2	127.4	128.6	129.9	131.1	132.3	132.0	131.8	131.5	131.2	131.0
95°	123.6	124.6	125.6	126.5	127.5	128.5	128.3	128.0	127.8	127.5	127.3
97.5°	119.4	120.5	121.6	122.6	123.7	124.8	124.6	124.4	124.3	124.1	123.9
100°	115.9	117.0	118.1	119.2	120.3	121.4	121.2	120.9	120.7	120.5	120.2
102.5°	111.7	112.7	113.8	114.8	115.8	116.9	116.8	116.6	116.5	116.4	116.2
105°	108.0	109.1	110.1	111.2	112.2	113.3	113.1	113.0	112.9	112.7	112.6
107.5°	104.1	105.1	106.1	107.0	108.0	109.0	108.9	108.7	108.6	108.5	108.3
110°	99.8	100.7	101.7	102.6	103.6	104.5	104.5	104.4	104.4	104.3	104.3

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	95.7	96.6	97.5	98.5	99.4	100.3	100.2	100.2	100.1	100.1	100.0
115°	91.2	92.1	93.0	94.0	94.9	95.8	95.8	95.7	95.7	95.7	95.7
117.5°	86.6	87.5	88.4	89.3	90.2	91.1	91.1	91.1	91.1	91.1	91.1
120°	81.9	82.7	83.6	84.5	85.4	86.3	86.3	86.4	86.4	86.5	86.5
122.5°	77.5	78.3	79.2	80.0	80.9	81.8	81.8	81.9	81.9	82.0	82.0
125°	73.0	73.8	74.6	75.4	76.2	77.0	77.0	77.1	77.2	77.2	77.3
127.5°	68.4	69.2	70.0	70.7	71.5	72.2	72.3	72.4	72.5	72.6	72.7
130°	63.9	64.6	65.3	66.0	66.7	67.4	67.5	67.7	67.8	67.9	68.0
132.5°	59.1	59.8	60.5	61.2	61.8	62.5	62.6	62.8	62.9	63.1	63.2
135°	54.6	55.2	55.8	56.5	57.1	57.7	57.9	58.1	58.2	58.4	58.5
137.5°	50.1	50.7	51.3	51.8	52.4	53.0	53.1	53.3	53.5	53.6	53.8
140°	45.7	46.2	46.7	47.3	47.8	48.3	48.5	48.7	48.9	49.1	49.3
142.5°	41.3	41.8	42.3	42.8	43.3	43.8	44.0	44.2	44.4	44.5	44.7
145°	37.1	37.5	38.0	38.5	38.9	39.4	39.6	39.8	40.0	40.2	40.3
147.5°	32.8	33.3	33.7	34.1	34.5	35.0	35.2	35.4	35.6	35.8	36.0
150°	28.7	29.1	29.5	30.0	30.4	30.8	31.0	31.2	31.4	31.6	31.8
152.5°	24.9	25.3	25.6	26.0	26.3	26.6	26.8	27.0	27.2	27.4	27.6
155°	21.1	21.5	21.8	22.2	22.5	22.8	23.0	23.2	23.3	23.5	23.7
157.5°	17.4	17.7	18.0	18.3	18.5	18.8	19.0	19.2	19.4	19.6	19.7
160°	13.8	14.1	14.4	14.7	15.0	15.2	15.4	15.6	15.7	15.9	16.1
162.5°	10.6	10.8	11.0	11.3	11.5	11.7	11.9	12.0	12.2	12.4	12.5
165°	7.6	7.8	8.0	8.2	8.4	8.6	8.7	8.8	9.0	9.1	9.2
167.5°	5.1	5.2	5.4	5.6	5.8	5.9	6.0	6.1	6.2	6.3	6.4
170°	2.9	3.0	3.1	3.2	3.3	3.5	3.5	3.6	3.7	3.8	3.9
172.5°	1.5	1.5	1.6	1.6	1.7	1.7	1.8	1.9	1.9	2.0	2.0
175°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.0	1.0	1.0
177.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2	97.2
2.5°	97.4	97.3	97.3	97.2	97.5	97.7	97.9	98.1	98.4	98.6	98.8
5°	98.9	98.9	98.8	98.8	98.9	99.0	99.1	99.3	99.4	99.5	99.6
7.5°	101.3	101.2	101.2	101.2	101.3	101.4	101.6	101.7	101.8	102.0	102.1
10°	105.0	104.8	104.7	104.6	104.6	104.7	104.8	104.9	105.0	105.0	105.1
12.5°	108.9	108.8	108.6	108.5	108.6	108.8	109.0	109.2	109.4	109.5	109.7
15°	113.5	113.3	113.2	113.1	113.1	113.1	113.2	113.2	113.3	113.3	113.4
17.5°	117.8	117.7	117.7	117.7	117.7	117.8	117.9	118.0	118.1	118.2	118.3
20°	122.5	122.4	122.3	122.2	122.3	122.4	122.5	122.6	122.7	122.8	122.9
22.5°	127.4	127.3	127.2	127.2	127.3	127.4	127.4	127.5	127.6	127.7	127.8
25°	131.5	131.4	131.2	131.1	131.1	131.2	131.2	131.2	131.3	131.3	131.4
27.5°	135.5	135.4	135.3	135.2	135.3	135.4	135.6	135.7	135.8	136.0	136.1
30°	139.3	139.1	138.9	138.7	138.7	138.7	138.6	138.6	138.6	138.6	138.5
32.5°	143.0	142.7	142.5	142.2	142.2	142.3	142.3	142.3	142.3	142.3	142.3
35°	146.6	146.3	146.1	145.8	145.9	146.1	146.2	146.3	146.4	146.6	146.7
37.5°	149.4	149.1	148.8	148.6	148.4	148.2	148.0	147.8	147.7	147.5	147.3
40°	152.2	151.8	151.5	151.1	150.9	150.7	150.4	150.2	150.0	149.7	149.5
42.5°	154.1	153.7	153.2	152.8	152.5	152.2	151.9	151.6	151.4	151.1	150.8
45°	155.7	155.2	154.6	154.1	153.9	153.7	153.4	153.2	153.0	152.8	152.6
47.5°	157.5	157.1	156.6	156.2	155.9	155.7	155.4	155.1	154.9	154.6	154.4
50°	158.7	158.2	157.7	157.2	156.8	156.4	156.0	155.6	155.2	154.8	154.4
52.5°	159.3	158.7	158.1	157.5	157.1	156.6	156.2	155.7	155.3	154.8	154.4
55°	160.1	159.6	159.0	158.5	158.0	157.5	157.1	156.6	156.1	155.6	155.1
57.5°	160.3	159.7	159.2	158.6	158.1	157.5	156.9	156.4	155.8	155.3	154.7
60°	160.3	159.8	159.2	158.7	158.0	157.4	156.8	156.1	155.5	154.9	154.3
62.5°	160.1	159.6	159.0	158.5	158.3	158.1	157.9	157.7	157.5	157.4	157.2
65°	159.4	158.9	158.5	158.0	157.3	156.7	156.1	155.5	154.8	154.2	153.6
67.5°	157.8	157.4	156.9	156.4	156.0	155.5	155.1	154.6	154.2	153.7	153.3
70°	156.5	156.0	155.5	155.1	154.5	153.9	153.4	152.8	152.3	151.7	151.1
72.5°	154.6	154.2	153.8	153.4	152.6	151.8	151.0	150.2	149.4	148.6	147.8
75°	152.6	152.2	151.7	151.3	150.8	150.3	149.8	149.2	148.7	148.2	147.7
77.5°	149.7	149.3	148.9	148.6	148.2	147.8	147.4	147.0	146.7	146.3	145.9
80°	146.8	146.4	146.1	145.7	145.3	144.8	144.4	143.9	143.4	143.0	142.5
82.5°	143.9	143.5	143.1	142.7	142.4	142.0	141.6	141.2	140.8	140.4	140.1
85°	141.1	140.8	140.5	140.2	139.7	139.2	138.6	138.1	137.6	137.1	136.6
87.5°	137.5	137.2	136.9	136.6	136.2	135.7	135.2	134.7	134.3	133.8	133.3
90°	134.1	133.8	133.5	133.3	132.6	132.0	131.4	130.8	130.2	129.6	129.0
92.5°	130.7	130.4	130.2	129.9	129.4	128.9	128.4	127.9	127.4	126.9	126.4
95°	127.0	126.8	126.5	126.3	125.7	125.1	124.6	124.0	123.4	122.9	122.3
97.5°	123.8	123.6	123.4	123.3	122.6	122.0	121.4	120.7	120.1	119.5	118.9
100°	120.0	119.8	119.6	119.3	118.8	118.3	117.8	117.3	116.7	116.2	115.7
102.5°	116.1	116.0	115.9	115.7	115.2	114.8	114.3	113.8	113.3	112.8	112.4
105°	112.5	112.3	112.2	112.1	111.6	111.1	110.7	110.2	109.8	109.3	108.9
107.5°	108.2	108.1	107.9	107.8	107.4	106.9	106.5	106.0	105.6	105.1	104.7
110°	104.2	104.2	104.1	104.1	103.6	103.1	102.7	102.2	101.7	101.3	100.8

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	100.0	99.9	99.9	99.8	99.5	99.2	98.9	98.6	98.3	98.0	97.6
115°	95.6	95.6	95.6	95.6	95.1	94.7	94.2	93.8	93.3	92.9	92.4
117.5°	91.1	91.1	91.1	91.1	90.7	90.3	89.9	89.5	89.1	88.7	88.3
120°	86.6	86.6	86.7	86.7	86.4	86.1	85.8	85.5	85.2	84.8	84.5
122.5°	82.0	82.1	82.1	82.2	81.9	81.6	81.3	81.0	80.7	80.4	80.1
125°	77.4	77.4	77.5	77.6	77.3	77.0	76.8	76.5	76.3	76.0	75.8
127.5°	72.8	72.8	72.9	73.0	72.7	72.5	72.2	71.9	71.7	71.4	71.1
130°	68.1	68.2	68.3	68.5	68.3	68.1	67.9	67.8	67.6	67.4	67.3
132.5°	63.4	63.5	63.7	63.8	63.6	63.5	63.3	63.1	62.9	62.8	62.6
135°	58.7	58.9	59.0	59.2	59.0	58.9	58.8	58.6	58.5	58.3	58.2
137.5°	53.9	54.1	54.3	54.4	54.3	54.2	54.2	54.1	54.0	53.9	53.8
140°	49.4	49.6	49.8	50.0	49.9	49.9	49.8	49.7	49.7	49.6	49.5
142.5°	44.9	45.1	45.3	45.4	45.4	45.4	45.4	45.3	45.3	45.3	45.2
145°	40.5	40.7	40.9	41.1	41.1	41.1	41.1	41.1	41.1	41.1	41.1
147.5°	36.1	36.3	36.5	36.7	36.7	36.7	36.7	36.7	36.7	36.7	36.7
150°	32.0	32.2	32.4	32.6	32.6	32.6	32.6	32.6	32.6	32.6	32.6
152.5°	27.7	27.9	28.1	28.3	28.3	28.4	28.4	28.5	28.5	28.6	28.6
155°	23.8	24.0	24.2	24.4	24.4	24.5	24.5	24.5	24.6	24.6	24.7
157.5°	19.9	20.1	20.3	20.5	20.5	20.6	20.6	20.7	20.8	20.8	20.9
160°	16.2	16.4	16.5	16.7	16.7	16.7	16.8	16.8	16.8	16.8	16.8
162.5°	12.7	12.8	13.0	13.1	13.2	13.2	13.2	13.3	13.3	13.4	13.4
165°	9.4	9.5	9.6	9.8	9.9	9.9	10.0	10.1	10.2	10.3	10.4
167.5°	6.5	6.7	6.8	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9
170°	4.0	4.1	4.2	4.2	4.2	4.3	4.3	4.3	4.3	4.3	4.3
172.5°	2.1	2.2	2.2	2.3	2.3	2.3	2.2	2.2	2.2	2.2	2.2
175°	1.0	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.0	1.0	1.0
177.5°	0.8	0.8	0.8	0.8	0.8	0.9	0.9	0.9	1.0	1.0	1.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600778
 CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	97.2	97.2
2.5°	99.1	99.3
5°	99.7	99.8
7.5°	102.3	102.4
10°	105.2	105.3
12.5°	109.9	110.1
15°	113.4	113.5
17.5°	118.4	118.5
20°	123.0	123.1
22.5°	127.8	127.9
25°	131.4	131.5
27.5°	136.2	136.4
30°	138.5	138.5
32.5°	142.3	142.3
35°	146.8	147.0
37.5°	147.1	147.0
40°	149.3	149.0
42.5°	150.5	150.2
45°	152.4	152.2
47.5°	154.1	153.8
50°	153.9	153.5
52.5°	153.9	153.5
55°	154.7	154.2
57.5°	154.1	153.6
60°	153.6	153.0
62.5°	157.0	156.8
65°	153.0	152.4
67.5°	152.9	152.4
70°	150.6	150.0
72.5°	147.0	146.2
75°	147.2	146.7
77.5°	145.5	145.1
80°	142.1	141.6
82.5°	139.7	139.3
85°	136.1	135.6
87.5°	132.8	132.4
90°	128.3	127.7
92.5°	125.9	125.4
95°	121.8	121.2
97.5°	118.2	117.6
100°	115.2	114.7
102.5°	111.9	111.4
105°	108.4	108.0
107.5°	104.2	103.8
110°	100.4	99.9

REPORT NUMBER: P600778
CATALOG NUMBER: FE10A35GLMW

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	97.3	97.0
115°	92.0	91.5
117.5°	87.9	87.5
120°	84.2	83.9
122.5°	79.8	79.5
125°	75.5	75.2
127.5°	70.9	70.6
130°	67.1	66.9
132.5°	62.4	62.2
135°	58.0	57.9
137.5°	53.7	53.6
140°	49.5	49.4
142.5°	45.2	45.2
145°	41.1	41.1
147.5°	36.7	36.7
150°	32.6	32.7
152.5°	28.6	28.7
155°	24.7	24.8
157.5°	20.9	21.0
160°	16.9	16.9
162.5°	13.4	13.5
165°	10.5	10.5
167.5°	6.9	6.9
170°	4.3	4.3
172.5°	2.1	2.1
175°	1.0	1.0
177.5°	1.0	1.1
180°	0.0	0.0

(END OF REPORT)