

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210371

Luminaire Tested: **PR8R20D010 - PR8M12WDMW - 4000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P210371  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR8R20D010 - PR8M12WDMW - 4000K  
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE WHITE FINISH  
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2305.1 lumens  
Efficiency: N/A  
Efficacy: 104.8 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 22  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210371

CATALOG NUMBER: PR8R20D010 - PR8M12WDMW - 4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P210371

CATALOG NUMBER: PR8R20D010 - PR8M12WDMW - 4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	27965
5°	28438
10°	28779
15°	29313
20°	29931
25°	30203
30°	30159
35°	30081
40°	29035
45°	26593
50°	22216
55°	18472
60°	15523
65°	12827
70°	11026
75°	8650
80°	5984
85°	6298



TEST NUMBER: P210371

CATALOG NUMBER: PR8R20D010 - PR8M12WDMW - 4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	87.5	3.8
10°-20°	259.8	11.3
20°-30°	408.0	17.7
30°-40°	497.4	21.6
40°-50°	464.9	20.2
50°-60°	310.1	13.5
60°-70°	178.4	7.7
70°-80°	82.3	3.6
80°-90°	16.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	755.4	32.8
0°-40°	1252.7	54.3
0°-60°	2027.7	88.0
0°-90°	2305.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2305.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	907	
5°	919	88
15°	918	260
25°	888	408
35°	799	497
45°	610	465
55°	344	310
65°	176	178
75°	73	82
85°	18	17
90°	0	



TEST NUMBER: P210371

CATALOG NUMBER: PR8R20D010 - PR8M12WDMW - 4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	906.9
2.5°	908.4
5°	918.7
7.5°	917.7
10°	919.1
12.5°	917.3
15°	918.2
17.5°	916.3
20°	912.1
22.5°	897.1
25°	887.7
27.5°	869.0
30°	847.0
32.5°	824.9
35°	799.1
37.5°	768.2
40°	721.3
42.5°	670.3
45°	609.8
47.5°	542.8
50°	463.1
52.5°	395.6
55°	343.6
57.5°	293.9
60°	251.7
62.5°	215.1
65°	175.8
67.5°	144.4
70°	122.3
72.5°	104.1
75°	72.6
77.5°	57.7
80°	33.7
82.5°	21.6
85°	17.8
87.5°	5.2
90°	0.0

(END OF REPORT)