

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P600779

Luminaire Tested: **FE10A35GLMW-NL**

Issue Date: 07/11/2022

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.



Test Information

Test Method: LM-79-08
 Report Number: P600779
 Test Lab: Third Party
 Issue Date: 07/11/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: FE10A35GLMW-NL
 Description: LED Entry Light w/ Night Light -White 3500K (Night Light)
 Light Source: 70 CRI LEDs
 Ballast/Driver: (1) Electronic Driver

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 38.9 lumens
 Efficiency: N/A
 Efficacy: 11.5 lumens/watt
 Luminous Opening: Point Source (0m x 0m x 0m)
 IES Classification: Type IV - V Long
 BUG Rating: B0 - U2 - G0


Input Watts (W): 3.39
 Input Voltage (V): 120.0
 Input Current (Ain): 0.028
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 0 fc
 Type IV - V Long - N/A

REPORT NUMBER: P600779
CATALOG NUMBER: FE10A35GLMW-NL

Luminous Intensity Polar Plot



— Vertical Plane Through 337.5-Deg Lateral - - - Horizontal Cone Through 87.5-Deg Vertical

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	4.1	3.7	7.8
	% Fixture	10.6	9.6	20.2
Street Side	Lumens	15.9	15.1	31.1
	% Fixture	40.9	38.9	79.8
Total	Lumens	20.0	18.9	38.9
	% Fixture	51.5	48.5	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	0.0	0.1
10°-20°	0.2	0.5
20°-30°	0.6	1.6
30°-40°	1.3	3.4
40°-50°	2.2	5.6
50°-60°	3.0	7.8
60°-70°	3.8	9.7
70°-80°	4.3	11.1
80°-90°	4.6	11.8
90°-100°	4.5	11.6
100°-110°	4.1	10.7
110°-120°	3.5	9.1
120°-130°	2.8	7.1
130°-140°	1.9	5.0
140°-150°	1.2	3.1
150°-160°	0.6	1.5
160°-170°	0.2	0.4
170°-180°	0.0	0.0
0°-90°	20.0	51.5
0°-180°	38.9	100.0




REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	0.7	1.7			
FM (30°-60°)	5.2	13.3			
FH (60°-80°)	6.4	16.6			G0/660
FVH (80°-90°)	3.6	9.4			G0/10
BL (0°-30°)	0.2	0.5	B0/110		
BM (30°-60°)	1.3	3.4	B0/220		
BH (60°-80°)	1.7	4.3	B0/110		G0/110
BVH (80°-90°)	0.9	2.4			G0/10
UL (90°-100°)	4.5	11.6		U1/10	
UH (100°-180°)	14.3	36.9		U2/50	

BUG Rating: B0-U2-G0
 Type IV V Long



REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
7.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
10°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
12.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
15°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
17.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
20°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
22.5°	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0	2.0
25°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
27.5°	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7	2.7
30°	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0	3.0
32.5°	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4	3.4
35°	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7	3.7
37.5°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.0
40°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.3
42.5°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
45°	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0	5.0
47.5°	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.3	5.2
50°	5.5	5.5	5.5	5.5	5.5	5.5	5.5	5.6	5.6	5.6	5.5
52.5°	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8	5.8
55°	6.0	6.0	6.0	6.0	6.0	6.0	6.1	6.1	6.1	6.1	6.0
57.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.2
60°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.4
62.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.6
65°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.8
67.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
70°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.1
72.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.2
75°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.3
77.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.4
80°	7.5	7.5	7.5	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.5
82.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.5
85°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
87.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
90°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.5
92.5°	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.5
95°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.6	7.6	7.6	7.5
97.5°	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.4
100°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.3
102.5°	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.2
105°	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.1
107.5°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
110°	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.8

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.6
115°	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5	6.5
117.5°	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3	6.3
120°	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1
122.5°	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
125°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.6
127.5°	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4	5.4
130°	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
132.5°	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
135°	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.6
137.5°	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
140°	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
142.5°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.9	3.9	3.8
145°	3.5	3.5	3.5	3.5	3.6	3.6	3.6	3.6	3.6	3.6	3.5
147.5°	3.2	3.2	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.3	3.2
150°	2.9	2.9	2.9	3.0	3.0	3.0	3.0	3.0	3.0	3.0	2.9
152.5°	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6	2.6
155°	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3	2.3
157.5°	1.9	1.9	1.9	1.9	1.9	1.9	2.0	2.0	2.0	2.0	1.9
160°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6
162.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
165°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
167.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
170°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
172.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
7.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
10°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
12.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
15°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	0.9	0.9	0.9
17.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.2	1.2	1.2	1.2	1.2
20°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.5	1.5	1.5	1.5
22.5°	2.0	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.8	1.8	1.8
25°	2.3	2.3	2.3	2.3	2.2	2.2	2.2	2.2	2.1	2.1	2.1
27.5°	2.6	2.6	2.6	2.6	2.6	2.5	2.5	2.5	2.4	2.4	2.4
30°	3.0	3.0	2.9	2.9	2.9	2.9	2.8	2.8	2.8	2.7	2.7
32.5°	3.3	3.3	3.3	3.2	3.2	3.2	3.2	3.1	3.1	3.0	2.9
35°	3.7	3.6	3.6	3.6	3.5	3.5	3.5	3.4	3.4	3.3	3.2
37.5°	4.0	4.0	3.9	3.9	3.9	3.8	3.8	3.7	3.7	3.6	3.5
40°	4.3	4.3	4.2	4.2	4.2	4.1	4.1	4.0	4.0	3.9	3.8
42.5°	4.6	4.6	4.5	4.5	4.4	4.4	4.4	4.3	4.2	4.1	4.1
45°	4.9	4.9	4.8	4.8	4.7	4.7	4.6	4.6	4.5	4.4	4.3
47.5°	5.2	5.1	5.1	5.0	5.0	4.9	4.9	4.8	4.8	4.7	4.6
50°	5.5	5.4	5.3	5.3	5.2	5.2	5.1	5.1	5.0	4.9	4.8
52.5°	5.7	5.7	5.6	5.5	5.5	5.4	5.4	5.3	5.2	5.1	5.0
55°	5.9	5.9	5.8	5.8	5.7	5.7	5.6	5.6	5.4	5.3	5.2
57.5°	6.2	6.1	6.1	6.0	5.9	5.9	5.8	5.8	5.6	5.5	5.4
60°	6.4	6.3	6.3	6.2	6.1	6.1	6.0	6.0	5.8	5.7	5.6
62.5°	6.6	6.5	6.4	6.4	6.3	6.3	6.2	6.1	6.0	5.9	5.8
65°	6.7	6.7	6.6	6.5	6.5	6.4	6.4	6.3	6.2	6.0	5.9
67.5°	6.9	6.8	6.8	6.7	6.6	6.6	6.5	6.4	6.3	6.2	6.0
70°	7.0	7.0	6.9	6.8	6.8	6.7	6.6	6.6	6.4	6.3	6.2
72.5°	7.2	7.1	7.0	6.9	6.9	6.8	6.7	6.7	6.5	6.4	6.3
75°	7.3	7.2	7.1	7.1	7.0	6.9	6.8	6.8	6.6	6.5	6.4
77.5°	7.3	7.3	7.2	7.1	7.1	7.0	6.9	6.8	6.7	6.6	6.4
80°	7.4	7.3	7.3	7.2	7.1	7.1	7.0	6.9	6.8	6.6	6.5
82.5°	7.5	7.4	7.3	7.2	7.2	7.1	7.0	6.9	6.8	6.7	6.5
85°	7.5	7.4	7.3	7.3	7.2	7.1	7.0	7.0	6.8	6.7	6.6
87.5°	7.5	7.4	7.4	7.3	7.2	7.1	7.1	7.0	6.8	6.7	6.6
90°	7.5	7.4	7.3	7.3	7.2	7.1	7.0	7.0	6.8	6.7	6.6
92.5°	7.5	7.4	7.3	7.2	7.2	7.1	7.0	6.9	6.8	6.7	6.5
95°	7.4	7.3	7.3	7.2	7.1	7.0	7.0	6.9	6.8	6.6	6.5
97.5°	7.3	7.3	7.2	7.1	7.0	7.0	6.9	6.8	6.7	6.6	6.4
100°	7.3	7.2	7.1	7.0	7.0	6.9	6.8	6.7	6.6	6.5	6.3
102.5°	7.2	7.1	7.0	6.9	6.9	6.8	6.7	6.6	6.5	6.4	6.3
105°	7.0	7.0	6.9	6.8	6.8	6.7	6.6	6.5	6.4	6.3	6.2
107.5°	6.9	6.8	6.8	6.7	6.6	6.6	6.5	6.4	6.3	6.2	6.0
110°	6.8	6.7	6.6	6.6	6.5	6.4	6.3	6.3	6.2	6.0	5.9

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	6.6	6.5	6.4	6.4	6.3	6.3	6.2	6.1	6.0	5.9	5.8
115°	6.4	6.3	6.3	6.2	6.2	6.1	6.0	6.0	5.8	5.7	5.6
117.5°	6.2	6.2	6.1	6.0	6.0	5.9	5.8	5.8	5.7	5.6	5.4
120°	6.0	6.0	5.9	5.8	5.8	5.7	5.7	5.6	5.5	5.4	5.3
122.5°	5.8	5.7	5.7	5.6	5.6	5.5	5.5	5.4	5.3	5.2	5.1
125°	5.6	5.5	5.5	5.4	5.4	5.3	5.3	5.2	5.1	5.0	4.9
127.5°	5.3	5.3	5.2	5.2	5.1	5.1	5.0	5.0	4.9	4.8	4.7
130°	5.1	5.1	5.0	5.0	4.9	4.9	4.8	4.8	4.7	4.6	4.5
132.5°	4.9	4.8	4.8	4.7	4.7	4.6	4.6	4.5	4.4	4.3	4.2
135°	4.6	4.6	4.5	4.5	4.4	4.4	4.3	4.3	4.2	4.1	4.0
137.5°	4.3	4.3	4.2	4.2	4.2	4.1	4.1	4.0	4.0	3.9	3.8
140°	4.1	4.0	4.0	3.9	3.9	3.9	3.8	3.8	3.7	3.6	3.5
142.5°	3.8	3.7	3.7	3.7	3.6	3.6	3.5	3.5	3.4	3.4	3.3
145°	3.5	3.5	3.4	3.4	3.4	3.3	3.3	3.2	3.2	3.1	3.1
147.5°	3.2	3.2	3.1	3.1	3.1	3.0	3.0	3.0	2.9	2.9	2.8
150°	2.9	2.9	2.8	2.8	2.8	2.8	2.7	2.7	2.6	2.6	2.6
152.5°	2.6	2.6	2.5	2.5	2.5	2.5	2.4	2.4	2.4	2.3	2.3
155°	2.3	2.2	2.2	2.2	2.2	2.2	2.1	2.1	2.1	2.1	2.0
157.5°	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.8	1.8	1.8	1.8
160°	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.6	1.5	1.5	1.5
162.5°	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3	1.3
165°	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
167.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
170°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
172.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
5°	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2
7.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
10°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.4	0.4
12.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.6	0.6	0.6	0.6	0.6
15°	0.9	0.9	0.9	0.9	0.9	0.9	0.8	0.8	0.8	0.8	0.8
17.5°	1.2	1.2	1.1	1.1	1.1	1.1	1.1	1.0	1.0	1.0	1.0
20°	1.4	1.4	1.4	1.4	1.3	1.3	1.3	1.3	1.2	1.2	1.2
22.5°	1.7	1.7	1.7	1.6	1.6	1.6	1.5	1.5	1.4	1.4	1.4
25°	2.0	2.0	1.9	1.9	1.9	1.8	1.8	1.7	1.7	1.6	1.6
27.5°	2.3	2.3	2.2	2.2	2.1	2.1	2.0	2.0	1.9	1.9	1.8
30°	2.6	2.5	2.5	2.4	2.4	2.3	2.3	2.2	2.1	2.1	2.0
32.5°	2.9	2.8	2.8	2.7	2.6	2.6	2.5	2.4	2.4	2.3	2.2
35°	3.2	3.1	3.0	3.0	2.9	2.8	2.8	2.7	2.6	2.5	2.4
37.5°	3.5	3.4	3.3	3.2	3.2	3.1	3.0	2.9	2.8	2.7	2.6
40°	3.7	3.6	3.6	3.5	3.4	3.3	3.2	3.1	3.0	2.9	2.8
42.5°	4.0	3.9	3.8	3.7	3.6	3.6	3.4	3.3	3.2	3.1	3.0
45°	4.2	4.1	4.0	4.0	3.9	3.8	3.7	3.6	3.4	3.3	3.2
47.5°	4.5	4.4	4.3	4.2	4.1	4.0	3.9	3.8	3.6	3.5	3.4
50°	4.7	4.6	4.5	4.4	4.3	4.2	4.1	3.9	3.8	3.7	3.6
52.5°	4.9	4.8	4.7	4.6	4.5	4.4	4.3	4.1	4.0	3.9	3.7
55°	5.1	5.0	4.9	4.8	4.7	4.6	4.4	4.3	4.2	4.0	3.9
57.5°	5.3	5.2	5.1	5.0	4.8	4.7	4.6	4.5	4.3	4.2	4.0
60°	5.5	5.4	5.2	5.1	5.0	4.9	4.7	4.6	4.5	4.3	4.2
62.5°	5.6	5.5	5.4	5.3	5.2	5.0	4.9	4.7	4.6	4.4	4.3
65°	5.8	5.7	5.5	5.4	5.3	5.2	5.0	4.9	4.7	4.6	4.4
67.5°	5.9	5.8	5.7	5.5	5.4	5.3	5.1	5.0	4.8	4.7	4.5
70°	6.0	5.9	5.8	5.7	5.5	5.4	5.2	5.1	4.9	4.8	4.6
72.5°	6.1	6.0	5.9	5.8	5.6	5.5	5.3	5.2	5.0	4.8	4.7
75°	6.2	6.1	6.0	5.8	5.7	5.6	5.4	5.2	5.1	4.9	4.7
77.5°	6.3	6.2	6.0	5.9	5.8	5.6	5.5	5.3	5.1	5.0	4.8
80°	6.4	6.2	6.1	6.0	5.8	5.7	5.5	5.3	5.2	5.0	4.8
82.5°	6.4	6.3	6.1	6.0	5.9	5.7	5.5	5.4	5.2	5.0	4.9
85°	6.4	6.3	6.1	6.0	5.9	5.7	5.6	5.4	5.2	5.0	4.9
87.5°	6.4	6.3	6.2	6.0	5.9	5.7	5.6	5.4	5.2	5.1	4.9
90°	6.4	6.3	6.1	6.0	5.9	5.7	5.6	5.4	5.2	5.0	4.9
92.5°	6.4	6.3	6.1	6.0	5.8	5.7	5.5	5.4	5.2	5.0	4.9
95°	6.4	6.2	6.1	5.9	5.8	5.7	5.5	5.3	5.2	5.0	4.8
97.5°	6.3	6.2	6.0	5.9	5.8	5.6	5.5	5.3	5.1	4.9	4.8
100°	6.2	6.1	6.0	5.8	5.7	5.6	5.4	5.2	5.1	4.9	4.7
102.5°	6.1	6.0	5.9	5.7	5.6	5.5	5.3	5.2	5.0	4.8	4.7
105°	6.0	5.9	5.8	5.6	5.5	5.4	5.2	5.1	4.9	4.7	4.6
107.5°	5.9	5.8	5.7	5.5	5.4	5.3	5.1	5.0	4.8	4.7	4.5
110°	5.8	5.7	5.5	5.4	5.3	5.2	5.0	4.9	4.7	4.5	4.4

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	5.6	5.5	5.4	5.3	5.2	5.0	4.9	4.7	4.6	4.4	4.3
115°	5.5	5.4	5.3	5.1	5.0	4.9	4.8	4.6	4.5	4.3	4.2
117.5°	5.3	5.2	5.1	5.0	4.9	4.8	4.6	4.5	4.3	4.2	4.0
120°	5.2	5.0	4.9	4.8	4.7	4.6	4.5	4.3	4.2	4.0	3.9
122.5°	5.0	4.9	4.8	4.7	4.5	4.4	4.3	4.2	4.0	3.9	3.8
125°	4.8	4.7	4.6	4.5	4.4	4.3	4.1	4.0	3.9	3.7	3.6
127.5°	4.6	4.5	4.4	4.3	4.2	4.1	4.0	3.8	3.7	3.6	3.5
130°	4.4	4.3	4.2	4.1	4.0	3.9	3.8	3.6	3.5	3.4	3.3
132.5°	4.2	4.1	4.0	3.9	3.8	3.7	3.6	3.5	3.4	3.2	3.1
135°	3.9	3.8	3.8	3.7	3.6	3.5	3.4	3.3	3.2	3.1	3.0
137.5°	3.7	3.6	3.5	3.5	3.4	3.3	3.2	3.1	3.0	2.9	2.8
140°	3.5	3.4	3.3	3.2	3.2	3.1	3.0	2.9	2.8	2.7	2.6
142.5°	3.2	3.2	3.1	3.0	3.0	2.9	2.8	2.7	2.6	2.6	2.5
145°	3.0	2.9	2.9	2.8	2.8	2.7	2.6	2.5	2.5	2.4	2.3
147.5°	2.8	2.7	2.7	2.6	2.5	2.5	2.4	2.4	2.3	2.2	2.1
150°	2.5	2.5	2.4	2.4	2.3	2.3	2.2	2.2	2.1	2.0	2.0
152.5°	2.3	2.2	2.2	2.2	2.1	2.1	2.0	2.0	1.9	1.9	1.8
155°	2.0	2.0	2.0	1.9	1.9	1.9	1.8	1.8	1.7	1.7	1.6
157.5°	1.8	1.7	1.7	1.7	1.7	1.6	1.6	1.6	1.5	1.5	1.5
160°	1.5	1.5	1.5	1.4	1.4	1.4	1.4	1.4	1.3	1.3	1.3
162.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.1	1.1	1.1	1.1
165°	1.0	1.0	1.0	1.0	1.0	1.0	0.9	0.9	0.9	0.9	0.9
167.5°	0.8	0.8	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
170°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
172.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1
7.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2
10°	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.2
12.5°	0.6	0.6	0.5	0.5	0.5	0.5	0.4	0.4	0.4	0.4	0.3
15°	0.7	0.7	0.7	0.7	0.6	0.6	0.6	0.5	0.5	0.5	0.4
17.5°	0.9	0.9	0.9	0.8	0.8	0.8	0.7	0.7	0.6	0.6	0.6
20°	1.1	1.1	1.1	1.0	1.0	0.9	0.9	0.8	0.8	0.7	0.7
22.5°	1.3	1.3	1.2	1.2	1.1	1.1	1.0	1.0	0.9	0.9	0.8
25°	1.5	1.5	1.4	1.4	1.3	1.3	1.2	1.1	1.1	1.0	0.9
27.5°	1.7	1.7	1.6	1.6	1.5	1.4	1.4	1.3	1.2	1.1	1.1
30°	1.9	1.9	1.8	1.8	1.7	1.6	1.5	1.4	1.4	1.3	1.2
32.5°	2.2	2.1	2.0	1.9	1.8	1.8	1.7	1.6	1.5	1.4	1.3
35°	2.4	2.3	2.2	2.1	2.0	1.9	1.8	1.7	1.7	1.6	1.5
37.5°	2.6	2.5	2.4	2.3	2.2	2.1	2.0	1.9	1.8	1.7	1.6
40°	2.7	2.6	2.5	2.5	2.3	2.2	2.1	2.0	1.9	1.8	1.7
42.5°	2.9	2.8	2.7	2.6	2.5	2.4	2.3	2.2	2.1	2.0	1.8
45°	3.1	3.0	2.9	2.8	2.7	2.5	2.4	2.3	2.2	2.1	2.0
47.5°	3.3	3.2	3.1	2.9	2.8	2.7	2.6	2.4	2.3	2.2	2.1
50°	3.4	3.3	3.2	3.1	2.9	2.8	2.7	2.6	2.4	2.3	2.2
52.5°	3.6	3.5	3.3	3.2	3.1	2.9	2.8	2.7	2.5	2.4	2.3
55°	3.8	3.6	3.5	3.3	3.2	3.1	2.9	2.8	2.7	2.5	2.4
57.5°	3.9	3.7	3.6	3.5	3.3	3.2	3.0	2.9	2.7	2.6	2.5
60°	4.0	3.9	3.7	3.6	3.4	3.3	3.1	3.0	2.8	2.7	2.5
62.5°	4.1	4.0	3.8	3.7	3.5	3.4	3.2	3.1	2.9	2.8	2.6
65°	4.2	4.1	3.9	3.8	3.6	3.5	3.3	3.2	3.0	2.8	2.7
67.5°	4.3	4.2	4.0	3.9	3.7	3.6	3.4	3.2	3.1	2.9	2.8
70°	4.4	4.3	4.1	3.9	3.8	3.6	3.5	3.3	3.1	3.0	2.8
72.5°	4.5	4.3	4.2	4.0	3.9	3.7	3.5	3.4	3.2	3.0	2.9
75°	4.6	4.4	4.2	4.1	3.9	3.7	3.6	3.4	3.2	3.1	2.9
77.5°	4.6	4.5	4.3	4.1	3.9	3.8	3.6	3.4	3.3	3.1	2.9
80°	4.7	4.5	4.3	4.2	4.0	3.8	3.6	3.5	3.3	3.1	3.0
82.5°	4.7	4.5	4.3	4.2	4.0	3.8	3.7	3.5	3.3	3.1	3.0
85°	4.7	4.5	4.4	4.2	4.0	3.8	3.7	3.5	3.3	3.2	3.0
87.5°	4.7	4.5	4.4	4.2	4.0	3.8	3.7	3.5	3.3	3.2	3.0
90°	4.7	4.5	4.4	4.2	4.0	3.8	3.7	3.5	3.3	3.1	3.0
92.5°	4.7	4.5	4.3	4.2	4.0	3.8	3.6	3.5	3.3	3.1	3.0
95°	4.7	4.5	4.3	4.1	4.0	3.8	3.6	3.5	3.3	3.1	2.9
97.5°	4.6	4.4	4.3	4.1	3.9	3.8	3.6	3.4	3.2	3.1	2.9
100°	4.6	4.4	4.2	4.1	3.9	3.7	3.5	3.4	3.2	3.0	2.9
102.5°	4.5	4.3	4.2	4.0	3.8	3.7	3.5	3.3	3.2	3.0	2.8
105°	4.4	4.3	4.1	3.9	3.8	3.6	3.4	3.3	3.1	2.9	2.8
107.5°	4.3	4.2	4.0	3.8	3.7	3.5	3.4	3.2	3.0	2.9	2.7
110°	4.2	4.1	3.9	3.8	3.6	3.5	3.3	3.1	3.0	2.8	2.7

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	4.1	4.0	3.8	3.7	3.5	3.4	3.2	3.1	2.9	2.7	2.6
115°	4.0	3.9	3.7	3.6	3.4	3.3	3.1	3.0	2.8	2.7	2.5
117.5°	3.9	3.8	3.6	3.5	3.3	3.2	3.0	2.9	2.7	2.6	2.4
120°	3.8	3.6	3.5	3.3	3.2	3.1	2.9	2.8	2.6	2.5	2.4
122.5°	3.6	3.5	3.4	3.2	3.1	2.9	2.8	2.7	2.5	2.4	2.3
125°	3.5	3.4	3.2	3.1	3.0	2.8	2.7	2.6	2.4	2.3	2.2
127.5°	3.3	3.2	3.1	3.0	2.8	2.7	2.6	2.5	2.3	2.2	2.1
130°	3.2	3.1	2.9	2.8	2.7	2.6	2.5	2.3	2.2	2.1	2.0
132.5°	3.0	2.9	2.8	2.7	2.6	2.5	2.3	2.2	2.1	2.0	1.9
135°	2.9	2.8	2.7	2.5	2.4	2.3	2.2	2.1	2.0	1.9	1.8
137.5°	2.7	2.6	2.5	2.4	2.3	2.2	2.1	2.0	1.9	1.8	1.7
140°	2.5	2.4	2.4	2.3	2.2	2.1	2.0	1.9	1.8	1.7	1.6
142.5°	2.4	2.3	2.2	2.1	2.0	1.9	1.9	1.8	1.7	1.6	1.5
145°	2.2	2.2	2.1	2.0	1.9	1.8	1.7	1.7	1.6	1.5	1.4
147.5°	2.1	2.0	1.9	1.9	1.8	1.7	1.6	1.6	1.5	1.4	1.3
150°	1.9	1.9	1.8	1.7	1.7	1.6	1.5	1.5	1.4	1.3	1.2
152.5°	1.8	1.7	1.7	1.6	1.5	1.5	1.4	1.3	1.3	1.2	1.2
155°	1.6	1.6	1.5	1.5	1.4	1.4	1.3	1.2	1.2	1.1	1.1
157.5°	1.4	1.4	1.4	1.3	1.3	1.2	1.2	1.1	1.1	1.0	1.0
160°	1.2	1.2	1.2	1.2	1.1	1.1	1.0	1.0	0.9	0.9	0.8
162.5°	1.0	1.0	1.0	1.0	0.9	0.9	0.9	0.8	0.8	0.8	0.7
165°	0.8	0.8	0.8	0.8	0.8	0.7	0.7	0.7	0.6	0.6	0.6
167.5°	0.6	0.6	0.6	0.6	0.6	0.6	0.5	0.5	0.5	0.5	0.4
170°	0.5	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3	0.3
172.5°	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
7.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
10°	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1
12.5°	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1
15°	0.4	0.4	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2
17.5°	0.5	0.5	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.2
20°	0.6	0.6	0.5	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.3
22.5°	0.8	0.7	0.7	0.6	0.6	0.5	0.5	0.4	0.4	0.4	0.3
25°	0.9	0.8	0.8	0.7	0.7	0.6	0.6	0.5	0.5	0.4	0.4
27.5°	1.0	0.9	0.9	0.8	0.8	0.7	0.7	0.6	0.5	0.5	0.4
30°	1.1	1.1	1.0	0.9	0.9	0.8	0.7	0.7	0.6	0.6	0.5
32.5°	1.3	1.2	1.1	1.0	1.0	0.9	0.8	0.8	0.7	0.6	0.5
35°	1.4	1.3	1.2	1.1	1.1	1.0	0.9	0.8	0.8	0.7	0.6
37.5°	1.5	1.4	1.3	1.2	1.2	1.1	1.0	0.9	0.8	0.7	0.7
40°	1.6	1.5	1.4	1.3	1.2	1.2	1.1	1.0	0.9	0.8	0.7
42.5°	1.7	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.9	0.8
45°	1.8	1.7	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8
47.5°	1.9	1.8	1.7	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9
50°	2.0	1.9	1.8	1.7	1.6	1.5	1.4	1.2	1.1	1.0	0.9
52.5°	2.1	2.0	1.9	1.8	1.7	1.5	1.4	1.3	1.2	1.1	0.9
55°	2.2	2.1	2.0	1.8	1.7	1.6	1.5	1.4	1.2	1.1	1.0
57.5°	2.3	2.2	2.0	1.9	1.8	1.7	1.5	1.4	1.3	1.1	1.0
60°	2.4	2.2	2.1	2.0	1.8	1.7	1.6	1.5	1.3	1.2	1.1
62.5°	2.5	2.3	2.2	2.0	1.9	1.8	1.6	1.5	1.4	1.2	1.1
65°	2.5	2.4	2.2	2.1	2.0	1.8	1.7	1.5	1.4	1.3	1.1
67.5°	2.6	2.4	2.3	2.1	2.0	1.9	1.7	1.6	1.4	1.3	1.1
70°	2.6	2.5	2.3	2.2	2.0	1.9	1.7	1.6	1.5	1.3	1.2
72.5°	2.7	2.5	2.4	2.2	2.1	1.9	1.8	1.6	1.5	1.3	1.2
75°	2.7	2.6	2.4	2.3	2.1	2.0	1.8	1.7	1.5	1.4	1.2
77.5°	2.8	2.6	2.4	2.3	2.1	2.0	1.8	1.7	1.5	1.4	1.2
80°	2.8	2.6	2.5	2.3	2.1	2.0	1.8	1.7	1.5	1.4	1.2
82.5°	2.8	2.6	2.5	2.3	2.2	2.0	1.8	1.7	1.5	1.4	1.2
85°	2.8	2.6	2.5	2.3	2.2	2.0	1.9	1.7	1.5	1.4	1.2
87.5°	2.8	2.6	2.5	2.3	2.2	2.0	1.9	1.7	1.5	1.4	1.2
90°	2.8	2.6	2.5	2.3	2.2	2.0	1.8	1.7	1.5	1.4	1.2
92.5°	2.8	2.6	2.5	2.3	2.1	2.0	1.8	1.7	1.5	1.4	1.2
95°	2.8	2.6	2.4	2.3	2.1	2.0	1.8	1.7	1.5	1.4	1.2
97.5°	2.7	2.6	2.4	2.3	2.1	2.0	1.8	1.7	1.5	1.3	1.2
100°	2.7	2.5	2.4	2.2	2.1	1.9	1.8	1.6	1.5	1.3	1.2
102.5°	2.7	2.5	2.3	2.2	2.1	1.9	1.8	1.6	1.5	1.3	1.2
105°	2.6	2.5	2.3	2.2	2.0	1.9	1.7	1.6	1.4	1.3	1.1
107.5°	2.6	2.4	2.3	2.1	2.0	1.8	1.7	1.5	1.4	1.3	1.1
110°	2.5	2.3	2.2	2.1	1.9	1.8	1.6	1.5	1.4	1.2	1.1

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	2.4	2.3	2.1	2.0	1.9	1.7	1.6	1.5	1.3	1.2	1.0
115°	2.4	2.2	2.1	2.0	1.8	1.7	1.6	1.4	1.3	1.1	1.0
117.5°	2.3	2.1	2.0	1.9	1.8	1.6	1.5	1.4	1.2	1.1	1.0
120°	2.2	2.1	1.9	1.8	1.7	1.6	1.4	1.3	1.2	1.1	0.9
122.5°	2.1	2.0	1.9	1.7	1.6	1.5	1.4	1.3	1.1	1.0	0.9
125°	2.0	1.9	1.8	1.7	1.6	1.4	1.3	1.2	1.1	1.0	0.9
127.5°	1.9	1.8	1.7	1.6	1.5	1.4	1.3	1.1	1.0	0.9	0.8
130°	1.9	1.7	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8
132.5°	1.8	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7
135°	1.7	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7
137.5°	1.6	1.5	1.4	1.3	1.2	1.1	1.0	0.9	0.8	0.7	0.6
140°	1.5	1.4	1.3	1.2	1.1	1.0	1.0	0.9	0.8	0.7	0.6
142.5°	1.4	1.3	1.2	1.1	1.1	1.0	0.9	0.8	0.7	0.7	0.6
145°	1.3	1.2	1.2	1.1	1.0	0.9	0.8	0.8	0.7	0.6	0.5
147.5°	1.2	1.2	1.1	1.0	0.9	0.9	0.8	0.7	0.7	0.6	0.5
150°	1.2	1.1	1.0	1.0	0.9	0.8	0.8	0.7	0.6	0.6	0.5
152.5°	1.1	1.0	1.0	0.9	0.8	0.8	0.7	0.7	0.6	0.5	0.5
155°	1.0	0.9	0.9	0.8	0.8	0.7	0.7	0.6	0.6	0.5	0.4
157.5°	0.9	0.9	0.8	0.8	0.7	0.7	0.6	0.6	0.5	0.5	0.4
160°	0.8	0.8	0.7	0.7	0.6	0.6	0.5	0.5	0.5	0.4	0.4
162.5°	0.7	0.6	0.6	0.6	0.5	0.5	0.5	0.4	0.4	0.4	0.3
165°	0.6	0.5	0.5	0.5	0.4	0.4	0.4	0.3	0.3	0.3	0.3
167.5°	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.2	0.2	0.2
170°	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1
172.5°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
7.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
10°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
12.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
15°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
17.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1
20°	0.3	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1
22.5°	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1
25°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1
27.5°	0.4	0.4	0.3	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1
30°	0.4	0.4	0.4	0.3	0.3	0.3	0.2	0.2	0.1	0.1	0.1
32.5°	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
35°	0.5	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1
37.5°	0.6	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.2	0.1
40°	0.6	0.6	0.5	0.5	0.4	0.4	0.3	0.2	0.2	0.2	0.2
42.5°	0.7	0.6	0.6	0.5	0.4	0.4	0.3	0.2	0.2	0.2	0.2
45°	0.7	0.7	0.6	0.5	0.5	0.4	0.3	0.3	0.2	0.2	0.2
47.5°	0.8	0.7	0.6	0.6	0.5	0.4	0.3	0.3	0.2	0.2	0.2
50°	0.8	0.7	0.7	0.6	0.5	0.4	0.4	0.3	0.2	0.2	0.2
52.5°	0.9	0.8	0.7	0.6	0.5	0.5	0.4	0.3	0.2	0.2	0.2
55°	0.9	0.8	0.7	0.6	0.6	0.5	0.4	0.3	0.2	0.2	0.2
57.5°	0.9	0.8	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2	0.2
60°	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2	0.2
62.5°	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2	0.2
65°	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2	0.2
67.5°	1.0	0.9	0.8	0.7	0.6	0.5	0.5	0.4	0.3	0.2	0.2
70°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2
72.5°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2
75°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2
77.5°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2
80°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2
82.5°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.3	0.2
85°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.3	0.2
87.5°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.3	0.2
90°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.3	0.3
92.5°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.3	0.2
95°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2
97.5°	1.1	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2
100°	1.1	1.0	0.9	0.8	0.7	0.6	0.4	0.3	0.2	0.2	0.2
102.5°	1.1	1.0	0.9	0.7	0.6	0.5	0.4	0.3	0.2	0.2	0.2
105°	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2	0.2
107.5°	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2	0.2
110°	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2	0.2

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	1.0	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.2	0.2	0.2
115°	0.9	0.8	0.7	0.6	0.6	0.5	0.4	0.3	0.2	0.2	0.2
117.5°	0.9	0.8	0.7	0.6	0.5	0.4	0.4	0.3	0.2	0.2	0.1
120°	0.9	0.8	0.7	0.6	0.5	0.4	0.3	0.3	0.2	0.2	0.1
122.5°	0.8	0.7	0.7	0.6	0.5	0.4	0.3	0.2	0.2	0.1	0.1
125°	0.8	0.7	0.6	0.5	0.5	0.4	0.3	0.2	0.2	0.1	0.1
127.5°	0.7	0.7	0.6	0.5	0.4	0.4	0.3	0.2	0.1	0.1	0.1
130°	0.7	0.6	0.6	0.5	0.4	0.3	0.3	0.2	0.1	0.1	0.1
132.5°	0.7	0.6	0.5	0.5	0.4	0.3	0.3	0.2	0.1	0.1	0.1
135°	0.6	0.6	0.5	0.4	0.4	0.3	0.2	0.2	0.1	0.1	0.1
137.5°	0.6	0.5	0.5	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
140°	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1
142.5°	0.5	0.5	0.4	0.4	0.3	0.3	0.2	0.1	0.1	0.1	0.1
145°	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
147.5°	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
150°	0.5	0.4	0.4	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
152.5°	0.4	0.4	0.3	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
155°	0.4	0.4	0.3	0.3	0.3	0.2	0.2	0.1	0.1	0.1	0.1
157.5°	0.4	0.3	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1
160°	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.1	0.1	0.1	0.1
162.5°	0.3	0.3	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1
165°	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1
167.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0
170°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0
172.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
7.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
10°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
12.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
15°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
17.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
20°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
22.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
25°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
27.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
30°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
32.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2
35°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2
37.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2
40°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
42.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
45°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
47.5°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
50°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
52.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
55°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
57.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
60°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
62.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
65°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
67.5°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
70°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
72.5°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
75°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
77.5°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
80°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
82.5°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
85°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
87.5°	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.2	0.2	0.2
90°	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.4
92.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3
95°	0.2	0.2	0.2	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
97.5°	0.2	0.2	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.2	0.2
100°	0.2	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.2
102.5°	0.2	0.1	0.1	0.1	0.1	0.1	0.0	0.1	0.1	0.1	0.2
105°	0.2	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1	0.2
107.5°	0.2	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1	0.2
110°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.1	0.1	0.1	0.2

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1	0.1
115°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1	0.1
117.5°	0.1	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.1	0.1	0.1
120°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.1
122.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.1
125°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.1
127.5°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.1
130°	0.1	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.1	0.1	0.1
132.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1
135°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1
137.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1
140°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1
142.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1
145°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
147.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
150°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
152.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
155°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
157.5°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
160°	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
162.5°	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
7.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
10°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
12.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2
15°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2
17.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.3
20°	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.3	0.3
22.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.3	0.3	0.3	0.4
25°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4
27.5°	0.1	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5
30°	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.5
32.5°	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.6
35°	0.2	0.2	0.2	0.2	0.2	0.3	0.4	0.4	0.5	0.6	0.6
37.5°	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.5	0.5	0.6	0.7
40°	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.6	0.6	0.7
42.5°	0.2	0.2	0.2	0.3	0.3	0.4	0.4	0.5	0.6	0.7	0.8
45°	0.2	0.2	0.3	0.3	0.3	0.4	0.5	0.6	0.6	0.7	0.8
47.5°	0.2	0.2	0.3	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.8
50°	0.2	0.2	0.3	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.9
52.5°	0.2	0.3	0.3	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.9
55°	0.2	0.3	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
57.5°	0.2	0.3	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
60°	0.2	0.3	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
62.5°	0.3	0.3	0.3	0.4	0.4	0.5	0.6	0.7	0.8	0.9	1.1
65°	0.3	0.3	0.3	0.4	0.4	0.5	0.6	0.7	0.9	1.0	1.1
67.5°	0.3	0.3	0.3	0.4	0.4	0.5	0.6	0.8	0.9	1.0	1.1
70°	0.3	0.3	0.3	0.4	0.4	0.5	0.6	0.8	0.9	1.0	1.1
72.5°	0.3	0.3	0.3	0.4	0.4	0.5	0.7	0.8	0.9	1.0	1.1
75°	0.3	0.3	0.3	0.4	0.4	0.5	0.7	0.8	0.9	1.0	1.1
77.5°	0.3	0.3	0.4	0.4	0.4	0.5	0.7	0.8	0.9	1.0	1.2
80°	0.3	0.3	0.4	0.4	0.4	0.6	0.7	0.8	0.9	1.0	1.2
82.5°	0.3	0.3	0.4	0.4	0.4	0.6	0.7	0.8	0.9	1.0	1.2
85°	0.3	0.3	0.4	0.4	0.5	0.6	0.7	0.8	0.9	1.1	1.2
87.5°	0.3	0.3	0.4	0.4	0.4	0.6	0.7	0.8	0.9	1.0	1.2
90°	0.4	0.4	0.4	0.4	0.4	0.5	0.7	0.8	0.9	1.0	1.2
92.5°	0.3	0.3	0.4	0.4	0.4	0.5	0.7	0.8	0.9	1.0	1.1
95°	0.3	0.3	0.3	0.4	0.4	0.5	0.7	0.8	0.9	1.0	1.1
97.5°	0.2	0.3	0.3	0.4	0.4	0.5	0.6	0.8	0.9	1.0	1.1
100°	0.2	0.3	0.3	0.3	0.4	0.5	0.6	0.7	0.9	1.0	1.1
102.5°	0.2	0.3	0.3	0.3	0.4	0.5	0.6	0.7	0.8	1.0	1.1
105°	0.2	0.2	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.9	1.0
107.5°	0.2	0.2	0.3	0.3	0.3	0.5	0.6	0.7	0.8	0.9	1.0
110°	0.2	0.2	0.3	0.3	0.3	0.4	0.5	0.7	0.8	0.9	1.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	0.2	0.2	0.2	0.3	0.3	0.4	0.5	0.6	0.7	0.8	1.0
115°	0.2	0.2	0.2	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.9
117.5°	0.2	0.2	0.2	0.3	0.3	0.4	0.5	0.6	0.7	0.8	0.9
120°	0.2	0.2	0.2	0.2	0.3	0.4	0.5	0.6	0.7	0.8	0.8
122.5°	0.1	0.2	0.2	0.2	0.3	0.3	0.4	0.5	0.6	0.7	0.8
125°	0.1	0.2	0.2	0.2	0.2	0.3	0.4	0.5	0.6	0.7	0.8
127.5°	0.1	0.2	0.2	0.2	0.2	0.3	0.4	0.5	0.6	0.6	0.7
130°	0.1	0.1	0.2	0.2	0.2	0.3	0.4	0.4	0.5	0.6	0.7
132.5°	0.1	0.1	0.1	0.2	0.2	0.3	0.3	0.4	0.5	0.6	0.6
135°	0.1	0.1	0.1	0.2	0.2	0.2	0.3	0.4	0.5	0.5	0.6
137.5°	0.1	0.1	0.1	0.1	0.2	0.2	0.3	0.3	0.4	0.5	0.5
140°	0.1	0.1	0.1	0.1	0.1	0.2	0.3	0.3	0.4	0.4	0.5
142.5°	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.3	0.3	0.4	0.4
145°	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.3	0.3	0.4	0.4
147.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.3	0.3	0.4
150°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.3	0.3
152.5°	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.2	0.3
155°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.2	0.2	0.2
157.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.2	0.2
160°	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1
162.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1
165°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.1	0.1
167.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2
5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
7.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2
10°	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3
12.5°	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.4
15°	0.2	0.2	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.5
17.5°	0.3	0.3	0.3	0.3	0.4	0.4	0.5	0.5	0.5	0.6	0.6
20°	0.3	0.4	0.4	0.4	0.5	0.5	0.5	0.6	0.6	0.7	0.7
22.5°	0.4	0.4	0.4	0.5	0.5	0.6	0.6	0.7	0.7	0.8	0.8
25°	0.4	0.5	0.5	0.6	0.6	0.7	0.7	0.8	0.9	0.9	1.0
27.5°	0.5	0.5	0.6	0.7	0.7	0.8	0.8	0.9	1.0	1.0	1.1
30°	0.6	0.6	0.7	0.7	0.8	0.9	0.9	1.0	1.1	1.2	1.2
32.5°	0.6	0.7	0.7	0.8	0.9	1.0	1.0	1.1	1.2	1.3	1.4
35°	0.7	0.7	0.8	0.9	1.0	1.1	1.1	1.2	1.3	1.4	1.5
37.5°	0.7	0.8	0.9	1.0	1.0	1.1	1.2	1.3	1.4	1.5	1.6
40°	0.8	0.9	0.9	1.0	1.1	1.2	1.3	1.4	1.5	1.6	1.7
42.5°	0.8	0.9	1.0	1.1	1.2	1.3	1.4	1.5	1.6	1.7	1.8
45°	0.9	1.0	1.1	1.2	1.3	1.4	1.5	1.6	1.7	1.8	2.0
47.5°	0.9	1.0	1.1	1.2	1.3	1.5	1.6	1.7	1.8	1.9	2.1
50°	1.0	1.1	1.2	1.3	1.4	1.5	1.7	1.8	1.9	2.0	2.2
52.5°	1.0	1.1	1.2	1.3	1.5	1.6	1.7	1.9	2.0	2.1	2.3
55°	1.1	1.2	1.3	1.4	1.5	1.7	1.8	1.9	2.1	2.2	2.3
57.5°	1.1	1.2	1.3	1.4	1.6	1.7	1.9	2.0	2.2	2.3	2.4
60°	1.1	1.2	1.3	1.5	1.6	1.8	1.9	2.1	2.2	2.4	2.5
62.5°	1.2	1.3	1.4	1.5	1.7	1.8	2.0	2.1	2.3	2.4	2.6
65°	1.2	1.3	1.4	1.6	1.7	1.9	2.0	2.2	2.3	2.5	2.6
67.5°	1.2	1.3	1.4	1.6	1.8	1.9	2.1	2.2	2.4	2.5	2.7
70°	1.2	1.4	1.5	1.6	1.8	2.0	2.1	2.3	2.4	2.6	2.8
72.5°	1.3	1.4	1.5	1.7	1.8	2.0	2.1	2.3	2.5	2.6	2.8
75°	1.3	1.4	1.5	1.7	1.8	2.0	2.2	2.3	2.5	2.7	2.8
77.5°	1.3	1.4	1.5	1.7	1.9	2.0	2.2	2.4	2.5	2.7	2.9
80°	1.3	1.4	1.5	1.7	1.9	2.0	2.2	2.4	2.5	2.7	2.9
82.5°	1.3	1.4	1.5	1.7	1.9	2.0	2.2	2.4	2.5	2.7	2.9
85°	1.3	1.4	1.5	1.7	1.9	2.0	2.2	2.4	2.5	2.7	2.9
87.5°	1.3	1.4	1.5	1.7	1.9	2.0	2.2	2.4	2.5	2.7	2.9
90°	1.3	1.4	1.5	1.7	1.9	2.0	2.2	2.4	2.5	2.7	2.9
92.5°	1.3	1.4	1.5	1.7	1.8	2.0	2.2	2.4	2.5	2.7	2.9
95°	1.3	1.4	1.5	1.7	1.8	2.0	2.2	2.3	2.5	2.7	2.8
97.5°	1.2	1.4	1.5	1.6	1.8	2.0	2.1	2.3	2.5	2.6	2.8
100°	1.2	1.3	1.5	1.6	1.8	1.9	2.1	2.3	2.4	2.6	2.8
102.5°	1.2	1.3	1.4	1.6	1.7	1.9	2.1	2.2	2.4	2.5	2.7
105°	1.2	1.3	1.4	1.5	1.7	1.9	2.0	2.2	2.3	2.5	2.6
107.5°	1.1	1.2	1.4	1.5	1.7	1.8	2.0	2.1	2.3	2.4	2.6
110°	1.1	1.2	1.3	1.5	1.6	1.8	1.9	2.1	2.2	2.4	2.5

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	1.1	1.2	1.3	1.4	1.6	1.7	1.9	2.0	2.2	2.3	2.5
115°	1.0	1.1	1.2	1.4	1.5	1.7	1.8	1.9	2.1	2.2	2.4
117.5°	1.0	1.1	1.2	1.3	1.5	1.6	1.7	1.9	2.0	2.2	2.3
120°	0.9	1.0	1.1	1.3	1.4	1.5	1.7	1.8	1.9	2.1	2.2
122.5°	0.9	1.0	1.1	1.2	1.3	1.5	1.6	1.7	1.9	2.0	2.1
125°	0.9	0.9	1.0	1.2	1.3	1.4	1.5	1.7	1.8	1.9	2.0
127.5°	0.8	0.9	1.0	1.1	1.2	1.3	1.5	1.6	1.7	1.8	1.9
130°	0.8	0.8	0.9	1.0	1.1	1.3	1.4	1.5	1.6	1.7	1.8
132.5°	0.7	0.8	0.9	1.0	1.1	1.2	1.3	1.4	1.5	1.6	1.7
135°	0.7	0.7	0.8	0.9	1.0	1.1	1.2	1.3	1.4	1.5	1.6
137.5°	0.6	0.7	0.7	0.8	0.9	1.0	1.1	1.2	1.3	1.4	1.5
140°	0.6	0.6	0.7	0.8	0.9	0.9	1.0	1.1	1.2	1.3	1.4
142.5°	0.5	0.6	0.6	0.7	0.8	0.9	0.9	1.0	1.1	1.2	1.3
145°	0.5	0.5	0.6	0.6	0.7	0.8	0.9	0.9	1.0	1.1	1.2
147.5°	0.4	0.4	0.5	0.6	0.6	0.7	0.8	0.8	0.9	1.0	1.0
150°	0.3	0.4	0.4	0.5	0.6	0.6	0.7	0.7	0.8	0.9	0.9
152.5°	0.3	0.3	0.4	0.4	0.5	0.5	0.6	0.6	0.7	0.8	0.8
155°	0.2	0.3	0.3	0.4	0.4	0.5	0.5	0.6	0.6	0.7	0.7
157.5°	0.2	0.2	0.3	0.3	0.3	0.4	0.4	0.5	0.5	0.5	0.6
160°	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.4	0.4	0.4	0.5
162.5°	0.1	0.1	0.1	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.4
165°	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.3	0.3
167.5°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
170°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1
172.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3
7.5°	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4
10°	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5
12.5°	0.4	0.4	0.4	0.5	0.5	0.5	0.6	0.6	0.6	0.7	0.7
15°	0.5	0.5	0.6	0.6	0.6	0.7	0.7	0.8	0.8	0.8	0.9
17.5°	0.6	0.7	0.7	0.8	0.8	0.8	0.9	0.9	1.0	1.0	1.1
20°	0.8	0.8	0.9	0.9	1.0	1.0	1.1	1.1	1.2	1.2	1.3
22.5°	0.9	0.9	1.0	1.1	1.1	1.2	1.3	1.3	1.4	1.4	1.5
25°	1.0	1.1	1.2	1.2	1.3	1.4	1.4	1.5	1.6	1.7	1.7
27.5°	1.2	1.2	1.3	1.4	1.5	1.5	1.6	1.7	1.8	1.9	1.9
30°	1.3	1.4	1.5	1.6	1.6	1.7	1.8	1.9	2.0	2.1	2.1
32.5°	1.4	1.5	1.6	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.3
35°	1.6	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.4	2.5	2.5
37.5°	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.4	2.5	2.6	2.7
40°	1.8	1.9	2.0	2.2	2.3	2.4	2.5	2.6	2.7	2.8	2.9
42.5°	1.9	2.1	2.2	2.3	2.4	2.5	2.7	2.8	2.9	3.0	3.1
45°	2.1	2.2	2.3	2.4	2.6	2.7	2.8	2.9	3.1	3.2	3.3
47.5°	2.2	2.3	2.4	2.6	2.7	2.8	3.0	3.1	3.2	3.4	3.5
50°	2.3	2.4	2.6	2.7	2.8	3.0	3.1	3.2	3.4	3.5	3.6
52.5°	2.4	2.5	2.7	2.8	3.0	3.1	3.2	3.4	3.5	3.7	3.8
55°	2.5	2.6	2.8	2.9	3.1	3.2	3.4	3.5	3.7	3.8	3.9
57.5°	2.6	2.7	2.9	3.0	3.2	3.3	3.5	3.6	3.8	3.9	4.1
60°	2.7	2.8	3.0	3.1	3.3	3.4	3.6	3.8	3.9	4.1	4.2
62.5°	2.7	2.9	3.1	3.2	3.4	3.5	3.7	3.9	4.0	4.2	4.3
65°	2.8	3.0	3.1	3.3	3.5	3.6	3.8	4.0	4.1	4.3	4.4
67.5°	2.9	3.0	3.2	3.4	3.5	3.7	3.9	4.0	4.2	4.4	4.5
70°	2.9	3.1	3.3	3.4	3.6	3.8	3.9	4.1	4.3	4.5	4.6
72.5°	3.0	3.1	3.3	3.5	3.7	3.8	4.0	4.2	4.4	4.5	4.7
75°	3.0	3.2	3.3	3.5	3.7	3.9	4.1	4.2	4.4	4.6	4.7
77.5°	3.0	3.2	3.4	3.6	3.7	3.9	4.1	4.3	4.5	4.6	4.8
80°	3.0	3.2	3.4	3.6	3.8	3.9	4.1	4.3	4.5	4.7	4.8
82.5°	3.1	3.2	3.4	3.6	3.8	4.0	4.1	4.3	4.5	4.7	4.9
85°	3.1	3.2	3.4	3.6	3.8	4.0	4.2	4.3	4.5	4.7	4.9
87.5°	3.1	3.2	3.4	3.6	3.8	4.0	4.1	4.3	4.5	4.7	4.9
90°	3.0	3.2	3.4	3.6	3.8	4.0	4.1	4.3	4.5	4.7	4.9
92.5°	3.0	3.2	3.4	3.6	3.7	3.9	4.1	4.3	4.5	4.7	4.8
95°	3.0	3.2	3.4	3.5	3.7	3.9	4.1	4.3	4.4	4.6	4.8
97.5°	3.0	3.1	3.3	3.5	3.7	3.8	4.0	4.2	4.4	4.6	4.7
100°	2.9	3.1	3.3	3.4	3.6	3.8	4.0	4.1	4.3	4.5	4.7
102.5°	2.9	3.0	3.2	3.4	3.6	3.7	3.9	4.1	4.3	4.4	4.6
105°	2.8	3.0	3.2	3.3	3.5	3.7	3.8	4.0	4.2	4.3	4.5
107.5°	2.7	2.9	3.1	3.2	3.4	3.6	3.8	3.9	4.1	4.3	4.4
110°	2.7	2.8	3.0	3.2	3.3	3.5	3.7	3.8	4.0	4.2	4.3

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	2.6	2.8	2.9	3.1	3.2	3.4	3.6	3.7	3.9	4.0	4.2
115°	2.5	2.7	2.8	3.0	3.1	3.3	3.5	3.6	3.8	3.9	4.1
117.5°	2.4	2.6	2.7	2.9	3.0	3.2	3.3	3.5	3.6	3.8	3.9
120°	2.3	2.5	2.6	2.8	2.9	3.1	3.2	3.4	3.5	3.7	3.8
122.5°	2.2	2.4	2.5	2.7	2.8	3.0	3.1	3.2	3.4	3.5	3.7
125°	2.1	2.3	2.4	2.6	2.7	2.8	3.0	3.1	3.2	3.4	3.5
127.5°	2.0	2.2	2.3	2.4	2.6	2.7	2.8	3.0	3.1	3.2	3.3
130°	1.9	2.1	2.2	2.3	2.4	2.6	2.7	2.8	2.9	3.1	3.2
132.5°	1.8	1.9	2.1	2.2	2.3	2.4	2.5	2.7	2.8	2.9	3.0
135°	1.7	1.8	1.9	2.1	2.2	2.3	2.4	2.5	2.6	2.7	2.8
137.5°	1.6	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.5	2.6	2.7
140°	1.5	1.6	1.7	1.8	1.9	2.0	2.1	2.2	2.3	2.4	2.5
142.5°	1.4	1.5	1.5	1.6	1.7	1.8	1.9	2.0	2.1	2.2	2.3
145°	1.2	1.3	1.4	1.5	1.6	1.7	1.8	1.8	1.9	2.0	2.1
147.5°	1.1	1.2	1.3	1.4	1.4	1.5	1.6	1.7	1.8	1.8	1.9
150°	1.0	1.1	1.1	1.2	1.3	1.4	1.4	1.5	1.6	1.6	1.7
152.5°	0.9	0.9	1.0	1.1	1.1	1.2	1.3	1.3	1.4	1.5	1.5
155°	0.8	0.8	0.9	0.9	1.0	1.0	1.1	1.2	1.2	1.3	1.3
157.5°	0.6	0.7	0.7	0.8	0.8	0.9	0.9	1.0	1.0	1.1	1.1
160°	0.5	0.6	0.6	0.6	0.7	0.7	0.8	0.8	0.9	0.9	0.9
162.5°	0.4	0.4	0.5	0.5	0.5	0.6	0.6	0.7	0.7	0.7	0.8
165°	0.3	0.3	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.6	0.6
167.5°	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4
170°	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3
172.5°	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
7.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.4
10°	0.5	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6	0.6
12.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.8
15°	0.9	0.9	0.9	0.9	0.9	1.0	1.0	1.0	1.0	1.0	1.0
17.5°	1.1	1.1	1.1	1.1	1.2	1.2	1.2	1.2	1.3	1.3	1.3
20°	1.3	1.3	1.4	1.4	1.4	1.4	1.5	1.5	1.5	1.6	1.6
22.5°	1.5	1.6	1.6	1.6	1.7	1.7	1.7	1.8	1.8	1.8	1.9
25°	1.7	1.8	1.8	1.9	1.9	2.0	2.0	2.1	2.1	2.1	2.2
27.5°	2.0	2.0	2.1	2.1	2.2	2.2	2.3	2.3	2.4	2.4	2.5
30°	2.2	2.2	2.3	2.4	2.4	2.5	2.6	2.6	2.7	2.7	2.8
32.5°	2.4	2.5	2.5	2.6	2.7	2.8	2.8	2.9	3.0	3.0	3.1
35°	2.6	2.7	2.8	2.9	2.9	3.0	3.1	3.2	3.2	3.3	3.3
37.5°	2.8	2.9	3.0	3.1	3.2	3.3	3.3	3.4	3.5	3.6	3.6
40°	3.0	3.1	3.2	3.3	3.4	3.5	3.6	3.7	3.8	3.8	3.9
42.5°	3.2	3.3	3.4	3.5	3.6	3.7	3.8	3.9	4.0	4.1	4.2
45°	3.4	3.5	3.6	3.7	3.8	4.0	4.1	4.2	4.3	4.3	4.4
47.5°	3.6	3.7	3.8	3.9	4.1	4.2	4.3	4.4	4.5	4.6	4.6
50°	3.8	3.9	4.0	4.1	4.3	4.4	4.5	4.6	4.7	4.8	4.9
52.5°	3.9	4.1	4.2	4.3	4.4	4.6	4.7	4.8	4.9	5.0	5.1
55°	4.1	4.2	4.3	4.5	4.6	4.8	4.9	5.0	5.1	5.2	5.3
57.5°	4.2	4.4	4.5	4.6	4.8	4.9	5.1	5.2	5.3	5.4	5.5
60°	4.4	4.5	4.6	4.8	4.9	5.1	5.2	5.4	5.5	5.6	5.7
62.5°	4.5	4.6	4.8	4.9	5.1	5.2	5.4	5.5	5.6	5.7	5.8
65°	4.6	4.7	4.9	5.0	5.2	5.4	5.5	5.7	5.8	5.9	6.0
67.5°	4.7	4.8	5.0	5.2	5.3	5.5	5.6	5.8	5.9	6.0	6.1
70°	4.8	4.9	5.1	5.3	5.4	5.6	5.7	5.9	6.0	6.1	6.2
72.5°	4.9	5.0	5.2	5.3	5.5	5.7	5.8	6.0	6.1	6.2	6.3
75°	4.9	5.1	5.2	5.4	5.6	5.7	5.9	6.1	6.2	6.3	6.4
77.5°	5.0	5.1	5.3	5.5	5.6	5.8	6.0	6.1	6.2	6.4	6.5
80°	5.0	5.2	5.3	5.5	5.7	5.8	6.0	6.2	6.3	6.4	6.5
82.5°	5.0	5.2	5.4	5.5	5.7	5.9	6.0	6.2	6.3	6.4	6.6
85°	5.0	5.2	5.4	5.5	5.7	5.9	6.1	6.2	6.3	6.5	6.6
87.5°	5.0	5.2	5.4	5.5	5.7	5.9	6.1	6.2	6.3	6.5	6.6
90°	5.0	5.2	5.4	5.5	5.7	5.9	6.0	6.2	6.3	6.4	6.6
92.5°	5.0	5.2	5.3	5.5	5.7	5.8	6.0	6.2	6.3	6.4	6.5
95°	5.0	5.1	5.3	5.5	5.6	5.8	6.0	6.1	6.2	6.4	6.5
97.5°	4.9	5.1	5.2	5.4	5.6	5.7	5.9	6.1	6.2	6.3	6.4
100°	4.8	5.0	5.2	5.3	5.5	5.7	5.8	6.0	6.1	6.2	6.3
102.5°	4.8	4.9	5.1	5.2	5.4	5.6	5.7	5.9	6.0	6.1	6.2
105°	4.7	4.8	5.0	5.2	5.3	5.5	5.6	5.8	5.9	6.0	6.1
107.5°	4.6	4.7	4.9	5.0	5.2	5.4	5.5	5.7	5.8	5.9	6.0
110°	4.5	4.6	4.8	4.9	5.1	5.2	5.4	5.5	5.7	5.8	5.9

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	4.3	4.5	4.7	4.8	5.0	5.1	5.3	5.4	5.5	5.6	5.7
115°	4.2	4.4	4.5	4.7	4.8	5.0	5.1	5.2	5.4	5.5	5.6
117.5°	4.1	4.2	4.4	4.5	4.7	4.8	4.9	5.1	5.2	5.3	5.4
120°	3.9	4.1	4.2	4.4	4.5	4.6	4.8	4.9	5.0	5.1	5.2
122.5°	3.8	3.9	4.1	4.2	4.3	4.5	4.6	4.7	4.8	4.9	5.0
125°	3.6	3.8	3.9	4.0	4.1	4.3	4.4	4.5	4.6	4.7	4.8
127.5°	3.5	3.6	3.7	3.8	3.9	4.1	4.2	4.3	4.4	4.5	4.6
130°	3.3	3.4	3.5	3.6	3.7	3.9	4.0	4.1	4.2	4.3	4.4
132.5°	3.1	3.2	3.3	3.4	3.5	3.7	3.8	3.9	4.0	4.0	4.1
135°	2.9	3.0	3.1	3.2	3.3	3.4	3.5	3.6	3.7	3.8	3.9
137.5°	2.7	2.8	2.9	3.0	3.1	3.2	3.3	3.4	3.5	3.6	3.7
140°	2.6	2.6	2.7	2.8	2.9	3.0	3.1	3.2	3.2	3.3	3.4
142.5°	2.4	2.4	2.5	2.6	2.7	2.8	2.9	2.9	3.0	3.1	3.1
145°	2.2	2.2	2.3	2.4	2.5	2.5	2.6	2.7	2.8	2.8	2.9
147.5°	2.0	2.0	2.1	2.2	2.2	2.3	2.4	2.5	2.5	2.6	2.6
150°	1.8	1.8	1.9	2.0	2.0	2.1	2.1	2.2	2.3	2.3	2.3
152.5°	1.6	1.6	1.7	1.7	1.8	1.9	1.9	2.0	2.0	2.0	2.1
155°	1.4	1.4	1.5	1.5	1.6	1.6	1.7	1.7	1.8	1.8	1.8
157.5°	1.2	1.2	1.3	1.3	1.3	1.4	1.4	1.5	1.5	1.5	1.6
160°	1.0	1.0	1.1	1.1	1.1	1.2	1.2	1.2	1.3	1.3	1.3
162.5°	0.8	0.8	0.9	0.9	0.9	0.9	1.0	1.0	1.0	1.0	1.1
165°	0.6	0.6	0.7	0.7	0.7	0.7	0.8	0.8	0.8	0.8	0.8
167.5°	0.4	0.5	0.5	0.5	0.5	0.5	0.5	0.6	0.6	0.6	0.6
170°	0.3	0.3	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.4
172.5°	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
175°	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2
7.5°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.3	0.3	0.3	0.3
10°	0.6	0.6	0.6	0.6	0.6	0.6	0.5	0.5	0.5	0.5	0.5
12.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8	0.8
15°	1.0	1.0	1.0	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1
17.5°	1.3	1.3	1.3	1.3	1.4	1.4	1.4	1.4	1.4	1.4	1.4
20°	1.6	1.6	1.6	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
22.5°	1.9	1.9	2.0	2.0	2.0	2.0	2.0	2.0	2.1	2.1	2.1
25°	2.2	2.2	2.3	2.3	2.3	2.4	2.4	2.4	2.4	2.4	2.4
27.5°	2.5	2.5	2.6	2.6	2.7	2.7	2.7	2.7	2.7	2.7	2.8
30°	2.8	2.9	2.9	2.9	3.0	3.0	3.0	3.1	3.1	3.1	3.1
32.5°	3.1	3.2	3.2	3.3	3.3	3.4	3.4	3.4	3.4	3.4	3.4
35°	3.4	3.5	3.5	3.6	3.6	3.7	3.7	3.7	3.7	3.7	3.8
37.5°	3.7	3.7	3.8	3.9	3.9	4.0	4.0	4.0	4.0	4.1	4.1
40°	4.0	4.0	4.1	4.2	4.2	4.3	4.3	4.3	4.4	4.4	4.4
42.5°	4.2	4.3	4.4	4.4	4.5	4.6	4.6	4.6	4.6	4.7	4.7
45°	4.5	4.6	4.6	4.7	4.8	4.9	4.9	4.9	4.9	5.0	5.0
47.5°	4.7	4.8	4.9	5.0	5.0	5.1	5.2	5.2	5.2	5.2	5.3
50°	5.0	5.0	5.1	5.2	5.3	5.4	5.4	5.4	5.5	5.5	5.5
52.5°	5.2	5.3	5.4	5.4	5.5	5.6	5.6	5.7	5.7	5.7	5.8
55°	5.4	5.5	5.6	5.7	5.8	5.8	5.9	5.9	5.9	6.0	6.0
57.5°	5.6	5.7	5.8	5.9	6.0	6.1	6.1	6.1	6.2	6.2	6.2
60°	5.8	5.9	6.0	6.0	6.1	6.2	6.3	6.3	6.4	6.4	6.4
62.5°	5.9	6.0	6.1	6.2	6.3	6.4	6.5	6.5	6.5	6.6	6.6
65°	6.1	6.2	6.3	6.4	6.5	6.6	6.6	6.7	6.7	6.8	6.8
67.5°	6.2	6.3	6.4	6.5	6.6	6.7	6.8	6.8	6.9	6.9	7.0
70°	6.3	6.5	6.6	6.7	6.8	6.9	6.9	7.0	7.0	7.1	7.1
72.5°	6.4	6.6	6.7	6.8	6.9	7.0	7.0	7.1	7.1	7.2	7.2
75°	6.5	6.6	6.8	6.9	7.0	7.1	7.1	7.2	7.2	7.3	7.3
77.5°	6.6	6.7	6.8	6.9	7.1	7.2	7.2	7.3	7.3	7.3	7.4
80°	6.6	6.8	6.9	7.0	7.1	7.2	7.3	7.3	7.4	7.4	7.5
82.5°	6.7	6.8	6.9	7.0	7.2	7.3	7.3	7.4	7.4	7.4	7.5
85°	6.7	6.8	6.9	7.1	7.2	7.3	7.3	7.4	7.4	7.5	7.5
87.5°	6.7	6.8	6.9	7.1	7.2	7.3	7.3	7.4	7.4	7.5	7.5
90°	6.7	6.8	6.9	7.0	7.2	7.3	7.3	7.4	7.4	7.5	7.5
92.5°	6.6	6.8	6.9	7.0	7.1	7.2	7.3	7.3	7.4	7.4	7.5
95°	6.6	6.7	6.8	7.0	7.1	7.2	7.2	7.3	7.3	7.4	7.4
97.5°	6.5	6.7	6.8	6.9	7.0	7.1	7.2	7.2	7.3	7.3	7.3
100°	6.5	6.6	6.7	6.8	6.9	7.0	7.1	7.1	7.2	7.2	7.3
102.5°	6.4	6.5	6.6	6.7	6.8	6.9	7.0	7.0	7.1	7.1	7.2
105°	6.2	6.4	6.5	6.6	6.7	6.8	6.9	6.9	6.9	7.0	7.0
107.5°	6.1	6.2	6.3	6.5	6.6	6.7	6.7	6.8	6.8	6.8	6.9
110°	6.0	6.1	6.2	6.3	6.4	6.5	6.6	6.6	6.7	6.7	6.7

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	5.8	5.9	6.0	6.2	6.3	6.4	6.4	6.4	6.5	6.5	6.6
115°	5.7	5.8	5.9	6.0	6.1	6.2	6.2	6.3	6.3	6.4	6.4
117.5°	5.5	5.6	5.7	5.8	5.9	6.0	6.0	6.1	6.1	6.2	6.2
120°	5.3	5.4	5.5	5.6	5.7	5.8	5.8	5.9	5.9	6.0	6.0
122.5°	5.1	5.2	5.3	5.4	5.5	5.6	5.6	5.7	5.7	5.7	5.8
125°	4.9	5.0	5.1	5.2	5.3	5.4	5.4	5.4	5.5	5.5	5.6
127.5°	4.7	4.8	4.9	5.0	5.0	5.1	5.2	5.2	5.2	5.3	5.3
130°	4.5	4.5	4.6	4.7	4.8	4.9	4.9	5.0	5.0	5.0	5.1
132.5°	4.2	4.3	4.4	4.5	4.6	4.7	4.7	4.7	4.8	4.8	4.8
135°	4.0	4.1	4.1	4.2	4.3	4.4	4.4	4.5	4.5	4.5	4.6
137.5°	3.7	3.8	3.9	4.0	4.1	4.1	4.2	4.2	4.2	4.3	4.3
140°	3.5	3.6	3.6	3.7	3.8	3.9	3.9	3.9	3.9	4.0	4.0
142.5°	3.2	3.3	3.3	3.4	3.5	3.6	3.6	3.6	3.6	3.7	3.7
145°	2.9	3.0	3.1	3.1	3.2	3.2	3.3	3.3	3.3	3.4	3.4
147.5°	2.7	2.7	2.8	2.8	2.9	2.9	3.0	3.0	3.0	3.0	3.1
150°	2.4	2.4	2.5	2.5	2.6	2.6	2.6	2.7	2.7	2.7	2.8
152.5°	2.1	2.1	2.2	2.2	2.3	2.3	2.3	2.3	2.4	2.4	2.4
155°	1.8	1.9	1.9	1.9	2.0	2.0	2.0	2.0	2.1	2.1	2.1
157.5°	1.6	1.6	1.6	1.7	1.7	1.7	1.7	1.7	1.8	1.8	1.8
160°	1.3	1.3	1.4	1.4	1.4	1.4	1.4	1.5	1.5	1.5	1.5
162.5°	1.1	1.1	1.1	1.1	1.2	1.2	1.2	1.2	1.2	1.2	1.2
165°	0.8	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
167.5°	0.6	0.6	0.6	0.6	0.7	0.7	0.7	0.7	0.7	0.7	0.7
170°	0.4	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5
172.5°	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
2.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
7.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
10°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
12.5°	0.8	0.8	0.8	0.8	0.8	0.8	0.7	0.7	0.7	0.7	0.7
15°	1.1	1.1	1.1	1.1	1.1	1.0	1.0	1.0	1.0	1.0	1.0
17.5°	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.4	1.3	1.3	1.3
20°	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7	1.7
22.5°	2.1	2.1	2.1	2.1	2.1	2.1	2.1	2.0	2.0	2.0	2.0
25°	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4	2.4
27.5°	2.8	2.8	2.8	2.8	2.8	2.8	2.8	2.7	2.7	2.7	2.7
30°	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1	3.1
32.5°	3.4	3.5	3.5	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.4
35°	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.7
37.5°	4.1	4.1	4.1	4.2	4.1	4.1	4.1	4.1	4.1	4.1	4.1
40°	4.4	4.4	4.5	4.5	4.5	4.5	4.4	4.4	4.4	4.4	4.4
42.5°	4.7	4.7	4.8	4.8	4.8	4.8	4.7	4.7	4.7	4.7	4.7
45°	5.0	5.0	5.1	5.1	5.1	5.1	5.0	5.0	5.0	5.0	5.0
47.5°	5.3	5.3	5.3	5.4	5.4	5.3	5.3	5.3	5.3	5.3	5.3
50°	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6	5.6
52.5°	5.8	5.8	5.9	5.9	5.9	5.9	5.9	5.9	5.8	5.8	5.8
55°	6.0	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1
57.5°	6.3	6.3	6.3	6.4	6.4	6.3	6.3	6.3	6.3	6.3	6.3
60°	6.5	6.5	6.5	6.6	6.6	6.5	6.5	6.5	6.5	6.5	6.5
62.5°	6.7	6.7	6.8	6.8	6.8	6.8	6.8	6.7	6.7	6.7	6.7
65°	6.8	6.9	6.9	7.0	7.0	6.9	6.9	6.9	6.9	6.9	6.9
67.5°	7.0	7.0	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.1	7.0
70°	7.1	7.2	7.2	7.3	7.3	7.2	7.2	7.2	7.2	7.2	7.2
72.5°	7.3	7.3	7.3	7.4	7.4	7.4	7.4	7.3	7.3	7.3	7.3
75°	7.4	7.4	7.4	7.5	7.5	7.5	7.5	7.4	7.4	7.4	7.4
77.5°	7.4	7.5	7.5	7.6	7.6	7.5	7.5	7.5	7.5	7.5	7.5
80°	7.5	7.5	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
82.5°	7.5	7.6	7.6	7.7	7.7	7.7	7.6	7.6	7.6	7.6	7.6
85°	7.6	7.6	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.6	7.6
87.5°	7.6	7.6	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.7	7.6
90°	7.5	7.6	7.6	7.7	7.7	7.7	7.7	7.7	7.6	7.6	7.6
92.5°	7.5	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.6
95°	7.5	7.5	7.5	7.6	7.6	7.6	7.6	7.6	7.6	7.6	7.5
97.5°	7.4	7.4	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5	7.5
100°	7.3	7.3	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
102.5°	7.2	7.2	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3	7.3
105°	7.1	7.1	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2	7.2
107.5°	6.9	7.0	7.0	7.1	7.1	7.1	7.1	7.1	7.0	7.0	7.0
110°	6.8	6.8	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9	6.9

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	6.6	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7	6.7
115°	6.4	6.5	6.5	6.6	6.5	6.5	6.5	6.5	6.5	6.5	6.5
117.5°	6.2	6.3	6.3	6.4	6.4	6.3	6.3	6.3	6.3	6.3	6.3
120°	6.0	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1	6.1
122.5°	5.8	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9	5.9
125°	5.6	5.6	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7
127.5°	5.3	5.4	5.4	5.5	5.4	5.4	5.4	5.4	5.4	5.4	5.4
130°	5.1	5.1	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2	5.2
132.5°	4.8	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9	4.9
135°	4.6	4.6	4.6	4.7	4.7	4.7	4.7	4.7	4.7	4.7	4.7
137.5°	4.3	4.3	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4	4.4
140°	4.0	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1	4.1
142.5°	3.7	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8	3.8
145°	3.4	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5	3.5
147.5°	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2	3.2
150°	2.8	2.8	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9	2.9
152.5°	2.5	2.5	2.5	2.5	2.6	2.6	2.6	2.6	2.6	2.6	2.6
155°	2.1	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.2	2.3
157.5°	1.8	1.8	1.8	1.9	1.9	1.9	1.9	1.9	1.9	1.9	1.9
160°	1.5	1.5	1.5	1.5	1.5	1.5	1.6	1.6	1.6	1.6	1.6
162.5°	1.2	1.2	1.2	1.2	1.2	1.2	1.2	1.3	1.3	1.3	1.3
165°	0.9	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0	1.0
167.5°	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7	0.7
170°	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.5
172.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2
177.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600779
 CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	0.2	0.2
2.5°	0.2	0.2
5°	0.2	0.2
7.5°	0.3	0.3
10°	0.5	0.5
12.5°	0.7	0.7
15°	1.0	1.0
17.5°	1.3	1.3
20°	1.7	1.6
22.5°	2.0	2.0
25°	2.4	2.3
27.5°	2.7	2.7
30°	3.0	3.0
32.5°	3.4	3.4
35°	3.7	3.7
37.5°	4.1	4.1
40°	4.4	4.4
42.5°	4.7	4.7
45°	5.0	5.0
47.5°	5.3	5.3
50°	5.5	5.5
52.5°	5.8	5.8
55°	6.1	6.0
57.5°	6.3	6.3
60°	6.5	6.5
62.5°	6.7	6.7
65°	6.9	6.9
67.5°	7.0	7.0
70°	7.2	7.2
72.5°	7.3	7.3
75°	7.4	7.4
77.5°	7.5	7.5
80°	7.6	7.5
82.5°	7.6	7.6
85°	7.6	7.6
87.5°	7.6	7.6
90°	7.6	7.6
92.5°	7.6	7.6
95°	7.5	7.5
97.5°	7.5	7.5
100°	7.4	7.4
102.5°	7.3	7.3
105°	7.2	7.2
107.5°	7.0	7.0
110°	6.9	6.9

REPORT NUMBER: P600779
CATALOG NUMBER: FE10A35GLMW-NL

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	6.7	6.7
115°	6.5	6.5
117.5°	6.3	6.3
120°	6.1	6.1
122.5°	5.9	5.9
125°	5.7	5.7
127.5°	5.4	5.4
130°	5.2	5.2
132.5°	4.9	4.9
135°	4.7	4.7
137.5°	4.4	4.4
140°	4.1	4.1
142.5°	3.8	3.8
145°	3.5	3.5
147.5°	3.2	3.2
150°	2.9	2.9
152.5°	2.6	2.6
155°	2.3	2.3
157.5°	1.9	1.9
160°	1.6	1.6
162.5°	1.3	1.3
165°	1.0	1.0
167.5°	0.8	0.8
170°	0.5	0.5
172.5°	0.3	0.3
175°	0.2	0.2
177.5°	0.0	0.0
180°	0.0	0.0

(END OF REPORT)