

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P885706

Luminaire Tested: ML104LSFL95FS1E-TIR1D40FL-TL1RDSL B-340LM-4000K

Issue Date: 6/19/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P885706  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-128)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 6/19/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML104LSFL95FS1E-TIR1D40FL-TL1RDSL B-340LM-4000K  
Description: 1IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, METALLIC SILVER BAFFLED TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 4000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 430.4 lumens  
Efficiency: N/A  
Efficacy: 70.6 lumens/watt  
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.66  
Luminous Opening: Circular (Dia: 0.08' x H: 0')  
CIE Type: Direct

Input Watts (W): 6.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P885706  
CATALOG NUMBER: ML104LSFL95FS1E-TIR1D40FL-TL1RDSL B-340LM-4000K

### Luminous Intensity Polar Plot





TEST NUMBER: P885706

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D40FL-TL1RDSL B-340LM-4000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95																			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89																			
3	104	98	94	90	102	97	93	90	95	91	88	92	89	87	90	88	86	84																			
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80																			
5	96	88	83	79	94	87	82	79	85	81	78	84	80	77	82	79	77	75																			
6	91	84	78	74	90	83	78	74	81	77	74	80	76	73	79	75	73	71																			
7	88	79	74	70	86	79	74	70	78	73	70	76	72	69	75	72	69	68																			
8	84	76	70	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65																			
9	81	72	67	63	80	72	67	63	71	66	63	70	66	63	69	65	63	62																			
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1579820
5°	1550394
10°	1422630
15°	1190141
20°	882714
25°	596434
30°	352766
35°	177562
40°	100475
45°	47168
50°	29168
55°	18236
60°	12631
65°	9807
70°	6347
75°	8388
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 47168 cd/sqm



TEST NUMBER: P885706

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D40FL-TL1RDSL B-340LM-4000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	72.3	16.8
10°-20°	159.1	37.0
20°-30°	125.8	29.2
30°-40°	50.4	11.7
40°-50°	14.8	3.4
50°-60°	5.2	1.2
60°-70°	2.1	0.5
70°-80°	0.7	0.2
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	357.2	83.0
0°-40°	407.6	94.7
0°-60°	427.6	99.3
0°-90°	430.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	430.4	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	800	
5°	783	72
15°	582	159
25°	274	126
35°	74	50
45°	17	15
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P885706

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D40FL-TL1RDSL B-340LM-4000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	800.5
2.5°	800.5
5°	782.6
7.5°	751.0
10°	709.9
12.5°	653.1
15°	582.5
17.5°	504.5
20°	420.3
22.5°	342.3
25°	273.9
27.5°	213.8
30°	154.8
32.5°	105.3
35°	73.7
37.5°	53.7
40°	39.0
42.5°	25.3
45°	16.9
47.5°	11.6
50°	9.5
52.5°	7.4
55°	5.3
57.5°	4.2
60°	3.2
62.5°	3.2
65°	2.1
67.5°	1.1
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)