

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P885756

Luminaire Tested: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMWB-340LM-4000K

Issue Date: 6/19/2024

Test Information

Test Method: LM-79-2019
Report Number: P885756
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-133)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMWB-340LM-4000K
Description: 1IN ROUND ML FLEX, SELECTABLE CCT, WITH 55D TIR, MATTE WHITE BAFFLED TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 408.7 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.78
Luminous Opening: Circular (Dia: 0.08' x H: 0')
CIE Type: Direct


Input Watts (W): 6.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P885756

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMWB-340LM-4000K

Luminous Intensity Polar Plot





TEST NUMBER: P885756
 CATALOG NUMBER: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMWB-340LM-4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	85	79	75	91	84	79	75	82	77	74	80	76	73	79	75	73	71																			
6	89	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	70	66	83	75	69	65	74	69	65	72	68	65	71	67	64	63																			
8	81	71	66	62	79	71	65	62	70	65	61	69	64	61	68	64	61	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	61	58	56																			
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	58	55	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1107157
5°	1090585
10°	1033456
15°	935359
20°	806897
25°	657842
30°	424550
35°	223097
40°	119282
45°	58611
50°	35615
55°	25462
60°	24867
65°	24750
70°	24235
75°	24401
80°	23867
85°	24908

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 58611 cd/sqm



TEST NUMBER: P885756

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMWB-340LM-4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.4	12.6
10°-20°	127.1	31.1
20°-30°	133.7	32.7
30°-40°	62.4	15.3
40°-50°	18.3	4.5
50°-60°	6.9	1.7
60°-70°	5.0	1.2
70°-80°	3.1	0.8
80°-90°	0.9	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	312.2	76.4
0°-40°	374.6	91.7
0°-60°	399.8	97.8
0°-90°	408.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	408.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	561	
5°	550	51
15°	458	127
25°	302	134
35°	93	62
45°	21	18
55°	7	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P885756

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMWB-340LM-4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	561.0
2.5°	559.9
5°	550.5
7.5°	535.7
10°	515.7
12.5°	490.5
15°	457.8
17.5°	422.0
20°	384.2
22.5°	345.2
25°	302.1
27.5°	246.3
30°	186.3
32.5°	132.6
35°	92.6
37.5°	66.3
40°	46.3
42.5°	31.6
45°	21.0
47.5°	14.7
50°	11.6
52.5°	8.4
55°	7.4
57.5°	6.3
60°	6.3
62.5°	5.3
65°	5.3
67.5°	4.2
70°	4.2
72.5°	3.2
75°	3.2
77.5°	2.1
80°	2.1
82.5°	1.1
85°	1.1
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)