

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210471

Luminaire Tested: **PR8R30D010 - PR8M34WDMMS - 4000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210471
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8R30D010 - PR8M34WDMMS - 4000K
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE METALLIC SILVER FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3226.4 lumens
Efficiency: N/A
Efficacy: 113.2 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 28.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210471

CATALOG NUMBER: PR8R30D010 - PR8M34WDMMS - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P210471

CATALOG NUMBER: PR8R30D010 - PR8M34WDMMS - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95		96	94	92		92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80		86	82	79		83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69		77	72	68		74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60		69	64	59		67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52		63	57	52		61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46		57	51	46		55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41		52	46	41		51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37		48	42	37		47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34		44	38	33		43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31		41	35	30		40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	39147
5°	39804
10°	40286
15°	41032
20°	41895
25°	42278
30°	42212
35°	42109
40°	40644
45°	37225
50°	31096
55°	25854
60°	21727
65°	17949
70°	15435
75°	12117
80°	8382
85°	8810



TEST NUMBER: P210471

CATALOG NUMBER: PR8R30D010 - PR8M34WDMMS - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.5	3.8
10°-20°	363.7	11.3
20°-30°	571.1	17.7
30°-40°	696.2	21.6
40°-50°	650.7	20.2
50°-60°	434.0	13.5
60°-70°	249.7	7.7
70°-80°	115.1	3.6
80°-90°	23.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1057.3	32.8
0°-40°	1753.5	54.3
0°-60°	2838.3	88.0
0°-90°	3226.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3226.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1270	
5°	1286	122
15°	1285	364
25°	1243	571
35°	1119	696
45°	854	651
55°	481	434
65°	246	250
75°	102	115
85°	25	23
90°	0	



TEST NUMBER: P210471

CATALOG NUMBER: PR8R30D010 - PR8M34WDMMS - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1269.5
2.5°	1271.5
5°	1285.9
7.5°	1284.6
10°	1286.6
12.5°	1283.9
15°	1285.3
17.5°	1282.6
20°	1276.7
22.5°	1255.7
25°	1242.6
27.5°	1216.4
30°	1185.5
32.5°	1154.7
35°	1118.6
37.5°	1075.3
40°	1009.7
42.5°	938.2
45°	853.6
47.5°	759.7
50°	648.2
52.5°	553.7
55°	480.9
57.5°	411.4
60°	352.3
62.5°	301.1
65°	246.0
67.5°	202.1
70°	171.2
72.5°	145.6
75°	101.7
77.5°	80.7
80°	47.2
82.5°	30.2
85°	24.9
87.5°	7.2
90°	0.0

(END OF REPORT)