

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210449

Luminaire Tested: **PR8R30D010 - PR8M34WDMW - 3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P210449  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR8R30D010 - PR8M34WDMW - 3000K  
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE WHITE FINISH  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3199.6 lumens  
Efficiency: N/A  
Efficacy: 112.3 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 28.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210449

CATALOG NUMBER: PR8R30D010 - PR8M34WDMW - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P210449

CATALOG NUMBER: PR8R30D010 - PR8M34WDMW - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	38823
5°	39473
10°	39951
15°	40690
20°	41547
25°	41928
30°	41863
35°	41759
40°	40306
45°	36915
50°	30837
55°	25639
60°	21548
65°	17803
70°	15309
75°	12010
80°	8311
85°	8739



TEST NUMBER: P210449

CATALOG NUMBER: PR8R30D010 - PR8M34WDMW - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	121.5	3.8
10°-20°	360.7	11.3
20°-30°	566.4	17.7
30°-40°	690.4	21.6
40°-50°	645.3	20.2
50°-60°	430.4	13.5
60°-70°	247.6	7.7
70°-80°	114.2	3.6
80°-90°	23.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1048.6	32.8
0°-40°	1739.0	54.3
0°-60°	2814.7	88.0
0°-90°	3199.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3199.6	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1259	
5°	1275	121
15°	1275	361
25°	1232	566
35°	1109	690
45°	846	645
55°	477	430
65°	244	248
75°	101	114
85°	25	23
90°	0	



TEST NUMBER: P210449

CATALOG NUMBER: PR8R30D010 - PR8M34WDMW - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1259.0
2.5°	1260.9
5°	1275.2
7.5°	1273.9
10°	1275.9
12.5°	1273.3
15°	1274.6
17.5°	1272.0
20°	1266.1
22.5°	1245.3
25°	1232.3
27.5°	1206.3
30°	1175.7
32.5°	1145.1
35°	1109.3
37.5°	1066.4
40°	1001.3
42.5°	930.4
45°	846.5
47.5°	753.4
50°	642.8
52.5°	549.1
55°	476.9
57.5°	407.9
60°	349.4
62.5°	298.6
65°	244.0
67.5°	200.4
70°	169.8
72.5°	144.4
75°	100.8
77.5°	80.0
80°	46.8
82.5°	29.9
85°	24.7
87.5°	7.2
90°	0.0

(END OF REPORT)