

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210434

Luminaire Tested: **PR8R40D010 - PR8M34MDMB - 3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210434
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29049)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8R40D010 - PR8M34MDMB - 3000K
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE BLACK FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3986.6 lumens
Efficiency: N/A
Efficacy: 91.6 lumens/watt
Spacing Criteria (0/90/45): 1.04 / 1.04 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 43.5
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210434

CATALOG NUMBER: PR8R40D010 - PR8M34MDMB - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P210434

CATALOG NUMBER: PR8R40D010 - PR8M34MDMB - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	75	71		77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63		72	66	62		70	65	61	59
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	40		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	58	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	68232
5°	68077
10°	66482
15°	63784
20°	60160
25°	56990
30°	52598
35°	48233
40°	44911
45°	41128
50°	38973
55°	35117
60°	27426
65°	19321
70°	12181
75°	6827
80°	1900
85°	0



TEST NUMBER: P210434

CATALOG NUMBER: PR8R40D010 - PR8M34MDMB - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	207.5	5.2
10°-20°	559.8	14.0
20°-30°	766.5	19.2
30°-40°	805.3	20.2
40°-50°	734.4	18.4
50°-60°	574.9	14.4
60°-70°	270.0	6.8
70°-80°	66.6	1.7
80°-90°	1.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1533.8	38.5
0°-40°	2339.0	58.7
0°-60°	3648.3	91.5
0°-90°	3986.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	3986.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2213	
5°	2199	208
15°	1998	560
25°	1675	766
35°	1281	805
45°	943	734
55°	653	575
65°	265	270
75°	57	67
85°	0	2
90°	0	



TEST NUMBER: P210434

CATALOG NUMBER: PR8R40D010 - PR8M34MDMB - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	2212.7
2.5°	2202.9
5°	2199.3
7.5°	2174.2
10°	2123.2
12.5°	2060.6
15°	1998.0
17.5°	1920.1
20°	1833.3
22.5°	1753.7
25°	1675.0
27.5°	1581.0
30°	1477.2
32.5°	1377.9
35°	1281.3
37.5°	1199.9
40°	1115.7
42.5°	1031.6
45°	943.1
47.5°	871.5
50°	812.4
52.5°	745.3
55°	653.2
57.5°	550.3
60°	444.7
62.5°	349.8
65°	264.8
67.5°	191.5
70°	135.1
72.5°	92.2
75°	57.3
77.5°	31.3
80°	10.7
82.5°	0.9
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)