

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P885732

Luminaire Tested: ML104LSFL95FS1E-TIR1D40FL-TL1SDSL-340LM-5000K

Issue Date: 6/19/2024

Test Information

Test Method: LM-79-2019
Report Number: P885732
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-143)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML104LSFL95FS1E-TIR1D40FL-TL1SDSL-340LM-5000K
Description: 1IN SQUARE ML FLEX, SELECTABLE CCT, WITH 40D TIR, METALLIC SILVER TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 5000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 474.4 lumens
Efficiency: N/A
Efficacy: 77.8 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.69 / 0.68
Luminous Opening: Rectangular (W 0.08' x L: 0.08' x H: 0')
CIE Type: Direct

Input Watts (W): 6.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P885732
CATALOG NUMBER: ML104LSFL95FS1E-TIR1D40FL-TL1SDSL-340LM-5000K

Luminous Intensity Polar Plot





TEST NUMBER: P885732

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D40FL-TL1SDSL-340LM-5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	114	112	109	107	112	109	107	106	105	104	102	102	100	99	98	97	96	95								
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89								
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84								
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80								
5	96	88	83	79	94	87	82	79	85	81	78	84	80	77	82	79	77	75								
6	92	84	78	74	90	83	78	74	81	77	74	80	76	73	79	75	73	71								
7	88	79	74	70	86	79	74	70	78	73	70	76	72	69	75	72	69	68								
8	84	76	70	67	83	75	70	67	74	70	66	73	69	66	72	69	66	65								
9	81	72	67	63	80	72	67	63	71	66	63	70	66	63	69	65	63	61								
10	78	69	64	60	77	69	64	60	68	63	60	67	63	60	66	63	60	59								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1324799	1324799	1324799
5°	1302630	1302630	1300763
10°	1207045	1207045	1214443
15°	1010797	1023956	1031498
20°	751344	789942	772457
25°	510682	532744	536678
30°	293349	333262	308025
35°	148350	192817	152891
40°	80531	87613	80531
45°	33319	43622	35950
50°	19773	19773	19773
55°	12701	9458	12701
60°	7130	3720	7130
65°	4401	4401	8436
70°	5438	5438	5438
75°	7187	0	7187
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 43622 cd/sqm



TEST NUMBER: P885732

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D40FL-TL1SDSL-340LM-5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	77.7	16.4
10°-20°	174.3	36.7
20°-30°	142.1	30.0
30°-40°	59.1	12.5
40°-50°	15.4	3.2
50°-60°	3.8	0.8
60°-70°	1.5	0.3
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	394.1	83.1
0°-40°	453.2	95.5
0°-60°	472.5	99.6
0°-90°	474.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	474.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	855	855	855	855	855	
5°	837	837	837	838	836	78
15°	630	631	638	640	643	172
25°	299	307	312	315	314	136
35°	78	86	102	87	81	53
45°	15	18	20	18	16	14
55°	5	4	4	4	5	4
65°	1	1	1	1	2	2
75°	1	0	0	0	1	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P885732

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D40FL-TL1SDSL-340LM-5000K

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	854.7	854.7	854.7	854.7	854.7
2.5°	854.7	854.7	852.4	853.6	852.4
5°	837.2	837.2	837.2	838.3	836.0
7.5°	806.7	809.1	807.9	807.9	810.2
10°	766.9	766.9	766.9	768.1	771.6
12.5°	707.2	708.4	707.2	710.7	713.1
15°	629.9	631.1	638.1	640.5	642.8
17.5°	546.8	550.3	559.7	560.8	559.7
20°	455.5	464.8	478.9	475.4	468.3
22.5°	373.5	379.4	394.6	388.7	389.9
25°	298.6	306.8	311.5	315.0	313.8
27.5°	229.5	240.0	243.5	247.1	242.4
30°	163.9	176.8	186.2	185.0	172.1
32.5°	110.1	125.3	141.7	128.8	117.1
35°	78.4	85.5	101.9	86.6	80.8
37.5°	57.4	59.7	66.7	59.7	57.4
40°	39.8	42.2	43.3	42.2	39.8
42.5°	25.8	28.1	29.3	28.1	25.8
45°	15.2	17.6	19.9	17.6	16.4
47.5°	10.5	9.4	12.9	10.5	11.7
50°	8.2	7.0	8.2	8.2	8.2
52.5°	5.9	5.9	4.7	5.9	5.9
55°	4.7	3.5	3.5	3.5	4.7
57.5°	3.5	2.3	2.3	3.5	3.5
60°	2.3	2.3	1.2	2.3	2.3
62.5°	2.3	1.2	1.2	2.3	2.3
65°	1.2	1.2	1.2	1.2	2.3
67.5°	1.2	1.2	1.2	1.2	1.2
70°	1.2	1.2	1.2	1.2	1.2
72.5°	1.2	1.2	0.0	1.2	1.2
75°	1.2	0.0	0.0	0.0	1.2
77.5°	0.0	0.0	0.0	0.0	1.2
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)