

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886090

Luminaire Tested: ML204LSFL95FS1E-TIR1D25NFL-TL2RDSL-468LM-2700K

Issue Date: 7/18/2024

Test Information

Test Method: LM-79-2019
Report Number: P886090
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-72)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/18/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML204LSFL95FS1E-TIR1D25NFL-TL2RDSL-468LM-2700K
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 25D TIR, METALLIC SILVER TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 384.3 lumens
Efficiency: N/A
Efficacy: 48.0 lumens/watt
Spacing Criteria (0/90/45): 0.46 / 0.46 / 0.53
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886090

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D25NFL-TL2RDSL-468LM-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P886090

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D25NFL-TL2RDSL-468LM-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	110	105	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90			90																
3	105	100	96	92	103	98	95	91	96	93	90	94	91	89	91	89	87	86			86																
4	101	95	90	86	99	94	89	86	92	88	85	90	87	84	88	85	83	82			82																
5	97	90	85	82	96	89	85	81	88	84	81	86	83	80	85	82	79	78			78																
6	93	86	81	77	92	85	81	77	84	80	77	83	79	76	81	78	76	74			74																
7	90	82	77	74	89	82	77	74	80	76	73	79	76	73	78	75	72	71			71																
8	87	79	74	70	86	78	74	70	77	73	70	76	73	70	75	72	70	68			68																
9	84	76	71	67	83	75	71	67	74	70	67	74	70	67	73	69	67	66			66																
10	81	73	68	65	80	72	68	65	72	67	65	71	67	64	70	67	64	63			63																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	558111
5°	494670
10°	380753
15°	267906
20°	190486
25°	119057
30°	52527
35°	27766
40°	18871
45°	11722
50°	4529
55°	3613
60°	2467
65°	1985
70°	1154
75°	1525
80°	2273
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11722 cd/sqm



TEST NUMBER: P886090

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D25NFL-TL2RDSL-468LM-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.9	22.9
10°-20°	146.9	38.2
20°-30°	99.0	25.8
30°-40°	31.5	8.2
40°-50°	12.4	3.2
50°-60°	3.7	1.0
60°-70°	1.9	0.5
70°-80°	0.8	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	333.9	86.9
0°-40°	365.4	95.1
0°-60°	381.5	99.3
0°-90°	384.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	384.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1131	
5°	999	88
15°	524	147
25°	219	99
35°	46	31
45°	17	12
55°	4	4
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P886090

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D25NFL-TL2RDSL-468LM-2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1131.2
2.5°	1103.5
5°	998.8
7.5°	884.8
10°	760.0
12.5°	633.5
15°	524.5
17.5°	434.9
20°	362.8
22.5°	294.1
25°	218.7
27.5°	148.3
30°	92.2
32.5°	61.2
35°	46.1
37.5°	36.9
40°	29.3
42.5°	23.5
45°	16.8
47.5°	7.5
50°	5.9
52.5°	5.0
55°	4.2
57.5°	3.4
60°	2.5
62.5°	2.5
65°	1.7
67.5°	1.7
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.8
80°	0.8
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)