

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886140

Luminaire Tested: ML204LSFL95FS1E-TIR1D40FL-TL2RDMW-468LM-2700K

Issue Date: 6/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P886140
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-77)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML204LSFL95FS1E-TIR1D40FL-TL2RDMW-468LM-2700K
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, MATTE WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 501.8 lumens
Efficiency: N/A
Efficacy: 62.7 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.67
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886140

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D40FL-TL2RDMW-468LM-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P886140
 CATALOG NUMBER: ML204LSFL95FS1E-TIR1D40FL-TL2RDMW-468LM-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	111	109	107	111	109	107	105	105	103	102	101	100	99	98	97	96	94																			
2	109	104	100	97	106	102	99	96	99	96	94	96	94	92	93	91	90	88																			
3	104	98	93	89	102	96	92	89	94	90	87	91	88	86	89	87	85	83																			
4	99	92	87	83	97	91	86	83	89	85	82	87	83	81	85	82	80	78																			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74																			
6	91	83	77	73	89	82	77	73	80	76	72	79	75	72	78	74	71	70																			
7	87	78	73	69	86	78	73	69	77	72	69	75	71	68	74	71	68	67																			
8	83	75	69	65	82	74	69	65	73	68	65	72	68	65	71	67	65	63																			
9	80	71	66	62	79	71	66	62	70	65	62	69	65	62	68	64	61	60																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	62	59	58																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	442611
5°	433505
10°	397787
15°	334053
20°	256641
25°	173441
30°	108928
35°	54509
40°	26986
45°	11722
50°	7062
55°	5763
60°	5822
65°	5837
70°	6059
75°	6481
80°	7103
85°	4529

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 11722 cd/sqm



TEST NUMBER: P886140

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D40FL-TL2RDMW-468LM-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.0	16.1
10°-20°	179.7	35.8
20°-30°	147.6	29.4
30°-40°	61.7	12.3
40°-50°	15.3	3.1
50°-60°	6.6	1.3
60°-70°	5.2	1.0
70°-80°	3.5	0.7
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	408.3	81.4
0°-40°	470.0	93.7
0°-60°	491.9	98.0
0°-90°	501.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	501.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	897	
5°	875	81
15°	654	180
25°	319	148
35°	90	62
45°	17	15
55°	7	7
65°	5	5
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P886140

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D40FL-TL2RDMW-468LM-2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	897.1
2.5°	894.6
5°	875.3
7.5°	842.6
10°	794.0
12.5°	730.3
15°	654.0
17.5°	572.6
20°	488.8
22.5°	403.3
25°	318.6
27.5°	249.0
30°	191.2
32.5°	137.5
35°	90.5
37.5°	60.4
40°	41.9
42.5°	27.7
45°	16.8
47.5°	10.9
50°	9.2
52.5°	8.4
55°	6.7
57.5°	6.7
60°	5.9
62.5°	5.9
65°	5.0
67.5°	5.0
70°	4.2
72.5°	4.2
75°	3.4
77.5°	2.5
80°	2.5
82.5°	1.7
85°	0.8
87.5°	0.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)