

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210505

Luminaire Tested: **PR8S10D010 - PR8M12MDMW - 3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210505
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29044)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8S10D010 - PR8M12MDMW - 3500K
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE WHITE FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1121.5 lumens
Efficiency: N/A
Efficacy: 106.8 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210505

CATALOG NUMBER: PR8S10D010 - PR8M12MDMW - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P210505

CATALOG NUMBER: PR8S10D010 - PR8M12MDMW - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96		97	95	93		94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83		88	84	81		85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72		79	75	71		77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63		72	67	62		70	65	61	60
5	82	70	62	57	80	69	62	56	67	61	56		65	60	55		64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50		60	54	49		58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45		55	49	44		54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	41		51	45	40		50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37		47	41	37		46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34		44	38	34		43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	19334
5°	19266
10°	18765
15°	17992
20°	16975
25°	16076
30°	14852
35°	13563
40°	12660
45°	11565
50°	10933
55°	9849
60°	7697
65°	5363
70°	3399
75°	1918
80°	533
85°	0



TEST NUMBER: P210505

CATALOG NUMBER: PR8S10D010 - PR8M12MDMW - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.7	5.2
10°-20°	157.9	14.1
20°-30°	216.2	19.3
30°-40°	226.6	20.2
40°-50°	206.6	18.4
50°-60°	161.2	14.4
60°-70°	75.0	6.7
70°-80°	18.7	1.7
80°-90°	0.5	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	432.8	38.6
0°-40°	659.4	58.8
0°-60°	1027.2	91.6
0°-90°	1121.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1121.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	627	
5°	622	59
15°	564	158
25°	472	216
35°	360	227
45°	265	207
55°	183	161
65°	74	75
75°	16	19
85°	0	1
90°	0	



TEST NUMBER: P210505

CATALOG NUMBER: PR8S10D010 - PR8M12MDMW - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	627.0
2.5°	623.9
5°	622.4
7.5°	614.9
10°	599.3
12.5°	581.2
15°	563.6
17.5°	541.4
20°	517.3
22.5°	494.6
25°	472.5
27.5°	445.8
30°	417.1
32.5°	387.9
35°	360.3
37.5°	337.1
40°	314.5
42.5°	290.3
45°	265.2
47.5°	245.0
50°	227.9
52.5°	208.8
55°	183.2
57.5°	154.5
60°	124.8
62.5°	96.6
65°	73.5
67.5°	53.3
70°	37.7
72.5°	25.7
75°	16.1
77.5°	9.1
80°	3.0
82.5°	0.5
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)