

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210564

Luminaire Tested: **PR8S10D010 - PR8M12WDMB - 3000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210564
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8S10D010 - PR8M12WDMB - 3000K
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE BLACK FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 898.9 lumens
Efficiency: N/A
Efficacy: 85.6 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 10.5
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210564

CATALOG NUMBER: PR8S10D010 - PR8M12WDMB - 3000K

Luminous Intensity Polar Plot





TEST NUMBER: P210564

CATALOG NUMBER: PR8S10D010 - PR8M12WDMB - 3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	10907
5°	11091
10°	11222
15°	11432
20°	11672
25°	11779
30°	11761
35°	11730
40°	11323
45°	10370
50°	8664
55°	7204
60°	6056
65°	4998
70°	4301
75°	3372
80°	2344
85°	2441



TEST NUMBER: P210564

CATALOG NUMBER: PR8S10D010 - PR8M12WDMB - 3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	34.1	3.8
10°-20°	101.3	11.3
20°-30°	159.1	17.7
30°-40°	194.0	21.6
40°-50°	181.3	20.2
50°-60°	120.9	13.5
60°-70°	69.6	7.7
70°-80°	32.1	3.6
80°-90°	6.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	294.6	32.8
0°-40°	488.5	54.3
0°-60°	790.8	88.0
0°-90°	898.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	898.9	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	354	
5°	358	34
15°	358	101
25°	346	159
35°	312	194
45°	238	181
55°	134	121
65°	68	70
75°	28	32
85°	7	7
90°	0	



TEST NUMBER: P210564

CATALOG NUMBER: PR8S10D010 - PR8M12WDMB - 3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	353.7
2.5°	354.2
5°	358.3
7.5°	357.9
10°	358.4
12.5°	357.7
15°	358.1
17.5°	357.3
20°	355.7
22.5°	349.8
25°	346.2
27.5°	338.9
30°	330.3
32.5°	321.7
35°	311.6
37.5°	299.6
40°	281.3
42.5°	261.4
45°	237.8
47.5°	211.7
50°	180.6
52.5°	154.3
55°	134.0
57.5°	114.6
60°	98.2
62.5°	83.9
65°	68.5
67.5°	56.3
70°	47.7
72.5°	40.6
75°	28.3
77.5°	22.5
80°	13.2
82.5°	8.4
85°	6.9
87.5°	2.0
90°	0.0

(END OF REPORT)