

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886150

Luminaire Tested: ML204LSFL95FS1E-TIR1D40FL-TL2RDSL-468LM-2700K

Issue Date: 6/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P886150  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-78)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 6/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML204LSFL95FS1E-TIR1D40FL-TL2RDSL-468LM-2700K  
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, METALLIC SILVER TRIM  
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 492.7 lumens  
Efficiency: N/A  
Efficacy: 61.6 lumens/watt  
Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.67  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P886150  
CATALOG NUMBER: ML204LSFL95FS1E-TIR1D40FL-TL2RDSL-468LM-2700K

### Luminous Intensity Polar Plot





TEST NUMBER: P886150

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D40FL-TL2RDSL-468LM-2700K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	109	107	112	109	107	106	105	104	102	102	101	99	98	97	97	95																			
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	93	91	90																			
3	105	99	95	91	103	98	94	90	95	92	89	93	90	87	90	88	86	85																			
4	100	93	89	85	98	92	88	84	90	86	83	88	85	82	87	84	82	80																			
5	96	89	83	80	94	88	83	79	86	82	79	84	81	78	83	80	77	76																			
6	92	84	79	75	91	83	78	75	82	78	74	81	77	74	79	76	73	72																			
7	88	80	75	71	87	79	74	71	78	74	70	77	73	70	76	72	70	69																			
8	85	76	71	67	84	76	71	67	75	70	67	74	70	67	73	69	66	65																			
9	81	73	68	64	80	72	67	64	71	67	64	71	67	64	70	66	63	62																			
10	78	70	65	61	77	69	64	61	68	64	61	68	64	61	67	63	61	59																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	455389
5°	445490
10°	406554
15°	339569
20°	259267
25°	175673
30°	109383
35°	54509
40°	25376
45°	9350
50°	3838
55°	2150
60°	1677
65°	934
70°	1154
75°	1525
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 9350 cd/sqm



TEST NUMBER: P886150

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D40FL-TL2RDSL-468LM-2700K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	83.0	16.9
10°-20°	182.7	37.1
20°-30°	149.2	30.3
30°-40°	61.2	12.4
40°-50°	12.7	2.6
50°-60°	2.4	0.5
60°-70°	0.9	0.2
70°-80°	0.5	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	415.0	84.2
0°-40°	476.2	96.6
0°-60°	491.3	99.7
0°-90°	492.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	492.7	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	923	
5°	900	83
15°	665	183
25°	323	149
35°	90	61
45°	13	13
55°	2	2
65°	1	1
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P886150

CATALOG NUMBER: ML204LSFL95FS1E-TIR1D40FL-TL2RDSL-468LM-2700K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	923.0
2.5°	919.6
5°	899.5
7.5°	863.4
10°	811.5
12.5°	746.1
15°	664.8
17.5°	580.9
20°	493.8
22.5°	407.4
25°	322.7
27.5°	252.3
30°	192.0
32.5°	136.6
35°	90.5
37.5°	58.7
40°	39.4
42.5°	24.3
45°	13.4
47.5°	7.5
50°	5.0
52.5°	3.4
55°	2.5
57.5°	1.7
60°	1.7
62.5°	0.8
65°	0.8
67.5°	0.8
70°	0.8
72.5°	0.8
75°	0.8
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)