

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210511

Luminaire Tested: **PR8S15D010 - PR8M12MDMW - 4000K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210511
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29044)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8S15D010 - PR8M12MDMW - 4000K
Description: HALO 8" ROUND DOWNLIGHT, MEDIUM LENS, MATTE WHITE FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 4000K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1428.7 lumens
Efficiency: N/A
Efficacy: 95.2 lumens/watt
Spacing Criteria (0/90/45): 1.03 / 1.03 / 1.13
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 15
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210511

CATALOG NUMBER: PR8S15D010 - PR8M12MDMW - 4000K

Luminous Intensity Polar Plot





TEST NUMBER: P210511

CATALOG NUMBER: PR8S15D010 - PR8M12MDMW - 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	111	107	104	101	109	105	102	99	101	99	96	97	95	93	94	92	91	89
2	103	96	91	86	100	94	89	85	91	87	83	88	84	81	85	82	79	77
3	95	86	79	74	93	85	78	73	82	76	72	79	75	71	77	73	70	68
4	88	78	70	64	86	76	69	64	74	68	63	72	67	62	70	65	61	60
5	82	70	62	57	80	69	62	56	67	61	56	65	60	55	64	59	55	53
6	76	64	56	50	74	63	56	50	61	55	50	60	54	49	58	53	49	47
7	71	59	51	45	69	58	50	45	56	50	45	55	49	44	54	48	44	42
8	66	54	46	41	65	53	46	41	52	45	41	51	45	40	50	44	40	38
9	62	50	42	37	61	49	42	37	48	42	37	47	41	37	46	41	37	35
10	59	46	39	34	57	46	39	34	45	38	34	44	38	34	43	38	34	32

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24629
5°	24544
10°	23904
15°	22918
20°	21622
25°	20479
30°	18921
35°	17279
40°	16126
45°	14731
50°	13931
55°	12543
60°	9806
65°	6830
70°	4337
75°	2442
80°	675
85°	0



TEST NUMBER: P210511

CATALOG NUMBER: PR8S15D010 - PR8M12MDMW - 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.8	5.2
10°-20°	201.1	14.1
20°-30°	275.4	19.3
30°-40°	288.7	20.2
40°-50°	263.2	18.4
50°-60°	205.4	14.4
60°-70°	95.6	6.7
70°-80°	23.8	1.7
80°-90°	0.7	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	551.3	38.6
0°-40°	840.1	58.8
0°-60°	1308.6	91.6
0°-90°	1428.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1428.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	799	
5°	793	75
15°	718	201
25°	602	275
35°	459	289
45°	338	263
55°	233	205
65°	94	96
75°	20	24
85°	0	1
90°	0	



TEST NUMBER: P210511

CATALOG NUMBER: PR8S15D010 - PR8M12MDMW - 4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	798.7
2.5°	794.8
5°	792.9
7.5°	783.3
10°	763.4
12.5°	740.3
15°	717.9
17.5°	689.7
20°	658.9
22.5°	630.1
25°	601.9
27.5°	567.9
30°	531.4
32.5°	494.2
35°	459.0
37.5°	429.5
40°	400.6
42.5°	369.9
45°	337.8
47.5°	312.2
50°	290.4
52.5°	266.0
55°	233.3
57.5°	196.8
60°	159.0
62.5°	123.1
65°	93.6
67.5°	67.9
70°	48.1
72.5°	32.7
75°	20.5
77.5°	11.5
80°	3.8
82.5°	0.6
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)