

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886276

Luminaire Tested: ML204LSFL9FS1E-TIR1D25NFL-TL2RDMWB-550LM-3000K

Issue Date: 7/18/2024

Test Information

Test Method: LM-79-2019
Report Number: P886276
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-74)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 7/18/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML204LSFL9FS1E-TIR1D25NFL-TL2RDMWB-550LM-3000K
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 25D TIR, MATTE WHITE BAFFLED TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 488.2 lumens
Efficiency: N/A
Efficacy: 61.8 lumens/watt
Spacing Criteria (0/90/45): 0.46 / 0.46 / 0.54
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886276
CATALOG NUMBER: ML204LSFL9FS1E-TIR1D25NFL-TL2RDMWB-550LM-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P886276

CATALOG NUMBER: ML204LSFL9FS1E-TIR1D25NFL-TL2RDMWB-550LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																			
3	103	97	92	88	101	95	91	87	93	89	86	90	87	84	88	85	83	82																			
4	98	91	86	82	96	90	85	81	88	83	80	86	82	79	84	81	78	77																			
5	94	86	80	76	92	85	80	76	83	79	75	82	78	75	80	77	74	73																			
6	90	82	76	72	89	81	76	72	79	75	71	78	74	71	77	73	70	69																			
7	86	78	72	68	85	77	72	68	76	71	68	75	70	67	74	70	67	66																			
8	83	74	69	65	82	74	68	65	73	68	64	72	67	64	71	67	64	63																			
9	80	71	66	62	79	70	65	62	70	65	62	69	64	61	68	64	61	60																			
10	77	68	63	59	76	68	63	59	67	62	59	66	62	59	65	61	59	58																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	629059
5°	553804
10°	425842
15°	301924
20°	218838
25°	147147
30°	69333
35°	35416
40°	27888
45°	22328
50°	15044
55°	15053
60°	15295
65°	14476
70°	13416
75°	13725
80°	11649
85°	11888

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 22328 cd/sqm



TEST NUMBER: P886276

CATALOG NUMBER: ML204LSFL9FS1E-TIR1D25NFL-TL2RDMWB-550LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	98.4	20.2
10°-20°	165.9	34.0
20°-30°	120.9	24.8
30°-40°	41.7	8.5
40°-50°	23.6	4.8
50°-60°	15.7	3.2
60°-70°	12.2	2.5
70°-80°	7.5	1.5
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	385.2	78.9
0°-40°	426.9	87.4
0°-60°	466.2	95.5
0°-90°	488.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	488.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1275	
5°	1118	98
15°	591	166
25°	270	121
35°	59	42
45°	32	24
55°	18	16
65°	12	12
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P886276

CATALOG NUMBER: ML204LSFL9FS1E-TIR1D25NFL-TL2RDMWB-550LM-3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1275.0
2.5°	1243.1
5°	1118.2
7.5°	987.2
10°	850.0
12.5°	707.7
15°	591.1
17.5°	496.2
20°	416.8
22.5°	348.7
25°	270.3
27.5°	191.9
30°	121.7
32.5°	80.5
35°	58.8
37.5°	49.5
40°	43.3
42.5°	38.2
45°	32.0
47.5°	21.7
50°	19.6
52.5°	18.6
55°	17.5
57.5°	16.5
60°	15.5
62.5°	13.4
65°	12.4
67.5°	11.3
70°	9.3
72.5°	8.3
75°	7.2
77.5°	6.2
80°	4.1
82.5°	3.1
85°	2.1
87.5°	1.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)