

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886322

Luminaire Tested: ML204LSFL9FS1E-TIR1D40FL-TL2RDMB-550LM-3500K

Issue Date: 6/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P886322
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-79)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML204LSFL9FS1E-TIR1D40FL-TL2RDMB-550LM-3500K
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, MATTE BLACK TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 601.5 lumens
Efficiency: N/A
Efficacy: 76.1 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.67
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886322

CATALOG NUMBER: ML204LSFL9FS1E-TIR1D40FL-TL2RDMB-550LM-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P886322

CATALOG NUMBER: ML204LSFL9FS1E-TIR1D40FL-TL2RDMB-550LM-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95			95																
2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	92	90			90																
3	105	99	95	92	103	98	94	91	95	92	89	93	90	88	91	89	87	85			85																
4	101	94	89	86	99	93	88	85	91	87	84	89	86	83	87	84	82	81			81																
5	96	89	84	80	95	88	84	80	87	82	79	85	81	79	83	80	78	77			77																
6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73			73																
7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69			69																
8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66			66																
9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63			63																
10	79	70	65	62	78	70	65	62	69	65	62	68	64	62	68	64	61	60			60																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	564426
5°	552814
10°	505700
15°	422827
20°	323584
25°	216883
30°	133881
35°	63664
40°	28210
45°	8931
50°	2456
55°	946
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8931 cd/sqm



TEST NUMBER: P886322

CATALOG NUMBER: ML204LSFL9FS1E-TIR1D40FL-TL2RDMB-550LM-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	103.1	17.1
10°-20°	227.5	37.8
20°-30°	184.3	30.6
30°-40°	72.7	12.1
40°-50°	12.8	2.1
50°-60°	1.0	0.2
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	515.0	85.6
0°-40°	587.7	97.7
0°-60°	601.5	100.0
0°-90°	601.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	601.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1144	
5°	1116	103
15°	828	228
25°	398	184
35°	106	73
45°	13	13
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P886322

CATALOG NUMBER: ML204LSFL9FS1E-TIR1D40FL-TL2RDMB-550LM-3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1144.0
2.5°	1140.8
5°	1116.2
7.5°	1072.5
10°	1009.4
12.5°	927.2
15°	827.8
17.5°	724.2
20°	616.3
22.5°	505.2
25°	398.4
27.5°	308.7
30°	235.0
32.5°	165.6
35°	105.7
37.5°	67.3
40°	43.8
42.5°	26.7
45°	12.8
47.5°	5.3
50°	3.2
52.5°	2.1
55°	1.1
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)