

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210590

Luminaire Tested: **PR8S20D010 - PR8M12WDMMS - 3500K**

Issue Date: 03/03/2020

Test Information

Test Method: LM-79-08
Report Number: P210590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)
Test Lab: INNOVATION CENTER-P2
Issue Date: 03/03/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO COMMERCIAL
Catalog Number: PR8S20D010 - PR8M12WDMMS - 3500K
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE METALLIC SILVER FINISH
Light Source: (1) HIGH LUMEN LED 80CRI / 3500K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1995.7 lumens
Efficiency: N/A
Efficacy: 90.7 lumens/watt
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39
Luminous Opening: Circular (Dia: 0.67' x H: 0')
CIE Type: Direct


Input Watts (W): 22
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P210590

CATALOG NUMBER: PR8S20D010 - PR8M12WDMMS - 3500K

Luminous Intensity Polar Plot





TEST NUMBER: P210590

CATALOG NUMBER: PR8S20D010 - PR8M12WDMMS - 3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	24213
5°	24621
10°	24918
15°	25380
20°	25914
25°	26151
30°	26110
35°	26046
40°	25139
45°	23026
50°	19232
55°	15994
60°	13438
65°	11105
70°	9548
75°	7494
80°	5185
85°	5449



TEST NUMBER: P210590

CATALOG NUMBER: PR8S20D010 - PR8M12WDMMS - 3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.8	3.8
10°-20°	225.0	11.3
20°-30°	353.3	17.7
30°-40°	430.6	21.6
40°-50°	402.5	20.2
50°-60°	268.5	13.5
60°-70°	154.5	7.7
70°-80°	71.2	3.6
80°-90°	14.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	654.0	32.8
0°-40°	1084.6	54.3
0°-60°	1755.6	88.0
0°-90°	1995.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1995.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	785	
5°	795	76
15°	795	225
25°	769	353
35°	692	431
45°	528	402
55°	298	268
65°	152	154
75°	63	71
85°	15	14
90°	0	



TEST NUMBER: P210590

CATALOG NUMBER: PR8S20D010 - PR8M12WDMMS - 3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	785.2
2.5°	786.4
5°	795.4
7.5°	794.6
10°	795.8
12.5°	794.2
15°	795.0
17.5°	793.3
20°	789.7
22.5°	776.7
25°	768.6
27.5°	752.4
30°	733.3
32.5°	714.2
35°	691.9
37.5°	665.1
40°	624.5
42.5°	580.3
45°	528.0
47.5°	469.9
50°	400.9
52.5°	342.5
55°	297.5
57.5°	254.4
60°	217.9
62.5°	186.3
65°	152.2
67.5°	125.0
70°	105.9
72.5°	90.1
75°	62.9
77.5°	49.9
80°	29.2
82.5°	18.7
85°	15.4
87.5°	4.5
90°	0.0

(END OF REPORT)