

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: HALO COMMERCIAL

Report Number: P210639

Luminaire Tested: **PR8S30D010 - PR8M34WDMW - 3000K**

Issue Date: 03/03/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P210639  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (P29051)  
Test Lab: INNOVATION CENTER-P2  
Issue Date: 03/03/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO COMMERCIAL  
Catalog Number: PR8S30D010 - PR8M34WDMW - 3000K  
Description: HALO 8" ROUND DOWNLIGHT, WIDE LENS, MATTE WHITE FINISH  
Light Source: (1) HIGH LUMEN LED 80CRI / 3000K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2705.8 lumens  
Efficiency: N/A  
Efficacy: 94.9 lumens/watt  
Spacing Criteria (0/90/45): 1.37 / 1.37 / 1.39  
Luminous Opening: Circular (Dia: 0.67' x H: 0')  
CIE Type: Direct


Input Watts (W): 28.5  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P210639

CATALOG NUMBER: PR8S30D010 - PR8M34WDMW - 3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P210639

CATALOG NUMBER: PR8S30D010 - PR8M34WDMW - 3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	110	106	103	99	108	104	101	98	100	97	95	96	94	92	92	91	89	87
2	102	94	88	83	99	92	87	82	89	84	80	86	82	79	83	80	77	75
3	93	84	77	71	91	82	76	70	79	74	69	77	72	68	74	70	67	65
4	86	75	67	61	84	74	66	61	71	65	60	69	64	59	67	62	58	56
5	80	68	59	53	78	67	59	53	64	58	52	63	57	52	61	56	51	49
6	74	61	53	47	72	60	52	47	59	52	46	57	51	46	55	50	46	44
7	68	56	48	42	67	55	47	42	53	46	41	52	46	41	51	45	41	39
8	64	51	43	37	62	50	43	37	49	42	37	48	42	37	47	41	37	35
9	60	47	39	34	58	46	39	34	45	38	34	44	38	33	43	37	33	31
10	56	43	36	31	55	43	36	31	42	35	31	41	35	30	40	34	30	29

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	32828
5°	33381
10°	33783
15°	34408
20°	35135
25°	35453
30°	35400
35°	35314
40°	34083
45°	31215
50°	26078
55°	21682
60°	18218
65°	15053
70°	12947
75°	10163
80°	7032
85°	7395



TEST NUMBER: P210639

CATALOG NUMBER: PR8S30D010 - PR8M34WDMW - 3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	102.7	3.8
10°-20°	305.0	11.3
20°-30°	479.0	17.7
30°-40°	583.9	21.6
40°-50°	545.7	20.2
50°-60°	364.0	13.5
60°-70°	209.4	7.7
70°-80°	96.6	3.6
80°-90°	19.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	886.7	32.8
0°-40°	1470.5	54.3
0°-60°	2380.2	88.0
0°-90°	2705.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2705.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1065	
5°	1078	103
15°	1078	305
25°	1042	479
35°	938	584
45°	716	546
55°	403	364
65°	206	209
75°	85	97
85°	21	20
90°	0	



TEST NUMBER: P210639

CATALOG NUMBER: PR8S30D010 - PR8M34WDMW - 3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1064.6
2.5°	1066.3
5°	1078.4
7.5°	1077.3
10°	1078.9
12.5°	1076.7
15°	1077.8
17.5°	1075.6
20°	1070.7
22.5°	1053.1
25°	1042.0
27.5°	1020.0
30°	994.2
32.5°	968.3
35°	938.1
37.5°	901.8
40°	846.7
42.5°	786.8
45°	715.8
47.5°	637.1
50°	543.6
52.5°	464.4
55°	403.3
57.5°	345.0
60°	295.4
62.5°	252.5
65°	206.3
67.5°	169.5
70°	143.6
72.5°	122.1
75°	85.3
77.5°	67.7
80°	39.6
82.5°	25.3
85°	20.9
87.5°	6.1
90°	0.0

(END OF REPORT)