

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886466

Luminaire Tested: ML204LSFLD2W1E-TIR1D40FL-TL2RDMBB-400LM-3500K

Issue Date: 6/20/2024

Test Information

Test Method: LM-79-2019
Report Number: P886466
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-82)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/20/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML204LSFLD2W1E-TIR1D40FL-TL2RDMMBB-400LM-3500K
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, MATTE BLACK BAFFLED TRIM
Light Source: (1) D2W LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 409.2 lumens
Efficiency: N/A
Efficacy: 66.0 lumens/watt
Spacing Criteria (0/90/45): 0.68 / 0.68 / 0.67
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct

Input Watts (W): 6.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P886466
CATALOG NUMBER: ML204LSFLD2W1E-TIR1D40FL-TL2RDMBB-400LM-3500K

Luminous Intensity Polar Plot





TEST NUMBER: P886466

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D40FL-TL2RDMBB-400LM-3500K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	114	112	109	107	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	95	95
2	109	105	102	99	107	103	100	97	100	98	95	97	95	93	95	93	91	90	90	90	90
3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	88	86	85	85	85	85
4	100	94	89	85	99	93	88	85	91	87	84	89	85	83	87	84	82	81	81	81	81
5	96	89	84	80	95	88	83	80	86	82	79	85	81	78	83	80	78	76	76	76	76
6	92	84	79	76	91	84	79	75	82	78	75	81	77	74	80	76	74	73	73	73	73
7	88	80	75	71	87	80	75	71	79	74	71	77	73	71	76	73	70	69	69	69	69
8	85	77	71	68	84	76	71	68	75	71	67	74	70	67	73	70	67	66	66	66	66
9	82	73	68	65	81	73	68	64	72	67	64	71	67	64	70	67	64	63	63	63	63
10	78	70	65	62	78	70	65	61	69	64	61	68	64	61	67	64	61	60	60	60	60

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	379261
5°	370359
10°	340624
15°	284609
20°	217526
25°	148127
30°	92121
35°	46076
40°	19966
45°	7047
50°	2226
55°	602
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7047 cd/sqm



TEST NUMBER: P886466

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D40FL-TL2RDMBB-400LM-3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	69.2	16.9
10°-20°	153.0	37.4
20°-30°	125.4	30.6
30°-40°	51.5	12.6
40°-50°	9.4	2.3
50°-60°	0.8	0.2
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	347.6	84.9
0°-40°	399.0	97.5
0°-60°	409.2	100.0
0°-90°	409.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	409.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	769	
5°	748	69
15°	557	153
25°	272	125
35°	76	51
45°	10	9
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P886466
CATALOG NUMBER: ML204LSFLD2W1E-TIR1D40FL-TL2RDMBB-400LM-3500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	768.7
2.5°	765.8
5°	747.8
7.5°	719.6
10°	679.9
12.5°	624.4
15°	557.2
17.5°	485.0
20°	414.3
22.5°	343.6
25°	272.1
27.5°	210.0
30°	161.7
32.5°	117.7
35°	76.5
37.5°	47.6
40°	31.0
42.5°	18.8
45°	10.1
47.5°	4.3
50°	2.9
52.5°	1.4
55°	0.7
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)