

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P886492

Luminaire Tested: ML204LSFLD2W1E-TIR1D55WFL-TL2RDMW-400LM-3500K

Issue Date: 6/20/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P886492  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-83)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 6/20/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML204LSFLD2W1E-TIR1D55WFL-TL2RDMW-400LM-3500K  
Description: 2IN ROUND ML FLEX, SELECTABLE CCT, WITH 55D TIR, MATTE WHITE TRIM  
Light Source: (1) D2W LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 414.3 lumens  
Efficiency: N/A  
Efficacy: 66.8 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 0.86 / 0.82  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 6.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P886492  
CATALOG NUMBER: ML204LSFLD2W1E-TIR1D55WFL-TL2RDMW-400LM-3500K

### Luminous Intensity Polar Plot





TEST NUMBER: P886492  
 CATALOG NUMBER: ML204LSFLD2W1E-TIR1D55WFL-TL2RDMW-400LM-3500K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87																			
3	103	96	91	87	101	95	90	87	92	88	85	90	87	84	88	85	83	81																			
4	98	90	85	81	96	89	84	80	87	83	79	85	81	78	83	80	77	76																			
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	73	71																			
6	88	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	69	65	83	75	69	65	73	68	65	72	68	64	71	67	64	63																			
8	80	71	65	61	79	71	65	61	70	65	61	69	64	61	68	64	60	59																			
9	77	67	62	58	76	67	62	58	66	61	58	65	61	57	64	60	57	56																			
10	73	64	58	55	72	64	58	55	63	58	54	62	58	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	259024
5°	257488
10°	250345
15°	234195
20°	208915
25°	166255
30°	115992
35°	62218
40°	30206
45°	14094
50°	7215
55°	4989
60°	5032
65°	5020
70°	5193
75°	5528
80°	6251
85°	3963

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14094 cd/sqm



TEST NUMBER: P886492

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D55WFL-TL2RDMW-400LM-3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.0	11.8
10°-20°	127.5	30.8
20°-30°	137.8	33.3
30°-40°	68.6	16.6
40°-50°	17.6	4.3
50°-60°	5.6	1.4
60°-70°	4.1	1.0
70°-80°	2.9	0.7
80°-90°	1.1	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	314.3	75.9
0°-40°	383.0	92.4
0°-60°	406.3	98.1
0°-90°	414.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	414.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	525	
5°	520	49
15°	458	128
25°	305	138
35°	103	69
45°	20	18
55°	6	6
65°	4	4
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P886492

CATALOG NUMBER: ML204LSFLD2W1E-TIR1D55WFL-TL2RDMW-400LM-3500K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	525.0
2.5°	524.2
5°	519.9
7.5°	512.0
10°	499.7
12.5°	480.9
15°	458.5
17.5°	431.8
20°	397.9
22.5°	354.5
25°	305.4
27.5°	253.5
30°	203.6
32.5°	152.4
35°	103.3
37.5°	68.6
40°	46.9
42.5°	31.8
45°	20.2
47.5°	13.0
50°	9.4
52.5°	7.2
55°	5.8
57.5°	5.1
60°	5.1
62.5°	4.3
65°	4.3
67.5°	3.6
70°	3.6
72.5°	2.9
75°	2.9
77.5°	2.2
80°	2.2
82.5°	1.4
85°	0.7
87.5°	0.7
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)