

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P600772

Luminaire Tested: **FE08A40FDB**

Issue Date: 07/11/2022

Tested By:

Approved By:



NVLAP Lab Code: 200050-0

Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.



Test Information

Test Method: LM-79-08
 Report Number: P600772
 Test Lab: Third Party
 Issue Date: 07/11/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: FE08A40FDB
 Description: Standard LED Entry Light - Bronze 4000K
 Light Source: 70 CRI LEDs
 Ballast/Driver: (1) Electronic Driver

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 788.6 lumens
 Efficiency: N/A
 Efficacy: 105.0 lumens/watt
 Luminous Opening: Point Source (0m x 0m x 0m)
 IES Classification: Type IV - Short
 BUG Rating: B0 - U3 - G1


Input Watts (W): 7.51
 Input Voltage (V): 120.0
 Input Current (Ain): 0.063
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT

Measurement and Test Equipment			
Instrument	Identification Number	Calibration Date	Calibration Due Date
Photometer	GONIO 1 IN0055	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

Iso-Footcandle Lines of Horizontal Illumination


× Max cd
 - - - 1/2 Max cd



Based on 10 foot mounting height. Maximum calculated value = 0.7 fc
 Type IV - Short - N/A

REPORT NUMBER: P600772
CATALOG NUMBER: FE08A40FDB

Luminous Intensity Polar Plot



— Vertical Plane Through 315-Deg Lateral - - - Horizontal Cone Through 55-Deg Vertical

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB


FLUX DISTRIBUTION:

		Downward	Upward	Total
House Side	Lumens	245.8	73.8	319.6
	% Fixture	31.2	9.4	40.5
Street Side	Lumens	312.8	156.2	469.0
	% Fixture	39.7	19.8	59.5
Total	Lumens	558.6	230.0	788.6
	% Fixture	70.8	29.2	100.0

Coefficient of Utilization

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	6.1	0.8
10°-20°	21.4	2.7
20°-30°	40.5	5.1
30°-40°	59.9	7.6
40°-50°	75.9	9.6
50°-60°	87.2	11.1
60°-70°	92.5	11.7
70°-80°	91.2	11.6
80°-90°	83.9	10.6
90°-100°	73.0	9.3
100°-110°	58.4	7.4
110°-120°	42.3	5.4
120°-130°	28.0	3.5
130°-140°	16.5	2.1
140°-150°	8.1	1.0
150°-160°	3.1	0.4
160°-170°	0.6	0.1
170°-180°	0.0	0.0
0°-90°	558.6	70.8
0°-180°	788.6	100.0




REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

LUMINAIRE CLASSIFICATION SYSTEM LUMEN TABLE AND BUG RATING:

Zone	Lumens	% Fixture	Zone Rating/Lumen Limit		
			B	U	G
FL (0°-30°)	35.0	4.4			
FM (30°-60°)	121.1	15.4			
FH (60°-80°)	106.3	13.5			G0/660
FVH (80°-90°)	50.4	6.4			G1/100
BL (0°-30°)	33.0	4.2	B0/110		
BM (30°-60°)	101.8	12.9	B0/220		
BH (60°-80°)	77.4	9.8	B0/110		G0/110
BVH (80°-90°)	33.5	4.2			G1/100
UL (90°-100°)	73.0	9.3		U3/500	
UH (100°-180°)	157.0	19.9		U3/500	

BUG Rating: B0-U3-G1
 Type IV Short



REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (FULL):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.0
5°	64.0	64.0	64.0	64.0	64.0	63.9	63.9	63.9	63.9	63.9	63.8
7.5°	67.5	67.5	67.5	67.5	67.5	67.5	67.4	67.4	67.4	67.4	67.3
10°	71.0	71.0	70.9	70.9	70.9	70.9	70.8	70.8	70.8	70.7	70.7
12.5°	74.6	74.6	74.5	74.5	74.5	74.4	74.4	74.4	74.3	74.3	74.2
15°	78.0	78.0	77.9	77.9	77.9	77.8	77.8	77.7	77.7	77.7	77.6
17.5°	81.4	81.4	81.3	81.3	81.3	81.2	81.2	81.2	81.1	81.1	81.0
20°	84.6	84.6	84.6	84.5	84.5	84.5	84.5	84.4	84.4	84.4	84.3
22.5°	87.8	87.7	87.7	87.7	87.7	87.6	87.6	87.6	87.6	87.5	87.5
25°	90.8	90.7	90.7	90.6	90.5	90.5	90.4	90.4	90.3	90.2	90.2
27.5°	93.3	93.3	93.3	93.2	93.2	93.2	93.1	93.1	93.1	93.1	93.0
30°	95.9	95.9	95.9	95.9	95.9	95.8	95.8	95.8	95.8	95.8	95.7
32.5°	98.3	98.2	98.2	98.2	98.2	98.1	98.1	98.1	98.1	98.0	98.0
35°	100.4	100.4	100.3	100.3	100.3	100.3	100.3	100.3	100.3	100.3	100.2
37.5°	102.3	102.3	102.3	102.3	102.3	102.3	102.3	102.3	102.3	102.3	102.2
40°	103.8	103.8	103.9	103.9	103.9	103.9	103.9	103.9	103.9	103.9	103.9
42.5°	105.3	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4	105.4
45°	106.3	106.4	106.4	106.5	106.5	106.5	106.6	106.6	106.6	106.7	106.7
47.5°	107.1	107.2	107.2	107.3	107.3	107.4	107.4	107.5	107.5	107.6	107.6
50°	107.8	107.8	107.9	107.9	108.0	108.0	108.1	108.1	108.2	108.2	108.2
52.5°	108.2	108.2	108.3	108.4	108.4	108.5	108.6	108.6	108.7	108.8	108.8
55°	108.2	108.3	108.4	108.4	108.5	108.6	108.6	108.7	108.8	108.9	108.9
57.5°	108.2	108.2	108.3	108.4	108.5	108.5	108.6	108.7	108.8	108.9	108.9
60°	107.8	107.9	108.0	108.1	108.2	108.3	108.4	108.5	108.6	108.7	108.7
62.5°	107.1	107.2	107.3	107.4	107.5	107.6	107.7	107.8	107.9	108.0	108.0
65°	106.4	106.5	106.5	106.6	106.7	106.8	106.9	107.0	107.0	107.1	107.1
67.5°	105.1	105.2	105.3	105.4	105.5	105.6	105.7	105.8	105.9	106.0	106.0
70°	103.8	103.9	104.0	104.1	104.2	104.3	104.4	104.5	104.7	104.8	104.8
72.5°	102.1	102.2	102.3	102.5	102.6	102.7	102.8	102.9	103.0	103.1	103.1
75°	100.3	100.5	100.6	100.7	100.8	100.9	101.1	101.2	101.3	101.4	101.4
77.5°	98.4	98.5	98.6	98.7	98.8	99.0	99.1	99.2	99.3	99.4	99.4
80°	96.4	96.5	96.6	96.7	96.8	96.9	97.0	97.1	97.2	97.3	97.3
82.5°	94.2	94.3	94.4	94.5	94.6	94.7	94.8	94.9	95.0	95.1	95.2
85°	92.0	92.1	92.2	92.3	92.4	92.5	92.6	92.7	92.9	93.0	93.0
87.5°	89.8	89.9	90.0	90.1	90.2	90.3	90.4	90.5	90.6	90.7	90.7
90°	87.6	87.7	87.8	87.9	88.1	88.2	88.3	88.4	88.5	88.6	88.6
92.5°	85.5	85.6	85.7	85.8	85.9	86.0	86.0	86.1	86.2	86.3	86.3
95°	83.1	83.2	83.3	83.4	83.5	83.6	83.6	83.7	83.8	83.9	83.9
97.5°	80.7	80.8	80.9	81.0	81.1	81.2	81.3	81.4	81.5	81.6	81.6
100°	78.3	78.4	78.5	78.7	78.8	78.9	79.0	79.1	79.2	79.4	79.3
102.5°	75.9	76.0	76.0	76.1	76.2	76.3	76.4	76.4	76.5	76.6	76.6
105°	73.4	73.5	73.5	73.6	73.6	73.7	73.8	73.8	73.9	74.0	74.0
107.5°	70.8	70.8	70.9	70.9	71.0	71.1	71.1	71.2	71.3	71.3	71.3
110°	68.0	68.1	68.1	68.2	68.2	68.3	68.4	68.4	68.5	68.5	68.5

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	0°	2.5°	5°	7.5°	10°	12.5°	15°	17.5°	20°	22.5°	25°
112.5°	65.2	65.3	65.3	65.3	65.4	65.4	65.5	65.5	65.5	65.6	65.6
115°	62.3	62.3	62.4	62.4	62.5	62.5	62.6	62.6	62.6	62.7	62.6
117.5°	59.3	59.3	59.4	59.4	59.4	59.4	59.5	59.5	59.5	59.5	59.5
120°	56.3	56.3	56.4	56.4	56.4	56.5	56.5	56.5	56.5	56.6	56.5
122.5°	53.3	53.4	53.4	53.4	53.5	53.5	53.5	53.6	53.6	53.6	53.6
125°	50.2	50.3	50.3	50.3	50.3	50.3	50.3	50.4	50.4	50.4	50.3
127.5°	47.1	47.1	47.1	47.2	47.2	47.2	47.3	47.3	47.3	47.4	47.3
130°	44.1	44.1	44.1	44.1	44.1	44.1	44.1	44.2	44.2	44.2	44.1
132.5°	41.1	41.1	41.1	41.1	41.1	41.2	41.2	41.2	41.2	41.2	41.1
135°	38.0	38.0	38.1	38.1	38.1	38.1	38.2	38.2	38.2	38.2	38.1
137.5°	34.8	34.8	34.8	34.8	34.8	34.8	34.9	34.9	34.9	34.9	34.8
140°	31.7	31.7	31.7	31.7	31.7	31.7	31.7	31.8	31.8	31.8	31.7
142.5°	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.6	28.6	28.5
145°	25.5	25.5	25.5	25.5	25.6	25.6	25.6	25.6	25.7	25.7	25.6
147.5°	22.3	22.3	22.4	22.4	22.4	22.4	22.4	22.4	22.4	22.5	22.4
150°	19.4	19.4	19.4	19.4	19.4	19.5	19.5	19.5	19.5	19.5	19.5
152.5°	16.4	16.4	16.4	16.5	16.5	16.5	16.5	16.5	16.5	16.6	16.5
155°	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5	13.5
157.5°	10.6	10.6	10.6	10.7	10.7	10.7	10.7	10.8	10.8	10.8	10.8
160°	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	7.9	8.0
162.5°	5.4	5.4	5.4	5.5	5.5	5.5	5.6	5.6	5.6	5.6	5.6
165°	3.1	3.1	3.1	3.1	3.1	3.2	3.2	3.2	3.2	3.2	3.3
167.5°	1.4	1.4	1.4	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
170°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3
172.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	60.9	60.9	60.9	60.8	60.8	60.8	60.8	60.7	60.7	60.6	60.6
5°	63.8	63.7	63.6	63.6	63.5	63.5	63.4	63.4	63.3	63.2	63.1
7.5°	67.2	67.2	67.1	67.0	66.9	66.8	66.7	66.7	66.5	66.4	66.3
10°	70.6	70.5	70.4	70.3	70.2	70.2	70.1	70.0	69.9	69.8	69.7
12.5°	74.1	74.0	73.9	73.8	73.8	73.7	73.6	73.5	73.4	73.3	73.2
15°	77.5	77.4	77.3	77.2	77.1	77.1	77.0	76.9	76.8	76.7	76.6
17.5°	80.9	80.9	80.8	80.7	80.6	80.5	80.4	80.3	80.2	80.1	80.0
20°	84.2	84.1	84.0	83.9	83.8	83.8	83.7	83.6	83.4	83.3	83.2
22.5°	87.4	87.3	87.2	87.1	87.0	87.0	86.9	86.8	86.6	86.5	86.4
25°	90.1	90.0	90.0	89.9	89.8	89.8	89.7	89.6	89.5	89.4	89.3
27.5°	92.9	92.8	92.7	92.7	92.6	92.5	92.4	92.3	92.2	92.1	92.0
30°	95.6	95.5	95.4	95.4	95.3	95.2	95.1	95.0	94.9	94.8	94.7
32.5°	97.9	97.9	97.8	97.8	97.7	97.6	97.6	97.5	97.4	97.2	97.1
35°	100.2	100.1	100.1	100.0	99.9	99.9	99.8	99.8	99.6	99.5	99.4
37.5°	102.2	102.1	102.1	102.0	102.0	101.9	101.9	101.8	101.7	101.5	101.4
40°	103.9	103.8	103.8	103.8	103.7	103.7	103.7	103.7	103.5	103.4	103.2
42.5°	105.4	105.4	105.4	105.4	105.3	105.3	105.3	105.3	105.2	105.0	104.9
45°	106.6	106.6	106.6	106.6	106.6	106.6	106.6	106.5	106.4	106.3	106.1
47.5°	107.6	107.6	107.6	107.6	107.6	107.6	107.7	107.7	107.5	107.4	107.2
50°	108.2	108.2	108.3	108.3	108.3	108.3	108.3	108.3	108.2	108.0	107.9
52.5°	108.8	108.8	108.8	108.9	108.9	108.9	108.9	108.9	108.8	108.7	108.5
55°	108.9	108.9	108.9	108.9	108.9	109.0	109.0	109.0	108.9	108.7	108.6
57.5°	108.9	108.9	109.0	109.0	109.0	109.1	109.1	109.1	109.0	108.8	108.7
60°	108.7	108.8	108.8	108.8	108.8	108.8	108.8	108.9	108.7	108.6	108.5
62.5°	108.0	108.1	108.1	108.1	108.1	108.1	108.2	108.2	108.1	107.9	107.8
65°	107.1	107.2	107.2	107.2	107.2	107.2	107.2	107.2	107.1	107.0	106.9
67.5°	106.1	106.1	106.1	106.2	106.2	106.2	106.3	106.3	106.2	106.0	105.9
70°	104.8	104.8	104.8	104.8	104.8	104.8	104.8	104.8	104.7	104.6	104.5
72.5°	103.2	103.2	103.2	103.2	103.2	103.2	103.2	103.3	103.2	103.1	102.9
75°	101.4	101.4	101.4	101.5	101.5	101.5	101.5	101.5	101.4	101.3	101.2
77.5°	99.4	99.4	99.4	99.5	99.5	99.5	99.5	99.5	99.4	99.3	99.2
80°	97.4	97.4	97.4	97.4	97.4	97.4	97.5	97.5	97.4	97.3	97.2
82.5°	95.2	95.2	95.2	95.2	95.2	95.2	95.2	95.2	95.1	95.0	94.9
85°	93.0	93.0	93.0	93.0	93.0	93.0	93.1	93.1	93.0	92.9	92.7
87.5°	90.7	90.7	90.8	90.8	90.8	90.8	90.9	90.9	90.8	90.7	90.6
90°	88.6	88.7	88.7	88.7	88.7	88.7	88.7	88.7	88.6	88.5	88.4
92.5°	86.3	86.4	86.4	86.4	86.4	86.4	86.4	86.4	86.3	86.2	86.1
95°	83.9	83.9	83.9	83.9	83.9	84.0	84.0	84.0	83.9	83.8	83.7
97.5°	81.6	81.6	81.6	81.6	81.6	81.7	81.7	81.7	81.5	81.4	81.3
100°	79.3	79.3	79.3	79.3	79.2	79.2	79.2	79.2	79.0	78.8	78.7
102.5°	76.6	76.6	76.7	76.7	76.7	76.7	76.7	76.7	76.5	76.2	75.9
105°	74.0	74.0	74.0	74.0	74.0	74.0	74.0	74.0	73.7	73.4	73.0
107.5°	71.3	71.2	71.2	71.2	71.1	71.1	71.1	71.0	70.6	70.3	69.9
110°	68.5	68.5	68.5	68.5	68.5	68.5	68.5	68.5	68.0	67.5	66.9

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	27.5°	30°	32.5°	35°	37.5°	40°	42.5°	45°	47.5°	50°	52.5°
112.5°	65.6	65.5	65.5	65.5	65.5	65.4	65.4	65.4	64.8	64.2	63.7
115°	62.6	62.5	62.5	62.5	62.4	62.4	62.3	62.3	61.6	61.0	60.4
117.5°	59.5	59.5	59.4	59.4	59.4	59.3	59.3	59.3	58.6	57.9	57.2
120°	56.5	56.5	56.4	56.4	56.3	56.3	56.2	56.2	55.4	54.7	53.9
122.5°	53.5	53.4	53.3	53.3	53.2	53.1	53.1	53.0	52.2	51.4	50.7
125°	50.3	50.2	50.1	50.1	50.0	50.0	49.9	49.8	49.0	48.2	47.5
127.5°	47.2	47.1	47.1	47.0	46.9	46.8	46.7	46.7	45.8	45.0	44.2
130°	44.0	43.9	43.8	43.8	43.7	43.6	43.5	43.4	42.6	41.8	40.9
132.5°	41.0	40.9	40.8	40.7	40.6	40.5	40.4	40.3	39.5	38.6	37.8
135°	38.0	37.9	37.8	37.7	37.6	37.5	37.4	37.3	36.5	35.7	34.8
137.5°	34.7	34.6	34.5	34.4	34.4	34.3	34.2	34.1	33.3	32.5	31.7
140°	31.6	31.5	31.4	31.3	31.2	31.1	31.0	30.9	30.1	29.3	28.6
142.5°	28.4	28.3	28.2	28.1	28.0	28.0	27.9	27.8	27.1	26.4	25.7
145°	25.5	25.4	25.3	25.3	25.2	25.1	25.0	24.9	24.3	23.7	23.0
147.5°	22.3	22.3	22.2	22.1	22.1	22.0	21.9	21.9	21.4	20.9	20.3
150°	19.4	19.4	19.4	19.3	19.3	19.3	19.3	19.2	18.8	18.3	17.8
152.5°	16.5	16.5	16.5	16.4	16.4	16.4	16.4	16.3	16.0	15.6	15.3
155°	13.5	13.6	13.6	13.6	13.6	13.6	13.6	13.6	13.3	13.0	12.7
157.5°	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.9	10.7	10.5	10.3
160°	8.0	8.0	8.1	8.1	8.1	8.1	8.2	8.2	8.0	7.9	7.8
162.5°	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.7	5.6	5.5
165°	3.3	3.3	3.4	3.4	3.5	3.5	3.6	3.6	3.5	3.5	3.4
167.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5	1.5
170°	0.3	0.3	0.3	0.4	0.4	0.4	0.4	0.5	0.5	0.5	0.5
172.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.0	0.0	0.0	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	60.6	60.5	60.5	60.4	60.4	60.3	60.3	60.2	60.2	60.1	60.1
5°	63.0	63.0	62.9	62.8	62.7	62.6	62.5	62.4	62.2	62.1	62.0
7.5°	66.2	66.1	66.0	65.9	65.8	65.7	65.6	65.4	65.3	65.1	65.0
10°	69.6	69.5	69.4	69.3	69.2	69.1	68.9	68.8	68.7	68.5	68.4
12.5°	73.1	73.1	73.0	72.9	72.8	72.7	72.5	72.4	72.2	72.0	71.9
15°	76.5	76.4	76.3	76.1	76.0	75.9	75.8	75.6	75.5	75.3	75.1
17.5°	79.9	79.8	79.6	79.5	79.4	79.3	79.1	79.0	78.8	78.7	78.5
20°	83.1	83.0	82.8	82.7	82.6	82.5	82.3	82.2	82.0	81.9	81.8
22.5°	86.2	86.1	86.0	85.8	85.7	85.6	85.4	85.3	85.1	85.0	84.8
25°	89.2	89.0	88.9	88.8	88.7	88.6	88.4	88.3	88.1	88.0	87.8
27.5°	91.8	91.7	91.6	91.5	91.3	91.2	91.1	90.9	90.7	90.6	90.4
30°	94.5	94.4	94.3	94.2	94.0	93.9	93.8	93.6	93.5	93.3	93.2
32.5°	96.9	96.8	96.6	96.5	96.3	96.2	96.1	95.9	95.8	95.6	95.5
35°	99.2	99.1	99.0	98.8	98.7	98.6	98.4	98.3	98.1	98.0	97.8
37.5°	101.3	101.2	101.0	100.9	100.8	100.6	100.5	100.3	100.2	100.0	99.9
40°	103.1	103.0	102.8	102.7	102.5	102.4	102.3	102.1	102.0	101.8	101.7
42.5°	104.7	104.6	104.4	104.3	104.1	104.0	103.8	103.7	103.5	103.4	103.3
45°	106.0	105.9	105.7	105.6	105.5	105.4	105.2	105.0	104.9	104.7	104.6
47.5°	107.1	107.0	106.8	106.7	106.5	106.4	106.2	106.1	105.9	105.7	105.6
50°	107.8	107.6	107.5	107.3	107.2	107.1	106.9	106.8	106.7	106.5	106.4
52.5°	108.4	108.3	108.2	108.0	107.9	107.8	107.7	107.5	107.4	107.3	107.1
55°	108.5	108.4	108.3	108.2	108.0	107.9	107.8	107.7	107.6	107.4	107.3
57.5°	108.6	108.4	108.3	108.2	108.1	107.9	107.8	107.7	107.5	107.4	107.3
60°	108.3	108.2	108.1	107.9	107.8	107.7	107.5	107.4	107.3	107.2	107.0
62.5°	107.7	107.5	107.4	107.3	107.1	107.0	106.9	106.8	106.7	106.6	106.5
65°	106.8	106.7	106.5	106.4	106.3	106.2	106.1	106.0	105.9	105.9	105.8
67.5°	105.8	105.7	105.5	105.4	105.3	105.2	105.1	105.0	104.9	104.8	104.7
70°	104.4	104.3	104.2	104.1	104.0	103.8	103.7	103.7	103.6	103.5	103.4
72.5°	102.8	102.7	102.6	102.5	102.4	102.3	102.2	102.1	102.0	101.9	101.8
75°	101.1	101.0	100.9	100.8	100.7	100.6	100.5	100.4	100.3	100.2	100.2
77.5°	99.1	99.0	98.9	98.8	98.7	98.6	98.5	98.4	98.4	98.3	98.2
80°	97.1	97.0	96.8	96.7	96.6	96.5	96.5	96.4	96.3	96.2	96.2
82.5°	94.8	94.7	94.6	94.5	94.4	94.3	94.2	94.1	94.0	94.0	93.9
85°	92.6	92.5	92.4	92.3	92.2	92.1	92.0	91.9	91.8	91.7	91.6
87.5°	90.5	90.4	90.3	90.2	90.1	90.0	89.9	89.8	89.7	89.6	89.5
90°	88.3	88.2	88.1	88.0	87.9	87.8	87.7	87.6	87.4	87.3	87.2
92.5°	86.0	85.9	85.8	85.7	85.6	85.5	85.4	85.2	85.1	84.9	84.8
95°	83.6	83.5	83.4	83.3	83.2	83.1	82.9	82.8	82.6	82.4	82.3
97.5°	81.2	81.0	80.9	80.8	80.7	80.5	80.4	80.2	80.0	79.9	79.7
100°	78.5	78.3	78.2	78.0	77.8	77.7	77.3	77.0	76.6	76.3	76.0
102.5°	75.7	75.4	75.2	74.9	74.6	74.4	73.9	73.4	72.9	72.4	71.9
105°	72.7	72.3	72.0	71.6	71.3	70.9	70.3	69.6	68.9	68.2	67.5
107.5°	69.5	69.1	68.7	68.3	67.9	67.5	66.7	65.8	65.0	64.1	63.3
110°	66.4	65.9	65.4	64.9	64.4	63.9	62.9	62.0	61.0	60.0	59.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	55°	57.5°	60°	62.5°	65°	67.5°	70°	72.5°	75°	77.5°	80°
112.5°	63.1	62.5	61.9	61.4	60.8	60.2	59.1	57.9	56.8	55.7	54.6
115°	59.7	59.1	58.5	57.8	57.2	56.5	55.3	54.1	52.9	51.7	50.5
117.5°	56.5	55.8	55.1	54.4	53.7	53.0	51.7	50.5	49.2	47.9	46.6
120°	53.2	52.4	51.7	50.9	50.2	49.4	48.1	46.7	45.4	44.1	42.8
122.5°	49.9	49.1	48.3	47.5	46.8	46.0	44.6	43.2	41.8	40.4	39.0
125°	46.7	45.9	45.1	44.3	43.5	42.7	41.3	39.8	38.4	37.0	35.5
127.5°	43.3	42.5	41.6	40.8	40.0	39.1	37.7	36.3	34.9	33.4	32.0
130°	40.1	39.2	38.4	37.5	36.7	35.9	34.4	33.0	31.6	30.1	28.7
132.5°	36.9	36.1	35.3	34.4	33.6	32.8	31.4	29.9	28.5	27.1	25.7
135°	34.0	33.1	32.3	31.5	30.6	29.8	28.4	27.0	25.5	24.1	22.7
137.5°	30.9	30.1	29.3	28.5	27.7	26.8	25.5	24.1	22.7	21.3	19.9
140°	27.8	27.0	26.3	25.5	24.7	24.0	22.6	21.3	20.0	18.7	17.4
142.5°	25.1	24.4	23.7	23.0	22.3	21.7	20.3	18.9	17.5	16.2	14.8
145°	22.4	21.8	21.2	20.5	19.9	19.3	18.1	16.8	15.6	14.4	13.1
147.5°	19.8	19.3	18.8	18.3	17.8	17.3	16.2	15.1	14.1	13.0	11.9
150°	17.4	16.9	16.5	16.0	15.5	15.1	14.2	13.3	12.4	11.5	10.6
152.5°	14.9	14.5	14.2	13.8	13.5	13.1	12.4	11.6	10.9	10.1	9.4
155°	12.4	12.1	11.8	11.5	11.2	10.9	10.4	9.8	9.2	8.7	8.1
157.5°	10.1	9.9	9.7	9.4	9.2	9.0	8.6	8.1	7.7	7.3	6.8
160°	7.6	7.5	7.3	7.2	7.0	6.9	6.6	6.2	5.9	5.6	5.3
162.5°	5.4	5.3	5.2	5.1	5.0	4.9	4.6	4.4	4.2	3.9	3.7
165°	3.3	3.2	3.2	3.1	3.0	3.0	2.8	2.6	2.5	2.3	2.2
167.5°	1.5	1.5	1.5	1.5	1.5	1.5	1.4	1.3	1.2	1.1	1.0
170°	0.5	0.6	0.6	0.6	0.6	0.6	0.6	0.5	0.5	0.4	0.4
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	60.0	60.0	59.9	59.9	59.8	59.8	59.7	59.7	59.6	59.6	59.5
5°	61.9	61.7	61.6	61.5	61.4	61.3	61.2	61.1	61.0	60.9	60.7
7.5°	64.9	64.7	64.6	64.4	64.3	64.2	64.1	63.9	63.8	63.7	63.5
10°	68.2	68.1	67.9	67.8	67.6	67.5	67.3	67.2	67.0	66.9	66.7
12.5°	71.7	71.5	71.4	71.2	71.0	70.8	70.7	70.5	70.3	70.2	70.0
15°	75.0	74.8	74.7	74.5	74.3	74.2	74.0	73.8	73.7	73.5	73.3
17.5°	78.4	78.2	78.1	77.9	77.7	77.6	77.4	77.2	77.0	76.8	76.7
20°	81.6	81.5	81.3	81.2	81.0	80.8	80.6	80.4	80.2	80.0	79.8
22.5°	84.7	84.6	84.4	84.3	84.1	83.9	83.7	83.5	83.4	83.2	83.0
25°	87.6	87.5	87.3	87.2	87.0	86.8	86.7	86.5	86.3	86.2	86.0
27.5°	90.3	90.1	90.0	89.8	89.7	89.6	89.5	89.4	89.3	89.1	89.0
30°	93.0	92.9	92.7	92.6	92.4	92.3	92.1	92.0	91.8	91.7	91.5
32.5°	95.4	95.2	95.1	94.9	94.8	94.7	94.5	94.4	94.3	94.1	94.0
35°	97.7	97.5	97.4	97.2	97.1	97.0	96.8	96.7	96.6	96.4	96.3
37.5°	99.7	99.6	99.4	99.3	99.1	99.0	98.9	98.8	98.6	98.5	98.4
40°	101.5	101.4	101.3	101.1	101.0	100.9	100.8	100.7	100.5	100.4	100.3
42.5°	103.1	103.0	102.8	102.7	102.6	102.5	102.3	102.2	102.1	102.0	101.9
45°	104.4	104.2	104.1	103.9	103.8	103.7	103.6	103.6	103.5	103.4	103.3
47.5°	105.4	105.2	105.1	104.9	104.8	104.8	104.7	104.6	104.5	104.4	104.4
50°	106.2	106.1	106.0	105.8	105.8	105.7	105.6	105.5	105.4	105.4	105.3
52.5°	107.0	106.9	106.8	106.6	106.5	106.4	106.3	106.2	106.1	106.1	106.0
55°	107.2	107.1	106.9	106.8	106.7	106.6	106.6	106.5	106.4	106.3	106.2
57.5°	107.1	107.0	106.9	106.8	106.7	106.6	106.6	106.5	106.5	106.4	106.3
60°	106.9	106.8	106.7	106.6	106.5	106.5	106.4	106.4	106.3	106.3	106.2
62.5°	106.3	106.2	106.1	106.0	106.0	106.0	105.9	105.9	105.9	105.9	105.8
65°	105.7	105.6	105.5	105.4	105.4	105.3	105.3	105.3	105.2	105.2	105.1
67.5°	104.6	104.5	104.4	104.3	104.3	104.3	104.3	104.3	104.2	104.2	104.2
70°	103.3	103.2	103.1	103.0	103.0	103.0	103.0	103.0	103.0	103.0	102.9
72.5°	101.7	101.6	101.5	101.4	101.4	101.5	101.5	101.5	101.5	101.6	101.6
75°	100.1	100.0	99.9	99.8	99.8	99.9	99.9	99.9	99.9	99.9	99.9
77.5°	98.2	98.1	98.0	97.9	98.0	98.0	98.0	98.0	98.0	98.0	98.0
80°	96.1	96.0	96.0	95.9	95.9	95.9	95.9	95.9	95.9	95.9	95.9
82.5°	93.8	93.7	93.6	93.5	93.6	93.6	93.6	93.6	93.6	93.6	93.6
85°	91.6	91.5	91.4	91.3	91.3	91.3	91.3	91.3	91.3	91.3	91.3
87.5°	89.4	89.3	89.2	89.1	89.1	89.0	89.0	89.0	89.0	89.0	89.0
90°	87.0	86.9	86.8	86.6	86.6	86.5	86.4	86.4	86.3	86.3	86.2
92.5°	84.6	84.4	84.3	84.1	84.0	83.9	83.8	83.7	83.6	83.5	83.4
95°	82.1	82.0	81.8	81.6	81.5	81.3	81.1	81.0	80.8	80.7	80.5
97.5°	79.5	79.4	79.2	79.1	78.8	78.5	78.2	77.9	77.6	77.4	77.1
100°	75.6	75.3	74.9	74.6	74.3	74.0	73.7	73.4	73.1	72.8	72.5
102.5°	71.4	70.9	70.4	69.9	69.6	69.3	68.9	68.6	68.3	67.9	67.6
105°	66.8	66.2	65.5	64.8	64.5	64.1	63.8	63.5	63.1	62.8	62.5
107.5°	62.4	61.6	60.7	59.9	59.5	59.2	58.9	58.5	58.2	57.9	57.5
110°	58.1	57.1	56.1	55.2	54.8	54.5	54.1	53.8	53.4	53.1	52.7

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	82.5°	85°	87.5°	90°	92.5°	95°	97.5°	100°	102.5°	105°	107.5°
112.5°	53.5	52.3	51.2	50.1	49.7	49.4	49.0	48.7	48.3	48.0	47.6
115°	49.3	48.1	46.9	45.7	45.4	45.0	44.6	44.3	43.9	43.5	43.2
117.5°	45.3	44.1	42.8	41.5	41.2	40.8	40.4	40.1	39.7	39.4	39.0
120°	41.4	40.1	38.8	37.4	37.1	36.7	36.3	35.9	35.5	35.2	34.8
122.5°	37.6	36.2	34.8	33.4	33.1	32.7	32.3	32.0	31.6	31.2	30.9
125°	34.1	32.7	31.3	29.8	29.4	29.1	28.7	28.3	27.9	27.6	27.2
127.5°	30.6	29.1	27.7	26.3	25.9	25.6	25.2	24.9	24.5	24.1	23.8
130°	27.3	25.9	24.4	23.0	22.7	22.4	22.1	21.7	21.4	21.1	20.8
132.5°	24.3	22.9	21.5	20.0	19.7	19.4	19.1	18.8	18.5	18.2	17.9
135°	21.3	19.9	18.4	17.0	16.7	16.4	16.2	15.9	15.6	15.3	15.0
137.5°	18.5	17.2	15.8	14.4	14.1	13.9	13.6	13.3	13.0	12.8	12.5
140°	16.0	14.7	13.4	12.1	11.8	11.5	11.2	10.9	10.6	10.3	10.0
142.5°	13.4	12.1	10.7	9.3	9.1	8.8	8.6	8.3	8.1	7.9	7.6
145°	11.9	10.7	9.4	8.2	7.9	7.5	7.2	6.9	6.5	6.2	5.9
147.5°	10.8	9.7	8.6	7.6	7.1	6.7	6.3	5.9	5.4	5.0	4.6
150°	9.7	8.8	7.9	7.0	6.5	6.0	5.5	5.1	4.6	4.1	3.6
152.5°	8.7	7.9	7.2	6.4	5.9	5.4	4.9	4.3	3.8	3.3	2.8
155°	7.5	7.0	6.4	5.9	5.3	4.7	4.1	3.5	3.0	2.4	1.8
157.5°	6.4	5.9	5.5	5.1	4.5	4.0	3.5	2.9	2.4	1.9	1.3
160°	4.9	4.6	4.3	3.9	3.5	3.1	2.7	2.3	1.9	1.4	1.0
162.5°	3.5	3.2	3.0	2.8	2.5	2.2	1.9	1.6	1.3	1.0	0.7
165°	2.0	1.9	1.7	1.6	1.4	1.3	1.1	0.9	0.8	0.6	0.5
167.5°	0.9	0.8	0.8	0.7	0.6	0.5	0.5	0.4	0.4	0.3	0.2
170°	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	59.5	59.4	59.4	59.3	59.3	59.2	59.2	59.1	59.1	59.0	59.0
5°	60.6	60.5	60.5	60.4	60.3	60.2	60.1	60.1	60.0	59.9	59.8
7.5°	63.4	63.3	63.1	63.0	62.8	62.7	62.5	62.4	62.2	62.1	61.9
10°	66.6	66.4	66.2	66.1	65.9	65.7	65.6	65.4	65.2	65.1	64.9
12.5°	69.8	69.6	69.5	69.3	69.2	69.0	68.9	68.7	68.6	68.4	68.3
15°	73.1	73.0	72.8	72.7	72.6	72.4	72.3	72.1	72.0	71.8	71.7
17.5°	76.5	76.3	76.2	76.0	75.9	75.8	75.6	75.5	75.3	75.2	75.0
20°	79.7	79.5	79.3	79.2	79.1	79.0	78.8	78.7	78.6	78.5	78.3
22.5°	82.8	82.6	82.5	82.4	82.3	82.2	82.1	82.0	81.9	81.8	81.7
25°	85.8	85.6	85.5	85.4	85.3	85.2	85.1	85.0	84.9	84.8	84.7
27.5°	88.9	88.8	88.7	88.5	88.4	88.3	88.1	88.0	87.9	87.7	87.6
30°	91.4	91.2	91.1	91.0	90.8	90.7	90.6	90.5	90.3	90.2	90.1
32.5°	93.9	93.7	93.6	93.5	93.4	93.3	93.2	93.1	92.9	92.8	92.7
35°	96.2	96.0	95.9	95.7	95.5	95.4	95.2	95.0	94.9	94.7	94.5
37.5°	98.3	98.1	97.8	97.5	97.2	97.0	96.7	96.4	96.1	95.8	95.5
40°	100.2	100.1	99.6	99.1	98.7	98.2	97.7	97.2	96.8	96.3	95.8
42.5°	101.8	101.6	101.0	100.3	99.7	99.0	98.4	97.7	97.1	96.4	95.8
45°	103.2	103.1	102.2	101.4	100.5	99.7	98.8	98.0	97.1	96.3	95.4
47.5°	104.3	104.2	103.2	102.2	101.1	100.1	99.1	98.1	97.1	96.0	95.0
50°	105.2	105.1	103.9	102.7	101.5	100.3	99.1	97.9	96.7	95.6	94.4
52.5°	105.9	105.8	104.4	103.1	101.8	100.4	99.1	97.8	96.4	95.1	93.8
55°	106.1	106.0	104.6	103.1	101.6	100.2	98.7	97.2	95.8	94.3	92.9
57.5°	106.3	106.2	104.6	103.0	101.4	99.8	98.2	96.6	95.0	93.4	91.8
60°	106.2	106.1	104.4	102.7	100.9	99.2	97.5	95.8	94.1	92.3	90.6
62.5°	105.8	105.8	103.9	102.1	100.3	98.5	96.6	94.8	93.0	91.1	89.3
65°	105.1	105.1	103.1	101.2	99.3	97.4	95.5	93.6	91.7	89.8	87.9
67.5°	104.2	104.2	102.2	100.2	98.2	96.2	94.2	92.2	90.2	88.2	86.2
70°	102.9	102.9	100.9	98.8	96.7	94.7	92.6	90.5	88.5	86.4	84.3
72.5°	101.6	101.6	99.5	97.3	95.2	93.0	90.8	88.7	86.5	84.4	82.2
75°	99.9	99.9	97.7	95.5	93.3	91.1	88.9	86.7	84.5	82.3	80.1
77.5°	98.1	98.1	95.8	93.6	91.3	89.0	86.8	84.5	82.3	80.0	77.7
80°	96.0	96.0	93.7	91.4	89.1	86.8	84.4	82.1	79.8	77.5	75.2
82.5°	93.7	93.7	91.3	89.0	86.7	84.3	82.0	79.7	77.4	75.0	72.7
85°	91.3	91.3	88.9	86.6	84.2	81.8	79.5	77.1	74.7	72.4	70.0
87.5°	89.0	88.9	86.5	84.1	81.7	79.2	76.8	74.4	72.0	69.5	67.1
90°	86.1	86.1	83.6	81.2	78.7	76.3	73.9	71.4	69.0	66.5	64.1
92.5°	83.3	83.2	80.7	78.2	75.8	73.3	70.8	68.4	65.9	63.4	61.0
95°	80.3	80.2	77.7	75.3	72.8	70.4	67.9	65.4	63.0	60.5	58.1
97.5°	76.8	76.5	74.1	71.8	69.4	67.1	64.7	62.3	60.0	57.6	55.2
100°	72.2	71.9	69.7	67.5	65.3	63.1	60.9	58.7	56.5	54.3	52.1
102.5°	67.3	66.9	64.9	62.9	60.9	58.9	56.9	54.9	52.9	50.9	48.8
105°	62.1	61.8	60.0	58.2	56.5	54.7	52.9	51.1	49.3	47.6	45.8
107.5°	57.2	56.9	55.3	53.7	52.1	50.5	48.9	47.3	45.7	44.1	42.6
110°	52.4	52.0	50.6	49.2	47.8	46.4	44.9	43.5	42.1	40.7	39.3

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	110°	112.5°	115°	117.5°	120°	122.5°	125°	127.5°	130°	132.5°	135°
112.5°	47.3	46.9	45.7	44.5	43.2	42.0	40.8	39.6	38.3	37.1	35.9
115°	42.8	42.4	41.4	40.3	39.3	38.2	37.2	36.1	35.1	34.0	33.0
117.5°	38.7	38.3	37.4	36.5	35.6	34.7	33.7	32.8	31.9	31.0	30.1
120°	34.4	34.0	33.3	32.5	31.8	31.0	30.3	29.5	28.8	28.0	27.3
122.5°	30.5	30.1	29.5	28.9	28.3	27.7	27.1	26.5	25.9	25.3	24.7
125°	26.8	26.4	26.0	25.5	25.0	24.5	24.0	23.6	23.1	22.6	22.1
127.5°	23.4	23.1	22.7	22.4	22.0	21.7	21.3	20.9	20.6	20.2	19.9
130°	20.5	20.2	19.9	19.6	19.3	19.0	18.7	18.5	18.2	17.9	17.6
132.5°	17.5	17.2	17.0	16.8	16.6	16.4	16.2	16.0	15.8	15.6	15.4
135°	14.8	14.5	14.4	14.2	14.1	14.0	13.9	13.8	13.6	13.5	13.4
137.5°	12.2	12.0	11.9	11.9	11.8	11.8	11.7	11.7	11.6	11.6	11.6
140°	9.7	9.4	9.5	9.5	9.6	9.6	9.7	9.7	9.8	9.8	9.8
142.5°	7.4	7.1	7.2	7.3	7.5	7.6	7.7	7.8	7.9	8.0	8.1
145°	5.5	5.2	5.4	5.6	5.8	5.9	6.1	6.3	6.5	6.7	6.8
147.5°	4.2	3.8	3.9	4.1	4.2	4.4	4.6	4.7	4.9	5.0	5.2
150°	3.2	2.7	2.8	3.0	3.1	3.2	3.4	3.5	3.6	3.7	3.9
152.5°	2.2	1.7	1.8	1.9	2.1	2.2	2.3	2.4	2.5	2.6	2.8
155°	1.2	0.7	0.8	0.9	1.0	1.1	1.2	1.4	1.5	1.6	1.7
157.5°	0.8	0.3	0.3	0.4	0.4	0.5	0.6	0.6	0.7	0.7	0.8
160°	0.6	0.2	0.2	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.5
162.5°	0.4	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
165°	0.3	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
167.5°	0.2	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
170°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	58.9	58.9	58.8	58.8	58.7	58.7	58.6	58.6	58.5	58.5	58.5
5°	59.7	59.7	59.6	59.5	59.5	59.4	59.3	59.2	59.2	59.2	59.2
7.5°	61.8	61.7	61.6	61.5	61.4	61.3	61.2	61.1	61.0	61.0	61.0
10°	64.8	64.7	64.6	64.5	64.5	64.4	64.3	64.2	64.1	64.1	64.2
12.5°	68.2	68.1	68.0	67.9	67.9	67.8	67.7	67.6	67.5	67.5	67.6
15°	71.6	71.5	71.4	71.4	71.3	71.2	71.1	71.0	70.9	71.0	71.0
17.5°	75.0	74.9	74.8	74.7	74.6	74.6	74.5	74.4	74.3	74.4	74.4
20°	78.3	78.2	78.1	78.1	78.0	77.9	77.9	77.8	77.7	77.7	77.7
22.5°	81.6	81.5	81.4	81.3	81.1	81.0	80.9	80.8	80.7	80.8	80.8
25°	84.6	84.5	84.4	84.3	84.2	84.1	84.0	83.9	83.8	83.8	83.7
27.5°	87.4	87.3	87.1	86.9	86.8	86.6	86.5	86.3	86.1	85.9	85.7
30°	89.8	89.4	89.1	88.8	88.5	88.1	87.8	87.5	87.2	86.8	86.5
32.5°	92.1	91.5	90.8	90.2	89.6	89.0	88.3	87.7	87.1	86.6	86.1
35°	93.6	92.7	91.7	90.8	89.8	88.9	87.9	87.0	86.1	85.5	84.9
37.5°	94.2	93.0	91.8	90.6	89.3	88.1	86.9	85.6	84.4	83.7	83.0
40°	94.3	92.8	91.3	89.8	88.3	86.8	85.4	83.9	82.4	81.6	80.8
42.5°	94.1	92.3	90.6	88.8	87.1	85.4	83.6	81.9	80.1	79.2	78.3
45°	93.5	91.5	89.6	87.6	85.7	83.7	81.8	79.8	77.9	76.8	75.7
47.5°	92.9	90.7	88.6	86.4	84.2	82.1	79.9	77.8	75.6	74.4	73.2
50°	92.0	89.7	87.4	85.0	82.7	80.4	78.1	75.7	73.4	72.1	70.7
52.5°	91.2	88.7	86.2	83.6	81.1	78.6	76.0	73.5	71.0	69.5	68.1
55°	90.2	87.5	84.8	82.1	79.4	76.7	74.0	71.3	68.7	67.1	65.6
57.5°	89.0	86.1	83.3	80.4	77.6	74.8	71.9	69.1	66.3	64.6	63.0
60°	87.6	84.6	81.6	78.7	75.7	72.7	69.7	66.7	63.7	62.0	60.3
62.5°	86.2	83.1	80.0	76.9	73.8	70.6	67.5	64.4	61.3	59.5	57.7
65°	84.7	81.5	78.3	75.0	71.8	68.6	65.4	62.2	59.0	57.1	55.2
67.5°	82.8	79.5	76.2	72.9	69.6	66.3	63.0	59.6	56.3	54.4	52.5
70°	80.9	77.6	74.2	70.8	67.4	64.0	60.7	57.3	53.9	51.9	50.0
72.5°	78.8	75.3	71.9	68.4	65.0	61.5	58.1	54.6	51.2	49.2	47.2
75°	76.6	73.1	69.6	66.0	62.5	59.0	55.5	52.0	48.5	46.5	44.5
77.5°	74.2	70.6	67.1	63.5	60.0	56.4	52.8	49.3	45.7	43.7	41.7
80°	71.6	68.0	64.5	60.9	57.3	53.7	50.1	46.5	42.9	40.8	38.8
82.5°	69.1	65.4	61.8	58.2	54.6	50.9	47.3	43.7	40.1	38.1	36.0
85°	66.4	62.7	59.1	55.4	51.8	48.1	44.5	40.8	37.2	35.2	33.2
87.5°	63.5	59.9	56.2	52.6	49.0	45.4	41.8	38.1	34.5	32.5	30.6
90°	60.5	56.9	53.3	49.7	46.1	42.5	38.9	35.3	31.8	29.8	27.9
92.5°	57.4	53.9	50.3	46.8	43.3	39.7	36.2	32.7	29.1	27.3	25.4
95°	54.6	51.1	47.6	44.1	40.7	37.2	33.7	30.2	26.8	25.0	23.2
97.5°	51.8	48.4	45.0	41.6	38.1	34.7	31.3	27.9	24.5	22.8	21.1
100°	48.8	45.5	42.2	38.9	35.6	32.3	29.0	25.7	22.4	20.8	19.2
102.5°	45.7	42.5	39.4	36.2	33.1	29.9	26.8	23.6	20.5	18.9	17.4
105°	42.7	39.7	36.7	33.7	30.7	27.6	24.6	21.6	18.6	17.1	15.6
107.5°	39.7	36.8	34.0	31.1	28.2	25.4	22.5	19.7	16.8	15.4	14.0
110°	36.6	33.9	31.2	28.5	25.8	23.1	20.3	17.6	14.9	13.7	12.4

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	137.5°	140°	142.5°	145°	147.5°	150°	152.5°	155°	157.5°	160°	162.5°
112.5°	33.3	30.8	28.2	25.7	23.1	20.6	18.0	15.5	12.9	11.8	10.6
115°	30.6	28.2	25.7	23.3	20.9	18.5	16.1	13.7	11.3	10.2	9.1
117.5°	27.9	25.6	23.4	21.1	18.9	16.7	14.4	12.2	10.0	9.0	8.0
120°	25.2	23.1	21.0	18.9	16.9	14.8	12.7	10.6	8.5	7.6	6.8
122.5°	22.8	20.9	19.0	17.1	15.2	13.3	11.5	9.6	7.7	6.9	6.1
125°	20.4	18.7	17.0	15.3	13.6	11.9	10.2	8.5	6.8	6.1	5.4
127.5°	18.3	16.8	15.2	13.6	12.1	10.5	9.0	7.4	5.8	5.2	4.6
130°	16.2	14.8	13.4	12.0	10.6	9.2	7.8	6.4	5.1	4.5	4.0
132.5°	14.2	12.9	11.6	10.4	9.1	7.9	6.6	5.3	4.1	3.6	3.2
135°	12.3	11.2	10.2	9.1	8.0	6.9	5.8	4.8	3.7	3.3	2.9
137.5°	10.6	9.6	8.7	7.7	6.7	5.8	4.8	3.8	2.9	2.6	2.3
140°	9.0	8.2	7.4	6.6	5.8	5.0	4.2	3.4	2.6	2.4	2.1
142.5°	7.5	6.8	6.1	5.4	4.7	4.0	3.3	2.6	1.9	1.7	1.5
145°	6.3	5.7	5.1	4.6	4.0	3.5	2.9	2.3	1.8	1.6	1.4
147.5°	4.8	4.4	4.0	3.6	3.3	2.9	2.5	2.1	1.7	1.5	1.4
150°	3.6	3.2	2.9	2.6	2.3	2.0	1.6	1.3	1.0	0.9	0.8
152.5°	2.5	2.3	2.1	1.9	1.6	1.4	1.2	0.9	0.7	0.7	0.6
155°	1.6	1.5	1.4	1.2	1.1	1.0	0.9	0.8	0.7	0.6	0.6
157.5°	0.8	0.7	0.7	0.6	0.6	0.6	0.5	0.5	0.5	0.4	0.4
160°	0.4	0.4	0.4	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2
162.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
165°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
167.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
170°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	58.5	58.5	58.5	58.5	58.5	58.5	58.6	58.6	58.6	58.6	58.6
5°	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.2	59.3	59.3	59.3
7.5°	61.0	61.0	61.0	61.0	61.0	61.0	61.0	61.1	61.1	61.2	61.2
10°	64.2	64.2	64.2	64.3	64.3	64.3	64.3	64.4	64.4	64.4	64.5
12.5°	67.6	67.7	67.7	67.7	67.8	67.8	67.8	67.9	67.9	67.9	68.0
15°	71.0	71.1	71.1	71.1	71.2	71.2	71.2	71.3	71.3	71.3	71.4
17.5°	74.4	74.5	74.5	74.5	74.6	74.6	74.6	74.7	74.7	74.8	74.8
20°	77.8	77.8	77.8	77.8	77.8	77.8	77.9	77.9	78.0	78.0	78.1
22.5°	80.8	80.9	80.9	80.9	80.9	81.0	81.0	81.1	81.1	81.2	81.2
25°	83.6	83.6	83.5	83.5	83.4	83.4	83.3	83.4	83.5	83.7	83.8
27.5°	85.5	85.3	85.1	84.9	84.7	84.5	84.3	84.5	84.7	84.9	85.0
30°	86.1	85.7	85.4	85.0	84.6	84.3	83.9	84.2	84.5	84.7	85.0
32.5°	85.6	85.2	84.7	84.2	83.7	83.2	82.7	83.1	83.4	83.7	84.0
35°	84.3	83.7	83.2	82.6	82.0	81.4	80.8	81.2	81.6	82.0	82.3
37.5°	82.4	81.7	81.0	80.3	79.6	78.9	78.2	78.6	79.1	79.5	79.9
40°	80.0	79.2	78.4	77.5	76.7	75.9	75.1	75.6	76.1	76.6	77.0
42.5°	77.4	76.4	75.5	74.6	73.6	72.7	71.8	72.3	72.9	73.5	74.0
45°	74.7	73.6	72.5	71.5	70.4	69.4	68.3	68.9	69.6	70.2	70.9
47.5°	72.0	70.8	69.6	68.4	67.2	66.0	64.8	65.5	66.3	67.0	67.7
50°	69.4	68.0	66.7	65.4	64.0	62.7	61.4	62.2	63.0	63.8	64.6
52.5°	66.7	65.2	63.8	62.3	60.9	59.5	58.0	58.9	59.8	60.7	61.5
55°	64.0	62.5	60.9	59.4	57.8	56.3	54.7	55.7	56.6	57.6	58.5
57.5°	61.4	59.8	58.1	56.5	54.9	53.3	51.6	52.6	53.6	54.6	55.6
60°	58.6	56.9	55.3	53.6	51.9	50.2	48.5	49.5	50.6	51.6	52.7
62.5°	56.0	54.2	52.4	50.6	48.8	47.1	45.3	46.4	47.5	48.6	49.7
65°	53.4	51.5	49.7	47.8	46.0	44.1	42.3	43.4	44.5	45.7	46.8
67.5°	50.6	48.7	46.8	44.9	43.0	41.1	39.2	40.3	41.5	42.7	43.9
70°	48.0	46.1	44.1	42.2	40.2	38.2	36.3	37.5	38.6	39.8	41.0
72.5°	45.2	43.2	41.3	39.3	37.3	35.3	33.3	34.5	35.7	36.9	38.1
75°	42.5	40.5	38.5	36.5	34.5	32.5	30.5	31.7	32.9	34.1	35.3
77.5°	39.7	37.7	35.6	33.6	31.6	29.6	27.6	28.8	30.0	31.1	32.3
80°	36.8	34.7	32.7	30.7	28.6	26.6	24.5	25.7	26.9	28.1	29.3
82.5°	34.0	32.0	30.0	28.0	26.0	23.9	21.9	23.1	24.2	25.4	26.5
85°	31.2	29.2	27.2	25.2	23.2	21.2	19.2	20.4	21.5	22.7	23.8
87.5°	28.6	26.7	24.7	22.7	20.8	18.8	16.8	17.9	19.0	20.1	21.3
90°	26.0	24.1	22.2	20.3	18.4	16.4	14.5	15.6	16.7	17.8	18.8
92.5°	23.6	21.8	19.9	18.1	16.2	14.4	12.5	13.6	14.6	15.7	16.7
95°	21.4	19.7	17.9	16.1	14.3	12.6	10.8	11.8	12.8	13.8	14.8
97.5°	19.4	17.7	16.0	14.3	12.6	11.0	9.3	10.2	11.1	12.1	13.0
100°	17.6	15.9	14.3	12.7	11.1	9.5	7.8	8.7	9.6	10.5	11.4
102.5°	15.8	14.3	12.7	11.2	9.7	8.1	6.6	7.4	8.2	9.0	9.9
105°	14.1	12.6	11.1	9.6	8.1	6.6	5.1	5.9	6.7	7.5	8.3
107.5°	12.7	11.3	9.9	8.5	7.2	5.8	4.4	5.1	5.8	6.5	7.2
110°	11.1	9.8	8.5	7.2	5.9	4.6	3.4	4.0	4.6	5.3	5.9

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	165°	167.5°	170°	172.5°	175°	177.5°	180°	182.5°	185°	187.5°	190°
112.5°	9.4	8.3	7.1	6.0	4.8	3.7	2.5	3.1	3.6	4.2	4.8
115°	8.1	7.0	5.9	4.9	3.8	2.7	1.6	2.2	2.7	3.2	3.7
117.5°	7.0	6.0	5.0	4.1	3.1	2.1	1.1	1.6	2.0	2.5	3.0
120°	5.9	5.0	4.1	3.2	2.4	1.5	0.6	1.0	1.4	1.8	2.2
122.5°	5.3	4.5	3.7	2.9	2.1	1.3	0.5	0.8	1.2	1.5	1.9
125°	4.7	4.0	3.3	2.6	1.9	1.2	0.5	0.8	1.1	1.4	1.7
127.5°	4.0	3.4	2.8	2.2	1.6	1.0	0.4	0.6	0.9	1.1	1.4
130°	3.5	3.0	2.5	1.9	1.4	0.9	0.4	0.6	0.8	1.0	1.2
132.5°	2.8	2.4	2.0	1.5	1.1	0.7	0.3	0.4	0.6	0.8	0.9
135°	2.5	2.2	1.8	1.4	1.0	0.6	0.3	0.4	0.5	0.7	0.8
137.5°	2.0	1.7	1.4	1.1	0.8	0.6	0.3	0.4	0.5	0.5	0.6
140°	1.8	1.6	1.3	1.1	0.8	0.5	0.3	0.3	0.4	0.5	0.6
142.5°	1.4	1.2	1.0	0.8	0.6	0.4	0.3	0.3	0.3	0.4	0.4
145°	1.3	1.1	0.9	0.8	0.6	0.4	0.3	0.3	0.3	0.3	0.3
147.5°	1.2	1.1	0.9	0.7	0.6	0.4	0.3	0.3	0.3	0.3	0.3
150°	0.7	0.7	0.6	0.5	0.4	0.3	0.3	0.3	0.3	0.3	0.3
152.5°	0.6	0.5	0.5	0.4	0.4	0.3	0.3	0.3	0.3	0.3	0.3
155°	0.5	0.5	0.4	0.4	0.3	0.2	0.2	0.2	0.2	0.2	0.2
157.5°	0.4	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2	0.2	0.2
160°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
162.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1
165°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1
167.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
170°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
172.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
175°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
177.5°	0.1	0.1	0.1	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	58.7	58.7	58.7	58.7	58.8	58.8	58.8	58.9	58.9	58.9	58.9
5°	59.3	59.3	59.4	59.4	59.4	59.5	59.5	59.6	59.7	59.7	59.8
7.5°	61.3	61.3	61.4	61.4	61.5	61.6	61.7	61.8	61.9	62.0	62.1
10°	64.5	64.5	64.5	64.6	64.6	64.7	64.8	65.0	65.1	65.2	65.3
12.5°	68.0	68.0	68.0	68.1	68.1	68.2	68.3	68.4	68.5	68.6	68.7
15°	71.4	71.4	71.4	71.5	71.5	71.6	71.8	71.9	72.0	72.1	72.2
17.5°	74.8	74.9	74.9	75.0	75.0	75.1	75.2	75.4	75.5	75.6	75.7
20°	78.1	78.2	78.2	78.3	78.3	78.4	78.6	78.7	78.8	78.9	79.1
22.5°	81.3	81.3	81.4	81.4	81.5	81.6	81.7	81.9	82.0	82.2	82.3
25°	83.9	84.0	84.1	84.3	84.4	84.5	84.7	84.8	85.0	85.1	85.2
27.5°	85.2	85.4	85.6	85.8	85.9	86.2	86.5	86.9	87.2	87.5	87.8
30°	85.3	85.5	85.8	86.1	86.3	86.9	87.4	87.9	88.4	88.9	89.5
32.5°	84.3	84.7	85.0	85.3	85.6	86.4	87.2	88.1	88.9	89.7	90.5
35°	82.7	83.1	83.5	83.9	84.2	85.3	86.3	87.4	88.4	89.5	90.6
37.5°	80.3	80.8	81.2	81.6	82.0	83.3	84.6	85.9	87.2	88.6	89.9
40°	77.5	78.0	78.5	78.9	79.4	81.0	82.5	84.0	85.6	87.1	88.6
42.5°	74.6	75.2	75.7	76.3	76.9	78.6	80.4	82.2	83.9	85.7	87.4
45°	71.5	72.2	72.8	73.5	74.1	76.1	78.0	80.0	82.0	84.0	85.9
47.5°	68.5	69.2	70.0	70.7	71.5	73.6	75.8	78.0	80.1	82.3	84.5
50°	65.4	66.3	67.1	67.9	68.7	71.1	73.4	75.8	78.2	80.5	82.9
52.5°	62.4	63.3	64.2	65.1	66.0	68.5	71.1	73.6	76.2	78.7	81.3
55°	59.5	60.4	61.4	62.3	63.3	66.0	68.7	71.4	74.1	76.8	79.5
57.5°	56.5	57.5	58.5	59.5	60.5	63.4	66.2	69.1	72.0	74.8	77.7
60°	53.7	54.7	55.8	56.8	57.9	60.8	63.8	66.8	69.8	72.8	75.7
62.5°	50.8	51.9	53.0	54.1	55.2	58.3	61.4	64.5	67.6	70.7	73.8
65°	47.9	49.0	50.2	51.3	52.4	55.6	58.8	62.0	65.2	68.4	71.6
67.5°	45.0	46.2	47.4	48.5	49.7	53.0	56.2	59.5	62.8	66.0	69.3
70°	42.2	43.4	44.5	45.7	46.9	50.2	53.6	56.9	60.3	63.6	67.0
72.5°	39.2	40.4	41.6	42.8	44.0	47.4	50.8	54.2	57.6	61.0	64.5
75°	36.4	37.6	38.8	40.0	41.2	44.7	48.1	51.6	55.1	58.5	62.0
77.5°	33.5	34.7	35.9	37.1	38.3	41.8	45.3	48.8	52.3	55.8	59.3
80°	30.5	31.7	32.9	34.1	35.3	38.8	42.3	45.9	49.4	52.9	56.5
82.5°	27.7	28.9	30.0	31.2	32.3	35.9	39.4	43.0	46.6	50.1	53.7
85°	25.0	26.2	27.3	28.5	29.6	33.2	36.7	40.3	43.8	47.4	50.9
87.5°	22.4	23.5	24.6	25.7	26.8	30.3	33.9	37.4	41.0	44.5	48.1
90°	19.9	21.0	22.1	23.2	24.2	27.8	31.3	34.8	38.3	41.9	45.4
92.5°	17.7	18.8	19.8	20.9	21.9	25.4	28.8	32.2	35.7	39.1	42.5
95°	15.8	16.8	17.8	18.8	19.8	23.1	26.5	29.9	33.2	36.6	40.0
97.5°	13.9	14.9	15.8	16.7	17.7	20.9	24.2	27.5	30.8	34.1	37.4
100°	12.3	13.2	14.1	15.0	15.9	19.0	22.2	25.4	28.6	31.8	34.9
102.5°	10.7	11.5	12.3	13.1	14.0	17.0	20.1	23.2	26.2	29.3	32.4
105°	9.1	9.9	10.7	11.5	12.3	15.2	18.1	21.1	24.0	26.9	29.9
107.5°	7.9	8.6	9.3	10.0	10.7	13.4	16.2	19.0	21.7	24.5	27.3
110°	6.6	7.2	7.9	8.5	9.1	11.8	14.4	17.0	19.6	22.2	24.8

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	192.5°	195°	197.5°	200°	202.5°	205°	207.5°	210°	212.5°	215°	217.5°
112.5°	5.4	5.9	6.5	7.1	7.6	10.1	12.6	15.0	17.5	20.0	22.5
115°	4.2	4.7	5.2	5.7	6.2	8.6	10.9	13.2	15.5	17.8	20.2
117.5°	3.4	3.9	4.3	4.8	5.3	7.4	9.6	11.7	13.9	16.1	18.2
120°	2.6	3.1	3.5	3.9	4.3	6.3	8.3	10.3	12.4	14.4	16.4
122.5°	2.3	2.6	3.0	3.3	3.7	5.5	7.4	9.2	11.0	12.9	14.7
125°	2.0	2.3	2.6	2.9	3.2	4.8	6.5	8.1	9.8	11.4	13.1
127.5°	1.6	1.9	2.1	2.4	2.6	4.1	5.6	7.1	8.5	10.0	11.5
130°	1.4	1.6	1.8	2.0	2.2	3.6	4.9	6.2	7.5	8.8	10.1
132.5°	1.1	1.3	1.4	1.6	1.8	2.9	4.1	5.3	6.4	7.6	8.7
135°	1.0	1.1	1.2	1.4	1.5	2.5	3.5	4.5	5.5	6.5	7.5
137.5°	0.7	0.8	0.9	1.0	1.1	2.0	2.9	3.7	4.6	5.5	6.4
140°	0.6	0.7	0.8	0.8	0.9	1.7	2.4	3.1	3.8	4.6	5.3
142.5°	0.4	0.5	0.5	0.6	0.6	1.2	1.8	2.4	3.0	3.7	4.3
145°	0.3	0.4	0.4	0.4	0.4	0.9	1.4	1.9	2.4	2.9	3.4
147.5°	0.3	0.3	0.3	0.3	0.3	0.7	1.1	1.5	1.8	2.2	2.6
150°	0.3	0.3	0.3	0.3	0.3	0.5	0.8	1.1	1.4	1.7	1.9
152.5°	0.3	0.3	0.3	0.3	0.3	0.4	0.6	0.8	1.0	1.2	1.4
155°	0.2	0.2	0.2	0.3	0.3	0.4	0.5	0.6	0.7	0.8	1.0
157.5°	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.4	0.5	0.6	0.6
160°	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3	0.3	0.3	0.4
162.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2	0.2
165°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.2
167.5°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.2	0.2	0.2
170°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
172.5°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.0	0.0	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	59.0	59.0	59.0	59.1	59.1	59.2	59.3	59.3	59.4	59.4	59.5
5°	59.8	59.9	60.0	60.1	60.2	60.3	60.4	60.5	60.6	60.7	60.8
7.5°	62.2	62.3	62.5	62.6	62.7	62.9	63.0	63.2	63.3	63.4	63.6
10°	65.4	65.5	65.6	65.8	65.9	66.1	66.3	66.4	66.6	66.7	66.9
12.5°	68.8	68.9	69.0	69.1	69.3	69.5	69.6	69.8	70.0	70.1	70.3
15°	72.4	72.5	72.6	72.8	72.9	73.1	73.2	73.4	73.5	73.7	73.9
17.5°	75.8	76.0	76.1	76.2	76.4	76.5	76.6	76.8	76.9	77.0	77.2
20°	79.2	79.3	79.4	79.6	79.7	79.8	80.0	80.1	80.2	80.4	80.5
22.5°	82.4	82.6	82.7	82.9	83.0	83.1	83.3	83.4	83.6	83.7	83.8
25°	85.4	85.5	85.7	85.8	86.0	86.1	86.3	86.4	86.6	86.7	86.9
27.5°	88.1	88.4	88.7	88.8	88.9	89.1	89.2	89.3	89.4	89.6	89.7
30°	90.0	90.5	91.0	91.2	91.4	91.5	91.7	91.9	92.0	92.2	92.4
32.5°	91.3	92.1	92.9	93.2	93.4	93.6	93.9	94.1	94.3	94.5	94.8
35°	91.6	92.7	93.7	94.1	94.5	94.9	95.3	95.7	96.1	96.5	96.9
37.5°	91.2	92.5	93.8	94.4	95.1	95.7	96.3	97.0	97.6	98.2	98.9
40°	90.2	91.7	93.3	94.1	95.0	95.9	96.8	97.7	98.6	99.5	100.4
42.5°	89.2	91.0	92.7	93.9	95.0	96.1	97.3	98.4	99.5	100.7	101.8
45°	87.9	89.9	91.9	93.3	94.6	96.0	97.4	98.8	100.2	101.5	102.9
47.5°	86.6	88.8	91.0	92.6	94.2	95.8	97.4	99.0	100.6	102.3	103.9
50°	85.3	87.7	90.0	91.8	93.6	95.4	97.2	99.0	100.8	102.6	104.4
52.5°	83.9	86.4	89.0	91.0	92.9	94.9	96.9	98.9	100.9	102.9	104.9
55°	82.2	84.9	87.7	89.8	92.0	94.1	96.3	98.5	100.6	102.8	105.0
57.5°	80.6	83.5	86.3	88.7	91.0	93.3	95.6	98.0	100.3	102.6	104.9
60°	78.7	81.7	84.7	87.2	89.7	92.2	94.7	97.2	99.7	102.1	104.6
62.5°	76.8	79.9	83.0	85.7	88.3	90.9	93.5	96.2	98.8	101.4	104.0
65°	74.8	78.0	81.2	84.0	86.7	89.5	92.2	94.9	97.7	100.4	103.2
67.5°	72.6	75.8	79.1	82.0	84.8	87.7	90.5	93.4	96.3	99.1	102.0
70°	70.4	73.7	77.1	80.0	83.0	85.9	88.9	91.8	94.8	97.7	100.7
72.5°	67.9	71.3	74.7	77.8	80.8	83.9	86.9	90.0	93.0	96.1	99.1
75°	65.5	68.9	72.4	75.5	78.6	81.8	84.9	88.0	91.1	94.2	97.4
77.5°	62.8	66.3	69.8	73.0	76.1	79.3	82.5	85.6	88.8	92.0	95.1
80°	60.0	63.5	67.1	70.3	73.5	76.8	80.0	83.2	86.4	89.7	92.9
82.5°	57.3	60.8	64.4	67.7	70.9	74.2	77.4	80.7	83.9	87.1	90.4
85°	54.5	58.0	61.6	64.9	68.1	71.4	74.7	78.0	81.2	84.5	87.8
87.5°	51.6	55.1	58.7	62.0	65.3	68.6	71.9	75.2	78.5	81.8	85.1
90°	48.9	52.5	56.0	59.2	62.5	65.8	69.0	72.3	75.6	78.8	82.1
92.5°	46.0	49.4	52.8	56.1	59.3	62.6	65.8	69.0	72.3	75.5	78.8
95°	43.3	46.7	50.1	53.3	56.4	59.6	62.8	66.0	69.2	72.4	75.6
97.5°	40.7	44.0	47.3	50.4	53.5	56.6	59.7	62.8	65.9	69.0	72.1
100°	38.1	41.3	44.5	47.4	50.3	53.1	56.0	58.9	61.8	64.7	67.6
102.5°	35.4	38.5	41.6	44.2	46.9	49.5	52.1	54.8	57.4	60.1	62.7
105°	32.8	35.8	38.7	41.1	43.5	45.8	48.2	50.6	53.0	55.4	57.8
107.5°	30.1	32.8	35.6	37.8	40.0	42.2	44.4	46.6	48.8	50.9	53.1
110°	27.5	30.1	32.7	34.7	36.6	38.6	40.5	42.5	44.4	46.4	48.3

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	220°	222.5°	225°	227.5°	230°	232.5°	235°	237.5°	240°	242.5°	245°
112.5°	24.9	27.4	29.9	31.6	33.3	35.0	36.7	38.4	40.1	41.8	43.6
115°	22.5	24.8	27.1	28.6	30.1	31.6	33.1	34.6	36.1	37.5	39.0
117.5°	20.4	22.5	24.7	25.9	27.2	28.5	29.7	31.0	32.3	33.5	34.8
120°	18.4	20.4	22.4	23.5	24.6	25.6	26.7	27.8	28.8	29.9	31.0
122.5°	16.5	18.4	20.2	21.1	22.0	22.9	23.8	24.7	25.6	26.4	27.3
125°	14.7	16.4	18.0	18.8	19.5	20.2	21.0	21.7	22.4	23.1	23.9
127.5°	13.0	14.5	15.9	16.6	17.2	17.8	18.4	19.0	19.7	20.3	20.9
130°	11.4	12.8	14.1	14.6	15.0	15.5	16.0	16.5	17.0	17.5	17.9
132.5°	9.9	11.1	12.2	12.6	13.0	13.4	13.8	14.1	14.5	14.9	15.3
135°	8.5	9.5	10.5	10.8	11.1	11.4	11.7	12.0	12.2	12.5	12.8
137.5°	7.3	8.1	9.0	9.2	9.4	9.6	9.8	10.0	10.2	10.4	10.6
140°	6.0	6.8	7.5	7.6	7.7	7.9	8.0	8.1	8.3	8.4	8.5
142.5°	4.9	5.5	6.1	6.2	6.3	6.3	6.4	6.5	6.6	6.6	6.7
145°	3.9	4.4	4.9	4.9	5.0	5.0	5.1	5.2	5.2	5.3	5.3
147.5°	3.0	3.4	3.7	3.8	3.9	3.9	4.0	4.0	4.1	4.1	4.2
150°	2.2	2.5	2.8	2.8	2.8	2.8	2.9	2.9	2.9	3.0	3.0
152.5°	1.5	1.7	1.9	1.9	2.0	2.0	2.0	2.1	2.1	2.1	2.1
155°	1.1	1.2	1.3	1.3	1.4	1.4	1.4	1.4	1.4	1.5	1.5
157.5°	0.7	0.8	0.9	0.9	0.9	0.9	0.9	0.9	0.9	1.0	1.0
160°	0.4	0.4	0.5	0.5	0.5	0.5	0.5	0.5	0.5	0.6	0.6
162.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
165°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
167.5°	0.2	0.2	0.3	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1
170°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
172.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	59.5	59.6	59.6	59.7	59.7	59.8	59.8	59.9	59.9	60.0	60.0
5°	60.9	61.1	61.2	61.3	61.4	61.5	61.7	61.8	61.9	62.0	62.2
7.5°	63.7	63.8	64.0	64.1	64.2	64.4	64.5	64.6	64.7	64.9	65.0
10°	67.1	67.2	67.3	67.5	67.6	67.8	67.9	68.1	68.2	68.4	68.5
12.5°	70.5	70.6	70.8	70.9	71.1	71.3	71.4	71.6	71.7	71.9	72.0
15°	74.0	74.2	74.3	74.5	74.6	74.7	74.9	75.0	75.2	75.3	75.5
17.5°	77.3	77.5	77.6	77.8	77.9	78.1	78.2	78.4	78.5	78.7	78.8
20°	80.6	80.8	80.9	81.1	81.2	81.4	81.5	81.7	81.8	82.0	82.1
22.5°	84.0	84.1	84.2	84.4	84.5	84.6	84.8	84.9	85.0	85.2	85.3
25°	87.0	87.1	87.3	87.4	87.5	87.6	87.8	87.9	88.0	88.1	88.3
27.5°	89.8	89.9	90.1	90.2	90.3	90.4	90.6	90.7	90.8	90.9	91.1
30°	92.5	92.6	92.7	92.9	93.0	93.1	93.2	93.3	93.4	93.5	93.7
32.5°	95.0	95.1	95.2	95.4	95.5	95.6	95.7	95.8	95.9	96.0	96.2
35°	97.3	97.4	97.5	97.7	97.8	97.9	98.0	98.1	98.2	98.3	98.5
37.5°	99.5	99.6	99.7	99.8	99.9	100.1	100.2	100.3	100.4	100.5	100.6
40°	101.3	101.4	101.5	101.6	101.7	101.9	102.0	102.1	102.2	102.3	102.4
42.5°	102.9	103.0	103.1	103.2	103.3	103.4	103.5	103.6	103.7	103.8	103.9
45°	104.3	104.4	104.5	104.6	104.7	104.8	104.9	105.0	105.1	105.2	105.3
47.5°	105.5	105.6	105.6	105.7	105.8	105.9	105.9	106.0	106.1	106.2	106.3
50°	106.2	106.3	106.4	106.5	106.6	106.7	106.7	106.8	106.9	107.0	107.1
52.5°	106.9	107.0	107.0	107.1	107.2	107.3	107.4	107.4	107.5	107.6	107.7
55°	107.1	107.2	107.3	107.4	107.5	107.6	107.7	107.8	107.8	107.9	108.0
57.5°	107.3	107.3	107.4	107.5	107.5	107.6	107.7	107.7	107.8	107.9	108.0
60°	107.1	107.2	107.2	107.3	107.3	107.4	107.5	107.5	107.6	107.6	107.7
62.5°	106.7	106.7	106.8	106.8	106.9	106.9	107.0	107.0	107.1	107.1	107.2
65°	105.9	106.0	106.0	106.1	106.1	106.2	106.2	106.3	106.3	106.4	106.4
67.5°	104.8	104.9	104.9	105.0	105.0	105.1	105.2	105.2	105.3	105.3	105.4
70°	103.7	103.7	103.7	103.7	103.7	103.8	103.8	103.8	103.8	103.9	103.9
72.5°	102.2	102.2	102.2	102.2	102.3	102.3	102.3	102.3	102.3	102.4	102.4
75°	100.5	100.5	100.5	100.5	100.5	100.5	100.5	100.5	100.5	100.5	100.5
77.5°	98.3	98.3	98.4	98.4	98.4	98.4	98.4	98.4	98.5	98.5	98.5
80°	96.1	96.2	96.2	96.2	96.2	96.2	96.3	96.3	96.3	96.3	96.4
82.5°	93.6	93.7	93.7	93.8	93.8	93.9	93.9	93.9	94.0	94.0	94.1
85°	91.1	91.1	91.2	91.3	91.3	91.4	91.5	91.5	91.6	91.7	91.7
87.5°	88.5	88.5	88.6	88.7	88.8	88.9	89.0	89.1	89.2	89.3	89.3
90°	85.4	85.5	85.7	85.8	86.0	86.1	86.3	86.4	86.6	86.7	86.8
92.5°	82.0	82.2	82.5	82.7	82.9	83.2	83.4	83.6	83.8	84.1	84.2
95°	78.8	79.1	79.4	79.7	80.0	80.3	80.6	80.9	81.2	81.4	81.6
97.5°	75.2	75.6	76.0	76.4	76.8	77.2	77.6	78.0	78.4	78.8	78.9
100°	70.5	71.0	71.5	71.9	72.4	72.9	73.4	73.9	74.4	74.9	75.2
102.5°	65.3	65.8	66.3	66.8	67.3	67.8	68.3	68.8	69.3	69.8	70.3
105°	60.1	60.6	61.2	61.7	62.2	62.7	63.2	63.7	64.3	64.8	65.4
107.5°	55.3	55.8	56.4	56.9	57.4	57.9	58.4	58.9	59.5	60.0	60.8
110°	50.3	50.8	51.3	51.8	52.3	52.9	53.4	53.9	54.4	54.9	55.9

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	247.5°	250°	252.5°	255°	257.5°	260°	262.5°	265°	267.5°	270°	272.5°
112.5°	45.3	45.8	46.3	46.8	47.3	47.8	48.3	48.8	49.3	49.9	51.0
115°	40.5	41.1	41.6	42.1	42.7	43.2	43.8	44.3	44.8	45.4	46.6
117.5°	36.1	36.6	37.1	37.7	38.2	38.8	39.3	39.8	40.4	40.9	42.3
120°	32.0	32.6	33.1	33.6	34.2	34.7	35.2	35.7	36.3	36.8	38.2
122.5°	28.2	28.7	29.3	29.8	30.3	30.8	31.3	31.8	32.3	32.8	34.3
125°	24.6	25.1	25.6	26.1	26.6	27.1	27.6	28.0	28.5	29.0	30.5
127.5°	21.5	22.0	22.5	22.9	23.4	23.9	24.3	24.8	25.3	25.7	27.2
130°	18.4	18.9	19.4	19.8	20.3	20.7	21.2	21.7	22.1	22.6	24.1
132.5°	15.7	16.1	16.5	17.0	17.4	17.8	18.3	18.7	19.1	19.6	21.1
135°	13.1	13.5	13.9	14.3	14.7	15.1	15.5	15.9	16.3	16.7	18.1
137.5°	10.8	11.1	11.5	11.8	12.2	12.5	12.8	13.2	13.5	13.9	15.3
140°	8.6	8.9	9.2	9.4	9.7	9.9	10.2	10.5	10.7	11.0	12.4
142.5°	6.8	6.9	7.1	7.2	7.4	7.5	7.7	7.8	7.9	8.1	9.5
145°	5.4	5.5	5.7	5.8	6.0	6.1	6.3	6.4	6.6	6.7	8.0
147.5°	4.2	4.4	4.6	4.8	5.0	5.2	5.4	5.5	5.7	5.9	7.0
150°	3.0	3.2	3.5	3.7	3.9	4.1	4.3	4.6	4.8	5.0	6.0
152.5°	2.2	2.4	2.6	2.8	3.0	3.2	3.4	3.6	3.7	3.9	4.8
155°	1.5	1.7	1.9	2.0	2.2	2.4	2.5	2.7	2.9	3.0	3.7
157.5°	1.0	1.1	1.2	1.4	1.5	1.6	1.8	1.9	2.0	2.2	2.7
160°	0.6	0.7	0.8	0.9	0.9	1.0	1.1	1.2	1.3	1.4	1.8
162.5°	0.3	0.3	0.4	0.4	0.4	0.4	0.4	0.4	0.5	0.5	0.9
165°	0.2	0.2	0.3	0.3	0.3	0.3	0.4	0.4	0.4	0.5	0.7
167.5°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.4
170°	0.1	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.2
172.5°	0.1	0.1	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.3	0.3
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	60.1	60.2	60.2	60.3	60.4	60.4	60.5	60.6	60.6	60.6	60.7
5°	62.3	62.4	62.5	62.6	62.8	62.9	63.0	63.1	63.2	63.3	63.4
7.5°	65.2	65.4	65.5	65.7	65.8	66.0	66.2	66.3	66.4	66.5	66.7
10°	68.7	68.8	69.0	69.1	69.3	69.5	69.6	69.8	69.9	70.0	70.1
12.5°	72.2	72.4	72.5	72.7	72.9	73.0	73.2	73.4	73.5	73.6	73.7
15°	75.6	75.8	76.0	76.1	76.3	76.4	76.6	76.7	76.9	77.0	77.1
17.5°	79.0	79.2	79.3	79.5	79.7	79.8	80.0	80.1	80.3	80.4	80.5
20°	82.3	82.4	82.6	82.8	82.9	83.1	83.3	83.4	83.6	83.7	83.8
22.5°	85.5	85.6	85.8	86.0	86.1	86.3	86.4	86.6	86.7	86.8	87.0
25°	88.4	88.6	88.8	88.9	89.1	89.2	89.4	89.5	89.7	89.8	89.9
27.5°	91.2	91.4	91.5	91.6	91.8	91.9	92.1	92.2	92.3	92.5	92.6
30°	93.8	94.0	94.1	94.3	94.4	94.6	94.7	94.9	95.0	95.1	95.3
32.5°	96.3	96.5	96.6	96.7	96.9	97.0	97.2	97.3	97.4	97.6	97.7
35°	98.6	98.8	98.9	99.0	99.2	99.3	99.5	99.6	99.7	99.8	100.0
37.5°	100.8	100.9	101.0	101.1	101.3	101.4	101.5	101.6	101.8	101.9	102.0
40°	102.6	102.7	102.8	102.9	103.0	103.2	103.3	103.4	103.5	103.6	103.8
42.5°	104.0	104.1	104.3	104.4	104.5	104.6	104.7	104.9	105.0	105.1	105.3
45°	105.4	105.6	105.7	105.9	106.0	106.1	106.3	106.4	106.5	106.6	106.8
47.5°	106.4	106.5	106.7	106.8	106.9	107.0	107.2	107.3	107.4	107.5	107.6
50°	107.2	107.3	107.4	107.5	107.6	107.7	107.8	107.9	108.1	108.2	108.3
52.5°	107.8	107.9	108.0	108.1	108.2	108.3	108.4	108.5	108.6	108.7	108.8
55°	108.1	108.2	108.3	108.3	108.4	108.5	108.6	108.7	108.8	108.9	109.0
57.5°	108.0	108.1	108.2	108.3	108.4	108.5	108.6	108.7	108.8	108.9	109.0
60°	107.8	107.8	107.9	108.0	108.1	108.1	108.2	108.3	108.4	108.5	108.6
62.5°	107.3	107.3	107.4	107.5	107.5	107.6	107.7	107.7	107.8	107.9	108.0
65°	106.5	106.5	106.6	106.7	106.7	106.8	106.8	106.9	107.0	107.1	107.2
67.5°	105.4	105.5	105.5	105.6	105.6	105.7	105.7	105.8	105.9	105.9	106.0
70°	104.0	104.1	104.1	104.2	104.3	104.3	104.4	104.5	104.5	104.6	104.7
72.5°	102.4	102.5	102.5	102.6	102.6	102.7	102.7	102.8	102.8	102.9	103.0
75°	100.6	100.6	100.7	100.7	100.8	100.9	100.9	101.0	101.0	101.1	101.2
77.5°	98.6	98.6	98.7	98.7	98.8	98.8	98.9	98.9	99.0	99.1	99.1
80°	96.4	96.5	96.5	96.6	96.7	96.7	96.8	96.8	96.9	97.0	97.0
82.5°	94.1	94.2	94.3	94.3	94.4	94.5	94.5	94.6	94.6	94.7	94.7
85°	91.8	91.8	91.9	91.9	92.0	92.0	92.1	92.2	92.2	92.3	92.4
87.5°	89.4	89.5	89.6	89.6	89.7	89.8	89.8	89.9	90.0	90.1	90.1
90°	86.9	87.0	87.1	87.2	87.4	87.5	87.6	87.7	87.8	87.8	87.9
92.5°	84.4	84.5	84.6	84.8	84.9	85.0	85.2	85.3	85.4	85.5	85.5
95°	81.8	81.9	82.1	82.2	82.4	82.5	82.7	82.8	82.9	83.0	83.1
97.5°	79.1	79.3	79.5	79.7	79.9	80.1	80.3	80.5	80.6	80.7	80.8
100°	75.5	75.8	76.1	76.4	76.6	76.9	77.2	77.5	77.7	77.8	78.0
102.5°	70.8	71.3	71.8	72.2	72.7	73.2	73.7	74.2	74.4	74.7	74.9
105°	66.1	66.8	67.4	68.1	68.8	69.4	70.1	70.7	71.1	71.4	71.7
107.5°	61.6	62.4	63.2	64.0	64.8	65.6	66.4	67.2	67.6	68.0	68.4
110°	56.9	57.9	58.8	59.8	60.8	61.8	62.7	63.7	64.2	64.7	65.2

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	275°	277.5°	280°	282.5°	285°	287.5°	290°	292.5°	295°	297.5°	300°
112.5°	52.1	53.3	54.4	55.6	56.7	57.8	59.0	60.1	60.7	61.3	61.9
115°	47.9	49.1	50.3	51.5	52.8	54.0	55.2	56.5	57.1	57.8	58.4
117.5°	43.6	44.9	46.3	47.6	49.0	50.3	51.7	53.0	53.7	54.4	55.1
120°	39.6	41.0	42.4	43.9	45.3	46.7	48.1	49.5	50.3	51.0	51.7
122.5°	35.8	37.2	38.7	40.2	41.6	43.1	44.6	46.0	46.8	47.6	48.3
125°	32.0	33.6	35.1	36.6	38.1	39.6	41.1	42.6	43.4	44.2	45.0
127.5°	28.7	30.2	31.7	33.2	34.7	36.2	37.7	39.2	40.0	40.9	41.7
130°	25.6	27.1	28.5	30.0	31.5	33.0	34.5	36.0	36.8	37.6	38.5
132.5°	22.5	24.0	25.5	26.9	28.4	29.9	31.3	32.8	33.6	34.4	35.3
135°	19.6	21.0	22.4	23.9	25.3	26.8	28.2	29.6	30.5	31.3	32.1
137.5°	16.7	18.1	19.5	20.9	22.4	23.8	25.2	26.6	27.4	28.3	29.1
140°	13.8	15.2	16.6	18.0	19.4	20.8	22.2	23.7	24.5	25.3	26.1
142.5°	11.0	12.4	13.9	15.3	16.8	18.2	19.7	21.1	21.8	22.6	23.3
145°	9.3	10.6	11.9	13.2	14.5	15.9	17.2	18.5	19.2	19.8	20.5
147.5°	8.2	9.3	10.4	11.5	12.6	13.7	14.9	16.0	16.6	17.3	17.9
150°	6.9	7.9	8.9	9.9	10.8	11.8	12.8	13.7	14.3	14.8	15.4
152.5°	5.6	6.4	7.2	8.1	8.9	9.7	10.6	11.4	11.9	12.4	12.9
155°	4.4	5.1	5.8	6.4	7.1	7.8	8.5	9.2	9.6	10.0	10.5
157.5°	3.3	3.9	4.5	5.1	5.6	6.2	6.8	7.4	7.7	8.0	8.4
160°	2.3	2.8	3.2	3.7	4.1	4.6	5.1	5.5	5.8	6.1	6.3
162.5°	1.2	1.6	2.0	2.4	2.7	3.1	3.5	3.9	4.1	4.3	4.5
165°	0.9	1.2	1.4	1.6	1.9	2.1	2.3	2.6	2.7	2.8	2.9
167.5°	0.5	0.7	0.8	0.9	1.1	1.2	1.3	1.4	1.5	1.6	1.7
170°	0.3	0.4	0.4	0.5	0.5	0.6	0.6	0.7	0.7	0.7	0.7
172.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.3
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	60.7	60.7	60.8	60.8	60.9	60.9	60.9	61.0	61.0	61.0	61.1
5°	63.5	63.6	63.6	63.7	63.8	63.9	64.0	64.0	64.1	64.2	64.2
7.5°	66.8	66.9	67.0	67.1	67.2	67.3	67.4	67.4	67.5	67.5	67.6
10°	70.2	70.4	70.5	70.6	70.7	70.8	70.9	71.0	71.1	71.1	71.2
12.5°	73.8	73.9	74.1	74.2	74.3	74.4	74.5	74.6	74.6	74.7	74.8
15°	77.2	77.3	77.5	77.6	77.7	77.8	77.9	78.0	78.1	78.1	78.2
17.5°	80.6	80.8	80.9	81.0	81.1	81.2	81.3	81.4	81.5	81.6	81.7
20°	83.9	84.1	84.2	84.3	84.5	84.6	84.7	84.7	84.8	84.9	84.9
22.5°	87.1	87.2	87.4	87.5	87.7	87.8	87.8	87.9	88.0	88.0	88.1
25°	90.0	90.1	90.3	90.4	90.5	90.6	90.7	90.7	90.8	90.9	90.9
27.5°	92.7	92.9	93.0	93.1	93.2	93.4	93.4	93.5	93.5	93.6	93.7
30°	95.4	95.5	95.6	95.8	95.9	96.0	96.1	96.1	96.2	96.3	96.3
32.5°	97.8	97.9	98.1	98.2	98.3	98.4	98.5	98.6	98.6	98.7	98.8
35°	100.1	100.2	100.3	100.4	100.6	100.7	100.7	100.8	100.8	100.9	100.9
37.5°	102.1	102.3	102.4	102.5	102.6	102.8	102.8	102.9	102.9	102.9	103.0
40°	103.9	104.0	104.1	104.2	104.4	104.5	104.5	104.5	104.6	104.6	104.7
42.5°	105.4	105.6	105.7	105.8	106.0	106.1	106.1	106.2	106.2	106.2	106.2
45°	106.9	107.0	107.1	107.2	107.3	107.4	107.4	107.4	107.4	107.5	107.5
47.5°	107.8	107.9	108.0	108.1	108.2	108.3	108.3	108.4	108.4	108.4	108.4
50°	108.4	108.6	108.7	108.8	108.9	109.1	109.1	109.0	109.0	109.0	109.0
52.5°	108.9	109.1	109.2	109.3	109.4	109.5	109.5	109.5	109.5	109.5	109.5
55°	109.2	109.3	109.4	109.5	109.7	109.8	109.8	109.8	109.7	109.7	109.7
57.5°	109.1	109.2	109.3	109.4	109.5	109.7	109.6	109.6	109.6	109.6	109.6
60°	108.7	108.9	109.0	109.1	109.2	109.3	109.3	109.3	109.3	109.3	109.3
62.5°	108.1	108.2	108.3	108.4	108.5	108.6	108.6	108.6	108.6	108.6	108.6
65°	107.2	107.3	107.4	107.5	107.6	107.7	107.7	107.7	107.7	107.7	107.7
67.5°	106.1	106.2	106.3	106.4	106.5	106.6	106.6	106.5	106.5	106.5	106.5
70°	104.8	104.9	105.0	105.1	105.2	105.3	105.2	105.2	105.2	105.2	105.2
72.5°	103.0	103.1	103.2	103.2	103.3	103.4	103.4	103.4	103.4	103.4	103.4
75°	101.2	101.3	101.4	101.4	101.5	101.6	101.6	101.6	101.6	101.6	101.6
77.5°	99.2	99.3	99.3	99.4	99.5	99.5	99.5	99.5	99.5	99.5	99.5
80°	97.1	97.1	97.2	97.3	97.3	97.4	97.4	97.4	97.4	97.4	97.4
82.5°	94.8	94.8	94.9	95.0	95.0	95.1	95.1	95.1	95.1	95.1	95.0
85°	92.5	92.5	92.6	92.7	92.8	92.8	92.8	92.8	92.8	92.8	92.9
87.5°	90.2	90.3	90.4	90.5	90.5	90.6	90.6	90.6	90.6	90.6	90.6
90°	88.0	88.1	88.1	88.2	88.3	88.4	88.4	88.4	88.4	88.4	88.4
92.5°	85.6	85.7	85.8	85.9	85.9	86.0	86.0	86.0	86.0	86.1	86.1
95°	83.2	83.3	83.4	83.5	83.6	83.6	83.7	83.7	83.7	83.7	83.7
97.5°	80.9	81.0	81.1	81.2	81.3	81.4	81.4	81.4	81.4	81.4	81.4
100°	78.1	78.3	78.5	78.6	78.8	78.9	78.9	78.9	78.9	79.0	79.0
102.5°	75.2	75.4	75.7	75.9	76.2	76.4	76.5	76.5	76.5	76.5	76.5
105°	72.0	72.3	72.7	73.0	73.3	73.6	73.6	73.7	73.7	73.7	73.7
107.5°	68.8	69.2	69.6	70.0	70.4	70.9	70.9	70.9	70.9	71.0	71.0
110°	65.7	66.2	66.7	67.2	67.7	68.2	68.2	68.2	68.2	68.2	68.3

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	302.5°	305°	307.5°	310°	312.5°	315°	317.5°	320°	322.5°	325°	327.5°
112.5°	62.4	63.0	63.6	64.2	64.8	65.3	65.4	65.4	65.4	65.4	65.5
115°	59.1	59.7	60.4	61.0	61.7	62.3	62.3	62.4	62.4	62.4	62.5
117.5°	55.8	56.5	57.2	57.9	58.5	59.2	59.3	59.4	59.4	59.5	59.5
120°	52.5	53.2	54.0	54.7	55.4	56.2	56.2	56.3	56.3	56.3	56.4
122.5°	49.1	49.9	50.7	51.4	52.2	53.0	53.0	53.1	53.2	53.2	53.3
125°	45.8	46.6	47.4	48.2	49.0	49.8	49.9	49.9	50.0	50.1	50.2
127.5°	42.5	43.3	44.1	44.9	45.7	46.5	46.6	46.7	46.8	46.9	46.9
130°	39.3	40.1	40.9	41.7	42.6	43.4	43.5	43.6	43.7	43.7	43.8
132.5°	36.1	36.9	37.8	38.6	39.4	40.2	40.3	40.4	40.5	40.6	40.7
135°	32.9	33.8	34.6	35.4	36.3	37.1	37.2	37.3	37.4	37.5	37.6
137.5°	29.9	30.7	31.5	32.4	33.2	34.0	34.1	34.2	34.3	34.4	34.5
140°	26.9	27.7	28.5	29.3	30.0	30.8	30.9	31.0	31.1	31.2	31.3
142.5°	24.0	24.8	25.5	26.2	27.0	27.7	27.8	27.9	28.0	28.1	28.2
145°	21.2	21.9	22.6	23.3	23.9	24.6	24.7	24.8	24.9	25.0	25.1
147.5°	18.5	19.2	19.8	20.5	21.1	21.7	21.8	21.9	22.0	22.1	22.2
150°	16.0	16.5	17.1	17.6	18.2	18.7	18.8	18.9	19.0	19.1	19.1
152.5°	13.4	13.8	14.3	14.8	15.3	15.8	15.9	16.0	16.1	16.2	16.3
155°	10.9	11.3	11.8	12.2	12.6	13.1	13.1	13.2	13.3	13.4	13.4
157.5°	8.7	9.1	9.4	9.8	10.1	10.4	10.5	10.6	10.6	10.7	10.7
160°	6.6	6.9	7.1	7.4	7.7	7.9	8.0	8.0	8.1	8.1	8.1
162.5°	4.7	4.9	5.1	5.3	5.5	5.6	5.7	5.7	5.7	5.8	5.8
165°	3.1	3.2	3.3	3.4	3.6	3.7	3.7	3.7	3.7	3.7	3.7
167.5°	1.7	1.8	1.9	2.0	2.0	2.1	2.1	2.0	2.0	2.0	2.0
170°	0.7	0.8	0.8	0.8	0.8	0.9	0.8	0.8	0.8	0.8	0.8
172.5°	0.3	0.3	0.3	0.3	0.3	0.3	0.3	0.2	0.2	0.2	0.2
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
0°	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3	59.3
2.5°	61.1	61.1	61.2	61.2	61.2	61.2	61.1	61.1	61.1	61.1	61.1
5°	64.3	64.4	64.4	64.5	64.4	64.4	64.3	64.3	64.2	64.2	64.1
7.5°	67.6	67.7	67.8	67.8	67.8	67.7	67.7	67.7	67.6	67.6	67.6
10°	71.3	71.4	71.5	71.6	71.5	71.4	71.4	71.3	71.2	71.2	71.1
12.5°	74.9	74.9	75.0	75.1	75.0	75.0	74.9	74.9	74.8	74.8	74.7
15°	78.3	78.4	78.4	78.5	78.5	78.4	78.4	78.3	78.2	78.2	78.1
17.5°	81.7	81.8	81.9	82.0	81.9	81.9	81.8	81.7	81.7	81.6	81.5
20°	85.0	85.1	85.1	85.2	85.1	85.1	85.0	84.9	84.9	84.8	84.7
22.5°	88.2	88.2	88.3	88.3	88.3	88.2	88.1	88.1	88.0	87.9	87.9
25°	91.0	91.0	91.1	91.2	91.1	91.1	91.0	91.0	90.9	90.9	90.9
27.5°	93.7	93.8	93.9	93.9	93.8	93.8	93.7	93.7	93.6	93.5	93.5
30°	96.4	96.4	96.5	96.6	96.5	96.4	96.4	96.3	96.2	96.2	96.1
32.5°	98.8	98.9	99.0	99.0	99.0	98.9	98.8	98.7	98.6	98.5	98.4
35°	101.0	101.0	101.1	101.2	101.1	101.0	100.9	100.8	100.7	100.6	100.5
37.5°	103.0	103.1	103.1	103.2	103.1	103.0	102.9	102.8	102.7	102.6	102.5
40°	104.7	104.7	104.8	104.8	104.7	104.6	104.5	104.4	104.3	104.2	104.1
42.5°	106.3	106.3	106.3	106.3	106.2	106.1	106.0	105.9	105.8	105.7	105.6
45°	107.5	107.5	107.5	107.5	107.4	107.2	107.1	107.0	106.9	106.7	106.6
47.5°	108.4	108.4	108.4	108.4	108.3	108.1	108.0	107.8	107.7	107.6	107.4
50°	109.0	109.0	109.0	109.0	108.9	108.7	108.6	108.5	108.3	108.2	108.0
52.5°	109.5	109.5	109.5	109.5	109.4	109.2	109.1	108.9	108.8	108.6	108.5
55°	109.7	109.7	109.7	109.7	109.5	109.4	109.2	109.0	108.9	108.7	108.6
57.5°	109.6	109.6	109.6	109.6	109.4	109.3	109.1	109.0	108.8	108.6	108.5
60°	109.3	109.3	109.3	109.3	109.1	109.0	108.8	108.6	108.5	108.3	108.2
62.5°	108.6	108.6	108.6	108.6	108.5	108.3	108.1	108.0	107.8	107.6	107.5
65°	107.7	107.7	107.6	107.6	107.5	107.4	107.2	107.1	106.9	106.8	106.7
67.5°	106.5	106.5	106.5	106.5	106.3	106.1	106.0	105.8	105.7	105.5	105.4
70°	105.1	105.1	105.1	105.1	104.9	104.8	104.6	104.5	104.4	104.2	104.1
72.5°	103.4	103.4	103.4	103.4	103.3	103.1	103.0	102.9	102.7	102.6	102.4
75°	101.6	101.6	101.6	101.6	101.4	101.3	101.1	101.0	100.9	100.7	100.6
77.5°	99.5	99.5	99.4	99.4	99.3	99.2	99.1	99.0	98.9	98.8	98.6
80°	97.4	97.4	97.4	97.4	97.2	97.1	97.0	96.9	96.8	96.7	96.6
82.5°	95.0	95.0	95.0	95.0	94.9	94.8	94.7	94.6	94.5	94.4	94.3
85°	92.9	92.9	92.9	92.9	92.8	92.7	92.6	92.5	92.4	92.3	92.2
87.5°	90.5	90.5	90.5	90.5	90.4	90.4	90.3	90.2	90.1	90.1	90.0
90°	88.4	88.4	88.4	88.4	88.3	88.2	88.1	88.0	88.0	87.9	87.8
92.5°	86.1	86.1	86.1	86.1	86.0	86.0	85.9	85.8	85.8	85.7	85.6
95°	83.8	83.8	83.8	83.8	83.8	83.7	83.6	83.5	83.4	83.4	83.3
97.5°	81.4	81.4	81.4	81.4	81.3	81.3	81.2	81.1	81.0	81.0	80.9
100°	79.0	79.0	79.0	79.0	78.9	78.8	78.8	78.7	78.6	78.5	78.5
102.5°	76.6	76.6	76.6	76.6	76.5	76.5	76.4	76.3	76.2	76.1	76.0
105°	73.7	73.8	73.8	73.8	73.8	73.7	73.7	73.6	73.6	73.5	73.5
107.5°	71.0	71.1	71.1	71.1	71.1	71.0	71.0	71.0	70.9	70.9	70.8
110°	68.3	68.3	68.3	68.4	68.3	68.3	68.2	68.2	68.2	68.1	68.1

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	330°	332.5°	335°	337.5°	340°	342.5°	345°	347.5°	350°	352.5°	355°
112.5°	65.5	65.5	65.5	65.5	65.5	65.5	65.4	65.4	65.4	65.3	65.3
115°	62.5	62.5	62.6	62.6	62.6	62.5	62.5	62.5	62.4	62.4	62.4
117.5°	59.6	59.7	59.7	59.8	59.7	59.7	59.6	59.6	59.5	59.5	59.4
120°	56.4	56.4	56.5	56.5	56.5	56.5	56.4	56.4	56.4	56.4	56.4
122.5°	53.4	53.4	53.5	53.6	53.5	53.5	53.5	53.5	53.4	53.4	53.4
125°	50.3	50.3	50.4	50.5	50.5	50.4	50.4	50.4	50.4	50.3	50.3
127.5°	47.0	47.1	47.2	47.3	47.3	47.2	47.2	47.2	47.2	47.1	47.1
130°	43.9	44.0	44.1	44.2	44.2	44.2	44.2	44.2	44.2	44.2	44.1
132.5°	40.8	40.9	41.0	41.1	41.1	41.1	41.1	41.1	41.1	41.1	41.1
135°	37.7	37.8	37.9	38.0	38.0	38.0	38.0	38.0	38.0	38.0	38.0
137.5°	34.6	34.7	34.8	34.9	34.9	34.9	34.9	34.9	34.8	34.8	34.8
140°	31.4	31.5	31.6	31.7	31.7	31.7	31.7	31.7	31.7	31.7	31.7
142.5°	28.2	28.3	28.4	28.5	28.5	28.5	28.5	28.5	28.5	28.5	28.5
145°	25.1	25.2	25.3	25.4	25.4	25.4	25.4	25.4	25.4	25.5	25.5
147.5°	22.2	22.3	22.4	22.5	22.5	22.5	22.4	22.4	22.4	22.4	22.4
150°	19.2	19.3	19.4	19.5	19.5	19.5	19.5	19.5	19.4	19.4	19.4
152.5°	16.3	16.4	16.5	16.6	16.6	16.6	16.5	16.5	16.5	16.5	16.5
155°	13.5	13.6	13.6	13.7	13.7	13.6	13.6	13.6	13.6	13.5	13.5
157.5°	10.8	10.8	10.9	11.0	10.9	10.9	10.8	10.8	10.7	10.7	10.7
160°	8.2	8.2	8.2	8.3	8.2	8.2	8.1	8.1	8.0	8.0	8.0
162.5°	5.8	5.8	5.9	5.9	5.8	5.8	5.7	5.7	5.6	5.6	5.5
165°	3.7	3.7	3.7	3.7	3.7	3.6	3.5	3.4	3.4	3.3	3.2
167.5°	1.9	1.9	1.9	1.8	1.8	1.7	1.7	1.7	1.6	1.6	1.5
170°	0.8	0.7	0.7	0.7	0.7	0.6	0.5	0.5	0.4	0.4	0.3
172.5°	0.2	0.2	0.2	0.2	0.2	0.2	0.2	0.1	0.1	0.1	0.1
175°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
177.5°	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1	0.1
180°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	357.5°	360°
0°	59.3	59.3
2.5°	61.0	61.0
5°	64.1	64.0
7.5°	67.6	67.5
10°	71.0	71.0
12.5°	74.6	74.6
15°	78.1	78.0
17.5°	81.5	81.4
20°	84.7	84.6
22.5°	87.8	87.8
25°	90.8	90.8
27.5°	93.4	93.3
30°	96.0	95.9
32.5°	98.4	98.3
35°	100.4	100.4
37.5°	102.4	102.3
40°	103.9	103.8
42.5°	105.4	105.3
45°	106.5	106.3
47.5°	107.3	107.1
50°	107.9	107.8
52.5°	108.3	108.2
55°	108.4	108.2
57.5°	108.3	108.2
60°	108.0	107.8
62.5°	107.3	107.1
65°	106.5	106.4
67.5°	105.2	105.1
70°	103.9	103.8
72.5°	102.3	102.1
75°	100.5	100.3
77.5°	98.5	98.4
80°	96.5	96.4
82.5°	94.3	94.2
85°	92.1	92.0
87.5°	89.9	89.8
90°	87.7	87.6
92.5°	85.6	85.5
95°	83.2	83.1
97.5°	80.8	80.7
100°	78.4	78.3
102.5°	76.0	75.9
105°	73.4	73.4
107.5°	70.8	70.8
110°	68.0	68.0

REPORT NUMBER: P600772
 CATALOG NUMBER: FE08A40FDB

CANDELA DISTRIBUTION (continued):

	357.5°	360°
112.5°	65.3	65.2
115°	62.3	62.3
117.5°	59.4	59.3
120°	56.3	56.3
122.5°	53.4	53.3
125°	50.3	50.2
127.5°	47.1	47.1
130°	44.1	44.1
132.5°	41.1	41.1
135°	38.0	38.0
137.5°	34.8	34.8
140°	31.7	31.7
142.5°	28.5	28.5
145°	25.5	25.5
147.5°	22.3	22.3
150°	19.4	19.4
152.5°	16.4	16.4
155°	13.5	13.5
157.5°	10.6	10.6
160°	7.9	7.9
162.5°	5.4	5.4
165°	3.2	3.1
167.5°	1.5	1.4
170°	0.3	0.2
172.5°	0.1	0.1
175°	0.1	0.1
177.5°	0.1	0.1
180°	0.0	0.0

(END OF REPORT)