

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P300513

Luminaire Tested: **ML4D09_27D2WE - TIR45FL40 - TL41RMW - TL42SMW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P300513
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1902-156-25)
Test Lab: INNOVATION CENTER(G1)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: HALO
Catalog Number: ML4D09_27D2WE - TIR45FL40 - TL41RMW - TL42SMW
Description: ML4 2700K, 900LM DIM-TO-WARM, 40 DEG FL OPTIC, WITH ROUND/SQUARE PINHOLE MATTE WHITE FLANGE
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 542.0 lumens
Efficiency: N/A
Efficacy: 48.4 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.56
Luminous Opening: Circular (Dia: 0.19' x H: 0')
CIE Type: Direct


Input Watts (W): 11.2
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P300513

CATALOG NUMBER: ML4D09_27D2WE - TIR45FL40 - TL41RMW - TL42SMW

Luminous Intensity Polar Plot





TEST NUMBER: P300513

CATALOG NUMBER: ML4D09_27D2WE - TIR45FL40 - TL41RMW - TL42SMW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	112	110	108	112	110	108	107	106	105	103		103	101	100		99	98	97	96
2	110	106	103	100	108	105	102	99	102	99	97		99	97	95		96	94	93	92
3	106	101	97	94	104	100	96	93	97	94	92		95	93	90		93	91	89	88
4	102	96	92	89	101	95	91	88	93	90	87		92	89	86		90	87	85	84
5	99	92	88	84	97	91	87	84	90	86	83		88	85	83		87	84	82	81
6	95	88	84	80	94	88	83	80	86	82	80		85	82	79		84	81	79	77
7	92	85	80	77	91	84	80	77	83	79	76		82	79	76		81	78	76	74
8	89	82	77	74	88	81	77	74	80	76	73		79	76	73		78	75	73	72
9	86	79	74	71	85	78	74	71	77	73	71		77	73	70		76	73	70	69
10	83	76	71	68	83	76	71	68	75	71	68		74	71	68		73	70	68	67

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	579174
5°	555129
10°	484278
15°	367262
20°	234225
25°	111103
30°	42808
35°	18560
40°	10178
45°	6064
50°	3639
55°	2039
60°	1559
65°	922
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P300513

CATALOG NUMBER: ML4D09_27D2WE - TIR45FL40 - TL41RMW - TL42SMW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	23.8
10°-20°	246.5	45.5
20°-30°	125.5	23.2
30°-40°	28.0	5.2
40°-50°	9.0	1.7
50°-60°	3.1	0.6
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	501.2	92.5
0°-40°	529.2	97.6
0°-60°	541.2	99.9
0°-90°	542.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	542.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1486	
5°	1419	129
15°	910	247
25°	258	125
35°	39	28
45°	11	9
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P300513

CATALOG NUMBER: ML4D09_27D2WE - TIR45FL40 - TL41RMW - TL42SMW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1485.7
1°	1482.7
2°	1473.7
3°	1458.7
4°	1440.6
5°	1418.6
6°	1389.6
7°	1356.5
8°	1316.5
9°	1273.5
10°	1223.4
11°	1166.3
12°	1106.3
13°	1045.2
14°	979.1
15°	910.0
16°	841.0
17°	772.9
18°	704.8
19°	635.7
20°	564.6
21°	497.6
22°	431.5
23°	369.4
24°	310.4
25°	258.3
27.5°	157.2
30°	95.1
32.5°	60.1
35°	39.0
37.5°	27.0
40°	20.0
42.5°	15.0
45°	11.0
47.5°	8.0
50°	6.0
52.5°	5.0
55°	3.0
57.5°	2.0
60°	2.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P300513

CATALOG NUMBER: ML4D09_27D2WE - TIR45FL40 - TL41RMW - TL42SMW

CANDELA DISTRIBUTION (continued):

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)