

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P300498

Luminaire Tested: **ML4D09\_27D2WE - TIR45NFL25 - TL41RMW - TL42SMW**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P300498  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1902-156-8)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO  
Catalog Number: ML4D09\_27D2WE - TIR45NFL25 - TL41RMW - TL42SMW  
Description: ML4 2700K, 900LM DIM-TO-WARM, 25 DEG NFL OPTIC, WITH ROUND/SQUARE PINHOLE MATTE WHITE FLANGE  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 524.0 lumens  
Efficiency: N/A  
Efficacy: 46.8 lumens/watt  
Spacing Criteria (0/90/45): 0.46 / 0.46 / 0.44  
Luminous Opening: Circular (Dia: 0.19' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P300498

CATALOG NUMBER: ML4D09\_27D2WE - TIR45NFL25 - TL41RMW - TL42SMW

### Luminous Intensity Polar Plot





TEST NUMBER: P300498

CATALOG NUMBER: ML4D09\_27D2WE - TIR45NFL25 - TL41RMW - TL42SMW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	115	113	111	109	113	111	109	107	107	105	104		103	102	101		100	99	98	96
2	111	107	104	102	109	106	103	101	103	100	99		100	98	96		97	96	95	93
3	107	103	99	96	106	101	98	95	99	96	94		97	94	92		95	93	91	90
4	104	99	95	91	102	98	94	91	96	92	90		94	91	89		92	90	88	87
5	101	95	91	88	99	94	90	87	92	89	86		91	88	86		89	87	85	84
6	98	91	87	84	97	91	87	84	89	86	83		88	85	83		87	84	82	81
7	95	88	84	81	94	88	84	81	87	83	81		86	82	80		85	82	80	79
8	92	86	81	78	91	85	81	78	84	81	78		83	80	78		82	80	77	76
9	90	83	79	76	89	82	79	76	82	78	76		81	78	75		80	77	75	74
10	87	80	76	74	87	80	76	74	79	76	73		79	76	73		78	75	73	72

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	820051
5°	770747
10°	592067
15°	353055
20°	165899
25°	70972
30°	31510
35°	15229
40°	8142
45°	4410
50°	1819
55°	1359
60°	780
65°	0
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P300498

CATALOG NUMBER: ML4D09\_27D2WE - TIR45NFL25 - TL41RMW - TL42SMW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	172.6	32.9
10°-20°	237.8	45.4
20°-30°	83.4	15.9
30°-40°	22.0	4.2
40°-50°	6.4	1.2
50°-60°	1.6	0.3
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	493.8	94.2
0°-40°	515.7	98.4
0°-60°	523.6	99.9
0°-90°	524.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	524.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2104	
5°	1970	173
15°	875	238
25°	165	83
35°	32	22
45°	8	6
55°	2	2
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P300498

CATALOG NUMBER: ML4D09\_27D2WE - TIR45NFL25 - TL41RMW - TL42SMW

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2103.6
1°	2100.6
2°	2091.6
3°	2067.6
4°	2027.6
5°	1969.6
6°	1896.7
7°	1814.7
8°	1718.7
9°	1610.7
10°	1495.7
11°	1374.8
12°	1247.8
13°	1122.8
14°	995.8
15°	874.8
16°	756.9
17°	648.9
18°	554.9
19°	471.9
20°	399.9
21°	335.9
22°	282.9
23°	239.0
24°	199.0
25°	165.0
27.5°	106.0
30°	70.0
32.5°	47.0
35°	32.0
37.5°	22.0
40°	16.0
42.5°	11.0
45°	8.0
47.5°	5.0
50°	3.0
52.5°	2.0
55°	2.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0



TEST NUMBER: P300498

CATALOG NUMBER: ML4D09\_27D2WE - TIR45NFL25 - TL41RMW - TL42SMW

**CANDELA DISTRIBUTION (continued):**

	0°
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)