

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: HALO

Report Number: P300488

Luminaire Tested: **ML4D09\_27D2WE - TIR45SP15 - TL41RBCU - TL42SBCU**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-41-14  
Report Number: P300488  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-1902-156-68)  
Test Lab: INNOVATION CENTER(G1)  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: HALO  
Catalog Number: ML4D09\_27D2WE - TIR45SP15 - TL41RBCU - TL42SBCU  
Description: ML4 2700K, 900LM DIM-TO-WARM, 15 DEG SP OPTIC, WITH ROUND/SQUARE PINHOLE BRUSHED COPPER FLANGE  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 487.0 lumens  
Efficiency: N/A  
Efficacy: 43.5 lumens/watt  
Spacing Criteria (0/90/45): 0.32 / 0.32 / 0.32  
Luminous Opening: Circular (Dia: 0.19' x H: 0')  
CIE Type: Direct


Input Watts (W): 11.2  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P300488

CATALOG NUMBER: ML4D09\_27D2WE - TIR45SP15 - TL41RBCU - TL42SBCU

### Luminous Intensity Polar Plot





TEST NUMBER: P300488

CATALOG NUMBER: ML4D09\_27D2WE - TIR45SP15 - TL41RBCU - TL42SBCU

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97
2	112	109	106	103	110	107	104	102	104	102	100	101	99	98	98	97	96	95
3	109	104	101	98	107	103	100	98	101	98	96	98	96	95	96	95	93	92
4	106	101	97	94	104	100	96	94	98	95	93	96	94	92	94	92	91	90
5	103	98	94	91	102	97	93	91	95	92	90	94	91	89	92	90	89	87
6	100	95	91	88	99	94	91	88	93	90	87	92	89	87	91	88	86	85
7	98	92	88	86	97	92	88	86	91	87	85	90	87	85	89	86	84	83
8	96	90	86	84	95	89	86	83	89	85	83	88	85	83	87	84	83	82
9	94	88	84	82	93	87	84	81	87	83	81	86	83	81	85	83	81	80
10	92	86	82	80	91	85	82	80	85	82	79	84	81	79	84	81	79	78

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1319816
5°	1139332
10°	591117
15°	248245
20°	106617
25°	47315
30°	20256
35°	10470
40°	5598
45°	2757
50°	1819
55°	680
60°	780
65°	922
70°	0
75°	0
80°	0
85°	0



TEST NUMBER: P300488

CATALOG NUMBER: ML4D09\_27D2WE - TIR45SP15 - TL41RBCU - TL42SBCU

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	228.3	46.9
10°-20°	182.5	37.5
20°-30°	55.2	11.3
30°-40°	14.7	3.0
40°-50°	4.4	0.9
50°-60°	1.3	0.3
60°-70°	0.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	466.0	95.7
0°-40°	480.7	98.7
0°-60°	486.4	99.9
0°-90°	487.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	487.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3386	
5°	2912	228
15°	615	182
25°	110	55
35°	22	15
45°	5	4
55°	1	1
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P300488

CATALOG NUMBER: ML4D09\_27D2WE - TIR45SP15 - TL41RBCU - TL42SBCU

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3385.6
1°	3377.6
2°	3342.6
3°	3262.6
4°	3120.6
5°	2911.5
6°	2649.5
7°	2356.4
8°	2055.4
9°	1766.3
10°	1493.3
11°	1259.2
12°	1053.2
13°	885.2
14°	735.1
15°	615.1
17.5°	394.1
20°	257.0
22.5°	169.0
25°	110.0
27.5°	71.0
30°	45.0
32.5°	30.0
35°	22.0
37.5°	16.0
40°	11.0
42.5°	7.0
45°	5.0
47.5°	4.0
50°	3.0
52.5°	2.0
55°	1.0
57.5°	1.0
60°	1.0
62.5°	1.0
65°	1.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0



TEST NUMBER: P300488

CATALOG NUMBER: ML4D09\_27D2WE - TIR45SP15 - TL41RBCU - TL42SBCU

CANDELA DISTRIBUTION (continued):

90° |  $\frac{0^\circ}{0.0}$

(END OF REPORT)