

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601343

Luminaire Tested: **ML4DM06FL9FS1E - TIR4D40FL - TL41R_ TL42S_ 4000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601343
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM06FL9FS1E - TIR4D40FL - TL41R_ TL42S_ 4000K
 Description: DIRECT MOUNT, 40D OPTIC, OPEN TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 4000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 882.2 lumens
 Efficiency: N/A
 Efficacy: 106.3 lumens/watt
 Spacing Criteria (0/90/45): 0.67 / 0.67 / 0.63
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 8.3
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601343
CATALOG NUMBER: ML4DM06FL9FS1E - TIR4D40FL - TL41R_ TL42S_ 4000K

Luminous Intensity Polar Plot



TEST NUMBER: P601343
 CATALOG NUMBER: ML4DM06FL9FS1E - TIR4D40FL - TL41R_ TL42S_ 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	114	112	110	108	112	110	108	106	106	104	103		102	101	100		99	98	97	95
2	110	106	102	99	108	104	101	98	101	98	96		98	96	94		95	93	92	90
3	105	100	96	92	103	98	95	91	96	93	90		94	91	89		91	89	87	86
4	101	95	90	86	99	94	89	86	92	88	85		90	87	84		88	85	83	82
5	97	90	85	81	96	89	85	81	87	83	80		86	82	80		84	81	79	78
6	93	86	81	77	92	85	80	77	84	79	76		82	79	76		81	78	75	74
7	90	82	77	73	89	81	77	73	80	76	73		79	75	72		78	75	72	71
8	86	78	73	70	85	78	73	70	77	73	69		76	72	69		75	72	69	68
9	83	75	70	67	82	75	70	67	74	69	66		73	69	66		72	69	66	65
10	80	72	67	64	79	72	67	64	71	67	64		70	66	63		70	66	63	62

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	584766
5°	566872
10°	518822
15°	441517
20°	320203
25°	182392
30°	86778
35°	45255
40°	22671
45°	10851
50°	6239
55°	2918
60°	695
65°	822
70°	0
75°	0
80°	0
85°	0

TEST NUMBER: P601343
 CATALOG NUMBER: ML4DM06FL9FS1E - TIR4D40FL - TL41R_ TL42S_ 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	165.6	18.8
10°-20°	366.5	41.5
20°-30°	244.5	27.7
30°-40°	78.3	8.9
40°-50°	21.3	2.4
50°-60°	5.3	0.6
60°-70°	0.7	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	776.6	88.0
0°-40°	854.9	96.9
0°-60°	881.5	99.9
0°-90°	882.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	882.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1852	
5°	1788	166
15°	1351	367
25°	524	245
35°	117	78
45°	24	21
55°	5	5
65°	1	1
75°	0	0
85°	0	0
90°	0	

TEST NUMBER: P601343
CATALOG NUMBER: ML4DM06FL9FS1E - TIR4D40FL - TL41R_ TL42S_ 4000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1851.9
1°	1850.8
2°	1855.0
3°	1830.7
4°	1815.9
5°	1788.4
6°	1766.2
7°	1732.4
8°	1704.9
9°	1660.4
10°	1618.1
11°	1580.1
12°	1524.0
13°	1472.2
14°	1414.0
15°	1350.6
17.5°	1169.7
20°	952.9
22.5°	723.4
25°	523.5
27.5°	355.4
30°	238.0
32.5°	165.0
35°	117.4
37.5°	83.6
40°	55.0
42.5°	36.0
45°	24.3
47.5°	18.0
50°	12.7
52.5°	8.5
55°	5.3
57.5°	3.2
60°	1.1
62.5°	1.1
65°	1.1
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269


NVLAP Lab Code: 200050-0



TEST NUMBER: P601343
CATALOG NUMBER: ML4DM06FL9FS1E - TIR4D40FL - TL41R_ TL42S_ 4000K

CANDELA DISTRIBUTION (continued):



(END OF REPORT)