

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P885748

Luminaire Tested: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMW-340LM-2700K

Issue Date: 6/19/2024

Test Information

Test Method: LM-79-2019
Report Number: P885748
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-130)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMW-340LM-2700K
Description: 1IN ROUND ML FLEX, SELECTABLE CCT, WITH 55D TIR, MATTE WHITE TRIM
Light Source: (1) HCL SELECTABLE LUMEN LED 95CRI / 2700K CCT
Ballast/Driver: -

Summary


Lumens per Lamp: N/A
Luminaire Lumens: 351.7 lumens
Efficiency: N/A
Efficacy: 57.7 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.77
Luminous Opening: Circular (Dia: 0.08' x H: 0')
CIE Type: Direct

Input Watts (W): 6.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P885748
CATALOG NUMBER: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMW-340LM-2700K

Luminous Intensity Polar Plot





TEST NUMBER: P885748

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMW-340LM-2700K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	102	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81																			
4	98	90	85	80	96	89	84	80	87	82	79	85	81	78	83	80	77	76																			
5	93	85	79	75	91	84	78	74	82	77	74	80	76	73	79	75	72	71																			
6	88	80	74	70	87	79	74	70	78	73	69	76	72	69	75	71	68	67																			
7	84	75	70	65	83	75	69	65	73	69	65	72	68	65	71	67	64	63																			
8	81	71	66	62	79	71	65	61	70	65	61	69	64	61	68	64	61	59																			
9	77	68	62	58	76	67	62	58	66	61	58	65	61	58	65	60	57	56																			
10	74	64	59	55	73	64	59	55	63	58	55	62	58	55	62	58	55	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	967036
5°	952900
10°	902596
15°	809705
20°	696216
25°	560940
30°	344790
35°	186717
40°	99702
45°	50238
50°	30396
55°	24774
60°	21314
65°	25217
70°	25966
75°	27451
80°	20457
85°	20379

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 50238 cd/sqm



TEST NUMBER: P885748

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMW-340LM-2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	44.9	12.8
10°-20°	109.9	31.3
20°-30°	113.9	32.4
30°-40°	51.5	14.6
40°-50°	15.6	4.4
50°-60°	6.5	1.9
60°-70°	5.0	1.4
70°-80°	3.4	1.0
80°-90°	1.0	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	268.7	76.4
0°-40°	320.2	91.0
0°-60°	342.2	97.3
0°-90°	351.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	351.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	490	
5°	481	45
15°	396	110
25°	258	114
35°	78	51
45°	18	16
55°	7	7
65°	5	5
75°	4	3
85°	1	1
90°	0	



TEST NUMBER: P885748

CATALOG NUMBER: ML104LSFL95FS1E-TIR1D55WFL-TL1RDMW-340LM-2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	490.0
2.5°	489.1
5°	481.0
7.5°	467.5
10°	450.4
12.5°	425.2
15°	396.3
17.5°	363.0
20°	331.5
22.5°	300.0
25°	257.6
27.5°	206.3
30°	151.3
32.5°	108.1
35°	77.5
37.5°	55.8
40°	38.7
42.5°	27.0
45°	18.0
47.5°	12.6
50°	9.9
52.5°	8.1
55°	7.2
57.5°	6.3
60°	5.4
62.5°	5.4
65°	5.4
67.5°	4.5
70°	4.5
72.5°	3.6
75°	3.6
77.5°	2.7
80°	1.8
82.5°	1.8
85°	0.9
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)