

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P677532

Luminaire Tested: ML4DM06FL9FS1E-TL40R2GMW-3000K

Issue Date: 4/25/2023

**Test Information**

Test Method: LM-79-2019  
Report Number: P677532  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-2304-979-1)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 4/25/2023  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: HALO  
Catalog Number: ML4DM06FL9FS1E-TL40R2GMW-3000K  
Description: DIRECT MOUNT, CONICAL LENS TRIM  
Light Source: (1) SELECTABLE LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 432.0 lumens  
Efficiency: N/A  
Efficacy: 52.1 lumens/watt  
Spacing Criteria (0/90/45): 1.15 / 1.15 / 1.23  
Luminous Opening: Circular (Dia: 0.33' x H: 0')  
CIE Type: Direct

Input Watts (W): 8.3  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT



TEST NUMBER: P677532  
CATALOG NUMBER: ML4DM06FL9FS1E-TL40R2GMW-3000K

### Luminous Intensity Polar Plot





TEST NUMBER: P677532

CATALOG NUMBER: ML4DM06FL9FS1E-TL40R2GMW-3000K

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	111	107	103	100	108	105	102	99	101	98	96	97	95	93	93	92	90	88																			
2	103	96	90	85	100	94	89	84	90	86	82	87	84	80	84	81	79	77																			
3	95	86	79	73	92	84	78	73	81	76	71	79	74	70	76	72	69	67																			
4	88	77	70	64	86	76	69	63	74	67	62	71	66	62	69	65	61	59																			
5	81	70	62	56	79	69	61	56	67	60	55	65	59	55	63	58	54	52																			
6	76	64	56	50	74	63	55	50	61	54	49	59	53	49	58	53	48	47																			
7	70	58	50	45	69	57	50	45	56	49	44	55	48	44	53	48	44	42																			
8	66	53	46	40	64	53	45	40	52	45	40	50	44	40	49	44	40	38																			
9	62	49	42	37	60	49	42	37	48	41	36	47	41	36	46	40	36	34																			
10	58	46	38	34	57	45	38	33	44	38	33	43	37	33	43	37	33	31																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	26840
5°	26695
10°	26377
15°	26114
20°	25399
25°	24565
30°	23700
35°	22496
40°	20980
45°	18892
50°	16157
55°	13161
60°	9892
65°	7326
70°	5410
75°	5242
80°	4262
85°	4246

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 18892 cd/sqm



TEST NUMBER: P677532

CATALOG NUMBER: ML4DM06FL9FS1E-TL40R2GMW-3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	20.4	4.7
10°-20°	57.4	13.3
20°-30°	83.2	19.3
30°-40°	93.2	21.6
40°-50°	83.2	19.3
50°-60°	54.7	12.7
60°-70°	25.6	5.9
70°-80°	11.2	2.6
80°-90°	3.0	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	161.1	37.3
0°-40°	254.4	58.9
0°-60°	392.2	90.8
0°-90°	432.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	432.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	218	
5°	216	20
15°	204	57
25°	180	83
35°	149	93
45°	108	83
55°	61	55
65°	25	26
75°	11	11
85°	3	3
90°	0	



TEST NUMBER: P677532

CATALOG NUMBER: ML4DM06FL9FS1E-TL40R2GMW-3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	217.6
2.5°	215.6
5°	215.6
7.5°	214.6
10°	210.6
12.5°	207.6
15°	204.5
17.5°	199.5
20°	193.5
22.5°	187.5
25°	180.5
27.5°	174.5
30°	166.4
32.5°	158.4
35°	149.4
37.5°	140.4
40°	130.3
42.5°	120.3
45°	108.3
47.5°	96.3
50°	84.2
52.5°	72.2
55°	61.2
57.5°	50.1
60°	40.1
62.5°	32.1
65°	25.1
67.5°	19.1
70°	15.0
72.5°	13.0
75°	11.0
77.5°	8.0
80°	6.0
82.5°	4.0
85°	3.0
87.5°	1.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)