

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P885889

Luminaire Tested: ML104LSFL9FS1E-TIR1D40FL-TL1RDSL-400LM-3000K

Issue Date: 6/19/2024


Test Information

Test Method: LM-79-2019
Report Number: P885889
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-125)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML104LSFL9FS1E-TIR1D40FL-TL1RDSL-400LM-3000K
Description: 1IN ROUND ML FLEX, SELECTABLE CCT, WITH 40D TIR, METALLIC SILVER TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 442.5 lumens
Efficiency: N/A
Efficacy: 73.7 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.66
Luminous Opening: Circular (Dia: 0.08' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P885889

CATALOG NUMBER: ML104LSFL9FS1E-TIR1D40FL-TL1RDSL-400LM-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P885889

CATALOG NUMBER: ML104LSFL9FS1E-TIR1D40FL-TL1RDSL-400LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20																	
RC	80									70									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																								
RCR																																																						
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																																				
1	114	111	109	107	112	109	107	105	105	104	102	102	100	99	98	97	96	95																																				
2	109	105	101	98	107	103	100	97	100	97	95	97	95	93	94	92	91	89																																				
3	104	99	94	91	102	97	93	90	95	91	88	92	89	87	90	88	86	84																																				
4	100	93	88	84	98	92	87	84	90	86	83	88	85	82	86	83	81	80																																				
5	96	88	83	79	94	87	83	79	86	81	78	84	80	78	83	79	77	76																																				
6	92	84	78	75	90	83	78	74	82	77	74	80	76	73	79	76	73	72																																				
7	88	80	74	71	87	79	74	70	78	73	70	77	73	70	76	72	69	68																																				
8	84	76	71	67	83	75	70	67	74	70	67	73	69	66	73	69	66	65																																				
9	81	73	67	64	80	72	67	64	71	67	64	70	66	63	70	66	63	62																																				
10	78	69	64	61	77	69	64	61	68	64	61	68	63	61	67	63	60	59																																				

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1679681
5°	1642910
10°	1497579
15°	1229983
20°	902456
25°	616903
30°	345246
35°	179971
40°	101505
45°	43540
50°	25483
55°	17892
60°	12236
65°	9807
70°	5770
75°	7625
80°	11365
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 43540 cd/sqm



TEST NUMBER: P885889

CATALOG NUMBER: ML104LSFL9FS1E-TIR1D40FL-TL1RDSL-400LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.5	17.3
10°-20°	164.6	37.2
20°-30°	128.2	29.0
30°-40°	50.8	11.5
40°-50°	14.4	3.2
50°-60°	4.7	1.1
60°-70°	2.1	0.5
70°-80°	1.1	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	369.3	83.5
0°-40°	420.1	94.9
0°-60°	439.2	99.3
0°-90°	442.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	442.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	851	
5°	829	76
15°	602	165
25°	283	128
35°	75	51
45°	16	14
55°	5	5
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P885889

CATALOG NUMBER: ML104LSFL9FS1E-TIR1D40FL-TL1RDSL-400LM-3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	851.1
2.5°	849.0
5°	829.3
7.5°	794.0
10°	747.3
12.5°	682.9
15°	602.0
17.5°	514.8
20°	429.7
22.5°	351.8
25°	283.3
27.5°	214.8
30°	151.5
32.5°	105.9
35°	74.7
37.5°	56.0
40°	39.4
42.5°	24.9
45°	15.6
47.5°	11.4
50°	8.3
52.5°	6.2
55°	5.2
57.5°	4.2
60°	3.1
62.5°	2.1
65°	2.1
67.5°	2.1
70°	1.0
72.5°	1.0
75°	1.0
77.5°	1.0
80°	1.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)