

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601322

Luminaire Tested: **ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 4000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601322
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 4000K
 Description: DIRECT MOUNT, 25D WW OPTIC, OPEN TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 4000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 525.0 lumens
 Efficiency: N/A
 Efficacy: 63.3 lumens/watt
 Spacing Criteria (0/90/45): 1.31 / 0.61 / 0.81
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 8.3
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601322
CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 4000K

Luminous Intensity Polar Plot



TEST NUMBER: P601322

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 4000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	102	102	102	100
1	113	110	107	105	111	108	106	103	104	102	100	100	99	97	97	96	94	94	94	94	93
2	107	102	97	94	105	100	96	93	97	93	91	94	91	89	91	89	87	87	87	87	85
3	101	94	89	84	99	93	88	84	90	86	82	87	84	81	85	82	80	80	80	80	78
4	95	87	81	77	93	86	80	76	84	79	75	82	78	74	80	76	73	73	73	73	72
5	90	81	75	70	88	80	74	70	78	73	69	76	72	68	75	71	68	68	68	68	66
6	85	75	69	64	83	75	68	64	73	68	64	72	67	63	70	66	63	63	63	63	61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	58	58	58	57
8	76	66	60	55	75	65	59	55	64	59	55	63	58	55	62	58	54	54	54	54	53
9	72	62	56	51	71	61	55	51	60	55	51	60	54	51	59	54	51	51	51	51	49
10	69	58	52	48	68	58	52	48	57	52	48	56	51	48	55	51	48	48	48	48	46

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	165745	165745	165745
5°	214114	160673	123302
10°	275651	136848	81666
15°	331938	108859	60216
20°	374775	83873	43650
25°	394851	62052	32681
30°	363958	44228	26362
35°	285948	29836	22897
40°	212490	18096	20239
45°	137183	12280	18041
50°	80318	8892	16064
55°	42610	6166	14203
60°	17935	3284	12504
65°	6426	2540	9638
70°	831	1570	5539
75°	1098	1098	0
80°	0	0	0
85°	0	0	0

TEST NUMBER: P601322
 CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	9.2
10°-20°	125.3	23.9
20°-30°	153.1	29.2
30°-40°	114.6	21.8
40°-50°	56.8	10.8
50°-60°	20.9	4.0
60°-70°	5.2	1.0
70°-80°	0.7	0.1
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	326.8	62.2
0°-40°	441.4	84.1
0°-60°	519.1	98.9
0°-90°	525.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	525.0	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	525	525	525	525	525	
5°	676	608	507	416	389	71
15°	1015	638	333	202	184	289
25°	1133	455	178	90	94	508
35°	742	219	77	41	59	468
45°	307	71	28	23	40	245
55°	77	20	11	10	26	74
65°	9	3	3	3	13	10
75°	1	1	1	0	0	1
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P601322

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 4000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	524.9	524.9	524.9	524.9	524.9	524.9	524.9	524.9	524.9	524.9	524.9
2.5°	591.2	591.2	598.1	586.9	586.9	583.4	558.5	543.9	527.5	503.4	475.0
5°	675.5	692.7	679.0	660.0	671.2	666.1	607.5	554.2	506.9	460.4	415.6
7.5°	783.9	788.2	776.2	752.1	746.9	743.5	642.8	555.0	472.4	402.7	351.1
10°	859.7	865.7	860.5	851.9	822.7	815.8	654.0	522.3	426.8	352.8	290.9
12.5°	956.9	955.2	947.4	922.5	888.9	879.5	647.1	493.1	378.6	296.9	238.4
15°	1015.4	1025.8	1014.6	948.3	932.8	908.7	638.5	453.5	333.0	257.3	202.2
17.5°	1066.2	1061.9	1040.4	998.2	958.6	937.1	605.0	395.8	292.6	214.3	166.9
20°	1115.3	1116.1	1082.6	1030.9	967.2	928.5	555.0	356.3	249.6	176.4	138.5
22.5°	1137.6	1135.9	1092.9	1016.3	942.3	902.7	507.7	311.5	209.1	142.8	111.0
25°	1133.3	1102.3	1073.9	983.6	900.1	851.9	455.2	272.8	178.1	120.5	89.5
27.5°	1078.2	1062.8	1014.6	924.2	827.8	778.8	389.8	233.2	148.9	94.7	73.1
30°	998.2	980.1	922.5	847.6	721.1	682.4	332.2	191.0	121.3	80.9	60.2
32.5°	879.5	865.7	806.3	708.2	609.3	565.4	275.4	152.3	98.1	59.4	49.1
35°	741.8	740.9	688.4	608.4	505.1	460.4	218.6	122.2	77.4	47.3	41.3
37.5°	636.8	614.4	562.8	488.8	401.9	364.9	171.2	95.5	57.7	37.0	34.4
40°	515.5	506.0	451.8	389.0	312.4	284.8	126.5	71.4	43.9	30.1	31.0
42.5°	414.8	401.9	357.1	296.0	241.8	219.4	96.4	55.1	34.4	25.8	27.5
45°	307.2	301.2	275.4	220.3	179.0	163.5	71.4	43.0	27.5	21.5	23.2
47.5°	223.7	216.9	198.8	163.5	129.9	120.5	55.1	33.6	22.4	17.2	18.1
50°	163.5	159.2	147.2	118.8	95.5	87.8	41.3	25.8	18.1	13.8	15.5
52.5°	112.7	114.5	104.1	84.3	68.0	62.8	31.0	18.9	14.6	11.2	12.9
55°	77.4	75.7	71.4	55.1	43.9	40.4	19.8	12.9	11.2	8.6	9.5
57.5°	47.3	47.3	43.9	34.4	27.5	25.8	12.0	8.6	7.7	6.0	7.7
60°	28.4	28.4	24.1	19.8	16.4	14.6	6.9	5.2	5.2	4.3	6.0
62.5°	15.5	15.5	13.8	11.2	8.6	7.7	4.3	4.3	3.4	3.4	5.2
65°	8.6	7.7	6.9	5.2	4.3	4.3	2.6	3.4	3.4	3.4	3.4
67.5°	3.4	3.4	3.4	2.6	2.6	2.6	1.7	2.6	2.6	2.6	2.6
70°	0.9	1.7	1.7	1.7	0.9	0.9	1.7	1.7	1.7	1.7	1.7
72.5°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9
75°	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.9	0.0
77.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.9	0.9	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601322
 CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL41R_ TL42S_ 4000K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	524.9	524.9
2.5°	475.9	468.1
5°	398.4	389.0
7.5°	316.7	310.7
10°	259.0	254.7
12.5°	218.6	216.0
15°	185.0	184.2
17.5°	155.8	153.2
20°	127.4	129.9
22.5°	105.0	103.3
25°	88.6	93.8
27.5°	75.7	82.6
30°	66.3	72.3
32.5°	56.8	66.3
35°	49.9	59.4
37.5°	44.7	53.4
40°	41.3	49.1
42.5°	36.1	45.6
45°	31.8	40.4
47.5°	27.5	36.1
50°	25.0	32.7
52.5°	21.5	29.3
55°	18.1	25.8
57.5°	16.4	23.2
60°	13.8	19.8
62.5°	10.3	16.4
65°	7.7	12.9
67.5°	5.2	9.5
70°	2.6	6.0
72.5°	0.9	1.7
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)