

LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for
Cooper Lighting Solutions
(formerly Eaton)

Brand: HALO

Report Number: P601328

Luminaire Tested: **ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 5000K**

Issue Date: 7/29/2022

Tested By:

Approved By:



Cooper Lighting Solutions laboratories have been accredited by National Voluntary Laboratory Accreditation Program (NVLAP) that it adheres to the requirements of ISO/IEC 17025:2005 and appropriate IESNA test methods. This report must not be used to claim product certification, approval or endorsement by NVLAP, NIST or any agency of the Federal Government. Results contained in this report are valid for luminaire sample tested, as supplied by requestor. Information related to the luminaire tested has been supplied by requestor and can affect the validity of the test results. Report shall not be reproduced except in full without approval of Cooper Lighting Solutions Lighting Laboratory. Test performed at address noted above.

Test Information

Test Method: LM-79-08
 Report Number: P601328
 Test Lab: COOPER LIGHTING SOLUTIONS
 Issue Date: 7/29/2022
 Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
 Product Line: HALO
 Catalog Number: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 5000K
 Description: DIRECT MOUNT, 25D WW OPTIC, DIFFUSE CLEAR LENS TRIM
 Light Source: (1) SELECTABLE LUMEN LED 90CRI / 5000K CCT
 Ballast/Driver: -

Summary

Lumens per Lamp: N/A
 Luminaire Lumens: 639.2 lumens
 Efficiency: N/A
 Efficacy: 77.0 lumens/watt
 Spacing Criteria (0/90/45): 1.33 / 0.62 / 0.83
 Luminous Opening: Circular (Dia: 0.21' x H: 0')
 CIE Type: Direct


Input Watts (W): 8.3
 Input Voltage (V): NR
 Input Current (Ain): NR
 Voltage Rise (V): NR
 Power Factor: NR
 Total Harmonic Distortion (THDi): NR
 Frequency (hertz): 60
 Stabilization Time: NR
 Operation Time: NR
 Ambient Temperature (°C): NR
 Test Distance: 25 FT



Meas		Calibration Due Date	
Instrument	Identificatio		
Photometer	GONIO 1 11111111	4/22/2021	10/22/2021
Power Meter	XITRON 2801 IN0197	12/1/2020	12/1/2021
AC Power Source	CHROMA 61505 IN0196	12/1/2020	12/1/2021
DC Power Supply	AGILENT E3634A IN0198	11/30/2020	11/30/2021
Room Thermometer	ONSET IN0143	12/1/2020	12/1/2021

TEST NUMBER: P601328
CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 5000K

Luminous Intensity Polar Plot



TEST NUMBER: P601328

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 5000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	113	110	107	105	110	108	105	103	104	102	100	100	98	97	97	95	94	92
2	107	101	97	93	104	100	96	92	96	93	90	93	91	88	91	88	86	85
3	101	94	88	84	99	92	87	83	89	85	82	87	83	80	85	82	79	78
4	95	87	81	76	93	85	80	75	83	78	75	81	77	74	79	76	73	71
5	89	80	74	69	88	79	73	69	78	72	68	76	71	68	74	70	67	65
6	84	75	68	64	83	74	68	63	72	67	63	71	66	62	70	65	62	60
7	80	70	63	59	78	69	63	58	68	62	58	66	62	58	65	61	57	56
8	76	65	59	54	74	65	59	54	64	58	54	62	57	54	61	57	53	52
9	72	61	55	51	70	61	55	50	60	54	50	59	54	50	58	53	50	48
10	68	58	51	47	67	57	51	47	56	51	47	55	50	47	55	50	47	45

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°
0°	194764	194764	194764
5°	251929	188154	145395
10°	327145	166571	100295
15°	389539	131906	71559
20°	450180	100305	48288
25°	459446	75500	39684
30°	429661	54802	31029
35°	352404	37083	27716
40°	262903	24155	24155
45°	177195	16299	21212
50°	103701	11937	18471
55°	54777	8533	14589
60°	26524	4863	11178
65°	10759	3288	7397
70°	5078	2031	4062
75°	2684	1342	0
80°	2000	2000	0
85°	0	0	0

TEST NUMBER: P601328

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	57.3	9.0
10°-20°	148.2	23.2
20°-30°	181.6	28.4
30°-40°	142.3	22.3
40°-50°	73.3	11.5
50°-60°	27.8	4.4
60°-70°	7.1	1.1
70°-80°	1.4	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	387.1	60.6
0°-40°	529.5	82.8
0°-60°	630.6	98.7
0°-90°	639.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	639.2	100.0

CANDELA DISTRIBUTION:

	0°	45°	90°	135°	180°	Flux
0°	617	617	617	617	617	
5°	795	720	594	503	459	83
15°	1192	758	404	242	219	340
25°	1319	542	217	113	114	599
35°	914	287	96	53	72	567
45°	397	100	36	29	48	309
55°	100	31	16	13	26	96
65°	14	6	4	4	10	18
75°	2	1	1	1	0	3
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0

TEST NUMBER: P601328

CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 5000K

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	22.5°	45°	67.5°	90°	112.5°	135°
0°	616.8	616.8	616.8	616.8	616.8	616.8	616.8	616.8	616.8	616.8	616.8
2.5°	695.3	692.0	709.7	684.2	667.7	689.8	669.9	646.7	622.3	581.4	560.4
5°	794.8	797.0	800.3	792.6	789.3	787.0	719.6	656.6	593.6	531.7	503.0
7.5°	908.6	887.6	900.9	871.1	876.6	861.1	766.0	646.7	564.9	485.3	417.8
10°	1020.3	997.1	1008.1	980.5	973.9	960.6	792.6	620.1	519.5	412.3	354.8
12.5°	1115.3	1105.4	1094.3	1056.8	1043.5	1007.0	792.6	584.8	455.4	355.9	289.6
15°	1191.6	1181.7	1169.5	1120.9	1080.0	1047.9	758.3	535.0	403.5	305.1	242.1
17.5°	1254.6	1215.9	1217.0	1147.4	1112.0	1070.0	725.1	484.2	349.3	255.3	205.6
20°	1339.7	1269.0	1256.8	1182.8	1116.5	1070.0	666.6	428.9	298.5	215.6	169.1
22.5°	1326.5	1263.5	1277.8	1168.4	1097.7	1078.9	601.3	370.3	256.5	181.3	136.0
25°	1318.7	1273.4	1249.1	1131.9	1046.8	987.1	541.6	323.9	216.7	149.2	112.8
27.5°	1285.6	1217.0	1180.6	1062.3	968.3	919.7	470.9	274.1	181.3	118.3	95.1
30°	1178.4	1128.6	1089.9	966.1	866.6	820.2	407.9	227.7	150.3	97.3	75.2
32.5°	1062.3	1019.2	959.5	857.8	743.9	698.6	338.3	194.6	122.7	77.4	63.0
35°	914.2	878.8	822.4	719.6	610.2	590.3	287.4	155.9	96.2	61.9	53.1
37.5°	770.5	739.5	682.0	589.2	504.1	475.3	232.1	124.9	77.4	50.8	45.3
40°	637.8	601.3	563.8	473.1	403.5	372.5	178.0	97.3	58.6	40.9	38.7
42.5°	507.4	485.3	444.4	378.0	309.5	289.6	132.6	73.0	46.4	34.3	33.2
45°	396.8	373.6	334.9	290.7	233.2	217.8	99.5	56.4	36.5	27.6	28.7
47.5°	289.6	278.6	253.1	215.6	178.0	160.3	75.2	44.2	28.7	23.2	24.3
50°	211.1	200.1	187.9	153.7	123.8	119.4	56.4	34.3	24.3	18.8	19.9
52.5°	145.9	144.8	131.5	109.4	90.6	82.9	43.1	26.5	19.9	15.5	16.6
55°	99.5	98.4	89.5	76.3	64.1	58.6	31.0	19.9	15.5	12.2	13.3
57.5°	64.1	65.2	59.7	52.0	42.0	38.7	21.0	14.4	11.1	8.8	9.9
60°	42.0	42.0	36.5	33.2	26.5	24.3	14.4	9.9	7.7	6.6	7.7
62.5°	25.4	26.5	23.2	18.8	16.6	14.4	8.8	6.6	5.5	4.4	5.5
65°	14.4	15.5	13.3	11.1	9.9	8.8	5.5	4.4	4.4	3.3	4.4
67.5°	8.8	8.8	7.7	6.6	5.5	5.5	3.3	3.3	3.3	3.3	3.3
70°	5.5	5.5	4.4	4.4	3.3	3.3	2.2	3.3	2.2	2.2	2.2
72.5°	3.3	3.3	2.2	2.2	2.2	2.2	2.2	2.2	2.2	1.1	1.1
75°	2.2	2.2	2.2	2.2	1.1	1.1	1.1	1.1	1.1	1.1	1.1
77.5°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	0.0
80°	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	1.1	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0	0.0

TEST NUMBER: P601328
 CATALOG NUMBER: ML4DM06AWW9FS1E - TIR4D25AWW - TL43R2G_ TL44S2G_ 5000K

CANDELA DISTRIBUTION (continued):

	157.5°	180°
0°	616.8	616.8
2.5°	547.2	549.4
5°	472.0	458.7
7.5°	392.4	371.4
10°	317.2	312.8
12.5°	267.5	262.0
15°	224.4	218.9
17.5°	187.9	178.0
20°	157.0	143.7
22.5°	130.4	131.5
25°	111.6	113.9
27.5°	96.2	98.4
30°	80.7	85.1
32.5°	73.0	79.6
35°	63.0	71.9
37.5°	56.4	65.2
40°	49.7	58.6
42.5°	44.2	53.1
45°	38.7	47.5
47.5°	34.3	43.1
50°	28.7	37.6
52.5°	24.3	32.1
55°	19.9	26.5
57.5°	16.6	22.1
60°	13.3	17.7
62.5°	9.9	13.3
65°	6.6	9.9
67.5°	4.4	6.6
70°	3.3	4.4
72.5°	1.1	2.2
75°	0.0	0.0
77.5°	0.0	0.0
80°	0.0	0.0
82.5°	0.0	0.0
85°	0.0	0.0
87.5°	0.0	0.0
90°	0.0	0.0

(END OF REPORT)