

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: HALO

Report Number: P885934

Luminaire Tested: ML104LSFL9FS1E-TIR1D55WFL-TL1RDMBB-400LM-3000K

Issue Date: 6/19/2024

Test Information

Test Method: LM-79-2019
Report Number: P885934
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2402-314-135)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 6/19/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: HALO
Catalog Number: ML104LSFL9FS1E-TIR1D55WFL-TL1RDMMB-400LM-3000K
Description: 1IN ROUND ML FLEX, SELECTABLE CCT, WITH 55D TIR, MATTE BLACK BAFFLED TRIM
Light Source: (1) STANDARD SELECTABLE LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 379.2 lumens
Efficiency: N/A
Efficacy: 63.2 lumens/watt
Spacing Criteria (0/90/45): 0.81 / 0.81 / 0.78
Luminous Opening: Circular (Dia: 0.08' x H: 0')
CIE Type: Direct


Input Watts (W): 6
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT



TEST NUMBER: P885934

CATALOG NUMBER: ML104LSFL9FS1E-TIR1D55WFL-TL1RDMMB-400LM-3000K

Luminous Intensity Polar Plot





TEST NUMBER: P885934

CATALOG NUMBER: ML104LSFL9FS1E-TIR1D55WFL-TL1RDMBB-400LM-3000K

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			
1	114	111	109	107	111	109	107	105	105	104	102	101	100	99	98	97	96	94			
2	109	104	101	97	107	103	99	96	99	97	94	96	94	92	94	92	90	89			
3	104	98	93	90	102	97	92	89	94	90	88	92	89	86	89	87	85	83			
4	99	92	87	83	97	91	86	83	89	85	82	87	84	81	85	82	80	78			
5	95	87	82	78	93	86	81	77	84	80	77	83	79	76	81	78	75	74			
6	90	82	77	73	89	81	76	72	80	75	72	79	75	71	77	74	71	70			
7	86	78	72	68	85	77	72	68	76	71	68	75	71	67	74	70	67	66			
8	83	74	68	64	81	73	68	64	72	67	64	71	67	64	70	66	64	62			
9	79	70	65	61	78	70	64	61	69	64	61	68	64	60	67	63	60	59			
10	76	67	61	58	75	66	61	58	65	61	57	65	60	57	64	60	57	56			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1088408
5°	1073944
10°	1019629
15°	918401
20°	789045
25°	643470
30°	410193
35°	208159
40°	104597
45°	40749
50°	12895
55°	3441
60°	0
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 40749 cd/sqm



TEST NUMBER: P885934

CATALOG NUMBER: ML104LSFL9FS1E-TIR1D55WFL-TL1RDMMB-400LM-3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.7	13.4
10°-20°	124.8	32.9
20°-30°	130.8	34.5
30°-40°	58.6	15.5
40°-50°	13.2	3.5
50°-60°	1.1	0.3
60°-70°	0.0	0.0
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	306.2	80.7
0°-40°	364.8	96.2
0°-60°	379.2	100.0
0°-90°	379.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	379.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	552	
5°	542	51
15°	450	125
25°	296	131
35°	86	59
45°	15	13
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P885934

CATALOG NUMBER: ML104LSFL9FS1E-TIR1D55WFL-TL1RDMBB-400LM-3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	551.5
2.5°	551.5
5°	542.1
7.5°	527.6
10°	508.8
12.5°	481.8
15°	449.5
17.5°	414.2
20°	375.7
22.5°	339.2
25°	295.5
27.5°	240.4
30°	180.0
32.5°	127.0
35°	86.4
37.5°	60.4
40°	40.6
42.5°	25.0
45°	14.6
47.5°	8.3
50°	4.2
52.5°	2.1
55°	1.0
57.5°	0.0
60°	0.0
62.5°	0.0
65°	0.0
67.5°	0.0
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)